

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220516

Luminaire Tested: **9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220516  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1215.5 lumens  
Efficiency: N/A  
Efficacy: 60.5 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220516

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220516

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2284729
5°	1750315
10°	734277
15°	309877
20°	201594
25°	88336
30°	11951
35°	4497
40°	3206
45°	2481
50°	2183
55°	2141
60°	1754
65°	1245
70°	513
75°	0
80°	0
85°	0



TEST NUMBER: P220516

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	598.6	49.2
10°-20°	417.4	34.3
20°-30°	172.1	14.2
30°-40°	13.6	1.1
40°-50°	6.5	0.5
50°-60°	4.7	0.4
60°-70°	2.4	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1188.1	97.7
0°-40°	1201.7	98.9
0°-60°	1212.9	99.8
0°-90°	1215.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1215.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10419	
5°	7952	599
15°	1365	417
25°	365	172
35°	17	14
45°	8	6
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220516

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10419.2
1°	10286.3
2°	9974.9
3°	9468.1
4°	8791.5
5°	7951.7
6°	7017.4
7°	6038.2
8°	5031.1
9°	4108.0
10°	3297.7
11°	2656.4
12°	2181.7
13°	1831.8
14°	1576.4
15°	1365.0
16°	1194.5
17°	1083.2
18°	997.6
19°	922.3
20°	863.9
21°	810.2
22°	728.6
23°	617.3
24°	490.8
25°	365.1
26°	253.8
27°	152.1
28°	84.9
29°	56.8
30°	47.2
32.5°	30.4
35°	16.8
37.5°	12.8
40°	11.2
42.5°	9.6
45°	8.0
47.5°	7.2
50°	6.4
52.5°	5.6
55°	5.6
57.5°	4.8
60°	4.0
62.5°	3.2
65°	2.4



TEST NUMBER: P220516

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-S-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)