

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P253150

Luminaire Tested: **3002A-25LED4000-SP-UNV-NBR**

Test Date: 11/19/12

Test Information

Test Method: LM-79-08
Report Number: P253150
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P22979)
Test Lab: INNOVATION CENTER P2
Test Date: 11/19/12
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 3002A-25LED4000-SP-UNV-NBR
Description: LUMIERE MONACO INGRADE TEST FIXTURE WITH SPOT OPTICS
Light Source: (7) 4000K CCT, 80 CRI LEDS
LBA-8057XPG2-4K
Ballast/Driver: -
ESS030W-1000-24-CPL

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1416.5 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
N/A
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Indirect

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P253150
CATALOG NUMBER: 3002A-25LED4000-SP-UNV-NBR

Luminous Intensity Polar Plot





TEST NUMBER: P253150

CATALOG NUMBER: 3002A-25LED4000-SP-UNV-NBR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°
95°	0
100°	0
105°	0
110°	0
115°	0
120°	200
125°	337
130°	457
135°	557
140°	645
145°	1189
150°	2935
155°	3136
160°	4374
165°	15515
170°	147470
175°	1328681



TEST NUMBER: P253150

CATALOG NUMBER: 3002A-25LED4000-SP-UNV-NBR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.9	0.1
120°-130°	2.7	0.2
130°-140°	4.0	0.3
140°-150°	10.7	0.8
150°-160°	19.1	1.3
160°-170°	114.5	8.1
170°-180°	1265.0	89.3
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	0.9	0.1
90°-150°	18.2	1.3
90°-180°	1417.0	100.0
0°-180°	1416.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
90°	0	
95°	0	0
105°	0	0
115°	0	1
125°	3	3
135°	6	4
145°	14	11
155°	40	19
165°	209	115
175°	18486	###
180°	44300	



TEST NUMBER: P253150
CATALOG NUMBER: 3002A-25LED4000-SP-UNV-NBR

CANDELA DISTRIBUTION (FULL):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	1.4
120°	1.4
122.5°	2.7
125°	2.7
127.5°	4.1
130°	4.1
132.5°	4.1
135°	5.5
137.5°	5.5
140°	6.9
142.5°	9.5
145°	13.6
147.5°	26.0
150°	35.5
152.5°	38.3
155°	39.7
157.5°	42.4
160°	57.4
162.5°	105.3
165°	209.3
167.5°	577.2
170°	2028.3
172.5°	6729.1
175°	18485.9
175.5°	21671.3
176°	24988.0
176.5°	28549.5
177°	32353.0
177.5°	35861.1
178°	38949.4
178.5°	41295.1
179°	42914.5
179.5°	43940.2
180°	44299.9

(END OF REPORT)