

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247012

Luminaire Tested: **203-SS-8LED2710-12-CS-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247012
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-36)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 2700K 95 CRI 10° NSP LED
SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 212.8 lumens
Efficiency: N/A
Efficacy: 28.4 lumens/watt
Spacing Criteria (0/90/45): 0.38 / 0.38 / 0.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247012
CATALOG NUMBER: 203-SS-8LED2710-12-CS-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: P247012

CATALOG NUMBER: 203-SS-8LED2710-12-CS-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	98	97	95				95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85				85
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	85	82	81				81
5	97	90	85	81	95	89	84	81	87	83	80	86	82	79	84	81	79	77				77
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74				74
7	90	82	77	74	89	81	77	73	80	76	73	79	75	73	78	75	72	71				71
8	87	79	74	70	86	78	74	70	77	73	70	76	73	70	76	72	70	68				68
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66				66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	418879
5°	358967
10°	242830
15°	137554
20°	71878
25°	39740
30°	24953
35°	17587
40°	13525
45°	10815
50°	8443
55°	6279
60°	3651
65°	2101
70°	1298
75°	1716
80°	0
85°	0



TEST NUMBER: P247012

CATALOG NUMBER: 203-SS-8LED2710-12-CS-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	28.8
10°-20°	75.8	35.6
20°-30°	35.4	16.6
30°-40°	18.7	8.8
40°-50°	12.2	5.7
50°-60°	6.5	3.1
60°-70°	2.1	1.0
70°-80°	0.8	0.4
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.5	81.0
0°-40°	191.2	89.8
0°-60°	209.9	98.6
0°-90°	212.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	849	
5°	725	61
15°	269	76
25°	73	35
35°	29	19
45°	16	12
55°	7	6
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P247012

CATALOG NUMBER: 203-SS-8LED2710-12-CS-DIFF

CANDELA DISTRIBUTION (FULL):

	0°
0°	849.0
1°	840.8
2°	821.6
3°	795.1
4°	763.2
5°	724.8
6°	682.8
7°	635.4
8°	585.2
9°	534.0
10°	484.7
12.5°	368.8
15°	269.3
17.5°	191.7
20°	136.9
22.5°	98.6
25°	73.0
27.5°	54.8
30°	43.8
32.5°	34.7
35°	29.2
37.5°	24.6
40°	21.0
42.5°	18.3
45°	15.5
47.5°	13.7
50°	11.0
52.5°	9.1
55°	7.3
57.5°	5.5
60°	3.7
62.5°	2.7
65°	1.8
67.5°	1.8
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)