

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220513

Luminaire Tested: **9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220513  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 5000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1577.2 lumens  
Efficiency: N/A  
Efficacy: 78.5 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220513

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220513

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2964543
5°	2271115
10°	952755
15°	402091
20°	261566
25°	114611
30°	15521
35°	5836
40°	4151
45°	3225
50°	2831
55°	2791
60°	2281
65°	1608
70°	641
75°	0
80°	0
85°	0



TEST NUMBER: P220513

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	776.8	49.2
10°-20°	541.6	34.3
20°-30°	223.2	14.2
30°-40°	17.6	1.1
40°-50°	8.4	0.5
50°-60°	6.2	0.4
60°-70°	3.1	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.6	97.7
0°-40°	1559.2	98.9
0°-60°	1573.7	99.8
0°-90°	1577.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1577.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13519	
5°	10318	777
15°	1771	542
25°	474	223
35°	22	18
45°	10	8
55°	7	6
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220513

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	13519.4
1°	13346.9
2°	12942.8
3°	12285.2
4°	11407.4
5°	10317.7
6°	9105.4
7°	7834.9
8°	6528.0
9°	5330.2
10°	4278.9
11°	3446.8
12°	2830.8
13°	2376.8
14°	2045.5
15°	1771.2
16°	1549.9
17°	1405.5
18°	1294.4
19°	1196.7
20°	1120.9
21°	1051.3
22°	945.3
23°	800.9
24°	636.8
25°	473.7
26°	329.3
27°	197.4
28°	110.1
29°	73.8
30°	61.3
32.5°	39.5
35°	21.8
37.5°	16.6
40°	14.5
42.5°	12.5
45°	10.4
47.5°	9.3
50°	8.3
52.5°	7.3
55°	7.3
57.5°	6.2
60°	5.2
62.5°	4.2
65°	3.1



TEST NUMBER: P220513

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-S-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.1
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)