

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P246985

Luminaire Tested: **203-SS-8LED3036-12-BK-LSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246985  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-33)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED3036-12-BK-LSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD BLACK, LINEAR SPREAD LENS  
Light Source: (1) SORAA 3000K 95 CRI LED  
SM16-07-36D-930-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 271.0 lumens  
Efficiency: N/A  
Efficacy: 34.7 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.02 / 0.74  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246985  
CATALOG NUMBER: 203-SS-8LED3036-12-BK-LSL

### Luminous Intensity Polar Plot





TEST NUMBER: P246985

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LSL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90				
3	105	99	95	91	103	98	94	90	95	92	89	93	90	87	90	88	86	85				
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	82	80				
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76				
6	92	84	79	75	90	83	78	75	82	77	74	80	77	74	79	76	73	72				
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68				
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65				
9	81	72	67	64	80	72	67	64	71	67	63	70	66	63	69	66	63	62				
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	209933	209933	209933
5°	200632	215143	225692
10°	170988	210967	242029
15°	124989	193791	246351
20°	68886	155465	225296
25°	27981	104250	184328
30°	9115	56059	139920
35°	4276	19214	80107
40°	2254	5732	28532
45°	1256	2442	6210
50°	691	1382	2072
55°	774	774	774
60°	888	888	888
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P246985

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LSL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.9	15.1
10°-20°	101.5	37.5
20°-30°	88.1	32.5
30°-40°	34.9	12.9
40°-50°	4.5	1.7
50°-60°	1.0	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.6	85.1
0°-40°	265.4	98.0
0°-60°	270.8	100.0
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	426	426	426	426	426	
5°	405	417	434	451	456	37
15°	245	287	379	456	482	65
25°	51	75	192	308	339	26
35°	7	10	32	101	133	5
45°	2	3	4	7	9	2
55°	1	1	1	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P246985

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LSL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	425.5	425.5	425.5	425.5	425.5
1°	422.9	423.7	425.5	427.3	428.2
2°	419.3	422.0	426.4	430.8	432.6
3°	415.8	421.1	429.1	437.0	440.6
4°	411.3	419.3	432.6	443.2	448.6
5°	405.1	416.7	434.4	451.2	455.7
6°	397.1	412.2	436.2	455.7	462.8
7°	385.6	406.0	436.2	460.1	469.8
8°	373.2	396.3	431.7	463.6	477.8
9°	358.1	385.6	427.3	466.3	480.5
10°	341.3	372.3	421.1	467.2	483.1
11°	322.7	358.1	415.8	466.3	484.9
12°	305.0	342.2	410.4	465.4	485.8
13°	285.5	325.3	400.7	463.6	485.8
14°	265.9	306.7	390.1	460.1	485.8
15°	244.7	287.2	379.4	455.7	482.3
16°	221.6	266.8	367.0	451.2	476.0
17°	199.5	246.4	352.8	442.4	469.0
18°	175.5	221.6	335.1	429.9	455.7
19°	154.3	197.7	316.5	415.8	442.4
20°	131.2	173.8	296.1	400.7	429.1
21°	109.9	150.7	277.5	383.9	414.9
22°	91.3	126.8	258.9	367.9	397.1
23°	76.2	106.4	235.8	351.9	377.6
24°	62.9	89.5	213.6	332.4	357.3
25°	51.4	75.4	191.5	308.5	338.6
26°	42.6	62.9	171.1	287.2	320.0
27°	33.7	51.4	150.7	265.1	300.5
28°	26.6	41.7	132.1	245.6	281.0
29°	21.3	32.8	114.4	220.7	262.4
30°	16.0	26.6	98.4	201.2	245.6
32.5°	9.8	15.1	59.4	155.1	189.7
35°	7.1	9.8	31.9	101.1	133.0
37.5°	4.4	6.2	16.0	56.7	71.8
40°	3.5	4.4	8.9	26.6	44.3
42.5°	2.7	3.5	5.3	12.4	17.7
45°	1.8	2.7	3.5	7.1	8.9
47.5°	1.8	1.8	1.8	3.5	4.4
50°	0.9	0.9	1.8	1.8	2.7
52.5°	0.9	0.9	0.9	1.8	1.8
55°	0.9	0.9	0.9	0.9	0.9
57.5°	0.9	0.9	0.9	0.9	0.9
60°	0.9	0.9	0.9	0.9	0.9
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P246985

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LSL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)