

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220597

Luminaire Tested: **9003-W1-FL-LED3090-M-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220597  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-FL-LED3090-M-WT-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3000K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1295.4 lumens  
Efficiency: N/A  
Efficacy: 64.4 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220597

CATALOG NUMBER: 9003-W1-FL-LED3090-M-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220597

CATALOG NUMBER: 9003-W1-FL-LED3090-M-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	84	81	80
7	94	88	83	80	93	87	83	80	86	82	80		85	82	79		84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77		82	79	77		82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75		80	77	74		79	76	74	73
10	86	79	75	73	86	79	75	72	78	75	72		78	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1201724
5°	1091963
10°	771751
15°	417051
20°	221803
25°	163171
30°	65884
35°	12608
40°	6612
45°	2977
50°	2456
55°	2141
60°	1754
65°	1660
70°	1539
75°	1356
80°	1010
85°	2013



TEST NUMBER: P220597

CATALOG NUMBER: 9003-W1-FL-LED3090-M-WT-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	425.0	32.8
10°-20°	518.5	40.0
20°-30°	285.4	22.0
30°-40°	47.3	3.7
40°-50°	8.7	0.7
50°-60°	5.0	0.4
60°-70°	3.2	0.2
70°-80°	1.7	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1229.0	94.9
0°-40°	1276.3	98.5
0°-60°	1290.0	99.6
0°-90°	1295.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1295.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5480	
5°	4961	425
15°	1837	519
25°	674	285
35°	47	47
45°	10	9
55°	6	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P220597

CATALOG NUMBER: 9003-W1-FL-LED3090-M-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5480.3
1°	5446.8
2°	5390.1
3°	5300.7
4°	5149.1
5°	4960.8
6°	4733.3
7°	4462.8
8°	4154.7
9°	3817.1
10°	3466.0
11°	3111.6
12°	2763.7
13°	2430.9
14°	2123.6
15°	1837.1
16°	1589.7
17°	1367.1
18°	1193.1
19°	1054.2
20°	950.5
21°	871.5
22°	814.0
23°	773.3
24°	732.6
25°	674.4
26°	601.7
27°	520.3
28°	431.8
29°	344.8
30°	260.2
32.5°	94.2
35°	47.1
37.5°	33.5
40°	23.1
42.5°	12.0
45°	9.6
47.5°	8.8
50°	7.2
52.5°	6.4
55°	5.6
57.5°	4.8
60°	4.0
62.5°	4.0
65°	3.2



TEST NUMBER: P220597

CATALOG NUMBER: 9003-W1-FL-LED3090-M-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.4
70°	2.4
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)