

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220703

Luminaire Tested: **9003-W1-FL-LED3590-W-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29479)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-FL-LED3590-W-BK-L2-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1317.2 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220703

CATALOG NUMBER: 9003-W1-FL-LED3590-W-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220703

CATALOG NUMBER: 9003-W1-FL-LED3590-W-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	88	84	81		87	83	80		85	82	79	78
5	94	86	81	77	93	86	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	68	64	72	67	64		71	66	63		70	66	63	62
9	79	70	64	61	78	69	64	60	68	64	60		68	63	60		67	63	60	59
10	75	66	61	57	75	66	61	57	65	60	57		64	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430711
5°	433963
10°	410012
15°	352692
20°	302753
25°	250539
30°	133641
35°	60793
40°	38873
45°	25553
50°	17910
55°	8946
60°	2105
65°	2075
70°	2052
75°	1356
80°	1010
85°	2013



TEST NUMBER: P220703

CATALOG NUMBER: 9003-W1-FL-LED3590-W-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.2	14.0
10°-20°	434.5	33.0
20°-30°	444.0	33.7
30°-40°	160.8	12.2
40°-50°	66.2	5.0
50°-60°	21.4	1.6
60°-70°	3.8	0.3
70°-80°	1.8	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.7	80.7
0°-40°	1223.5	92.9
0°-60°	1311.1	99.5
0°-90°	1317.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1317.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1964	
5°	1972	184
15°	1554	434
25°	1036	444
35°	227	161
45°	82	66
55°	23	21
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P220703

CATALOG NUMBER: 9003-W1-FL-LED3590-W-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1964.2
1°	1958.6
2°	1959.4
3°	1966.7
4°	1973.1
5°	1971.5
6°	1965.8
7°	1948.1
8°	1919.8
9°	1882.6
10°	1841.4
11°	1792.1
12°	1737.9
13°	1677.3
14°	1614.2
15°	1553.6
16°	1495.4
17°	1444.5
18°	1397.6
19°	1345.9
20°	1297.4
21°	1251.3
22°	1206.0
23°	1162.4
24°	1110.6
25°	1035.5
26°	943.3
27°	843.1
28°	737.2
29°	630.5
30°	527.8
32.5°	316.9
35°	227.1
37.5°	175.4
40°	135.8
42.5°	103.5
45°	82.4
47.5°	66.3
50°	52.5
52.5°	38.8
55°	23.4
57.5°	6.5
60°	4.8
62.5°	4.0
65°	4.0



TEST NUMBER: P220703

CATALOG NUMBER: 9003-W1-FL-LED3590-W-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.2
70°	3.2
72.5°	2.4
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)