

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-32

Luminaire Tested: **203-SS-8LED4036-12-BK-DIFF**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-32
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-32)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4036-12-BK-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, DIFFUSED LENS
Light Source: (1) SORAA 4000K 95 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 264.3 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): 12.0
Input Current (Ain): 0.682
Voltage Rise (V): NR
Power Factor: 0.9908
Total Harmonic Distortion (THDi): 27.3%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 24.9
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-32
CATALOG NUMBER: 203-SS-8LED4036-12-BK-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-32

CATALOG NUMBER: 203-SS-8LED4036-12-BK-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77
6	92	85	79	76	91	84	79	76	82	78	75	81	77	75	80	77	74	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	68	74	70	67	66
9	82	74	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62	69	64	62	68	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262478
5°	253575
10°	226949
15°	187458
20°	139137
25°	91457
30°	54692
35°	27706
40°	12881
45°	5582
50°	2303
55°	860
60°	987
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-32
 CATALOG NUMBER: 203-SS-8LED4036-12-BK-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	17.8
10°-20°	100.3	38.0
20°-30°	77.3	29.3
30°-40°	31.1	11.8
40°-50°	7.1	2.7
50°-60°	1.3	0.5
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.6	85.0
0°-40°	255.7	96.8
0°-60°	264.2	100.0
0°-90°	264.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	264.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	532	
5°	512	47
15°	367	100
25°	168	77
35°	46	31
45°	8	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-32

CATALOG NUMBER: 203-SS-8LED4036-12-BK-DIFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	532
1°	530
2°	527
3°	523
4°	518
5°	512
6°	504
7°	494
8°	481
9°	467
10°	453
11°	436
12°	420
13°	402
14°	385
15°	367
16°	348
17°	328
18°	308
19°	287
20°	265
21°	243
22°	223
23°	204
24°	186
25°	168
26°	151
27°	137
28°	122
29°	108
30°	96
32.5°	68
35°	46
37.5°	32
40°	20
42.5°	13
45°	8
47.5°	5
50°	3
52.5°	2
55°	1
57.5°	1
60°	1
62.5°	0
65°	0



TEST NUMBER: G2-1802-569-32
CATALOG NUMBER: 203-SS-8LED4036-12-BK-DIFF

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)