

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220604

Luminaire Tested: **9003-W1-FL-LED4097-M-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220604  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-FL-LED4097-M-WT-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 4000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1287.1 lumens  
Efficiency: N/A  
Efficacy: 64.0 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220604

CATALOG NUMBER: 9003-W1-FL-LED4097-M-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220604

CATALOG NUMBER: 9003-W1-FL-LED4097-M-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 112 | 111 | 109 | 107 | 107 | 105 | 104 | 103 | 102 | 101 | 99  | 99  | 98  | 96  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 103 | 100 | 102 | 100 | 98  | 99  | 98  | 96  | 97  | 95  | 94  | 93  |
| 3   | 107 | 102 | 99  | 96  | 105 | 101 | 98  | 95  | 98  | 96  | 93  | 96  | 94  | 92  | 94  | 92  | 91  | 89  |
| 4   | 104 | 98  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 89  | 87  | 86  |
| 5   | 100 | 94  | 90  | 87  | 99  | 93  | 89  | 86  | 92  | 88  | 86  | 90  | 87  | 85  | 89  | 86  | 84  | 83  |
| 6   | 97  | 91  | 86  | 83  | 96  | 90  | 86  | 83  | 89  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 81  | 80  |
| 7   | 94  | 88  | 83  | 80  | 93  | 87  | 83  | 80  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 78  |
| 8   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 77  | 83  | 80  | 77  | 82  | 79  | 77  | 82  | 79  | 76  | 75  |
| 9   | 89  | 82  | 78  | 75  | 88  | 82  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 74  | 79  | 76  | 74  | 73  |
| 10  | 86  | 79  | 75  | 73  | 86  | 79  | 75  | 72  | 78  | 75  | 72  | 78  | 74  | 72  | 77  | 74  | 72  | 71  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1193961 |
| 5°  | 1084897 |
| 10° | 766764  |
| 15° | 414372  |
| 20° | 220356  |
| 25° | 162106  |
| 30° | 65453   |
| 35° | 12528   |
| 40° | 6584    |
| 45° | 2946    |
| 50° | 2422    |
| 55° | 2141    |
| 60° | 1754    |
| 65° | 1660    |
| 70° | 1539    |
| 75° | 1356    |
| 80° | 1010    |
| 85° | 2013    |



TEST NUMBER: P220604

CATALOG NUMBER: 9003-W1-FL-LED4097-M-WT-L2-UNV

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 422.3  | 32.8      |
| 10°-20°   | 515.2  | 40.0      |
| 20°-30°   | 283.6  | 22.0      |
| 30°-40°   | 47.1   | 3.7       |
| 40°-50°   | 8.6    | 0.7       |
| 50°-60°   | 5.0    | 0.4       |
| 60°-70°   | 3.2    | 0.2       |
| 70°-80°   | 1.7    | 0.1       |
| 80°-90°   | 0.5    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1221.0 | 94.9      |
| 0°-40°    | 1268.1 | 98.5      |
| 0°-60°    | 1281.7 | 99.6      |
| 0°-90°    | 1287.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1287.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5445 |      |
| 5°  | 4929 | 422  |
| 15° | 1825 | 515  |
| 25° | 670  | 284  |
| 35° | 47   | 47   |
| 45° | 10   | 9    |
| 55° | 6    | 5    |
| 65° | 3    | 3    |
| 75° | 2    | 2    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P220604

CATALOG NUMBER: 9003-W1-FL-LED4097-M-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5444.9 |
| 1°    | 5411.6 |
| 2°    | 5355.3 |
| 3°    | 5266.5 |
| 4°    | 5115.8 |
| 5°    | 4928.7 |
| 6°    | 4702.7 |
| 7°    | 4433.9 |
| 8°    | 4127.8 |
| 9°    | 3792.4 |
| 10°   | 3443.6 |
| 11°   | 3091.5 |
| 12°   | 2745.8 |
| 13°   | 2415.2 |
| 14°   | 2109.9 |
| 15°   | 1825.3 |
| 16°   | 1579.5 |
| 17°   | 1358.2 |
| 18°   | 1185.4 |
| 19°   | 1047.4 |
| 20°   | 944.3  |
| 21°   | 865.8  |
| 22°   | 808.8  |
| 23°   | 768.3  |
| 24°   | 727.9  |
| 25°   | 670.0  |
| 26°   | 597.8  |
| 27°   | 517.0  |
| 28°   | 429.0  |
| 29°   | 342.5  |
| 30°   | 258.5  |
| 32.5° | 93.6   |
| 35°   | 46.8   |
| 37.5° | 33.3   |
| 40°   | 23.0   |
| 42.5° | 11.9   |
| 45°   | 9.5    |
| 47.5° | 8.7    |
| 50°   | 7.1    |
| 52.5° | 6.3    |
| 55°   | 5.6    |
| 57.5° | 4.8    |
| 60°   | 4.0    |
| 62.5° | 4.0    |
| 65°   | 3.2    |



TEST NUMBER: P220604

CATALOG NUMBER: 9003-W1-FL-LED4097-M-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 2.4 |
| 70°   | 2.4 |
| 72.5° | 1.6 |
| 75°   | 1.6 |
| 77.5° | 1.6 |
| 80°   | 0.8 |
| 82.5° | 0.8 |
| 85°   | 0.8 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)