

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2725-12-BK-OSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-31)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2725-12-BK-OSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK, OVERALL SPREAD LENS  
Light Source: (1) SORAA 2700K 95 CRI LED  
SM16-07-25D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	314.7 lumens	Max Intensity:	1290.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	39.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	26°H x 26°V	Field Angle (10%):	49.5°H x 49.5°V
Beam Lumens:	148.9 lumens	Field Lumens:	279.2 lumens
Beam Efficiency:	47.3%	Field Efficiency:	88.7%
Input Watts (W):	7.9		
Input Voltage (V):	NR		
Input Current (A <sub>in</sub> ):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

### Iso-Candela Plot





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.3	0.5	0.5	0.3	0.1	0.0	0.0	0.0	0.0	0.0	
30	0.0	0.0	0.0	0.0	0.1	0.5	2.0	3.7	3.7	2.0	0.5	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.2	1.9	6.8	14.1	14.1	6.8	1.9	0.2	0.0	0.0	0.0	0.0	
10	0.0	0.0	0.0	0.1	0.4	3.4	13.7	30.6	30.6	13.7	3.4	0.4	0.1	0.0	0.0	0.0	0.0
0		0.0	0.0	0.1	0.4	3.4	13.7	30.6	30.6	13.7	3.4	0.4	0.1	0.0	0.0	0.0	
-10	0.0	0.0	0.0	0.1	0.4	3.4	13.7	30.6	30.6	13.7	3.4	0.4	0.1	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.2	1.9	6.8	14.1	14.1	6.8	1.9	0.2	0.0	0.0	0.0	0.0	
-30	0.0	0.0	0.0	0.0	0.1	0.5	2.0	3.7	3.7	2.0	0.5	0.1	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.1	0.3	0.5	0.5	0.3	0.1	0.0	0.0	0.0	0.0	0.0	
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

### Luminous Intensity Polar Plot



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

### Luminous Intensity Plot



**Beam:**  
 H Angle: 26°  
 V Angle: 26°  
 Lumens: 148.9  
 Efficiency: 47.3%

**Field:**  
 H Angle: 49.5°  
 V Angle: 49.5°  
 Lumens: 279.2  
 Efficiency: 88.7%

**Spill:**  
 Lumens: 35.4  
 Efficiency: 11.3%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	1	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	1	1	1	1
26.25°	0	0	0	0	0	0	0	1	1	1	1
25°	0	0	0	0	0	0	0	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	1	1	1	1	1	1
18.75°	0	0	0	0	0	1	1	1	1	1	1
17.5°	0	0	0	0	0	1	1	1	1	1	1
16.25°	0	0	0	0	0	1	1	1	1	1	1
15°	0	0	0	0	0	1	1	1	1	1	1
13.75°	0	0	0	0	1	1	1	1	1	1	1
12.5°	0	0	0	0	1	1	1	1	1	1	1
11.25°	0	0	0	0	1	1	1	1	1	1	1
10°	0	0	0	0	1	1	1	1	1	1	1
8.75°	0	0	0	0	1	1	1	1	1	1	1
7.5°	0	0	0	0	1	1	1	1	1	1	1
6.25°	0	0	0	0	1	1	1	1	1	1	1
5°	0	0	0	0	1	1	1	1	1	1	1
3.75°	0	0	0	0	1	1	1	1	1	1	1
2.5°	0	0	0	0	1	1	1	1	1	1	1
1.25°	0	0	0	0	1	1	1	1	1	1	1
0°	0	0	0	0	1	1	1	1	1	1	1
-1.25°	0	0	0	0	1	1	1	1	1	1	1
-2.5°	0	0	0	0	1	1	1	1	1	1	1
-3.75°	0	0	0	0	1	1	1	1	1	1	1
-5°	0	0	0	0	1	1	1	1	1	1	1
-6.25°	0	0	0	0	1	1	1	1	1	1	1
-7.5°	0	0	0	0	1	1	1	1	1	1	1
-8.75°	0	0	0	0	1	1	1	1	1	1	1
-10°	0	0	0	0	1	1	1	1	1	1	1
-11.25°	0	0	0	0	1	1	1	1	1	1	1
-12.5°	0	0	0	0	1	1	1	1	1	1	1
-13.75°	0	0	0	0	1	1	1	1	1	1	1
-15°	0	0	0	0	0	1	1	1	1	1	1
-16.25°	0	0	0	0	0	1	1	1	1	1	1
-17.5°	0	0	0	0	0	1	1	1	1	1	1
-18.75°	0	0	0	0	0	1	1	1	1	1	1
-20°	0	0	0	0	0	1	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	0	1	1	1	1
-26.25°	0	0	0	0	0	0	0	1	1	1	1
-27.5°	0	0	0	0	0	0	0	1	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	1	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	0	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
46.25°	0	0	0	0	0	0	0	1	1	1	1
45°	0	0	0	0	0	1	1	1	1	1	1
43.75°	0	0	0	0	1	1	1	1	1	1	1
42.5°	0	0	0	1	1	1	1	1	1	1	1
41.25°	0	0	0	1	1	1	1	1	1	1	1
40°	0	0	1	1	1	1	1	1	1	1	1
38.75°	0	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	1	1	1	1	1	1	1	1	1	1	2
32.5°	1	1	1	1	1	1	1	1	1	2	2
31.25°	1	1	1	1	1	1	1	1	2	2	2
30°	1	1	1	1	1	1	1	1	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	3
27.5°	1	1	1	1	1	1	2	2	2	3	3
26.25°	1	1	1	1	1	1	2	2	2	3	3
25°	1	1	1	1	1	2	2	2	3	3	3
23.75°	1	1	1	1	1	2	2	3	3	3	4
22.5°	1	1	1	1	2	2	2	3	3	4	4
21.25°	1	1	1	1	2	2	3	3	3	4	4
20°	1	1	1	1	2	2	3	3	4	4	4
18.75°	1	1	1	2	2	2	3	3	4	4	5
17.5°	1	1	1	2	2	3	3	3	4	4	5
16.25°	1	1	1	2	2	3	3	4	4	4	6
15°	1	1	2	2	2	3	3	4	4	5	6
13.75°	1	1	2	2	3	3	3	4	4	5	7
12.5°	1	1	2	2	3	3	4	4	4	6	7
11.25°	1	1	2	2	3	3	4	4	5	6	8
10°	1	2	2	2	3	3	4	4	5	7	8
8.75°	1	2	2	2	3	3	4	4	5	7	9
7.5°	1	2	2	3	3	3	4	4	6	7	9
6.25°	1	2	2	3	3	4	4	4	6	8	10
5°	1	2	2	3	3	4	4	5	6	8	10
3.75°	1	2	2	3	3	4	4	5	6	8	11
2.5°	1	2	2	3	3	4	4	5	6	8	11
1.25°	1	2	2	3	3	4	4	5	6	8	11
0°	1	2	2	3	3	4	4	5	6	8	11
-1.25°	1	2	2	3	3	4	4	5	6	8	11
-2.5°	1	2	2	3	3	4	4	5	6	8	11
-3.75°	1	2	2	3	3	4	4	5	6	8	11
-5°	1	2	2	3	3	4	4	5	6	8	10
-6.25°	1	2	2	3	3	4	4	4	6	8	10
-7.5°	1	2	2	3	3	3	4	4	6	7	9
-8.75°	1	2	2	2	3	3	4	4	5	7	9
-10°	1	2	2	2	3	3	4	4	5	7	8
-11.25°	1	1	2	2	3	3	4	4	5	6	8
-12.5°	1	1	2	2	3	3	4	4	4	6	7
-13.75°	1	1	2	2	3	3	3	4	4	5	7
-15°	1	1	2	2	2	3	3	4	4	5	6
-16.25°	1	1	1	2	2	3	3	4	4	4	6
-17.5°	1	1	1	2	2	3	3	3	4	4	5
-18.75°	1	1	1	2	2	2	3	3	4	4	5
-20°	1	1	1	1	2	2	3	3	4	4	4
-21.25°	1	1	1	1	2	2	3	3	3	4	4



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	1	1	1	1	2	2	2	3	3	4	4
-23.75°	1	1	1	1	1	2	2	3	3	3	4
-25°	1	1	1	1	1	2	2	2	3	3	3
-26.25°	1	1	1	1	1	1	2	2	2	3	3
-27.5°	1	1	1	1	1	1	2	2	2	3	3
-28.75°	1	1	1	1	1	1	1	2	2	2	3
-30°	1	1	1	1	1	1	1	1	2	2	2
-31.25°	1	1	1	1	1	1	1	1	2	2	2
-32.5°	1	1	1	1	1	1	1	1	1	2	2
-33.75°	1	1	1	1	1	1	1	1	1	1	2
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	0	1	1	1	1	1	1	1	1	1
-41.25°	0	0	0	1	1	1	1	1	1	1	1
-42.5°	0	0	0	1	1	1	1	1	1	1	1
-43.75°	0	0	0	0	1	1	1	1	1	1	1
-45°	0	0	0	0	0	1	1	1	1	1	1
-46.25°	0	0	0	0	0	0	0	1	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-48.75°	0	0	0	0	0	0	0	0	0	1	1
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	1	1	1	1	1
52.5°	0	0	0	0	1	1	1	1	1	1	1
51.25°	0	0	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	2	2	2	2	2
40°	1	1	1	1	1	2	2	2	2	3	3
38.75°	1	1	1	2	2	2	2	2	3	3	3
37.5°	1	1	2	2	2	2	3	3	3	3	4
36.25°	1	2	2	2	2	3	3	3	3	4	4
35°	2	2	2	3	3	3	3	4	4	4	4



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	2	2	3	3	3	3	4	4	4	4	5
32.5°	2	3	3	3	3	4	4	4	5	5	6
31.25°	3	3	3	3	4	4	4	5	6	7	8
30°	3	3	3	4	4	4	5	6	7	8	10
28.75°	3	3	4	4	4	5	6	7	8	10	12
27.5°	3	4	4	4	5	6	7	9	10	12	14
26.25°	4	4	4	5	6	7	9	11	12	14	17
25°	4	4	5	6	7	8	10	12	15	18	20
23.75°	4	4	5	7	8	10	12	14	18	21	25
22.5°	4	5	6	8	10	12	14	17	20	25	34
21.25°	5	6	7	9	11	13	16	20	24	34	43
20°	5	7	8	10	13	15	19	23	32	42	53
18.75°	6	7	9	12	14	18	21	30	40	50	63
17.5°	7	8	11	13	16	20	26	37	47	60	73
16.25°	7	9	12	14	18	22	32	43	56	69	83
15°	8	10	13	16	20	27	38	50	64	78	93
13.75°	9	11	14	18	22	32	44	57	72	87	104
12.5°	10	12	15	19	25	37	49	65	79	96	114
11.25°	10	13	17	21	30	42	56	71	87	105	124
10°	11	14	18	22	34	46	61	76	94	113	133
8.75°	12	15	19	25	37	50	66	82	100	120	142
7.5°	12	16	20	28	40	54	70	87	106	127	151
6.25°	13	16	21	30	43	58	74	92	112	134	159
5°	13	17	22	32	45	61	77	96	116	139	166
3.75°	13	18	22	34	47	63	80	99	120	143	171
2.5°	14	18	22	35	48	65	82	101	122	146	175
1.25°	14	18	23	36	49	66	83	102	124	148	178
0°	14	18	23	36	49	66	83	103	124	149	178
-1.25°	14	18	23	36	49	66	83	102	124	148	178
-2.5°	14	18	22	35	48	65	82	101	122	146	175
-3.75°	13	18	22	34	47	63	80	99	120	143	171
-5°	13	17	22	32	45	61	77	96	116	139	166
-6.25°	13	16	21	30	43	58	74	92	112	134	159
-7.5°	12	16	20	28	40	54	70	87	106	127	151
-8.75°	12	15	19	25	37	50	66	82	100	120	142
-10°	11	14	18	22	34	46	61	76	94	113	133
-11.25°	10	13	17	21	30	42	56	71	87	105	124
-12.5°	10	12	15	19	25	37	49	65	79	96	114
-13.75°	9	11	14	18	22	32	44	57	72	87	104
-15°	8	10	13	16	20	27	38	50	64	78	93
-16.25°	7	9	12	14	18	22	32	43	56	69	83
-17.5°	7	8	11	13	16	20	26	37	47	60	73
-18.75°	6	7	9	12	14	18	21	30	40	50	63
-20°	5	7	8	10	13	15	19	23	32	42	53
-21.25°	5	6	7	9	11	13	16	20	24	34	43





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	4	5	6	8	10	12	14	17	20	25	34
-23.75°	4	4	5	7	8	10	12	14	18	21	25
-25°	4	4	5	6	7	8	10	12	15	18	20
-26.25°	4	4	4	5	6	7	9	11	12	14	17
-27.5°	3	4	4	4	5	6	7	9	10	12	14
-28.75°	3	3	4	4	4	5	6	7	8	10	12
-30°	3	3	3	4	4	4	5	6	7	8	10
-31.25°	3	3	3	3	4	4	4	5	6	7	8
-32.5°	2	3	3	3	3	4	4	4	5	5	6
-33.75°	2	2	3	3	3	3	4	4	4	4	5
-35°	2	2	2	3	3	3	3	4	4	4	4
-36.25°	1	2	2	2	2	3	3	3	3	4	4
-37.5°	1	1	2	2	2	2	3	3	3	3	4
-38.75°	1	1	1	2	2	2	2	2	3	3	3
-40°	1	1	1	1	1	2	2	2	2	3	3
-41.25°	1	1	1	1	1	1	2	2	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	1	2
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	0	0	1	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	1	1	1	1	1	1	1
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	1	1	1	1	1
56.25°	0	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	2	2
46.25°	1	1	1	1	1	2	2	2	2	2	2
45°	1	1	2	2	2	2	2	2	2	2	2
43.75°	2	2	2	2	2	2	3	3	3	3	3
42.5°	2	2	2	3	3	3	3	3	3	3	3
41.25°	3	3	3	3	3	3	3	4	4	4	4
40°	3	3	3	3	4	4	4	4	4	4	4
38.75°	3	4	4	4	4	4	4	4	5	5	5
37.5°	4	4	4	4	4	5	5	6	6	7	7
36.25°	4	4	5	5	6	6	7	7	8	8	9
35°	5	5	6	7	7	8	9	10	10	11	12



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	6	7	7	8	9	10	11	12	13	14	15
32.5°	7	8	9	11	12	13	14	15	17	18	19
31.25°	9	10	12	13	14	16	18	19	21	22	25
30°	11	13	14	16	18	20	22	25	30	34	37
28.75°	13	15	18	20	22	27	32	37	42	46	50
27.5°	16	19	21	26	32	38	44	49	56	61	66
26.25°	20	23	30	37	43	50	57	65	71	76	82
25°	24	32	40	47	56	64	72	79	87	94	100
23.75°	34	42	50	60	69	78	87	96	105	113	120
22.5°	43	53	63	73	83	93	104	114	124	133	142
21.25°	53	65	75	86	98	110	122	134	145	157	168
20°	65	76	88	101	114	128	141	156	170	184	198
18.75°	75	88	102	117	131	147	164	181	198	215	233
17.5°	86	101	117	133	150	169	188	209	230	253	275
16.25°	98	114	131	150	170	191	215	241	268	295	322
15°	110	128	147	169	191	217	247	278	310	341	374
13.75°	122	141	164	188	215	247	281	317	355	393	432
12.5°	134	156	181	209	241	278	317	359	404	449	494
11.25°	145	170	198	230	268	310	355	404	455	507	559
10°	157	184	215	253	295	341	393	449	507	566	625
8.75°	168	198	233	275	322	374	432	494	559	625	692
7.5°	179	211	250	295	347	405	469	537	609	683	757
6.25°	188	223	266	315	371	434	503	577	655	736	817
5°	197	235	280	332	391	459	533	612	696	784	868
3.75°	204	244	291	345	409	480	557	641	730	822	910
2.5°	209	250	299	356	422	495	575	663	756	850	941
1.25°	212	254	304	363	430	504	587	676	772	868	959
0°	213	256	306	365	432	508	591	681	777	874	965
-1.25°	212	254	304	363	430	504	587	676	772	868	959
-2.5°	209	250	299	356	422	495	575	663	756	850	941
-3.75°	204	244	291	345	409	480	557	641	730	822	910
-5°	197	235	280	332	391	459	533	612	696	784	868
-6.25°	188	223	266	315	371	434	503	577	655	736	817
-7.5°	179	211	250	295	347	405	469	537	609	683	757
-8.75°	168	198	233	275	322	374	432	494	559	625	692
-10°	157	184	215	253	295	341	393	449	507	566	625
-11.25°	145	170	198	230	268	310	355	404	455	507	559
-12.5°	134	156	181	209	241	278	317	359	404	449	494
-13.75°	122	141	164	188	215	247	281	317	355	393	432
-15°	110	128	147	169	191	217	247	278	310	341	374
-16.25°	98	114	131	150	170	191	215	241	268	295	322
-17.5°	86	101	117	133	150	169	188	209	230	253	275
-18.75°	75	88	102	117	131	147	164	181	198	215	233
-20°	65	76	88	101	114	128	141	156	170	184	198
-21.25°	53	65	75	86	98	110	122	134	145	157	168



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	43	53	63	73	83	93	104	114	124	133	142
-23.75°	34	42	50	60	69	78	87	96	105	113	120
-25°	24	32	40	47	56	64	72	79	87	94	100
-26.25°	20	23	30	37	43	50	57	65	71	76	82
-27.5°	16	19	21	26	32	38	44	49	56	61	66
-28.75°	13	15	18	20	22	27	32	37	42	46	50
-30°	11	13	14	16	18	20	22	25	30	34	37
-31.25°	9	10	12	13	14	16	18	19	21	22	25
-32.5°	7	8	9	11	12	13	14	15	17	18	19
-33.75°	6	7	7	8	9	10	11	12	13	14	15
-35°	5	5	6	7	7	8	9	10	10	11	12
-36.25°	4	4	5	5	6	6	7	7	8	8	9
-37.5°	4	4	4	4	4	5	5	6	6	7	7
-38.75°	3	4	4	4	4	4	4	4	5	5	5
-40°	3	3	3	3	4	4	4	4	4	4	4
-41.25°	3	3	3	3	3	3	3	4	4	4	4
-42.5°	2	2	2	3	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	2	3	3	3	3	3
-45°	1	1	2	2	2	2	2	2	2	2	2
-46.25°	1	1	1	1	1	2	2	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	1	2	2
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	0	1	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	0	0	1	1	1	1	1
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	2	2	2	2	2	2
46.25°	2	2	2	2	2	2	2	2	2	2	2
45°	3	3	3	3	3	3	3	3	3	3	3
43.75°	3	3	3	3	3	3	3	3	3	3	3
42.5°	3	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	4	4	4	4
40°	4	4	5	5	5	5	5	5	5	5	5
38.75°	6	6	6	6	6	6	6	6	6	6	6
37.5°	7	8	8	8	8	8	8	8	8	8	8
36.25°	9	10	10	11	11	11	11	11	11	11	10
35°	12	13	13	13	14	14	14	14	14	13	13



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	16	16	17	18	18	18	18	18	18	18	17
32.5°	20	21	22	22	22	23	23	23	22	22	22
31.25°	28	30	32	34	35	36	36	36	35	34	32
30°	40	43	45	47	48	49	49	49	48	47	45
28.75°	54	58	61	63	65	66	66	66	65	63	61
27.5°	70	74	77	80	82	83	83	83	82	80	77
26.25°	87	92	96	99	101	102	103	102	101	99	96
25°	106	112	116	120	122	124	124	124	122	120	116
23.75°	127	134	139	143	146	148	149	148	146	143	139
22.5°	151	159	166	171	175	178	178	178	175	171	166
21.25°	179	188	197	204	209	212	213	212	209	204	197
20°	211	223	235	244	250	254	256	254	250	244	235
18.75°	250	266	280	291	299	304	306	304	299	291	280
17.5°	295	315	332	345	356	363	365	363	356	345	332
16.25°	347	371	391	409	422	430	432	430	422	409	391
15°	405	434	459	480	495	504	508	504	495	480	459
13.75°	469	503	533	557	575	587	591	587	575	557	533
12.5°	537	577	612	641	663	676	681	676	663	641	612
11.25°	609	655	696	730	756	772	777	772	756	730	696
10°	683	736	784	822	850	868	874	868	850	822	784
8.75°	757	817	868	910	941	959	965	959	941	910	868
7.5°	828	892	948	990	1022	1041	1047	1041	1022	990	948
6.25°	892	960	1016	1060	1092	1110	1116	1110	1092	1060	1016
5°	948	1016	1074	1117	1147	1166	1173	1166	1147	1117	1074
3.75°	990	1060	1117	1160	1192	1212	1218	1212	1192	1160	1117
2.5°	1022	1092	1147	1192	1224	1245	1252	1245	1224	1192	1147
1.25°	1041	1110	1166	1212	1245	1268	1277	1268	1245	1212	1166
0°	1047	1116	1173	1218	1252	1277	1291	1277	1252	1218	1173
-1.25°	1041	1110	1166	1212	1245	1268	1277	1268	1245	1212	1166
-2.5°	1022	1092	1147	1192	1224	1245	1252	1245	1224	1192	1147
-3.75°	990	1060	1117	1160	1192	1212	1218	1212	1192	1160	1117
-5°	948	1016	1074	1117	1147	1166	1173	1166	1147	1117	1074
-6.25°	892	960	1016	1060	1092	1110	1116	1110	1092	1060	1016
-7.5°	828	892	948	990	1022	1041	1047	1041	1022	990	948
-8.75°	757	817	868	910	941	959	965	959	941	910	868
-10°	683	736	784	822	850	868	874	868	850	822	784
-11.25°	609	655	696	730	756	772	777	772	756	730	696
-12.5°	537	577	612	641	663	676	681	676	663	641	612
-13.75°	469	503	533	557	575	587	591	587	575	557	533
-15°	405	434	459	480	495	504	508	504	495	480	459
-16.25°	347	371	391	409	422	430	432	430	422	409	391
-17.5°	295	315	332	345	356	363	365	363	356	345	332
-18.75°	250	266	280	291	299	304	306	304	299	291	280
-20°	211	223	235	244	250	254	256	254	250	244	235
-21.25°	179	188	197	204	209	212	213	212	209	204	197





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	151	159	166	171	175	178	178	178	175	171	166
-23.75°	127	134	139	143	146	148	149	148	146	143	139
-25°	106	112	116	120	122	124	124	124	122	120	116
-26.25°	87	92	96	99	101	102	103	102	101	99	96
-27.5°	70	74	77	80	82	83	83	83	82	80	77
-28.75°	54	58	61	63	65	66	66	66	65	63	61
-30°	40	43	45	47	48	49	49	49	48	47	45
-31.25°	28	30	32	34	35	36	36	36	35	34	32
-32.5°	20	21	22	22	22	23	23	23	22	22	22
-33.75°	16	16	17	18	18	18	18	18	18	18	17
-35°	12	13	13	13	14	14	14	14	14	13	13
-36.25°	9	10	10	11	11	11	11	11	11	11	10
-37.5°	7	8	8	8	8	8	8	8	8	8	8
-38.75°	6	6	6	6	6	6	6	6	6	6	6
-40°	4	4	5	5	5	5	5	5	5	5	5
-41.25°	4	4	4	4	4	4	4	4	4	4	4
-42.5°	3	4	4	4	4	4	4	4	4	4	4
-43.75°	3	3	3	3	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	2	2	2	2
-47.5°	2	2	2	2	2	2	2	2	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	1	1	0	0	0	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	2	2	1	1	1	1	1	1	1
46.25°	2	2	2	2	2	2	2	2	1	1	1
45°	3	3	2	2	2	2	2	2	2	2	2
43.75°	3	3	3	3	3	3	3	2	2	2	2
42.5°	4	3	3	3	3	3	3	3	3	3	2
41.25°	4	4	4	4	4	4	3	3	3	3	3
40°	4	4	4	4	4	4	4	4	4	3	3
38.75°	6	6	5	5	5	4	4	4	4	4	4
37.5°	8	7	7	7	6	6	5	5	4	4	4
36.25°	10	9	9	8	8	7	7	6	6	5	5
35°	13	12	12	11	10	10	9	8	7	7	6



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	16	16	15	14	13	12	11	10	9	8	7
32.5°	21	20	19	18	17	15	14	13	12	11	9
31.25°	30	28	25	22	21	19	18	16	14	13	12
30°	43	40	37	34	30	25	22	20	18	16	14
28.75°	58	54	50	46	42	37	32	27	22	20	18
27.5°	74	70	66	61	56	49	44	38	32	26	21
26.25°	92	87	82	76	71	65	57	50	43	37	30
25°	112	106	100	94	87	79	72	64	56	47	40
23.75°	134	127	120	113	105	96	87	78	69	60	50
22.5°	159	151	142	133	124	114	104	93	83	73	63
21.25°	188	179	168	157	145	134	122	110	98	86	75
20°	223	211	198	184	170	156	141	128	114	101	88
18.75°	266	250	233	215	198	181	164	147	131	117	102
17.5°	315	295	275	253	230	209	188	169	150	133	117
16.25°	371	347	322	295	268	241	215	191	170	150	131
15°	434	405	374	341	310	278	247	217	191	169	147
13.75°	503	469	432	393	355	317	281	247	215	188	164
12.5°	577	537	494	449	404	359	317	278	241	209	181
11.25°	655	609	559	507	455	404	355	310	268	230	198
10°	736	683	625	566	507	449	393	341	295	253	215
8.75°	817	757	692	625	559	494	432	374	322	275	233
7.5°	892	828	757	683	609	537	469	405	347	295	250
6.25°	960	892	817	736	655	577	503	434	371	315	266
5°	1016	948	868	784	696	612	533	459	391	332	280
3.75°	1060	990	910	822	730	641	557	480	409	345	291
2.5°	1092	1022	941	850	756	663	575	495	422	356	299
1.25°	1110	1041	959	868	772	676	587	504	430	363	304
0°	1116	1047	965	874	777	681	591	508	432	365	306
-1.25°	1110	1041	959	868	772	676	587	504	430	363	304
-2.5°	1092	1022	941	850	756	663	575	495	422	356	299
-3.75°	1060	990	910	822	730	641	557	480	409	345	291
-5°	1016	948	868	784	696	612	533	459	391	332	280
-6.25°	960	892	817	736	655	577	503	434	371	315	266
-7.5°	892	828	757	683	609	537	469	405	347	295	250
-8.75°	817	757	692	625	559	494	432	374	322	275	233
-10°	736	683	625	566	507	449	393	341	295	253	215
-11.25°	655	609	559	507	455	404	355	310	268	230	198
-12.5°	577	537	494	449	404	359	317	278	241	209	181
-13.75°	503	469	432	393	355	317	281	247	215	188	164
-15°	434	405	374	341	310	278	247	217	191	169	147
-16.25°	371	347	322	295	268	241	215	191	170	150	131
-17.5°	315	295	275	253	230	209	188	169	150	133	117
-18.75°	266	250	233	215	198	181	164	147	131	117	102
-20°	223	211	198	184	170	156	141	128	114	101	88
-21.25°	188	179	168	157	145	134	122	110	98	86	75



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	159	151	142	133	124	114	104	93	83	73	63
-23.75°	134	127	120	113	105	96	87	78	69	60	50
-25°	112	106	100	94	87	79	72	64	56	47	40
-26.25°	92	87	82	76	71	65	57	50	43	37	30
-27.5°	74	70	66	61	56	49	44	38	32	26	21
-28.75°	58	54	50	46	42	37	32	27	22	20	18
-30°	43	40	37	34	30	25	22	20	18	16	14
-31.25°	30	28	25	22	21	19	18	16	14	13	12
-32.5°	21	20	19	18	17	15	14	13	12	11	9
-33.75°	16	16	15	14	13	12	11	10	9	8	7
-35°	13	12	12	11	10	10	9	8	7	7	6
-36.25°	10	9	9	8	8	7	7	6	6	5	5
-37.5°	8	7	7	7	6	6	5	5	4	4	4
-38.75°	6	6	5	5	5	4	4	4	4	4	4
-40°	4	4	4	4	4	4	4	4	4	3	3
-41.25°	4	4	4	4	4	4	3	3	3	3	3
-42.5°	4	3	3	3	3	3	3	3	3	3	2
-43.75°	3	3	3	3	3	3	3	2	2	2	2
-45°	3	3	2	2	2	2	2	2	2	2	2
-46.25°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	2	2	2	2	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	1	0	0	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	1	1	0	0	0	0
52.5°	1	1	1	1	1	1	1	1	1	0	0
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	2	2	2	1	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	3	3	2	2	2	2	2	1	1	1	1
40°	3	3	3	3	2	2	2	2	1	1	1
38.75°	4	3	3	3	3	2	2	2	2	2	1
37.5°	4	4	4	3	3	3	3	2	2	2	2
36.25°	4	4	4	4	3	3	3	3	2	2	2
35°	5	5	4	4	4	4	3	3	3	3	2



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	7	6	5	4	4	4	4	3	3	3	3
32.5°	8	7	6	5	5	4	4	4	3	3	3
31.25°	10	9	8	7	6	5	4	4	4	3	3
30°	13	11	10	8	7	6	5	4	4	4	3
28.75°	15	13	12	10	8	7	6	5	4	4	4
27.5°	19	16	14	12	10	9	7	6	5	4	4
26.25°	23	20	17	14	12	11	9	7	6	5	4
25°	32	24	20	18	15	12	10	8	7	6	5
23.75°	42	34	25	21	18	14	12	10	8	7	5
22.5°	53	43	34	25	20	17	14	12	10	8	6
21.25°	65	53	43	34	24	20	16	13	11	9	7
20°	76	65	53	42	32	23	19	15	13	10	8
18.75°	88	75	63	50	40	30	21	18	14	12	9
17.5°	101	86	73	60	47	37	26	20	16	13	11
16.25°	114	98	83	69	56	43	32	22	18	14	12
15°	128	110	93	78	64	50	38	27	20	16	13
13.75°	141	122	104	87	72	57	44	32	22	18	14
12.5°	156	134	114	96	79	65	49	37	25	19	15
11.25°	170	145	124	105	87	71	56	42	30	21	17
10°	184	157	133	113	94	76	61	46	34	22	18
8.75°	198	168	142	120	100	82	66	50	37	25	19
7.5°	211	179	151	127	106	87	70	54	40	28	20
6.25°	223	188	159	134	112	92	74	58	43	30	21
5°	235	197	166	139	116	96	77	61	45	32	22
3.75°	244	204	171	143	120	99	80	63	47	34	22
2.5°	250	209	175	146	122	101	82	65	48	35	22
1.25°	254	212	178	148	124	102	83	66	49	36	23
0°	256	213	178	149	124	103	83	66	49	36	23
-1.25°	254	212	178	148	124	102	83	66	49	36	23
-2.5°	250	209	175	146	122	101	82	65	48	35	22
-3.75°	244	204	171	143	120	99	80	63	47	34	22
-5°	235	197	166	139	116	96	77	61	45	32	22
-6.25°	223	188	159	134	112	92	74	58	43	30	21
-7.5°	211	179	151	127	106	87	70	54	40	28	20
-8.75°	198	168	142	120	100	82	66	50	37	25	19
-10°	184	157	133	113	94	76	61	46	34	22	18
-11.25°	170	145	124	105	87	71	56	42	30	21	17
-12.5°	156	134	114	96	79	65	49	37	25	19	15
-13.75°	141	122	104	87	72	57	44	32	22	18	14
-15°	128	110	93	78	64	50	38	27	20	16	13
-16.25°	114	98	83	69	56	43	32	22	18	14	12
-17.5°	101	86	73	60	47	37	26	20	16	13	11
-18.75°	88	75	63	50	40	30	21	18	14	12	9
-20°	76	65	53	42	32	23	19	15	13	10	8
-21.25°	65	53	43	34	24	20	16	13	11	9	7





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	53	43	34	25	20	17	14	12	10	8	6
-23.75°	42	34	25	21	18	14	12	10	8	7	5
-25°	32	24	20	18	15	12	10	8	7	6	5
-26.25°	23	20	17	14	12	11	9	7	6	5	4
-27.5°	19	16	14	12	10	9	7	6	5	4	4
-28.75°	15	13	12	10	8	7	6	5	4	4	4
-30°	13	11	10	8	7	6	5	4	4	4	3
-31.25°	10	9	8	7	6	5	4	4	4	3	3
-32.5°	8	7	6	5	5	4	4	4	3	3	3
-33.75°	7	6	5	4	4	4	4	3	3	3	3
-35°	5	5	4	4	4	4	3	3	3	3	2
-36.25°	4	4	4	4	3	3	3	3	2	2	2
-37.5°	4	4	4	3	3	3	3	2	2	2	2
-38.75°	4	3	3	3	3	2	2	2	2	2	1
-40°	3	3	3	3	2	2	2	2	1	1	1
-41.25°	3	3	2	2	2	2	2	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	0	0
-53.75°	1	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	1	1	0	0	0	0	0	0	0	0	0
48.75°	1	1	1	1	0	0	0	0	0	0	0
47.5°	1	1	1	1	1	0	0	0	0	0	0
46.25°	1	1	1	1	1	1	0	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
43.75°	1	1	1	1	1	1	1	1	1	0	0
42.5°	1	1	1	1	1	1	1	1	1	1	0
41.25°	1	1	1	1	1	1	1	1	1	1	0
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	2	1	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	2	2	2	1	1	1	1	1	1	1	1
32.5°	3	2	2	2	1	1	1	1	1	1	1
31.25°	3	3	2	2	2	1	1	1	1	1	1
30°	3	3	2	2	2	1	1	1	1	1	1
28.75°	3	3	3	2	2	2	1	1	1	1	1
27.5°	4	3	3	3	2	2	2	1	1	1	1
26.25°	4	4	3	3	2	2	2	1	1	1	1
25°	4	4	3	3	3	2	2	2	1	1	1
23.75°	4	4	4	3	3	3	2	2	1	1	1
22.5°	5	4	4	4	3	3	2	2	2	1	1
21.25°	6	5	4	4	3	3	3	2	2	1	1
20°	7	5	4	4	4	3	3	2	2	1	1
18.75°	7	6	5	4	4	3	3	2	2	2	1
17.5°	8	7	5	4	4	3	3	3	2	2	1
16.25°	9	7	6	4	4	4	3	3	2	2	1
15°	10	8	6	5	4	4	3	3	2	2	2
13.75°	11	9	7	5	4	4	3	3	3	2	2
12.5°	12	10	7	6	4	4	4	3	3	2	2
11.25°	13	10	8	6	5	4	4	3	3	2	2
10°	14	11	8	7	5	4	4	3	3	2	2
8.75°	15	12	9	7	5	4	4	3	3	2	2
7.5°	16	12	9	7	6	4	4	3	3	3	2
6.25°	16	13	10	8	6	4	4	4	3	3	2
5°	17	13	10	8	6	5	4	4	3	3	2
3.75°	18	13	11	8	6	5	4	4	3	3	2
2.5°	18	14	11	8	6	5	4	4	3	3	2
1.25°	18	14	11	8	6	5	4	4	3	3	2
0°	18	14	11	8	6	5	4	4	3	3	2
-1.25°	18	14	11	8	6	5	4	4	3	3	2
-2.5°	18	14	11	8	6	5	4	4	3	3	2
-3.75°	18	13	11	8	6	5	4	4	3	3	2
-5°	17	13	10	8	6	5	4	4	3	3	2
-6.25°	16	13	10	8	6	4	4	4	3	3	2
-7.5°	16	12	9	7	6	4	4	3	3	3	2
-8.75°	15	12	9	7	5	4	4	3	3	2	2
-10°	14	11	8	7	5	4	4	3	3	2	2
-11.25°	13	10	8	6	5	4	4	3	3	2	2
-12.5°	12	10	7	6	4	4	4	3	3	2	2
-13.75°	11	9	7	5	4	4	3	3	3	2	2
-15°	10	8	6	5	4	4	3	3	2	2	2
-16.25°	9	7	6	4	4	4	3	3	2	2	1
-17.5°	8	7	5	4	4	3	3	3	2	2	1
-18.75°	7	6	5	4	4	3	3	2	2	2	1
-20°	7	5	4	4	4	3	3	2	2	1	1
-21.25°	6	5	4	4	3	3	3	2	2	1	1



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	5	4	4	4	3	3	2	2	2	1	1
-23.75°	4	4	4	3	3	3	2	2	1	1	1
-25°	4	4	3	3	3	2	2	2	1	1	1
-26.25°	4	4	3	3	2	2	2	1	1	1	1
-27.5°	4	3	3	3	2	2	2	1	1	1	1
-28.75°	3	3	3	2	2	2	1	1	1	1	1
-30°	3	3	2	2	2	1	1	1	1	1	1
-31.25°	3	3	2	2	2	1	1	1	1	1	1
-32.5°	3	2	2	2	1	1	1	1	1	1	1
-33.75°	2	2	2	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	0
-42.5°	1	1	1	1	1	1	1	1	1	1	0
-43.75°	1	1	1	1	1	1	1	1	1	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-46.25°	1	1	1	1	1	1	0	0	0	0	0
-47.5°	1	1	1	1	1	0	0	0	0	0	0
-48.75°	1	1	1	1	0	0	0	0	0	0	0
-50°	1	1	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	1	0	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	0	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	1	1	1	0	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	1	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	1	0	0	0	0	0
26.25°	1	1	1	1	1	1	0	0	0	0	0
25°	1	1	1	1	1	1	0	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	1	0	0	0
18.75°	1	1	1	1	1	1	1	1	0	0	0
17.5°	1	1	1	1	1	1	1	1	0	0	0
16.25°	1	1	1	1	1	1	1	1	0	0	0
15°	1	1	1	1	1	1	1	1	0	0	0
13.75°	1	1	1	1	1	1	1	1	1	0	0
12.5°	1	1	1	1	1	1	1	1	1	0	0
11.25°	1	1	1	1	1	1	1	1	1	0	0
10°	2	1	1	1	1	1	1	1	1	0	0
8.75°	2	1	1	1	1	1	1	1	1	0	0
7.5°	2	1	1	1	1	1	1	1	1	0	0
6.25°	2	1	1	1	1	1	1	1	1	0	0
5°	2	1	1	1	1	1	1	1	1	0	0
3.75°	2	1	1	1	1	1	1	1	1	0	0
2.5°	2	1	1	1	1	1	1	1	1	0	0
1.25°	2	1	1	1	1	1	1	1	1	0	0
0°	2	1	1	1	1	1	1	1	1	0	0
-1.25°	2	1	1	1	1	1	1	1	1	0	0
-2.5°	2	1	1	1	1	1	1	1	1	0	0
-3.75°	2	1	1	1	1	1	1	1	1	0	0
-5°	2	1	1	1	1	1	1	1	1	0	0
-6.25°	2	1	1	1	1	1	1	1	1	0	0
-7.5°	2	1	1	1	1	1	1	1	1	0	0
-8.75°	2	1	1	1	1	1	1	1	1	0	0
-10°	2	1	1	1	1	1	1	1	1	0	0
-11.25°	1	1	1	1	1	1	1	1	1	0	0
-12.5°	1	1	1	1	1	1	1	1	1	0	0
-13.75°	1	1	1	1	1	1	1	1	1	0	0
-15°	1	1	1	1	1	1	1	1	0	0	0
-16.25°	1	1	1	1	1	1	1	1	0	0	0
-17.5°	1	1	1	1	1	1	1	1	0	0	0
-18.75°	1	1	1	1	1	1	1	1	0	0	0
-20°	1	1	1	1	1	1	1	1	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	0	0	0	0	0
-26.25°	1	1	1	1	1	1	0	0	0	0	0
-27.5°	1	1	1	1	1	1	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	1	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	0	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	0	0	0	0	0	0	0	0	0
-37.5°	1	1	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P247020 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)