

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3025-12-CS-LSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-41)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3025-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-25D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	276.5 lumens	Max Intensity:	703.7 candela
Efficiency:	N/A	Max Intensity Angle:	-18.75°H x 0°V
Efficacy:	37.4 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	55.2°H x 22°V	Field Angle (10%):	72.8°H x 46.1°V
Beam Lumens:	149.7 lumens	Field Lumens:	249.8 lumens
Beam Efficiency:	54.1%	Field Efficiency:	90.3%
Input Watts (W):	7.4		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

Iso-Candela Plot




REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

Lumen Table




REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

Luminous Intensity Plot



Beam:
 H Angle: 55.2°
 V Angle: 22°
 Lumens: 149.7
 Efficiency: 54.1%

Field:
 H Angle: 72.8°
 V Angle: 46.1°
 Lumens: 249.8
 Efficiency: 90.3%

Spill:
 Lumens: 26.7
 Efficiency: 9.7%

— Vertical Distribution through -18.75-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	0	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	0	1	1
27.5°	0	0	0	0	0	0	0	0	0	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	0	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	0	1	1
-28.75°	0	0	0	0	0	0	0	0	0	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	0	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	0	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	2
23.75°	1	1	1	1	1	1	1	1	1	1	2
22.5°	1	1	1	1	1	1	1	1	1	1	2
21.25°	1	1	1	1	1	1	1	1	1	2	2
20°	1	1	1	1	1	1	1	1	1	2	2
18.75°	1	1	1	1	1	1	1	1	1	2	2
17.5°	1	1	1	1	1	1	1	1	2	2	2
16.25°	1	1	1	1	1	1	1	1	2	2	2
15°	1	1	1	1	1	1	1	1	2	2	2
13.75°	1	1	1	1	1	1	1	1	2	2	2
12.5°	1	1	1	1	1	1	1	1	2	2	2
11.25°	1	1	1	1	1	1	1	1	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	1	2	2	2	2
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	1	2	2	2
-12.5°	1	1	1	1	1	1	1	1	2	2	2
-13.75°	1	1	1	1	1	1	1	1	2	2	2
-15°	1	1	1	1	1	1	1	1	2	2	2
-16.25°	1	1	1	1	1	1	1	1	2	2	2
-17.5°	1	1	1	1	1	1	1	1	2	2	2
-18.75°	1	1	1	1	1	1	1	1	1	2	2
-20°	1	1	1	1	1	1	1	1	1	2	2
-21.25°	1	1	1	1	1	1	1	1	1	2	2



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	2
-23.75°	1	1	1	1	1	1	1	1	1	1	2
-25°	1	1	1	1	1	1	1	1	1	1	2
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	0	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	0	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	0	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	1	1
71.25°	0	0	0	1	1	1	1	1	1	1	1
70°	0	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	2
48.75°	1	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	1	2	2	2
45°	1	1	1	1	1	1	1	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	2	2	2	2	2	2
41.25°	1	1	1	1	1	2	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	2
38.75°	1	1	1	1	2	2	2	2	2	2	2
37.5°	1	1	1	2	2	2	2	2	2	2	3
36.25°	1	1	1	2	2	2	2	2	2	3	3
35°	1	1	2	2	2	2	2	2	3	3	3



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	2	2	2	2	2	3	3	3	3
32.5°	1	2	2	2	2	2	2	3	3	3	3
31.25°	1	2	2	2	2	2	2	3	3	3	3
30°	1	2	2	2	2	2	3	3	3	3	3
28.75°	2	2	2	2	2	2	3	3	3	3	3
27.5°	2	2	2	2	2	3	3	3	3	3	3
26.25°	2	2	2	2	2	3	3	3	3	3	4
25°	2	2	2	2	2	3	3	3	3	3	4
23.75°	2	2	2	2	3	3	3	3	3	3	4
22.5°	2	2	2	2	3	3	3	3	3	4	4
21.25°	2	2	2	2	3	3	3	3	3	4	4
20°	2	2	2	2	3	3	3	3	3	4	4
18.75°	2	2	2	2	3	3	3	3	4	4	4
17.5°	2	2	2	3	3	3	3	3	4	4	4
16.25°	2	2	2	3	3	3	3	3	4	4	4
15°	2	2	2	3	3	3	3	3	4	4	4
13.75°	2	2	2	3	3	3	3	4	4	4	4
12.5°	2	2	2	3	3	3	3	4	4	4	4
11.25°	2	2	2	3	3	3	3	4	4	4	4
10°	2	2	3	3	3	3	3	4	4	4	5
8.75°	2	2	3	3	3	3	3	4	4	4	5
7.5°	2	2	3	3	3	3	3	4	4	4	5
6.25°	2	2	3	3	3	3	3	4	4	4	5
5°	2	2	3	3	3	3	3	4	4	4	5
3.75°	2	2	3	3	3	3	3	4	4	4	5
2.5°	2	2	3	3	3	3	3	4	4	4	5
1.25°	2	2	3	3	3	3	3	4	4	4	5
0°	2	2	3	3	3	3	4	4	4	4	5
-1.25°	2	2	3	3	3	3	3	4	4	4	5
-2.5°	2	2	3	3	3	3	3	4	4	4	5
-3.75°	2	2	3	3	3	3	3	4	4	4	5
-5°	2	2	3	3	3	3	3	4	4	4	5
-6.25°	2	2	3	3	3	3	3	4	4	4	5
-7.5°	2	2	3	3	3	3	3	4	4	4	5
-8.75°	2	2	3	3	3	3	3	4	4	4	5
-10°	2	2	3	3	3	3	3	4	4	4	5
-11.25°	2	2	2	3	3	3	3	4	4	4	4
-12.5°	2	2	2	3	3	3	3	4	4	4	4
-13.75°	2	2	2	3	3	3	3	4	4	4	4
-15°	2	2	2	3	3	3	3	3	4	4	4
-16.25°	2	2	2	3	3	3	3	3	4	4	4
-17.5°	2	2	2	3	3	3	3	3	4	4	4
-18.75°	2	2	2	2	3	3	3	3	4	4	4
-20°	2	2	2	2	3	3	3	3	3	4	4
-21.25°	2	2	2	2	3	3	3	3	3	4	4



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	3	3	3	3	3	4	4
-23.75°	2	2	2	2	3	3	3	3	3	3	4
-25°	2	2	2	2	2	3	3	3	3	3	4
-26.25°	2	2	2	2	2	3	3	3	3	3	4
-27.5°	2	2	2	2	2	3	3	3	3	3	3
-28.75°	2	2	2	2	2	2	3	3	3	3	3
-30°	1	2	2	2	2	2	3	3	3	3	3
-31.25°	1	2	2	2	2	2	2	3	3	3	3
-32.5°	1	2	2	2	2	2	2	3	3	3	3
-33.75°	1	1	2	2	2	2	2	3	3	3	3
-35°	1	1	2	2	2	2	2	2	3	3	3
-36.25°	1	1	1	2	2	2	2	2	2	3	3
-37.5°	1	1	1	2	2	2	2	2	2	2	3
-38.75°	1	1	1	1	2	2	2	2	2	2	2
-40°	1	1	1	1	2	2	2	2	2	2	2
-41.25°	1	1	1	1	1	2	2	2	2	2	2
-42.5°	1	1	1	1	1	2	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	1	2	2	2	2
-46.25°	1	1	1	1	1	1	1	1	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	2	2
-50°	1	1	1	1	1	1	1	1	1	1	2
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	1	1	1	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	2
57.5°	1	1	1	1	1	1	1	2	2	2	2
56.25°	1	1	1	1	1	2	2	2	2	2	2
55°	1	1	1	1	2	2	2	2	2	2	2
53.75°	1	1	1	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	3	3	3	3	3	3	3	3
41.25°	2	2	3	3	3	3	3	3	3	3	3
40°	2	3	3	3	3	3	3	3	3	3	4
38.75°	3	3	3	3	3	3	3	3	3	4	4
37.5°	3	3	3	3	3	3	3	3	4	4	4
36.25°	3	3	3	3	3	3	3	4	4	4	4
35°	3	3	3	3	3	3	4	4	4	4	5



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	4	4	4	4	5	5
32.5°	3	3	3	3	4	4	4	4	5	5	5
31.25°	3	3	3	3	4	4	4	5	5	5	5
30°	3	3	3	4	4	4	5	5	5	5	6
28.75°	3	3	3	4	4	4	5	5	5	6	6
27.5°	4	3	4	4	4	5	5	5	6	6	7
26.25°	4	4	4	4	5	5	5	6	6	7	8
25°	4	4	4	4	5	5	5	6	7	8	8
23.75°	4	4	4	5	5	5	6	7	7	8	9
22.5°	4	4	4	5	5	6	6	7	8	9	11
21.25°	4	4	5	5	5	6	7	8	9	10	13
20°	4	4	5	5	6	6	7	8	9	12	15
18.75°	4	5	5	5	6	7	8	9	10	14	17
17.5°	4	5	5	5	6	7	8	9	12	15	20
16.25°	4	5	5	6	7	7	9	10	13	17	24
15°	5	5	5	6	7	8	9	11	15	19	28
13.75°	5	5	6	6	7	8	10	13	17	22	31
12.5°	5	5	6	7	7	9	10	14	18	26	35
11.25°	5	5	6	7	8	9	11	15	20	29	38
10°	5	6	6	7	8	10	12	17	22	32	42
8.75°	5	6	6	7	8	10	13	18	25	34	48
7.5°	5	6	6	7	9	11	14	19	27	37	53
6.25°	5	6	7	8	9	11	15	20	29	39	58
5°	6	6	7	8	9	11	16	21	31	41	62
3.75°	6	6	7	8	10	12	17	22	32	43	66
2.5°	6	6	7	8	10	12	17	23	34	45	70
1.25°	6	6	7	8	10	12	18	23	35	46	72
0°	6	6	7	8	10	12	18	24	35	47	74
-1.25°	6	6	7	8	10	12	18	23	35	46	72
-2.5°	6	6	7	8	10	12	17	23	34	45	70
-3.75°	6	6	7	8	10	12	17	22	32	43	66
-5°	6	6	7	8	9	11	16	21	31	41	62
-6.25°	5	6	7	8	9	11	15	20	29	39	58
-7.5°	5	6	6	7	9	11	14	19	27	37	53
-8.75°	5	6	6	7	8	10	13	18	25	34	48
-10°	5	6	6	7	8	10	12	17	22	32	42
-11.25°	5	5	6	7	8	9	11	15	20	29	38
-12.5°	5	5	6	7	7	9	10	14	18	26	35
-13.75°	5	5	6	6	7	8	10	13	17	22	31
-15°	5	5	5	6	7	8	9	11	15	19	28
-16.25°	4	5	5	6	7	7	9	10	13	17	24
-17.5°	4	5	5	5	6	7	8	9	12	15	20
-18.75°	4	5	5	5	6	7	8	9	10	14	17
-20°	4	4	5	5	6	6	7	8	9	12	15
-21.25°	4	4	5	5	5	6	7	8	9	10	13



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	5	5	6	6	7	8	9	11
-23.75°	4	4	4	5	5	5	6	7	7	8	9
-25°	4	4	4	4	5	5	5	6	7	8	8
-26.25°	4	4	4	4	5	5	5	6	6	7	8
-27.5°	4	3	4	4	4	5	5	5	6	6	7
-28.75°	3	3	3	4	4	4	5	5	5	6	6
-30°	3	3	3	4	4	4	5	5	5	5	6
-31.25°	3	3	3	3	4	4	4	5	5	5	5
-32.5°	3	3	3	3	4	4	4	4	5	5	5
-33.75°	3	3	3	3	3	4	4	4	4	5	5
-35°	3	3	3	3	3	3	4	4	4	4	5
-36.25°	3	3	3	3	3	3	3	4	4	4	4
-37.5°	3	3	3	3	3	3	3	3	4	4	4
-38.75°	3	3	3	3	3	3	3	3	3	4	4
-40°	2	3	3	3	3	3	3	3	3	3	4
-41.25°	2	2	3	3	3	3	3	3	3	3	3
-42.5°	2	2	2	3	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	2	2	2	2	2	2	2	2	2	2	3
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	1	2	2	2	2	2	2	2	2
-55°	1	1	1	1	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	4
45°	3	3	3	3	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	3	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	4	4	4	4
40°	4	4	4	4	4	4	4	4	5	5	5
38.75°	4	4	4	4	4	4	5	5	5	5	5
37.5°	4	4	4	4	5	5	5	5	6	6	6
36.25°	5	5	5	5	5	5	6	6	6	7	7
35°	5	5	5	5	5	6	6	7	7	8	8



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	6	6	7	7	8	8	9	9
32.5°	5	6	6	6	7	7	8	9	9	10	11
31.25°	6	6	7	7	8	9	9	10	11	12	13
30°	6	7	7	8	9	10	11	12	13	14	16
28.75°	7	8	8	10	11	12	13	14	15	17	19
27.5°	8	8	10	11	13	15	17	18	19	21	23
26.25°	8	10	12	13	16	19	21	24	25	26	31
25°	10	12	13	17	20	23	27	30	33	36	39
23.75°	12	14	17	21	24	30	35	39	44	47	50
22.5°	13	16	21	25	32	38	44	50	56	60	65
21.25°	15	20	26	32	40	47	56	63	69	76	81
20°	19	25	30	41	50	59	68	76	85	93	98
18.75°	23	30	39	50	60	72	82	92	102	110	117
17.5°	27	34	48	60	72	85	97	109	120	129	139
16.25°	32	43	57	71	85	99	113	126	138	151	164
15°	36	51	67	83	99	114	130	144	159	176	192
13.75°	42	59	75	94	112	130	147	163	182	203	221
12.5°	49	67	85	105	125	146	164	184	208	231	253
11.25°	56	75	95	116	138	161	183	207	235	262	287
10°	62	82	104	126	152	177	202	231	263	294	324
8.75°	69	90	113	137	166	193	222	256	294	330	364
7.5°	75	98	122	149	180	210	243	282	325	366	404
6.25°	81	105	130	160	194	227	264	308	357	402	444
5°	86	112	138	171	207	243	285	335	389	437	482
3.75°	91	118	145	182	220	259	305	361	419	471	518
2.5°	95	123	151	191	231	274	324	385	448	503	553
1.25°	98	127	156	199	242	288	341	407	476	533	586
0°	101	131	160	206	251	299	355	427	500	560	617
-1.25°	98	127	156	199	242	288	341	407	476	533	586
-2.5°	95	123	151	191	231	274	324	385	448	503	553
-3.75°	91	118	145	182	220	259	305	361	419	471	518
-5°	86	112	138	171	207	243	285	335	389	437	482
-6.25°	81	105	130	160	194	227	264	308	357	402	444
-7.5°	75	98	122	149	180	210	243	282	325	366	404
-8.75°	69	90	113	137	166	193	222	256	294	330	364
-10°	62	82	104	126	152	177	202	231	263	294	324
-11.25°	56	75	95	116	138	161	183	207	235	262	287
-12.5°	49	67	85	105	125	146	164	184	208	231	253
-13.75°	42	59	75	94	112	130	147	163	182	203	221
-15°	36	51	67	83	99	114	130	144	159	176	192
-16.25°	32	43	57	71	85	99	113	126	138	151	164
-17.5°	27	34	48	60	72	85	97	109	120	129	139
-18.75°	23	30	39	50	60	72	82	92	102	110	117
-20°	19	25	30	41	50	59	68	76	85	93	98
-21.25°	15	20	26	32	40	47	56	63	69	76	81



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	13	16	21	25	32	38	44	50	56	60	65
-23.75°	12	14	17	21	24	30	35	39	44	47	50
-25°	10	12	13	17	20	23	27	30	33	36	39
-26.25°	8	10	12	13	16	19	21	24	25	26	31
-27.5°	8	8	10	11	13	15	17	18	19	21	23
-28.75°	7	8	8	10	11	12	13	14	15	17	19
-30°	6	7	7	8	9	10	11	12	13	14	16
-31.25°	6	6	7	7	8	9	9	10	11	12	13
-32.5°	5	6	6	6	7	7	8	9	9	10	11
-33.75°	5	5	5	6	6	7	7	8	8	9	9
-35°	5	5	5	5	5	6	6	7	7	8	8
-36.25°	5	5	5	5	5	5	6	6	6	7	7
-37.5°	4	4	4	4	5	5	5	5	6	6	6
-38.75°	4	4	4	4	4	4	5	5	5	5	5
-40°	4	4	4	4	4	4	4	4	5	5	5
-41.25°	4	4	4	4	4	4	4	4	4	4	4
-42.5°	3	4	4	4	4	4	4	4	4	4	4
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	3	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	3	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	3	4
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	3	3	3	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	5	5
42.5°	4	4	4	4	4	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	5	5	5	5	6
40°	5	5	5	5	5	5	6	6	6	6	6
38.75°	6	6	6	6	6	6	7	7	7	7	7
37.5°	6	7	7	7	7	7	7	7	7	7	7
36.25°	7	8	8	8	8	8	8	8	8	8	8
35°	8	9	9	9	9	9	9	9	9	9	10



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	10	10	10	10	11	11	11	10	11	11	11
32.5°	11	12	12	13	13	13	13	12	12	13	13
31.25°	13	15	15	16	16	16	16	14	14	14	15
30°	17	18	19	20	21	20	19	18	17	18	18
28.75°	21	23	25	26	26	26	25	23	21	21	22
27.5°	27	29	31	33	34	34	32	30	27	27	28
26.25°	34	37	40	42	43	42	42	39	37	34	36
25°	43	48	51	53	54	54	53	51	48	45	46
23.75°	55	59	63	65	66	67	66	65	61	57	56
22.5°	68	72	76	79	81	82	81	79	76	72	67
21.25°	85	86	91	95	97	98	97	96	92	87	81
20°	103	106	107	111	114	115	115	113	110	105	99
18.75°	124	129	130	129	132	134	134	132	129	125	120
17.5°	148	154	156	154	152	154	154	153	151	148	143
16.25°	175	182	186	185	179	174	175	175	175	173	170
15°	205	214	221	222	215	202	199	201	202	201	198
13.75°	237	250	260	260	254	244	231	229	230	230	227
12.5°	273	291	300	302	297	288	276	261	260	260	258
11.25°	312	333	343	345	341	333	322	308	293	292	293
10°	355	376	387	390	387	379	368	355	341	329	329
8.75°	398	420	432	435	431	424	413	401	389	378	368
7.5°	439	463	475	480	476	468	457	446	435	425	418
6.25°	480	505	516	519	517	511	501	489	478	470	466
5°	520	545	555	557	553	545	536	528	520	513	509
3.75°	559	584	594	593	587	576	565	555	549	547	549
2.5°	597	622	631	629	621	607	592	581	573	570	572
1.25°	633	660	668	665	654	638	620	606	596	591	591
0°	668	696	704	700	688	669	648	632	618	612	609
-1.25°	633	660	668	665	654	638	620	606	596	591	591
-2.5°	597	622	631	629	621	607	592	581	573	570	572
-3.75°	559	584	594	593	587	576	565	555	549	547	549
-5°	520	545	555	557	553	545	536	528	520	513	509
-6.25°	480	505	516	519	517	511	501	489	478	470	466
-7.5°	439	463	475	480	476	468	457	446	435	425	418
-8.75°	398	420	432	435	431	424	413	401	389	378	368
-10°	355	376	387	390	387	379	368	355	341	329	329
-11.25°	312	333	343	345	341	333	322	308	293	292	293
-12.5°	273	291	300	302	297	288	276	261	260	260	258
-13.75°	237	250	260	260	254	244	231	229	230	230	227
-15°	205	214	221	222	215	202	199	201	202	201	198
-16.25°	175	182	186	185	179	174	175	175	175	173	170
-17.5°	148	154	156	154	152	154	154	153	151	148	143
-18.75°	124	129	130	129	132	134	134	132	129	125	120
-20°	103	106	107	111	114	115	115	113	110	105	99
-21.25°	85	86	91	95	97	98	97	96	92	87	81



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	68	72	76	79	81	82	81	79	76	72	67
-23.75°	55	59	63	65	66	67	66	65	61	57	56
-25°	43	48	51	53	54	54	53	51	48	45	46
-26.25°	34	37	40	42	43	42	42	39	37	34	36
-27.5°	27	29	31	33	34	34	32	30	27	27	28
-28.75°	21	23	25	26	26	26	25	23	21	21	22
-30°	17	18	19	20	21	20	19	18	17	18	18
-31.25°	13	15	15	16	16	16	16	14	14	14	15
-32.5°	11	12	12	13	13	13	13	12	12	13	13
-33.75°	10	10	10	10	11	11	11	10	11	11	11
-35°	8	9	9	9	9	9	9	9	9	9	10
-36.25°	7	8	8	8	8	8	8	8	8	8	8
-37.5°	6	7	7	7	7	7	7	7	7	7	7
-38.75°	6	6	6	6	6	6	7	7	7	7	7
-40°	5	5	5	5	5	5	6	6	6	6	6
-41.25°	5	5	5	5	5	5	5	5	5	5	6
-42.5°	4	4	4	4	4	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	3	3	3	4	4	4	4
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	0	0	0	0	0	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	4	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	6	6	6
40°	6	6	6	6	6	6	6	6	6	6	6
38.75°	7	7	7	7	7	7	7	7	7	7	7
37.5°	7	7	7	7	7	7	7	7	7	7	7
36.25°	8	8	9	9	9	9	8	9	9	9	9
35°	10	10	10	10	10	10	10	10	10	10	10



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	11	12	12	12	11	11	11	11	11	12	12
32.5°	13	13	13	13	13	13	12	13	13	13	13
31.25°	15	15	15	15	15	15	14	15	15	15	15
30°	18	18	18	18	17	17	16	17	17	18	18
28.75°	22	23	23	22	22	21	20	21	22	22	23
27.5°	29	29	29	29	28	27	26	27	28	29	29
26.25°	37	38	38	37	37	35	34	35	37	37	38
25°	47	47	48	47	46	45	43	45	46	47	48
23.75°	57	58	58	57	56	54	52	54	56	57	58
22.5°	69	69	69	69	67	65	63	65	67	69	69
21.25°	82	83	83	82	81	79	75	79	81	82	83
20°	97	98	99	98	96	93	90	93	96	98	99
18.75°	114	116	117	116	114	111	106	111	114	116	117
17.5°	137	137	138	137	135	131	125	131	135	137	138
16.25°	164	159	160	159	156	152	145	152	156	159	160
15°	192	183	183	183	181	176	169	176	181	183	183
13.75°	221	214	210	210	208	202	195	202	208	210	210
12.5°	255	248	241	241	240	235	227	235	240	241	241
11.25°	291	286	280	279	279	275	266	275	279	279	280
10°	330	328	324	321	323	320	311	320	323	321	324
8.75°	371	373	373	370	373	371	363	371	373	370	373
7.5°	415	420	423	424	425	425	418	425	425	424	423
6.25°	464	466	473	476	476	478	471	478	476	476	473
5°	509	514	518	524	526	528	521	528	526	524	518
3.75°	550	555	560	564	569	571	566	571	569	564	560
2.5°	579	589	593	597	601	604	602	604	601	597	593
1.25°	595	603	611	619	624	625	627	625	624	619	611
0°	609	615	620	627	631	633	637	633	631	627	620
-1.25°	595	603	611	619	624	625	627	625	624	619	611
-2.5°	579	589	593	597	601	604	602	604	601	597	593
-3.75°	550	555	560	564	569	571	566	571	569	564	560
-5°	509	514	518	524	526	528	521	528	526	524	518
-6.25°	464	466	473	476	476	478	471	478	476	476	473
-7.5°	415	420	423	424	425	425	418	425	425	424	423
-8.75°	371	373	373	370	373	371	363	371	373	370	373
-10°	330	328	324	321	323	320	311	320	323	321	324
-11.25°	291	286	280	279	279	275	266	275	279	279	280
-12.5°	255	248	241	241	240	235	227	235	240	241	241
-13.75°	221	214	210	210	208	202	195	202	208	210	210
-15°	192	183	183	183	181	176	169	176	181	183	183
-16.25°	164	159	160	159	156	152	145	152	156	159	160
-17.5°	137	137	138	137	135	131	125	131	135	137	138
-18.75°	114	116	117	116	114	111	106	111	114	116	117
-20°	97	98	99	98	96	93	90	93	96	98	99
-21.25°	82	83	83	82	81	79	75	79	81	82	83



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	69	69	69	69	67	65	63	65	67	69	69
-23.75°	57	58	58	57	56	54	52	54	56	57	58
-25°	47	47	48	47	46	45	43	45	46	47	48
-26.25°	37	38	38	37	37	35	34	35	37	37	38
-27.5°	29	29	29	29	28	27	26	27	28	29	29
-28.75°	22	23	23	22	22	21	20	21	22	22	23
-30°	18	18	18	18	17	17	16	17	17	18	18
-31.25°	15	15	15	15	15	15	14	15	15	15	15
-32.5°	13	13	13	13	13	13	12	13	13	13	13
-33.75°	11	12	12	12	11	11	11	11	11	12	12
-35°	10	10	10	10	10	10	10	10	10	10	10
-36.25°	8	8	9	9	9	9	8	9	9	9	9
-37.5°	7	7	7	7	7	7	7	7	7	7	7
-38.75°	7	7	7	7	7	7	7	7	7	7	7
-40°	6	6	6	6	6	6	6	6	6	6	6
-41.25°	6	6	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	4	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	0	0	0	0	0	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	4	4	3	3	3	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	5	5	4	4	4
41.25°	6	6	6	5	5	5	5	5	5	5	5
40°	6	6	6	6	6	6	6	5	5	5	5
38.75°	7	7	7	7	7	7	7	6	6	6	6
37.5°	7	7	7	7	7	7	7	7	7	7	7
36.25°	8	8	8	8	8	8	8	8	8	8	8
35°	10	10	10	9	9	9	9	9	9	9	9



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	12	11	11	11	11	10	11	11	11	10	10
32.5°	13	13	13	13	12	12	13	13	13	13	12
31.25°	15	15	15	14	14	14	16	16	16	16	15
30°	18	18	18	18	17	18	19	20	21	20	19
28.75°	23	22	22	21	21	23	25	26	26	26	25
27.5°	29	29	28	27	27	30	32	34	34	33	31
26.25°	38	37	36	34	37	39	42	42	43	42	40
25°	47	47	46	45	48	51	53	54	54	53	51
23.75°	58	57	56	57	61	65	66	67	66	65	63
22.5°	69	69	67	72	76	79	81	82	81	79	76
21.25°	83	82	81	87	92	96	97	98	97	95	91
20°	98	97	99	105	110	113	115	115	114	111	107
18.75°	116	114	120	125	129	132	134	134	132	129	130
17.5°	137	137	143	148	151	153	154	154	152	154	156
16.25°	159	164	170	173	175	175	175	174	179	185	186
15°	183	192	198	201	202	201	199	202	215	222	221
13.75°	214	221	227	230	230	229	231	244	254	260	260
12.5°	248	255	258	260	260	261	276	288	297	302	300
11.25°	286	291	293	292	293	308	322	333	341	345	343
10°	328	330	329	329	341	355	368	379	387	390	387
8.75°	373	371	368	378	389	401	413	424	431	435	432
7.5°	420	415	418	425	435	446	457	468	476	480	475
6.25°	466	464	466	470	478	489	501	511	517	519	516
5°	514	509	509	513	520	528	536	545	553	557	555
3.75°	555	550	549	547	549	555	565	576	587	593	594
2.5°	589	579	572	570	573	581	592	607	621	629	631
1.25°	603	595	591	591	596	606	620	638	654	665	668
0°	615	609	609	612	618	632	648	669	688	700	704
-1.25°	603	595	591	591	596	606	620	638	654	665	668
-2.5°	589	579	572	570	573	581	592	607	621	629	631
-3.75°	555	550	549	547	549	555	565	576	587	593	594
-5°	514	509	509	513	520	528	536	545	553	557	555
-6.25°	466	464	466	470	478	489	501	511	517	519	516
-7.5°	420	415	418	425	435	446	457	468	476	480	475
-8.75°	373	371	368	378	389	401	413	424	431	435	432
-10°	328	330	329	329	341	355	368	379	387	390	387
-11.25°	286	291	293	292	293	308	322	333	341	345	343
-12.5°	248	255	258	260	260	261	276	288	297	302	300
-13.75°	214	221	227	230	230	229	231	244	254	260	260
-15°	183	192	198	201	202	201	199	202	215	222	221
-16.25°	159	164	170	173	175	175	175	174	179	185	186
-17.5°	137	137	143	148	151	153	154	154	152	154	156
-18.75°	116	114	120	125	129	132	134	134	132	129	130
-20°	98	97	99	105	110	113	115	115	114	111	107
-21.25°	83	82	81	87	92	96	97	98	97	95	91



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	69	69	67	72	76	79	81	82	81	79	76
-23.75°	58	57	56	57	61	65	66	67	66	65	63
-25°	47	47	46	45	48	51	53	54	54	53	51
-26.25°	38	37	36	34	37	39	42	42	43	42	40
-27.5°	29	29	28	27	27	30	32	34	34	33	31
-28.75°	23	22	22	21	21	23	25	26	26	26	25
-30°	18	18	18	18	17	18	19	20	21	20	19
-31.25°	15	15	15	14	14	14	16	16	16	16	15
-32.5°	13	13	13	13	12	12	13	13	13	13	12
-33.75°	12	11	11	11	11	10	11	11	11	10	10
-35°	10	10	10	9	9	9	9	9	9	9	9
-36.25°	8	8	8	8	8	8	8	8	8	8	8
-37.5°	7	7	7	7	7	7	7	7	7	7	7
-38.75°	7	7	7	7	7	7	7	6	6	6	6
-40°	6	6	6	6	6	6	6	5	5	5	5
-41.25°	6	6	6	5	5	5	5	5	5	5	5
-42.5°	5	5	5	5	5	5	5	5	4	4	4
-43.75°	5	5	5	5	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	3	3	3	4	4
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	3	3	3	3
45°	4	4	4	4	4	4	4	4	4	3	3
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	5	5	4	4	4	4	4	4	4	4	4
40°	5	5	5	5	5	4	4	4	4	4	4
38.75°	6	6	5	5	5	5	5	4	4	4	4
37.5°	7	6	6	6	6	5	5	5	5	4	4
36.25°	8	7	7	7	6	6	6	5	5	5	5
35°	9	8	8	8	7	7	6	6	5	5	5



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	10	10	9	9	8	8	7	7	6	6	5
32.5°	12	11	11	10	9	9	8	7	7	6	6
31.25°	15	13	13	12	11	10	9	9	8	7	7
30°	18	17	16	14	13	12	11	10	9	8	7
28.75°	23	21	19	17	15	14	13	12	11	10	8
27.5°	29	27	23	21	19	18	17	15	13	11	10
26.25°	37	34	31	26	25	24	21	19	16	13	12
25°	48	43	39	36	33	30	27	23	20	17	13
23.75°	59	55	50	47	44	39	35	30	24	21	17
22.5°	72	68	65	60	56	50	44	38	32	25	21
21.25°	86	85	81	76	69	63	56	47	40	32	26
20°	106	103	98	93	85	76	68	59	50	41	30
18.75°	129	124	117	110	102	92	82	72	60	50	39
17.5°	154	148	139	129	120	109	97	85	72	60	48
16.25°	182	175	164	151	138	126	113	99	85	71	57
15°	214	205	192	176	159	144	130	114	99	83	67
13.75°	250	237	221	203	182	163	147	130	112	94	75
12.5°	291	273	253	231	208	184	164	146	125	105	85
11.25°	333	312	287	262	235	207	183	161	138	116	95
10°	376	355	324	294	263	231	202	177	152	126	104
8.75°	420	398	364	330	294	256	222	193	166	137	113
7.5°	463	439	404	366	325	282	243	210	180	149	122
6.25°	505	480	444	402	357	308	264	227	194	160	130
5°	545	520	482	437	389	335	285	243	207	171	138
3.75°	584	559	518	471	419	361	305	259	220	182	145
2.5°	622	597	553	503	448	385	324	274	231	191	151
1.25°	660	633	586	533	476	407	341	288	242	199	156
0°	696	668	617	560	500	427	355	299	251	206	160
-1.25°	660	633	586	533	476	407	341	288	242	199	156
-2.5°	622	597	553	503	448	385	324	274	231	191	151
-3.75°	584	559	518	471	419	361	305	259	220	182	145
-5°	545	520	482	437	389	335	285	243	207	171	138
-6.25°	505	480	444	402	357	308	264	227	194	160	130
-7.5°	463	439	404	366	325	282	243	210	180	149	122
-8.75°	420	398	364	330	294	256	222	193	166	137	113
-10°	376	355	324	294	263	231	202	177	152	126	104
-11.25°	333	312	287	262	235	207	183	161	138	116	95
-12.5°	291	273	253	231	208	184	164	146	125	105	85
-13.75°	250	237	221	203	182	163	147	130	112	94	75
-15°	214	205	192	176	159	144	130	114	99	83	67
-16.25°	182	175	164	151	138	126	113	99	85	71	57
-17.5°	154	148	139	129	120	109	97	85	72	60	48
-18.75°	129	124	117	110	102	92	82	72	60	50	39
-20°	106	103	98	93	85	76	68	59	50	41	30
-21.25°	86	85	81	76	69	63	56	47	40	32	26



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	72	68	65	60	56	50	44	38	32	25	21
-23.75°	59	55	50	47	44	39	35	30	24	21	17
-25°	48	43	39	36	33	30	27	23	20	17	13
-26.25°	37	34	31	26	25	24	21	19	16	13	12
-27.5°	29	27	23	21	19	18	17	15	13	11	10
-28.75°	23	21	19	17	15	14	13	12	11	10	8
-30°	18	17	16	14	13	12	11	10	9	8	7
-31.25°	15	13	13	12	11	10	9	9	8	7	7
-32.5°	12	11	11	10	9	9	8	7	7	6	6
-33.75°	10	10	9	9	8	8	7	7	6	6	5
-35°	9	8	8	8	7	7	6	6	5	5	5
-36.25°	8	7	7	7	6	6	6	5	5	5	5
-37.5°	7	6	6	6	6	5	5	5	5	4	4
-38.75°	6	6	5	5	5	5	5	4	4	4	4
-40°	5	5	5	5	5	4	4	4	4	4	4
-41.25°	5	5	4	4	4	4	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	3	3
-46.25°	4	4	4	4	4	4	4	3	3	3	3
-47.5°	4	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	1	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	1	1	1
55°	2	2	2	2	2	2	2	2	2	1	1
53.75°	2	2	2	2	2	2	2	2	2	2	1
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	4	3	3	3	3	3	3	3	3	3	2
41.25°	4	4	3	3	3	3	3	3	3	3	3
40°	4	4	4	3	3	3	3	3	3	3	3
38.75°	4	4	4	4	3	3	3	3	3	3	3
37.5°	4	4	4	4	4	3	3	3	3	3	3
36.25°	5	5	4	4	4	4	3	3	3	3	3
35°	5	5	5	4	4	4	4	3	3	3	3



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	5	5	4	4	4	4	3	3	3
32.5°	6	5	5	5	5	4	4	4	4	3	3
31.25°	6	6	5	5	5	5	4	4	4	3	3
30°	7	6	6	5	5	5	5	4	4	4	3
28.75°	8	7	6	6	5	5	5	4	4	4	3
27.5°	8	8	7	6	6	5	5	5	4	4	4
26.25°	10	8	8	7	6	6	5	5	5	4	4
25°	12	10	8	8	7	6	5	5	5	4	4
23.75°	14	12	9	8	7	7	6	5	5	5	4
22.5°	16	13	11	9	8	7	6	6	5	5	4
21.25°	20	15	13	10	9	8	7	6	5	5	5
20°	25	19	15	12	9	8	7	6	6	5	5
18.75°	30	23	17	14	10	9	8	7	6	5	5
17.5°	34	27	20	15	12	9	8	7	6	5	5
16.25°	43	32	24	17	13	10	9	7	7	6	5
15°	51	36	28	19	15	11	9	8	7	6	5
13.75°	59	42	31	22	17	13	10	8	7	6	6
12.5°	67	49	35	26	18	14	10	9	7	7	6
11.25°	75	56	38	29	20	15	11	9	8	7	6
10°	82	62	42	32	22	17	12	10	8	7	6
8.75°	90	69	48	34	25	18	13	10	8	7	6
7.5°	98	75	53	37	27	19	14	11	9	7	6
6.25°	105	81	58	39	29	20	15	11	9	8	7
5°	112	86	62	41	31	21	16	11	9	8	7
3.75°	118	91	66	43	32	22	17	12	10	8	7
2.5°	123	95	70	45	34	23	17	12	10	8	7
1.25°	127	98	72	46	35	23	18	12	10	8	7
0°	131	101	74	47	35	24	18	12	10	8	7
-1.25°	127	98	72	46	35	23	18	12	10	8	7
-2.5°	123	95	70	45	34	23	17	12	10	8	7
-3.75°	118	91	66	43	32	22	17	12	10	8	7
-5°	112	86	62	41	31	21	16	11	9	8	7
-6.25°	105	81	58	39	29	20	15	11	9	8	7
-7.5°	98	75	53	37	27	19	14	11	9	7	6
-8.75°	90	69	48	34	25	18	13	10	8	7	6
-10°	82	62	42	32	22	17	12	10	8	7	6
-11.25°	75	56	38	29	20	15	11	9	8	7	6
-12.5°	67	49	35	26	18	14	10	9	7	7	6
-13.75°	59	42	31	22	17	13	10	8	7	6	6
-15°	51	36	28	19	15	11	9	8	7	6	5
-16.25°	43	32	24	17	13	10	9	7	7	6	5
-17.5°	34	27	20	15	12	9	8	7	6	5	5
-18.75°	30	23	17	14	10	9	8	7	6	5	5
-20°	25	19	15	12	9	8	7	6	6	5	5
-21.25°	20	15	13	10	9	8	7	6	5	5	5



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	16	13	11	9	8	7	6	6	5	5	4
-23.75°	14	12	9	8	7	7	6	5	5	5	4
-25°	12	10	8	8	7	6	5	5	5	4	4
-26.25°	10	8	8	7	6	6	5	5	5	4	4
-27.5°	8	8	7	6	6	5	5	5	4	4	4
-28.75°	8	7	6	6	5	5	5	4	4	4	3
-30°	7	6	6	5	5	5	5	4	4	4	3
-31.25°	6	6	5	5	5	5	4	4	4	3	3
-32.5°	6	5	5	5	5	4	4	4	4	3	3
-33.75°	5	5	5	5	4	4	4	4	3	3	3
-35°	5	5	5	4	4	4	4	3	3	3	3
-36.25°	5	5	4	4	4	4	3	3	3	3	3
-37.5°	4	4	4	4	4	3	3	3	3	3	3
-38.75°	4	4	4	4	3	3	3	3	3	3	3
-40°	4	4	4	3	3	3	3	3	3	3	3
-41.25°	4	4	3	3	3	3	3	3	3	3	3
-42.5°	4	3	3	3	3	3	3	3	3	3	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	1
-55°	2	2	2	2	2	2	2	2	2	1	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	2	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	1	1	1	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	1	1	1	1	1	1	1	1	1
50°	2	2	2	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	2	2	2	2	2	1	1	1	1	1	1
45°	2	2	2	2	2	2	1	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	2	1	1	1
41.25°	2	2	2	2	2	2	2	2	1	1	1
40°	3	2	2	2	2	2	2	2	2	1	1
38.75°	3	3	2	2	2	2	2	2	2	1	1
37.5°	3	3	3	2	2	2	2	2	2	2	1
36.25°	3	3	3	3	2	2	2	2	2	2	1
35°	3	3	3	3	3	2	2	2	2	2	2



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	3	3	3	2	2	2	2	2
32.5°	3	3	3	3	3	3	2	2	2	2	2
31.25°	3	3	3	3	3	3	2	2	2	2	2
30°	3	3	3	3	3	3	3	2	2	2	2
28.75°	3	3	3	3	3	3	3	2	2	2	2
27.5°	3	4	3	3	3	3	3	3	2	2	2
26.25°	4	4	4	3	3	3	3	3	2	2	2
25°	4	4	4	3	3	3	3	3	2	2	2
23.75°	4	4	4	3	3	3	3	3	3	2	2
22.5°	4	4	4	4	3	3	3	3	3	2	2
21.25°	4	4	4	4	3	3	3	3	3	2	2
20°	4	4	4	4	3	3	3	3	3	2	2
18.75°	5	4	4	4	4	3	3	3	3	2	2
17.5°	5	4	4	4	4	3	3	3	3	3	2
16.25°	5	4	4	4	4	3	3	3	3	3	2
15°	5	5	4	4	4	3	3	3	3	3	2
13.75°	5	5	4	4	4	4	3	3	3	3	2
12.5°	5	5	4	4	4	4	3	3	3	3	2
11.25°	5	5	4	4	4	4	3	3	3	3	2
10°	6	5	5	4	4	4	3	3	3	3	3
8.75°	6	5	5	4	4	4	3	3	3	3	3
7.5°	6	5	5	4	4	4	3	3	3	3	3
6.25°	6	5	5	4	4	4	3	3	3	3	3
5°	6	6	5	4	4	4	3	3	3	3	3
3.75°	6	6	5	4	4	4	3	3	3	3	3
2.5°	6	6	5	4	4	4	3	3	3	3	3
1.25°	6	6	5	4	4	4	3	3	3	3	3
0°	6	6	5	4	4	4	4	3	3	3	3
-1.25°	6	6	5	4	4	4	3	3	3	3	3
-2.5°	6	6	5	4	4	4	3	3	3	3	3
-3.75°	6	6	5	4	4	4	3	3	3	3	3
-5°	6	6	5	4	4	4	3	3	3	3	3
-6.25°	6	5	5	4	4	4	3	3	3	3	3
-7.5°	6	5	5	4	4	4	3	3	3	3	3
-8.75°	6	5	5	4	4	4	3	3	3	3	3
-10°	6	5	5	4	4	4	3	3	3	3	3
-11.25°	5	5	4	4	4	4	3	3	3	3	2
-12.5°	5	5	4	4	4	4	3	3	3	3	2
-13.75°	5	5	4	4	4	4	3	3	3	3	2
-15°	5	5	4	4	4	3	3	3	3	3	2
-16.25°	5	4	4	4	4	3	3	3	3	3	2
-17.5°	5	4	4	4	4	3	3	3	3	3	2
-18.75°	5	4	4	4	4	3	3	3	3	2	2
-20°	4	4	4	4	3	3	3	3	3	2	2
-21.25°	4	4	4	4	3	3	3	3	3	2	2



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	4	3	3	3	3	3	2	2
-23.75°	4	4	4	3	3	3	3	3	3	2	2
-25°	4	4	4	3	3	3	3	3	2	2	2
-26.25°	4	4	4	3	3	3	3	3	2	2	2
-27.5°	3	4	3	3	3	3	3	3	2	2	2
-28.75°	3	3	3	3	3	3	3	2	2	2	2
-30°	3	3	3	3	3	3	3	2	2	2	2
-31.25°	3	3	3	3	3	3	2	2	2	2	2
-32.5°	3	3	3	3	3	3	2	2	2	2	2
-33.75°	3	3	3	3	3	3	2	2	2	2	2
-35°	3	3	3	3	3	2	2	2	2	2	2
-36.25°	3	3	3	3	2	2	2	2	2	2	1
-37.5°	3	3	3	2	2	2	2	2	2	2	1
-38.75°	3	3	2	2	2	2	2	2	2	1	1
-40°	3	2	2	2	2	2	2	2	2	1	1
-41.25°	2	2	2	2	2	2	2	2	1	1	1
-42.5°	2	2	2	2	2	2	2	2	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	1	1	1	1	1
-46.25°	2	2	2	2	2	1	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	2	1	1	1	1	1	1	1	1
-51.25°	2	2	1	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	0
-72.5°	1	1	1	1	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	2	1	1	1	1	1	1	1	1	1	1
31.25°	2	1	1	1	1	1	1	1	1	1	1
30°	2	1	1	1	1	1	1	1	1	1	1
28.75°	2	2	1	1	1	1	1	1	1	1	1
27.5°	2	2	1	1	1	1	1	1	1	1	1
26.25°	2	2	1	1	1	1	1	1	1	1	1
25°	2	2	2	1	1	1	1	1	1	1	1
23.75°	2	2	2	1	1	1	1	1	1	1	1
22.5°	2	2	2	1	1	1	1	1	1	1	1
21.25°	2	2	2	2	1	1	1	1	1	1	1
20°	2	2	2	2	1	1	1	1	1	1	1
18.75°	2	2	2	2	1	1	1	1	1	1	1
17.5°	2	2	2	2	2	1	1	1	1	1	1
16.25°	2	2	2	2	2	1	1	1	1	1	1
15°	2	2	2	2	2	1	1	1	1	1	1
13.75°	2	2	2	2	2	1	1	1	1	1	1
12.5°	2	2	2	2	2	1	1	1	1	1	1
11.25°	2	2	2	2	2	1	1	1	1	1	1
10°	2	2	2	2	2	2	1	1	1	1	1
8.75°	2	2	2	2	2	2	1	1	1	1	1
7.5°	2	2	2	2	2	2	1	1	1	1	1
6.25°	2	2	2	2	2	2	1	1	1	1	1
5°	2	2	2	2	2	2	1	1	1	1	1
3.75°	2	2	2	2	2	2	1	1	1	1	1
2.5°	2	2	2	2	2	2	1	1	1	1	1
1.25°	2	2	2	2	2	2	1	1	1	1	1
0°	2	2	2	2	2	2	1	1	1	1	1
-1.25°	2	2	2	2	2	2	1	1	1	1	1
-2.5°	2	2	2	2	2	2	1	1	1	1	1
-3.75°	2	2	2	2	2	2	1	1	1	1	1
-5°	2	2	2	2	2	2	1	1	1	1	1
-6.25°	2	2	2	2	2	2	1	1	1	1	1
-7.5°	2	2	2	2	2	2	1	1	1	1	1
-8.75°	2	2	2	2	2	2	1	1	1	1	1
-10°	2	2	2	2	2	2	1	1	1	1	1
-11.25°	2	2	2	2	2	1	1	1	1	1	1
-12.5°	2	2	2	2	2	1	1	1	1	1	1
-13.75°	2	2	2	2	2	1	1	1	1	1	1
-15°	2	2	2	2	2	1	1	1	1	1	1
-16.25°	2	2	2	2	2	1	1	1	1	1	1
-17.5°	2	2	2	2	2	1	1	1	1	1	1
-18.75°	2	2	2	2	1	1	1	1	1	1	1
-20°	2	2	2	2	1	1	1	1	1	1	1
-21.25°	2	2	2	2	1	1	1	1	1	1	1



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	1	1	1	1	1	1	1	1
-23.75°	2	2	2	1	1	1	1	1	1	1	1
-25°	2	2	2	1	1	1	1	1	1	1	1
-26.25°	2	2	1	1	1	1	1	1	1	1	1
-27.5°	2	2	1	1	1	1	1	1	1	1	1
-28.75°	2	2	1	1	1	1	1	1	1	1	1
-30°	2	1	1	1	1	1	1	1	1	1	1
-31.25°	2	1	1	1	1	1	1	1	1	1	1
-32.5°	2	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	0	0	0	0	0
-66.25°	1	1	1	1	1	0	0	0	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	1	1	1	0	0	0	0	0	0	0	0
-70°	1	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	0	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	0	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	0	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	0	0	0	0	0	0	0
27.5°	1	1	1	1	0	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	0	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	0	0	0	0	0	0	0
-28.75°	1	1	1	1	0	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	0	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	0	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	0	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P246980 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)