

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4036-12-CS-LSL**

Test Date: 04/06/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-45)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4036-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	317.2 lumens	Max Intensity:	559 candela
Efficiency:	N/A	Max Intensity Angle:	-11.25°H x 0°V
Efficacy:	41.7 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	59.6°H x 32.6°V	Field Angle (10%):	78.4°H x 52.6°V
Beam Lumens:	208.3 lumens	Field Lumens:	290.2 lumens
Beam Efficiency:	65.7%	Field Efficiency:	91.5%
Input Watts (W):	7.6		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.669		
Voltage Rise (V):	NR		
Power Factor:	0.9907		
Total Harmonic Distortion (THDi):	27.4		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.2		
Test Distance:	25 FT		


REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

Lumen Table




REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

Luminous Intensity Plot



Beam:
 H Angle: 59.6°
 V Angle: 32.6°
 Lumens: 208.3
 Efficiency: 65.7%

Field:
 H Angle: 78.4°
 V Angle: 52.6°
 Lumens: 290.2
 Efficiency: 91.5%

Spill:
 Lumens: 27
 Efficiency: 8.5%

— Vertical Distribution through -11.25-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	1
57.5°	0	0	0	0	0	0	0	0	0	0	1
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	0	1	1
51.25°	0	0	0	0	0	0	0	0	0	1	1
50°	0	0	0	0	0	0	0	0	1	1	1
48.75°	0	0	0	0	0	0	0	0	1	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
46.25°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	1	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
36.25°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	1	1	1	1	1
31.25°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	0	1	1	1	1	1
28.75°	0	0	0	0	0	0	1	1	1	1	1
27.5°	0	0	0	0	0	0	1	1	1	1	1
26.25°	0	0	0	0	0	0	1	1	1	1	1
25°	0	0	0	0	0	0	1	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	0	1	1	1	1	1
18.75°	0	0	0	0	0	0	1	1	1	1	1
17.5°	0	0	0	0	0	0	1	1	1	1	1
16.25°	0	0	0	0	0	0	1	1	1	1	1
15°	0	0	0	0	0	0	1	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	1	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	1	1	1	1	1
-16.25°	0	0	0	0	0	0	1	1	1	1	1
-17.5°	0	0	0	0	0	0	1	1	1	1	1
-18.75°	0	0	0	0	0	0	1	1	1	1	1
-20°	0	0	0	0	0	0	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	1	1	1	1	1
-26.25°	0	0	0	0	0	0	1	1	1	1	1
-27.5°	0	0	0	0	0	0	1	1	1	1	1
-28.75°	0	0	0	0	0	0	1	1	1	1	1
-30°	0	0	0	0	0	0	1	1	1	1	1
-31.25°	0	0	0	0	0	0	1	1	1	1	1
-32.5°	0	0	0	0	0	0	1	1	1	1	1
-33.75°	0	0	0	0	0	0	0	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-36.25°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-38.75°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-43.75°	0	0	0	0	0	0	0	1	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-48.75°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	1	1	1
-51.25°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	1
-58.75°	0	0	0	0	0	0	0	0	0	0	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	1
73.75°	0	0	0	0	0	0	0	0	1	1	1
72.5°	0	0	0	0	0	0	1	1	1	1	1
71.25°	0	0	0	0	0	1	1	1	1	1	1
70°	0	0	0	0	1	1	1	1	1	1	1
68.75°	0	0	0	1	1	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	0	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	2
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	2	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	1	2	2
36.25°	1	1	1	1	1	1	1	1	2	2	2
35°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	2	2	2	2
31.25°	1	1	1	1	1	1	1	2	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	2
27.5°	1	1	1	1	1	1	2	2	2	2	2
26.25°	1	1	1	1	1	1	2	2	2	2	2
25°	1	1	1	1	1	1	2	2	2	2	2
23.75°	1	1	1	1	1	1	2	2	2	2	2
22.5°	1	1	1	1	1	1	2	2	2	2	2
21.25°	1	1	1	1	1	1	2	2	2	2	2
20°	1	1	1	1	1	1	2	2	2	2	2
18.75°	1	1	1	1	1	2	2	2	2	2	2
17.5°	1	1	1	1	1	2	2	2	2	2	2
16.25°	1	1	1	1	1	2	2	2	2	2	2
15°	1	1	1	1	1	2	2	2	2	2	2
13.75°	1	1	1	1	1	2	2	2	2	2	2
12.5°	1	1	1	1	1	2	2	2	2	2	2
11.25°	1	1	1	1	1	2	2	2	2	2	2
10°	1	1	1	1	1	2	2	2	2	2	2
8.75°	1	1	1	1	1	2	2	2	2	2	2
7.5°	1	1	1	1	1	2	2	2	2	2	2
6.25°	1	1	1	1	1	2	2	2	2	2	2
5°	1	1	1	1	1	2	2	2	2	2	2
3.75°	1	1	1	1	1	2	2	2	2	2	2
2.5°	1	1	1	1	1	2	2	2	2	2	2
1.25°	1	1	1	1	1	2	2	2	2	2	2
0°	1	1	1	1	2	2	2	2	2	2	3
-1.25°	1	1	1	1	1	2	2	2	2	2	2
-2.5°	1	1	1	1	1	2	2	2	2	2	2
-3.75°	1	1	1	1	1	2	2	2	2	2	2
-5°	1	1	1	1	1	2	2	2	2	2	2
-6.25°	1	1	1	1	1	2	2	2	2	2	2
-7.5°	1	1	1	1	1	2	2	2	2	2	2
-8.75°	1	1	1	1	1	2	2	2	2	2	2
-10°	1	1	1	1	1	2	2	2	2	2	2
-11.25°	1	1	1	1	1	2	2	2	2	2	2
-12.5°	1	1	1	1	1	2	2	2	2	2	2
-13.75°	1	1	1	1	1	2	2	2	2	2	2
-15°	1	1	1	1	1	2	2	2	2	2	2
-16.25°	1	1	1	1	1	2	2	2	2	2	2
-17.5°	1	1	1	1	1	2	2	2	2	2	2
-18.75°	1	1	1	1	1	2	2	2	2	2	2
-20°	1	1	1	1	1	1	2	2	2	2	2
-21.25°	1	1	1	1	1	1	2	2	2	2	2



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	2	2	2	2	2
-23.75°	1	1	1	1	1	1	2	2	2	2	2
-25°	1	1	1	1	1	1	2	2	2	2	2
-26.25°	1	1	1	1	1	1	2	2	2	2	2
-27.5°	1	1	1	1	1	1	2	2	2	2	2
-28.75°	1	1	1	1	1	1	1	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	2	2	2	2
-32.5°	1	1	1	1	1	1	1	2	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	2	2	2
-36.25°	1	1	1	1	1	1	1	1	2	2	2
-37.5°	1	1	1	1	1	1	1	1	1	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	2	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	2
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	0	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	1	1	1	1	1	1	1	1
-70°	0	0	0	0	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	1	1	1	1	1	1
-72.5°	0	0	0	0	0	0	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	2	2	2
55°	1	1	1	1	1	1	1	2	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	2	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	2
47.5°	1	2	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	3
45°	2	2	2	2	2	2	2	2	2	3	3
43.75°	2	2	2	2	2	2	2	2	2	3	3
42.5°	2	2	2	2	2	2	2	2	3	3	3
41.25°	2	2	2	2	2	2	2	3	3	3	3
40°	2	2	2	2	2	2	2	3	3	3	4
38.75°	2	2	2	2	2	2	3	3	3	4	4
37.5°	2	2	2	2	2	2	3	3	3	4	4
36.25°	2	2	2	2	2	3	3	3	4	4	4
35°	2	2	2	2	2	3	3	4	4	4	4



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	3	3	3	4	4	4	4
32.5°	2	2	2	2	3	3	4	4	4	4	4
31.25°	2	2	2	3	3	3	4	4	4	4	4
30°	2	2	2	3	3	4	4	4	4	4	5
28.75°	2	2	2	3	3	4	4	4	4	4	5
27.5°	2	2	3	3	3	4	4	4	4	4	5
26.25°	2	2	3	3	4	4	4	4	4	5	5
25°	2	2	3	3	4	4	4	4	4	5	5
23.75°	2	2	3	3	4	4	4	4	5	5	5
22.5°	2	3	3	3	4	4	4	4	5	5	5
21.25°	2	3	3	4	4	4	4	4	5	5	5
20°	2	3	3	4	4	4	4	5	5	5	5
18.75°	2	3	3	4	4	4	4	5	5	5	5
17.5°	2	3	3	4	4	4	4	5	5	5	5
16.25°	3	3	3	4	4	4	4	5	5	5	6
15°	3	3	4	4	4	4	4	5	5	5	6
13.75°	3	3	4	4	4	4	5	5	5	6	6
12.5°	3	3	4	4	4	4	5	5	5	6	6
11.25°	3	3	4	4	4	4	5	5	5	6	6
10°	3	3	4	4	4	4	5	5	5	6	6
8.75°	3	3	4	4	4	4	5	5	6	6	6
7.5°	3	3	4	4	4	4	5	5	6	6	7
6.25°	3	3	4	4	4	4	5	5	6	6	7
5°	3	3	4	4	4	4	5	5	6	6	7
3.75°	3	3	4	4	4	4	5	5	6	6	7
2.5°	3	3	4	4	4	4	5	5	6	6	7
1.25°	3	3	4	4	4	4	5	5	6	6	7
0°	3	4	4	4	4	5	5	5	6	6	7
-1.25°	3	3	4	4	4	4	5	5	6	6	7
-2.5°	3	3	4	4	4	4	5	5	6	6	7
-3.75°	3	3	4	4	4	4	5	5	6	6	7
-5°	3	3	4	4	4	4	5	5	6	6	7
-6.25°	3	3	4	4	4	4	5	5	6	6	7
-7.5°	3	3	4	4	4	4	5	5	6	6	7
-8.75°	3	3	4	4	4	4	5	5	6	6	6
-10°	3	3	4	4	4	4	5	5	5	6	6
-11.25°	3	3	4	4	4	4	5	5	5	6	6
-12.5°	3	3	4	4	4	4	5	5	5	6	6
-13.75°	3	3	4	4	4	4	5	5	5	6	6
-15°	3	3	4	4	4	4	4	5	5	5	6
-16.25°	3	3	3	4	4	4	4	5	5	5	6
-17.5°	2	3	3	4	4	4	4	5	5	5	5
-18.75°	2	3	3	4	4	4	4	5	5	5	5
-20°	2	3	3	4	4	4	4	5	5	5	5
-21.25°	2	3	3	4	4	4	4	4	5	5	5



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	3	3	3	4	4	4	4	5	5	5
-23.75°	2	2	3	3	4	4	4	4	5	5	5
-25°	2	2	3	3	4	4	4	4	4	5	5
-26.25°	2	2	3	3	4	4	4	4	4	5	5
-27.5°	2	2	3	3	3	4	4	4	4	4	5
-28.75°	2	2	2	3	3	4	4	4	4	4	5
-30°	2	2	2	3	3	4	4	4	4	4	5
-31.25°	2	2	2	3	3	3	4	4	4	4	4
-32.5°	2	2	2	2	3	3	4	4	4	4	4
-33.75°	2	2	2	2	3	3	3	4	4	4	4
-35°	2	2	2	2	2	3	3	4	4	4	4
-36.25°	2	2	2	2	2	3	3	3	4	4	4
-37.5°	2	2	2	2	2	2	3	3	3	4	4
-38.75°	2	2	2	2	2	2	3	3	3	4	4
-40°	2	2	2	2	2	2	2	3	3	3	4
-41.25°	2	2	2	2	2	2	2	3	3	3	3
-42.5°	2	2	2	2	2	2	2	2	3	3	3
-43.75°	2	2	2	2	2	2	2	2	2	3	3
-45°	2	2	2	2	2	2	2	2	2	3	3
-46.25°	1	2	2	2	2	2	2	2	2	2	3
-47.5°	1	2	2	2	2	2	2	2	2	2	2
-48.75°	1	1	2	2	2	2	2	2	2	2	2
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	2	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	2	2	2	2
-56.25°	1	1	1	1	1	1	1	1	2	2	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	2	2
61.25°	1	1	1	1	1	1	1	2	2	2	2
60°	1	1	1	1	2	2	2	2	2	2	2
58.75°	1	1	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	3
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	2	3	3	3	3	3	3	3	3	3
48.75°	2	3	3	3	3	3	3	3	3	4	4
47.5°	3	3	3	3	3	3	3	4	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	4
45°	3	3	3	3	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	3	4	4	4	4	4	4	4	4	4	5
41.25°	4	4	4	4	4	4	4	4	5	5	5
40°	4	4	4	4	4	4	4	5	5	5	5
38.75°	4	4	4	4	4	4	5	5	5	5	6
37.5°	4	4	4	4	5	5	5	5	5	6	6
36.25°	4	4	4	5	5	5	5	5	6	6	6
35°	4	4	5	5	5	5	5	6	6	6	7



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	5	5	5	5	5	5	6	6	7	7
32.5°	4	5	5	5	5	5	6	6	7	7	8
31.25°	5	5	5	5	5	6	6	7	7	8	8
30°	5	5	5	5	5	6	6	7	8	8	9
28.75°	5	5	5	5	6	6	7	7	8	9	10
27.5°	5	5	5	6	6	7	7	8	9	10	12
26.25°	5	5	5	6	6	7	8	9	10	11	13
25°	5	5	6	6	7	7	9	10	11	13	15
23.75°	5	5	6	6	7	8	9	11	12	14	16
22.5°	5	6	6	7	8	9	10	12	14	16	19
21.25°	5	6	6	7	8	10	11	13	15	18	22
20°	6	6	7	7	9	10	12	15	17	21	26
18.75°	6	6	7	8	9	11	13	16	19	24	29
17.5°	6	6	7	8	10	12	15	17	21	27	35
16.25°	6	7	8	9	11	13	16	19	24	30	41
15°	6	7	8	9	12	14	17	21	27	34	48
13.75°	6	7	8	10	12	15	18	23	30	39	54
12.5°	7	8	8	11	13	16	19	26	33	45	59
11.25°	7	8	9	11	14	17	20	28	36	50	65
10°	7	8	9	12	15	18	22	31	40	55	71
8.75°	7	8	10	12	15	19	24	33	44	59	78
7.5°	7	8	10	13	16	20	26	35	48	63	84
6.25°	8	8	11	13	17	20	28	37	51	67	90
5°	8	9	11	14	17	21	30	39	54	70	96
3.75°	8	9	11	14	18	22	31	41	57	73	101
2.5°	8	9	12	15	18	22	32	43	59	76	105
1.25°	8	9	12	15	19	23	33	44	61	78	108
0°	8	9	12	15	19	23	34	45	62	79	110
-1.25°	8	9	12	15	19	23	33	44	61	78	108
-2.5°	8	9	12	15	18	22	32	43	59	76	105
-3.75°	8	9	11	14	18	22	31	41	57	73	101
-5°	8	9	11	14	17	21	30	39	54	70	96
-6.25°	8	8	11	13	17	20	28	37	51	67	90
-7.5°	7	8	10	13	16	20	26	35	48	63	84
-8.75°	7	8	10	12	15	19	24	33	44	59	78
-10°	7	8	9	12	15	18	22	31	40	55	71
-11.25°	7	8	9	11	14	17	20	28	36	50	65
-12.5°	7	8	8	11	13	16	19	26	33	45	59
-13.75°	6	7	8	10	12	15	18	23	30	39	54
-15°	6	7	8	9	12	14	17	21	27	34	48
-16.25°	6	7	8	9	11	13	16	19	24	30	41
-17.5°	6	6	7	8	10	12	15	17	21	27	35
-18.75°	6	6	7	8	9	11	13	16	19	24	29
-20°	6	6	7	7	9	10	12	15	17	21	26
-21.25°	5	6	6	7	8	10	11	13	15	18	22



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	6	6	7	8	9	10	12	14	16	19
-23.75°	5	5	6	6	7	8	9	11	12	14	16
-25°	5	5	6	6	7	7	9	10	11	13	15
-26.25°	5	5	5	6	6	7	8	9	10	11	13
-27.5°	5	5	5	6	6	7	7	8	9	10	12
-28.75°	5	5	5	5	6	6	7	7	8	9	10
-30°	5	5	5	5	5	6	6	7	8	8	9
-31.25°	5	5	5	5	5	6	6	7	7	8	8
-32.5°	4	5	5	5	5	5	6	6	7	7	8
-33.75°	4	5	5	5	5	5	5	6	6	7	7
-35°	4	4	5	5	5	5	5	6	6	6	7
-36.25°	4	4	4	5	5	5	5	5	6	6	6
-37.5°	4	4	4	4	5	5	5	5	5	6	6
-38.75°	4	4	4	4	4	4	5	5	5	5	6
-40°	4	4	4	4	4	4	4	5	5	5	5
-41.25°	4	4	4	4	4	4	4	4	5	5	5
-42.5°	3	4	4	4	4	4	4	4	4	4	5
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	3	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	3	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	4	4	4	4
-48.75°	2	3	3	3	3	3	3	3	3	4	4
-50°	2	2	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	3
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	2	2	2
65°	1	1	1	1	2	2	2	2	2	2	2
63.75°	1	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	3
57.5°	2	2	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	4	4	4	4	4
51.25°	3	3	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	5
48.75°	4	4	4	4	4	4	4	5	5	5	5
47.5°	4	4	4	4	4	5	5	5	5	5	5
46.25°	4	4	4	4	5	5	5	5	5	5	5
45°	4	4	5	5	5	5	5	5	5	6	6
43.75°	5	5	5	5	5	6	6	6	6	6	6
42.5°	5	5	5	6	6	6	6	6	6	6	7
41.25°	5	5	6	6	6	6	6	7	7	7	7
40°	6	6	6	6	6	7	7	7	7	7	7
38.75°	6	6	6	7	7	7	7	7	8	8	8
37.5°	6	7	7	7	7	7	8	8	9	9	9
36.25°	7	7	7	8	8	8	9	9	10	10	10
35°	7	7	8	8	8	9	10	10	11	11	12



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	8	8	8	9	10	10	11	12	12	13	14
32.5°	8	9	9	10	11	11	12	13	14	15	16
31.25°	9	10	11	12	13	13	14	15	17	18	19
30°	10	11	12	13	15	16	17	18	20	21	24
28.75°	11	13	14	16	17	19	21	22	23	27	30
27.5°	13	14	17	19	21	24	26	28	30	33	36
26.25°	15	17	20	22	26	30	33	37	39	41	48
25°	17	20	23	28	33	37	43	47	51	55	60
23.75°	20	23	28	35	40	48	54	60	67	72	76
22.5°	23	28	36	42	51	60	67	76	84	90	98
21.25°	27	35	43	52	63	72	84	94	103	112	120
20°	32	42	51	64	76	89	102	113	125	135	144
18.75°	39	50	63	77	90	107	121	134	147	158	169
17.5°	47	59	75	91	108	125	141	156	170	182	194
16.25°	54	70	88	106	126	145	162	178	193	206	220
15°	61	81	101	123	145	165	184	201	215	231	246
13.75°	69	91	112	138	164	185	205	222	239	257	272
12.5°	78	101	125	151	177	202	226	244	263	281	298
11.25°	87	110	137	164	191	217	241	263	287	304	324
10°	95	120	148	176	203	230	254	279	303	325	349
8.75°	103	129	158	187	215	243	268	293	316	340	366
7.5°	111	138	168	197	227	255	280	306	329	354	380
6.25°	118	146	176	207	237	266	292	317	341	367	394
5°	124	154	184	215	247	276	302	328	352	378	405
3.75°	129	160	191	223	256	285	312	337	362	388	415
2.5°	134	165	197	230	263	293	320	345	370	396	424
1.25°	138	170	201	236	270	300	327	352	377	404	430
0°	141	173	205	240	275	306	332	358	383	409	435
-1.25°	138	170	201	236	270	300	327	352	377	404	430
-2.5°	134	165	197	230	263	293	320	345	370	396	424
-3.75°	129	160	191	223	256	285	312	337	362	388	415
-5°	124	154	184	215	247	276	302	328	352	378	405
-6.25°	118	146	176	207	237	266	292	317	341	367	394
-7.5°	111	138	168	197	227	255	280	306	329	354	380
-8.75°	103	129	158	187	215	243	268	293	316	340	366
-10°	95	120	148	176	203	230	254	279	303	325	349
-11.25°	87	110	137	164	191	217	241	263	287	304	324
-12.5°	78	101	125	151	177	202	226	244	263	281	298
-13.75°	69	91	112	138	164	185	205	222	239	257	272
-15°	61	81	101	123	145	165	184	201	215	231	246
-16.25°	54	70	88	106	126	145	162	178	193	206	220
-17.5°	47	59	75	91	108	125	141	156	170	182	194
-18.75°	39	50	63	77	90	107	121	134	147	158	169
-20°	32	42	51	64	76	89	102	113	125	135	144
-21.25°	27	35	43	52	63	72	84	94	103	112	120



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	23	28	36	42	51	60	67	76	84	90	98
-23.75°	20	23	28	35	40	48	54	60	67	72	76
-25°	17	20	23	28	33	37	43	47	51	55	60
-26.25°	15	17	20	22	26	30	33	37	39	41	48
-27.5°	13	14	17	19	21	24	26	28	30	33	36
-28.75°	11	13	14	16	17	19	21	22	23	27	30
-30°	10	11	12	13	15	16	17	18	20	21	24
-31.25°	9	10	11	12	13	13	14	15	17	18	19
-32.5°	8	9	9	10	11	11	12	13	14	15	16
-33.75°	8	8	8	9	10	10	11	12	12	13	14
-35°	7	7	8	8	8	9	10	10	11	11	12
-36.25°	7	7	7	8	8	8	9	9	10	10	10
-37.5°	6	7	7	7	7	7	8	8	9	9	9
-38.75°	6	6	6	7	7	7	7	7	8	8	8
-40°	6	6	6	6	6	7	7	7	7	7	7
-41.25°	5	5	6	6	6	6	6	7	7	7	7
-42.5°	5	5	5	6	6	6	6	6	6	6	7
-43.75°	5	5	5	5	5	6	6	6	6	6	6
-45°	4	4	5	5	5	5	5	5	5	6	6
-46.25°	4	4	4	4	5	5	5	5	5	5	5
-47.5°	4	4	4	4	4	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	5	5	5	5
-50°	4	4	4	4	4	4	4	4	4	4	5
-51.25°	3	3	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	4	4	4	4	4
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	3
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	2	2	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	4	4	4	4	4
53.75°	3	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	5	5	5	5	5	5	5	5	5
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	6	6	6	7	7	7	7	7	7	7	7
42.5°	7	7	7	7	7	7	7	7	7	7	8
41.25°	7	7	7	8	8	8	8	8	8	8	8
40°	8	8	8	8	8	8	8	9	9	9	9
38.75°	9	9	9	9	9	9	9	10	10	10	10
37.5°	10	10	10	10	10	10	10	11	11	11	11
36.25°	11	11	11	12	12	12	12	12	12	13	13
35°	12	13	13	14	14	14	14	14	14	15	15



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	15	15	16	16	17	17	16	16	16	17	17
32.5°	17	18	19	20	20	20	19	18	19	20	20
31.25°	21	23	24	24	25	25	24	22	22	23	23
30°	26	28	29	31	32	31	30	28	27	28	29
28.75°	32	35	38	40	40	40	39	37	33	34	35
27.5°	42	45	48	50	52	52	50	46	43	42	44
26.25°	53	57	62	65	66	65	64	61	56	53	55
25°	66	73	78	81	83	83	82	78	74	67	70
23.75°	83	91	96	101	103	103	102	100	95	89	88
22.5°	104	111	118	123	126	127	127	124	120	113	107
21.25°	127	134	141	148	152	154	153	151	146	141	133
20°	153	160	168	175	180	182	181	180	176	171	165
18.75°	178	188	196	204	208	211	212	211	209	205	200
17.5°	206	216	225	233	238	242	245	246	245	242	238
16.25°	233	244	254	263	270	275	279	281	282	280	277
15°	259	273	284	294	303	310	315	318	318	317	314
13.75°	287	301	314	327	337	344	349	352	352	351	348
12.5°	314	330	346	360	370	376	381	383	384	383	379
11.25°	342	360	378	391	400	406	409	413	415	412	406
10°	369	391	409	421	429	433	437	441	441	437	431
8.75°	393	421	438	448	454	459	464	465	464	459	455
7.5°	408	437	459	473	479	484	488	488	486	482	479
6.25°	422	450	470	485	496	506	510	510	507	503	498
5°	434	460	481	495	507	517	524	528	528	521	514
3.75°	443	470	492	505	517	526	533	537	538	533	528
2.5°	451	479	501	514	526	535	541	544	544	539	535
1.25°	458	487	509	522	534	544	548	552	551	546	541
0°	462	493	516	529	541	551	555	558	559	553	547
-1.25°	458	487	509	522	534	544	548	552	551	546	541
-2.5°	451	479	501	514	526	535	541	544	544	539	535
-3.75°	443	470	492	505	517	526	533	537	538	533	528
-5°	434	460	481	495	507	517	524	528	528	521	514
-6.25°	422	450	470	485	496	506	510	510	507	503	498
-7.5°	408	437	459	473	479	484	488	488	486	482	479
-8.75°	393	421	438	448	454	459	464	465	464	459	455
-10°	369	391	409	421	429	433	437	441	441	437	431
-11.25°	342	360	378	391	400	406	409	413	415	412	406
-12.5°	314	330	346	360	370	376	381	383	384	383	379
-13.75°	287	301	314	327	337	344	349	352	352	351	348
-15°	259	273	284	294	303	310	315	318	318	317	314
-16.25°	233	244	254	263	270	275	279	281	282	280	277
-17.5°	206	216	225	233	238	242	245	246	245	242	238
-18.75°	178	188	196	204	208	211	212	211	209	205	200
-20°	153	160	168	175	180	182	181	180	176	171	165
-21.25°	127	134	141	148	152	154	153	151	146	141	133



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	104	111	118	123	126	127	127	124	120	113	107
-23.75°	83	91	96	101	103	103	102	100	95	89	88
-25°	66	73	78	81	83	83	82	78	74	67	70
-26.25°	53	57	62	65	66	65	64	61	56	53	55
-27.5°	42	45	48	50	52	52	50	46	43	42	44
-28.75°	32	35	38	40	40	40	39	37	33	34	35
-30°	26	28	29	31	32	31	30	28	27	28	29
-31.25°	21	23	24	24	25	25	24	22	22	23	23
-32.5°	17	18	19	20	20	20	19	18	19	20	20
-33.75°	15	15	16	16	17	17	16	16	16	17	17
-35°	12	13	13	14	14	14	14	14	14	15	15
-36.25°	11	11	11	12	12	12	12	12	12	13	13
-37.5°	10	10	10	10	10	10	10	11	11	11	11
-38.75°	9	9	9	9	9	9	9	10	10	10	10
-40°	8	8	8	8	8	8	8	9	9	9	9
-41.25°	7	7	7	8	8	8	8	8	8	8	8
-42.5°	7	7	7	7	7	7	7	7	7	7	8
-43.75°	6	6	6	7	7	7	7	7	7	7	7
-45°	6	6	6	6	6	6	6	6	6	6	6
-46.25°	5	5	5	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	5	5	5	5	5	5	5	5	5
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	4	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	4	4	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	1	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	2	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	3	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	4	3	3	3	3
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	5	5	5	5	5	5	5	5	5	5	5
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	7
42.5°	8	8	8	8	8	8	8	8	8	8	8
41.25°	8	8	9	9	9	9	9	9	9	9	9
40°	9	9	9	9	9	9	9	9	9	9	9
38.75°	10	10	10	10	10	10	10	10	10	10	10
37.5°	11	11	11	11	11	11	11	11	11	11	11
36.25°	13	13	13	13	13	13	13	13	13	13	13
35°	15	15	15	15	15	15	15	15	15	15	15



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	17	18	18	18	18	17	17	17	18	18	18
32.5°	20	20	20	20	20	19	19	19	20	20	20
31.25°	24	24	25	24	24	24	23	24	24	24	25
30°	29	30	30	29	29	28	27	28	29	29	30
28.75°	36	36	36	36	35	34	33	34	35	36	36
27.5°	45	45	45	45	44	43	41	43	44	45	45
26.25°	57	58	58	58	57	56	53	56	57	58	58
25°	73	74	75	74	73	71	68	71	73	74	75
23.75°	91	92	93	92	91	88	85	88	91	92	93
22.5°	111	113	114	114	112	109	105	109	112	114	114
21.25°	135	138	139	139	137	134	129	134	137	139	139
20°	163	166	168	168	166	161	155	161	166	168	168
18.75°	194	198	200	200	198	193	186	193	198	200	200
17.5°	232	233	235	233	230	224	215	224	230	233	235
16.25°	272	268	269	267	263	257	248	257	263	267	269
15°	309	302	301	299	295	288	279	288	295	299	301
13.75°	343	335	330	327	321	314	304	314	321	327	330
12.5°	373	365	356	354	350	343	334	343	350	354	356
11.25°	400	393	384	380	376	369	360	369	376	380	384
10°	426	420	412	405	401	394	385	394	401	405	412
8.75°	451	446	439	428	423	418	410	418	423	428	439
7.5°	476	470	461	450	443	438	430	438	443	450	461
6.25°	494	489	480	470	459	453	446	453	459	470	480
5°	509	505	497	485	473	466	460	466	473	485	497
3.75°	525	518	507	495	483	474	469	474	483	495	507
2.5°	535	529	515	502	489	479	475	479	489	502	515
1.25°	539	531	519	507	493	484	479	484	493	507	519
0°	544	536	523	509	494	486	484	486	494	509	523
-1.25°	539	531	519	507	493	484	479	484	493	507	519
-2.5°	535	529	515	502	489	479	475	479	489	502	515
-3.75°	525	518	507	495	483	474	469	474	483	495	507
-5°	509	505	497	485	473	466	460	466	473	485	497
-6.25°	494	489	480	470	459	453	446	453	459	470	480
-7.5°	476	470	461	450	443	438	430	438	443	450	461
-8.75°	451	446	439	428	423	418	410	418	423	428	439
-10°	426	420	412	405	401	394	385	394	401	405	412
-11.25°	400	393	384	380	376	369	360	369	376	380	384
-12.5°	373	365	356	354	350	343	334	343	350	354	356
-13.75°	343	335	330	327	321	314	304	314	321	327	330
-15°	309	302	301	299	295	288	279	288	295	299	301
-16.25°	272	268	269	267	263	257	248	257	263	267	269
-17.5°	232	233	235	233	230	224	215	224	230	233	235
-18.75°	194	198	200	200	198	193	186	193	198	200	200
-20°	163	166	168	168	166	161	155	161	166	168	168
-21.25°	135	138	139	139	137	134	129	134	137	139	139



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	111	113	114	114	112	109	105	109	112	114	114
-23.75°	91	92	93	92	91	88	85	88	91	92	93
-25°	73	74	75	74	73	71	68	71	73	74	75
-26.25°	57	58	58	58	57	56	53	56	57	58	58
-27.5°	45	45	45	45	44	43	41	43	44	45	45
-28.75°	36	36	36	36	35	34	33	34	35	36	36
-30°	29	30	30	29	29	28	27	28	29	29	30
-31.25°	24	24	25	24	24	24	23	24	24	24	25
-32.5°	20	20	20	20	20	19	19	19	20	20	20
-33.75°	17	18	18	18	18	17	17	17	18	18	18
-35°	15	15	15	15	15	15	15	15	15	15	15
-36.25°	13	13	13	13	13	13	13	13	13	13	13
-37.5°	11	11	11	11	11	11	11	11	11	11	11
-38.75°	10	10	10	10	10	10	10	10	10	10	10
-40°	9	9	9	9	9	9	9	9	9	9	9
-41.25°	8	8	9	9	9	9	9	9	9	9	9
-42.5°	8	8	8	8	8	8	8	8	8	8	8
-43.75°	7	7	7	7	7	7	7	7	7	7	7
-45°	6	6	6	6	6	6	6	6	6	6	6
-46.25°	6	6	6	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	5	5	5	5	5	5	5	5	5	5	5
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	3	3	4	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	3	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	2	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	1	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	4	4	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	5	5	5	5	5	5	5	5	5	5	5
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	5
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	6
42.5°	8	8	8	7	7	7	7	7	7	7	7
41.25°	8	8	8	8	8	8	8	8	8	8	7
40°	9	9	9	9	9	9	8	8	8	8	8
38.75°	10	10	10	10	10	10	9	9	9	9	9
37.5°	11	11	11	11	11	11	10	10	10	10	10
36.25°	13	13	13	13	12	12	12	12	12	12	11
35°	15	15	15	15	14	14	14	14	14	14	13



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	18	17	17	17	16	16	16	17	17	16	16
32.5°	20	20	20	20	19	18	19	20	20	20	19
31.25°	24	24	23	23	22	22	24	25	25	24	24
30°	30	29	29	28	27	28	30	31	32	31	29
28.75°	36	36	35	34	33	37	39	40	40	40	38
27.5°	45	45	44	42	43	46	50	52	52	50	48
26.25°	58	57	55	53	56	61	64	65	66	65	62
25°	74	73	70	67	74	78	82	83	83	81	78
23.75°	92	91	88	89	95	100	102	103	103	101	96
22.5°	113	111	107	113	120	124	127	127	126	123	118
21.25°	138	135	133	141	146	151	153	154	152	148	141
20°	166	163	165	171	176	180	181	182	180	175	168
18.75°	198	194	200	205	209	211	212	211	208	204	196
17.5°	233	232	238	242	245	246	245	242	238	233	225
16.25°	268	272	277	280	282	281	279	275	270	263	254
15°	302	309	314	317	318	318	315	310	303	294	284
13.75°	335	343	348	351	352	352	349	344	337	327	314
12.5°	365	373	379	383	384	383	381	376	370	360	346
11.25°	393	400	406	412	415	413	409	406	400	391	378
10°	420	426	431	437	441	441	437	433	429	421	409
8.75°	446	451	455	459	464	465	464	459	454	448	438
7.5°	470	476	479	482	486	488	488	484	479	473	459
6.25°	489	494	498	503	507	510	510	506	496	485	470
5°	505	509	514	521	528	528	524	517	507	495	481
3.75°	518	525	528	533	538	537	533	526	517	505	492
2.5°	529	535	535	539	544	544	541	535	526	514	501
1.25°	531	539	541	546	551	552	548	544	534	522	509
0°	536	544	547	553	559	558	555	551	541	529	516
-1.25°	531	539	541	546	551	552	548	544	534	522	509
-2.5°	529	535	535	539	544	544	541	535	526	514	501
-3.75°	518	525	528	533	538	537	533	526	517	505	492
-5°	505	509	514	521	528	528	524	517	507	495	481
-6.25°	489	494	498	503	507	510	510	506	496	485	470
-7.5°	470	476	479	482	486	488	488	484	479	473	459
-8.75°	446	451	455	459	464	465	464	459	454	448	438
-10°	420	426	431	437	441	441	437	433	429	421	409
-11.25°	393	400	406	412	415	413	409	406	400	391	378
-12.5°	365	373	379	383	384	383	381	376	370	360	346
-13.75°	335	343	348	351	352	352	349	344	337	327	314
-15°	302	309	314	317	318	318	315	310	303	294	284
-16.25°	268	272	277	280	282	281	279	275	270	263	254
-17.5°	233	232	238	242	245	246	245	242	238	233	225
-18.75°	198	194	200	205	209	211	212	211	208	204	196
-20°	166	163	165	171	176	180	181	182	180	175	168
-21.25°	138	135	133	141	146	151	153	154	152	148	141



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	113	111	107	113	120	124	127	127	126	123	118
-23.75°	92	91	88	89	95	100	102	103	103	101	96
-25°	74	73	70	67	74	78	82	83	83	81	78
-26.25°	58	57	55	53	56	61	64	65	66	65	62
-27.5°	45	45	44	42	43	46	50	52	52	50	48
-28.75°	36	36	35	34	33	37	39	40	40	40	38
-30°	30	29	29	28	27	28	30	31	32	31	29
-31.25°	24	24	23	23	22	22	24	25	25	24	24
-32.5°	20	20	20	20	19	18	19	20	20	20	19
-33.75°	18	17	17	17	16	16	16	17	17	16	16
-35°	15	15	15	15	14	14	14	14	14	14	13
-36.25°	13	13	13	13	12	12	12	12	12	12	11
-37.5°	11	11	11	11	11	11	10	10	10	10	10
-38.75°	10	10	10	10	10	10	9	9	9	9	9
-40°	9	9	9	9	9	9	8	8	8	8	8
-41.25°	8	8	8	8	8	8	8	8	8	8	7
-42.5°	8	8	8	7	7	7	7	7	7	7	7
-43.75°	7	7	7	7	7	7	7	7	7	7	6
-45°	6	6	6	6	6	6	6	6	6	6	6
-46.25°	6	6	6	6	6	6	6	6	6	6	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	5	5	5	5	5	5	5	5	5	5	5
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	2	2	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	3	3	3	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	4	3	3	3	3	3	3	3	3	3	3
52.5°	4	4	4	4	4	4	4	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	5	5	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	4	4	4
46.25°	5	5	5	5	5	5	5	5	5	4	4
45°	6	6	6	6	5	5	5	5	5	5	5
43.75°	6	6	6	6	6	6	6	6	5	5	5
42.5°	7	7	7	6	6	6	6	6	6	6	5
41.25°	7	7	7	7	7	7	6	6	6	6	6
40°	8	8	7	7	7	7	7	7	6	6	6
38.75°	9	9	8	8	8	7	7	7	7	7	6
37.5°	10	10	9	9	9	8	8	7	7	7	7
36.25°	11	11	10	10	10	9	9	8	8	8	7
35°	13	12	12	11	11	10	10	9	8	8	8



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	15	15	14	13	12	12	11	10	10	9	8
32.5°	18	17	16	15	14	13	12	11	11	10	9
31.25°	23	21	19	18	17	15	14	13	13	12	11
30°	28	26	24	21	20	18	17	16	15	13	12
28.75°	35	32	30	27	23	22	21	19	17	16	14
27.5°	45	42	36	33	30	28	26	24	21	19	17
26.25°	57	53	48	41	39	37	33	30	26	22	20
25°	73	66	60	55	51	47	43	37	33	28	23
23.75°	91	83	76	72	67	60	54	48	40	35	28
22.5°	111	104	98	90	84	76	67	60	51	42	36
21.25°	134	127	120	112	103	94	84	72	63	52	43
20°	160	153	144	135	125	113	102	89	76	64	51
18.75°	188	178	169	158	147	134	121	107	90	77	63
17.5°	216	206	194	182	170	156	141	125	108	91	75
16.25°	244	233	220	206	193	178	162	145	126	106	88
15°	273	259	246	231	215	201	184	165	145	123	101
13.75°	301	287	272	257	239	222	205	185	164	138	112
12.5°	330	314	298	281	263	244	226	202	177	151	125
11.25°	360	342	324	304	287	263	241	217	191	164	137
10°	391	369	349	325	303	279	254	230	203	176	148
8.75°	421	393	366	340	316	293	268	243	215	187	158
7.5°	437	408	380	354	329	306	280	255	227	197	168
6.25°	450	422	394	367	341	317	292	266	237	207	176
5°	460	434	405	378	352	328	302	276	247	215	184
3.75°	470	443	415	388	362	337	312	285	256	223	191
2.5°	479	451	424	396	370	345	320	293	263	230	197
1.25°	487	458	430	404	377	352	327	300	270	236	201
0°	493	462	435	409	383	358	332	306	275	240	205
-1.25°	487	458	430	404	377	352	327	300	270	236	201
-2.5°	479	451	424	396	370	345	320	293	263	230	197
-3.75°	470	443	415	388	362	337	312	285	256	223	191
-5°	460	434	405	378	352	328	302	276	247	215	184
-6.25°	450	422	394	367	341	317	292	266	237	207	176
-7.5°	437	408	380	354	329	306	280	255	227	197	168
-8.75°	421	393	366	340	316	293	268	243	215	187	158
-10°	391	369	349	325	303	279	254	230	203	176	148
-11.25°	360	342	324	304	287	263	241	217	191	164	137
-12.5°	330	314	298	281	263	244	226	202	177	151	125
-13.75°	301	287	272	257	239	222	205	185	164	138	112
-15°	273	259	246	231	215	201	184	165	145	123	101
-16.25°	244	233	220	206	193	178	162	145	126	106	88
-17.5°	216	206	194	182	170	156	141	125	108	91	75
-18.75°	188	178	169	158	147	134	121	107	90	77	63
-20°	160	153	144	135	125	113	102	89	76	64	51
-21.25°	134	127	120	112	103	94	84	72	63	52	43



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	111	104	98	90	84	76	67	60	51	42	36
-23.75°	91	83	76	72	67	60	54	48	40	35	28
-25°	73	66	60	55	51	47	43	37	33	28	23
-26.25°	57	53	48	41	39	37	33	30	26	22	20
-27.5°	45	42	36	33	30	28	26	24	21	19	17
-28.75°	35	32	30	27	23	22	21	19	17	16	14
-30°	28	26	24	21	20	18	17	16	15	13	12
-31.25°	23	21	19	18	17	15	14	13	13	12	11
-32.5°	18	17	16	15	14	13	12	11	11	10	9
-33.75°	15	15	14	13	12	12	11	10	10	9	8
-35°	13	12	12	11	11	10	10	9	8	8	8
-36.25°	11	11	10	10	10	9	9	8	8	8	7
-37.5°	10	10	9	9	9	8	8	7	7	7	7
-38.75°	9	9	8	8	8	7	7	7	7	7	6
-40°	8	8	7	7	7	7	7	7	6	6	6
-41.25°	7	7	7	7	7	7	6	6	6	6	6
-42.5°	7	7	7	6	6	6	6	6	6	6	5
-43.75°	6	6	6	6	6	6	6	6	5	5	5
-45°	6	6	6	6	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	4	4
-47.5°	5	5	5	5	5	5	5	5	4	4	4
-48.75°	5	5	5	5	5	5	4	4	4	4	4
-50°	5	5	5	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	3	3	3	3
-53.75°	4	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	1	1
-66.25°	2	2	2	2	2	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	2	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	3	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	4	4	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	4	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	3	3	3	3
45°	4	4	4	4	4	4	4	4	4	3	3
43.75°	5	5	4	4	4	4	4	4	4	4	4
42.5°	5	5	5	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	5	4	4	4	4	4	4
40°	6	6	5	5	5	5	4	4	4	4	4
38.75°	6	6	6	5	5	5	5	4	4	4	4
37.5°	7	6	6	6	5	5	5	5	5	4	4
36.25°	7	7	6	6	6	5	5	5	5	5	4
35°	7	7	7	6	6	6	5	5	5	5	5



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	8	8	7	7	6	6	5	5	5	5	5
32.5°	9	8	8	7	7	6	6	5	5	5	5
31.25°	10	9	8	8	7	7	6	6	5	5	5
30°	11	10	9	8	8	7	6	6	5	5	5
28.75°	13	11	10	9	8	7	7	6	6	5	5
27.5°	14	13	12	10	9	8	7	7	6	6	5
26.25°	17	15	13	11	10	9	8	7	6	6	5
25°	20	17	15	13	11	10	9	7	7	6	6
23.75°	23	20	16	14	12	11	9	8	7	6	6
22.5°	28	23	19	16	14	12	10	9	8	7	6
21.25°	35	27	22	18	15	13	11	10	8	7	6
20°	42	32	26	21	17	15	12	10	9	7	7
18.75°	50	39	29	24	19	16	13	11	9	8	7
17.5°	59	47	35	27	21	17	15	12	10	8	7
16.25°	70	54	41	30	24	19	16	13	11	9	8
15°	81	61	48	34	27	21	17	14	12	9	8
13.75°	91	69	54	39	30	23	18	15	12	10	8
12.5°	101	78	59	45	33	26	19	16	13	11	8
11.25°	110	87	65	50	36	28	20	17	14	11	9
10°	120	95	71	55	40	31	22	18	15	12	9
8.75°	129	103	78	59	44	33	24	19	15	12	10
7.5°	138	111	84	63	48	35	26	20	16	13	10
6.25°	146	118	90	67	51	37	28	20	17	13	11
5°	154	124	96	70	54	39	30	21	17	14	11
3.75°	160	129	101	73	57	41	31	22	18	14	11
2.5°	165	134	105	76	59	43	32	22	18	15	12
1.25°	170	138	108	78	61	44	33	23	19	15	12
0°	173	141	110	79	62	45	34	23	19	15	12
-1.25°	170	138	108	78	61	44	33	23	19	15	12
-2.5°	165	134	105	76	59	43	32	22	18	15	12
-3.75°	160	129	101	73	57	41	31	22	18	14	11
-5°	154	124	96	70	54	39	30	21	17	14	11
-6.25°	146	118	90	67	51	37	28	20	17	13	11
-7.5°	138	111	84	63	48	35	26	20	16	13	10
-8.75°	129	103	78	59	44	33	24	19	15	12	10
-10°	120	95	71	55	40	31	22	18	15	12	9
-11.25°	110	87	65	50	36	28	20	17	14	11	9
-12.5°	101	78	59	45	33	26	19	16	13	11	8
-13.75°	91	69	54	39	30	23	18	15	12	10	8
-15°	81	61	48	34	27	21	17	14	12	9	8
-16.25°	70	54	41	30	24	19	16	13	11	9	8
-17.5°	59	47	35	27	21	17	15	12	10	8	7
-18.75°	50	39	29	24	19	16	13	11	9	8	7
-20°	42	32	26	21	17	15	12	10	9	7	7
-21.25°	35	27	22	18	15	13	11	10	8	7	6



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	28	23	19	16	14	12	10	9	8	7	6
-23.75°	23	20	16	14	12	11	9	8	7	6	6
-25°	20	17	15	13	11	10	9	7	7	6	6
-26.25°	17	15	13	11	10	9	8	7	6	6	5
-27.5°	14	13	12	10	9	8	7	7	6	6	5
-28.75°	13	11	10	9	8	7	7	6	6	5	5
-30°	11	10	9	8	8	7	6	6	5	5	5
-31.25°	10	9	8	8	7	7	6	6	5	5	5
-32.5°	9	8	8	7	7	6	6	5	5	5	5
-33.75°	8	8	7	7	6	6	5	5	5	5	5
-35°	7	7	7	6	6	6	5	5	5	5	5
-36.25°	7	7	6	6	6	5	5	5	5	5	4
-37.5°	7	6	6	6	5	5	5	5	5	4	4
-38.75°	6	6	6	5	5	5	5	4	4	4	4
-40°	6	6	5	5	5	5	4	4	4	4	4
-41.25°	5	5	5	5	5	4	4	4	4	4	4
-42.5°	5	5	5	4	4	4	4	4	4	4	4
-43.75°	5	5	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	3	3
-46.25°	4	4	4	4	4	4	4	3	3	3	3
-47.5°	4	4	4	4	4	4	3	3	3	3	3
-48.75°	4	4	4	4	3	3	3	3	3	3	3
-50°	4	4	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	3	3	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	1	1
-61.25°	2	2	2	2	2	2	1	1	1	1	1
-62.5°	2	2	2	2	1	1	1	1	1	1	1
-63.75°	2	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	2	2	1	1	1	1	1	1
55°	2	2	2	2	2	2	1	1	1	1	1
53.75°	2	2	2	2	2	2	2	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	2	1	1
51.25°	2	2	2	2	2	2	2	2	2	2	1
50°	2	2	2	2	2	2	2	2	2	2	1
48.75°	3	2	2	2	2	2	2	2	2	2	2
47.5°	3	3	2	2	2	2	2	2	2	2	2
46.25°	3	3	3	2	2	2	2	2	2	2	2
45°	3	3	3	3	2	2	2	2	2	2	2
43.75°	3	3	3	3	2	2	2	2	2	2	2
42.5°	4	3	3	3	3	2	2	2	2	2	2
41.25°	4	4	3	3	3	3	2	2	2	2	2
40°	4	4	4	3	3	3	2	2	2	2	2
38.75°	4	4	4	4	3	3	3	2	2	2	2
37.5°	4	4	4	4	3	3	3	2	2	2	2
36.25°	4	4	4	4	4	3	3	3	2	2	2
35°	4	4	4	4	4	4	3	3	2	2	2



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	5	4	4	4	4	4	3	3	3	2	2
32.5°	5	4	4	4	4	4	4	3	3	2	2
31.25°	5	5	4	4	4	4	4	3	3	3	2
30°	5	5	5	4	4	4	4	4	3	3	2
28.75°	5	5	5	4	4	4	4	4	3	3	2
27.5°	5	5	5	4	4	4	4	4	3	3	3
26.25°	5	5	5	5	4	4	4	4	4	3	3
25°	5	5	5	5	4	4	4	4	4	3	3
23.75°	5	5	5	5	5	4	4	4	4	3	3
22.5°	6	5	5	5	5	4	4	4	4	3	3
21.25°	6	5	5	5	5	4	4	4	4	4	3
20°	6	6	5	5	5	5	4	4	4	4	3
18.75°	6	6	5	5	5	5	4	4	4	4	3
17.5°	6	6	5	5	5	5	4	4	4	4	3
16.25°	7	6	6	5	5	5	4	4	4	4	3
15°	7	6	6	5	5	5	4	4	4	4	4
13.75°	7	6	6	6	5	5	5	4	4	4	4
12.5°	8	7	6	6	5	5	5	4	4	4	4
11.25°	8	7	6	6	5	5	5	4	4	4	4
10°	8	7	6	6	5	5	5	4	4	4	4
8.75°	8	7	6	6	6	5	5	4	4	4	4
7.5°	8	7	7	6	6	5	5	4	4	4	4
6.25°	8	8	7	6	6	5	5	4	4	4	4
5°	9	8	7	6	6	5	5	4	4	4	4
3.75°	9	8	7	6	6	5	5	4	4	4	4
2.5°	9	8	7	6	6	5	5	4	4	4	4
1.25°	9	8	7	6	6	5	5	4	4	4	4
0°	9	8	7	6	6	5	5	5	4	4	4
-1.25°	9	8	7	6	6	5	5	4	4	4	4
-2.5°	9	8	7	6	6	5	5	4	4	4	4
-3.75°	9	8	7	6	6	5	5	4	4	4	4
-5°	9	8	7	6	6	5	5	4	4	4	4
-6.25°	8	8	7	6	6	5	5	4	4	4	4
-7.5°	8	7	7	6	6	5	5	4	4	4	4
-8.75°	8	7	6	6	6	5	5	4	4	4	4
-10°	8	7	6	6	5	5	5	4	4	4	4
-11.25°	8	7	6	6	5	5	5	4	4	4	4
-12.5°	8	7	6	6	5	5	5	4	4	4	4
-13.75°	7	6	6	6	5	5	5	4	4	4	4
-15°	7	6	6	5	5	5	4	4	4	4	4
-16.25°	7	6	6	5	5	5	4	4	4	4	3
-17.5°	6	6	5	5	5	5	4	4	4	4	3
-18.75°	6	6	5	5	5	5	4	4	4	4	3
-20°	6	6	5	5	5	5	4	4	4	4	3
-21.25°	6	5	5	5	5	4	4	4	4	4	3



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	6	5	5	5	5	4	4	4	4	3	3
-23.75°	5	5	5	5	5	4	4	4	4	3	3
-25°	5	5	5	5	4	4	4	4	4	3	3
-26.25°	5	5	5	5	4	4	4	4	4	3	3
-27.5°	5	5	5	4	4	4	4	4	3	3	3
-28.75°	5	5	5	4	4	4	4	4	3	3	2
-30°	5	5	5	4	4	4	4	4	3	3	2
-31.25°	5	5	4	4	4	4	4	3	3	3	2
-32.5°	5	4	4	4	4	4	4	3	3	2	2
-33.75°	5	4	4	4	4	4	3	3	3	2	2
-35°	4	4	4	4	4	4	3	3	2	2	2
-36.25°	4	4	4	4	4	3	3	3	2	2	2
-37.5°	4	4	4	4	3	3	3	2	2	2	2
-38.75°	4	4	4	4	3	3	3	2	2	2	2
-40°	4	4	4	3	3	3	2	2	2	2	2
-41.25°	4	4	3	3	3	3	2	2	2	2	2
-42.5°	4	3	3	3	3	2	2	2	2	2	2
-43.75°	3	3	3	3	2	2	2	2	2	2	2
-45°	3	3	3	3	2	2	2	2	2	2	2
-46.25°	3	3	3	2	2	2	2	2	2	2	2
-47.5°	3	3	2	2	2	2	2	2	2	2	2
-48.75°	3	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	2	1	1
-53.75°	2	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	2	1	1	1	1	1
-56.25°	2	2	2	2	2	1	1	1	1	1	1
-57.5°	2	2	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	0	0	0	0
71.25°	1	1	1	1	1	1	1	1	0	0	0
70°	1	1	1	1	1	1	1	1	1	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	1	1	1	1	1	1	1	1	1	1
45°	2	2	1	1	1	1	1	1	1	1	1
43.75°	2	2	1	1	1	1	1	1	1	1	1
42.5°	2	2	2	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	2	1	1	1	1	1	1	1
38.75°	2	2	2	2	1	1	1	1	1	1	1
37.5°	2	2	2	2	1	1	1	1	1	1	1
36.25°	2	2	2	2	2	1	1	1	1	1	1
35°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	2	1	1	1	1	1
31.25°	2	2	2	2	2	2	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	2	2	2	2	2	2	1	1	1	1	1
27.5°	2	2	2	2	2	2	2	1	1	1	1
26.25°	2	2	2	2	2	2	2	1	1	1	1
25°	2	2	2	2	2	2	2	1	1	1	1
23.75°	2	2	2	2	2	2	2	1	1	1	1
22.5°	3	2	2	2	2	2	2	1	1	1	1
21.25°	3	2	2	2	2	2	2	1	1	1	1
20°	3	2	2	2	2	2	2	1	1	1	1
18.75°	3	2	2	2	2	2	2	2	1	1	1
17.5°	3	2	2	2	2	2	2	2	1	1	1
16.25°	3	3	2	2	2	2	2	2	1	1	1
15°	3	3	2	2	2	2	2	2	1	1	1
13.75°	3	3	2	2	2	2	2	2	1	1	1
12.5°	3	3	2	2	2	2	2	2	1	1	1
11.25°	3	3	2	2	2	2	2	2	1	1	1
10°	3	3	2	2	2	2	2	2	1	1	1
8.75°	3	3	2	2	2	2	2	2	1	1	1
7.5°	3	3	2	2	2	2	2	2	1	1	1
6.25°	3	3	2	2	2	2	2	2	1	1	1
5°	3	3	2	2	2	2	2	2	1	1	1
3.75°	3	3	2	2	2	2	2	2	1	1	1
2.5°	3	3	2	2	2	2	2	2	1	1	1
1.25°	3	3	2	2	2	2	2	2	1	1	1
0°	4	3	3	2	2	2	2	2	2	1	1
-1.25°	3	3	2	2	2	2	2	2	1	1	1
-2.5°	3	3	2	2	2	2	2	2	1	1	1
-3.75°	3	3	2	2	2	2	2	2	1	1	1
-5°	3	3	2	2	2	2	2	2	1	1	1
-6.25°	3	3	2	2	2	2	2	2	1	1	1
-7.5°	3	3	2	2	2	2	2	2	1	1	1
-8.75°	3	3	2	2	2	2	2	2	1	1	1
-10°	3	3	2	2	2	2	2	2	1	1	1
-11.25°	3	3	2	2	2	2	2	2	1	1	1
-12.5°	3	3	2	2	2	2	2	2	1	1	1
-13.75°	3	3	2	2	2	2	2	2	1	1	1
-15°	3	3	2	2	2	2	2	2	1	1	1
-16.25°	3	3	2	2	2	2	2	2	1	1	1
-17.5°	3	2	2	2	2	2	2	2	1	1	1
-18.75°	3	2	2	2	2	2	2	2	1	1	1
-20°	3	2	2	2	2	2	2	1	1	1	1
-21.25°	3	2	2	2	2	2	2	1	1	1	1



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	3	2	2	2	2	2	2	1	1	1	1
-23.75°	2	2	2	2	2	2	2	1	1	1	1
-25°	2	2	2	2	2	2	2	1	1	1	1
-26.25°	2	2	2	2	2	2	2	1	1	1	1
-27.5°	2	2	2	2	2	2	2	1	1	1	1
-28.75°	2	2	2	2	2	2	1	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	2	1	1	1	1	1
-32.5°	2	2	2	2	2	2	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	2	1	1	1	1	1	1
-36.25°	2	2	2	2	2	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-38.75°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	2	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	2	1	1	1	1	1	1	1	1
-43.75°	2	2	1	1	1	1	1	1	1	1	1
-45°	2	2	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	1	1	0
-70°	1	1	1	1	1	1	1	1	1	0	0
-71.25°	1	1	1	1	1	1	1	1	0	0	0
-72.5°	1	1	1	1	1	1	1	0	0	0	0
-73.75°	1	1	1	1	1	0	0	0	0	0	0
-75°	1	1	1	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	0	0	0	0	0	0	0	0	0	0
62.5°	1	1	0	0	0	0	0	0	0	0	0
61.25°	1	1	0	0	0	0	0	0	0	0	0
60°	1	1	0	0	0	0	0	0	0	0	0
58.75°	1	1	1	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	0	0	0	0	0	0	0
51.25°	1	1	1	1	0	0	0	0	0	0	0
50°	1	1	1	1	1	0	0	0	0	0	0
48.75°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	0	0	0	0	0	0
46.25°	1	1	1	1	1	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	1	0	0	0	0	0
42.5°	1	1	1	1	1	1	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	0	0	0	0	0
37.5°	1	1	1	1	1	1	0	0	0	0	0
36.25°	1	1	1	1	1	1	0	0	0	0	0
35°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	1	1	0	0	0	0	0
32.5°	1	1	1	1	1	1	1	0	0	0	0
31.25°	1	1	1	1	1	1	1	0	0	0	0
30°	1	1	1	1	1	1	1	0	0	0	0
28.75°	1	1	1	1	1	1	1	0	0	0	0
27.5°	1	1	1	1	1	1	1	0	0	0	0
26.25°	1	1	1	1	1	1	1	0	0	0	0
25°	1	1	1	1	1	1	1	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	0	0	0	0
18.75°	1	1	1	1	1	1	1	0	0	0	0
17.5°	1	1	1	1	1	1	1	0	0	0	0
16.25°	1	1	1	1	1	1	1	0	0	0	0
15°	1	1	1	1	1	1	1	0	0	0	0
13.75°	1	1	1	1	1	1	1	0	0	0	0
12.5°	1	1	1	1	1	1	1	0	0	0	0
11.25°	1	1	1	1	1	1	1	0	0	0	0
10°	1	1	1	1	1	1	1	0	0	0	0
8.75°	1	1	1	1	1	1	1	0	0	0	0
7.5°	1	1	1	1	1	1	1	0	0	0	0
6.25°	1	1	1	1	1	1	1	0	0	0	0
5°	1	1	1	1	1	1	1	0	0	0	0
3.75°	1	1	1	1	1	1	1	0	0	0	0
2.5°	1	1	1	1	1	1	1	0	0	0	0
1.25°	1	1	1	1	1	1	1	0	0	0	0
0°	1	1	1	1	1	1	1	0	0	0	0
-1.25°	1	1	1	1	1	1	1	0	0	0	0
-2.5°	1	1	1	1	1	1	1	0	0	0	0
-3.75°	1	1	1	1	1	1	1	0	0	0	0
-5°	1	1	1	1	1	1	1	0	0	0	0
-6.25°	1	1	1	1	1	1	1	0	0	0	0
-7.5°	1	1	1	1	1	1	1	0	0	0	0
-8.75°	1	1	1	1	1	1	1	0	0	0	0
-10°	1	1	1	1	1	1	1	0	0	0	0
-11.25°	1	1	1	1	1	1	1	0	0	0	0
-12.5°	1	1	1	1	1	1	1	0	0	0	0
-13.75°	1	1	1	1	1	1	1	0	0	0	0
-15°	1	1	1	1	1	1	1	0	0	0	0
-16.25°	1	1	1	1	1	1	1	0	0	0	0
-17.5°	1	1	1	1	1	1	1	0	0	0	0
-18.75°	1	1	1	1	1	1	1	0	0	0	0
-20°	1	1	1	1	1	1	1	0	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	1	0	0	0	0
-26.25°	1	1	1	1	1	1	1	0	0	0	0
-27.5°	1	1	1	1	1	1	1	0	0	0	0
-28.75°	1	1	1	1	1	1	1	0	0	0	0
-30°	1	1	1	1	1	1	1	0	0	0	0
-31.25°	1	1	1	1	1	1	1	0	0	0	0
-32.5°	1	1	1	1	1	1	1	0	0	0	0
-33.75°	1	1	1	1	1	1	0	0	0	0	0
-35°	1	1	1	1	1	1	0	0	0	0	0
-36.25°	1	1	1	1	1	1	0	0	0	0	0
-37.5°	1	1	1	1	1	1	0	0	0	0	0
-38.75°	1	1	1	1	1	1	0	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	1	0	0	0	0	0
-43.75°	1	1	1	1	1	1	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	1	0	0	0	0	0	0
-47.5°	1	1	1	1	1	0	0	0	0	0	0
-48.75°	1	1	1	1	1	0	0	0	0	0	0
-50°	1	1	1	1	1	0	0	0	0	0	0
-51.25°	1	1	1	1	0	0	0	0	0	0	0
-52.5°	1	1	1	1	0	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-58.75°	1	1	1	0	0	0	0	0	0	0	0
-60°	1	1	0	0	0	0	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	1	1	0	0	0	0	0	0	0	0	0
-63.75°	1	0	0	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-45 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)