

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE**

Issue Date: 4/9/2020

Test Information

Test Method: LM-79-2019
Report Number: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2001-623-1)
Test Lab: INNOVATION CENTER
Issue Date: 4/9/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE
Description: LUMIERE EON LED LUMINAIRE
CEILING WALL MOUNT, ONE LIGHTBAR, TYPE 2 WITH EDGE GLOW
Light Source: 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp:	N/A	NEMA Type:	7H x 7V
Luminaire Lumens:	489 lumens	Max Intensity:	152 candela
Efficiency:	N/A	Max Intensity Angle:	-35°H x 23.75°V
Efficacy:	58.2 lumens/watt		
Luminous Opening:	Rectangular w/ Sides (W: 0.38' x L: 0.21' x H: 0.01')		
Beam Angle (50%):	139.1°H x 103.6°V	Field Angle (10%):	166.9°H x 147.3°V
Beam Lumens:	411.2 lumens	Field Lumens:	481.9 lumens
Beam Efficiency:	84.1%	Field Efficiency:	98.5%
Input Watts (W):	8.4		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE


Iso-Candela Plot






REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

Lumen Table




REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

Luminous Intensity Polar Plot



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

Luminous Intensity Plot



Beam:
 H Angle: 139.1°
 V Angle: 103.6°
 Lumens: 411.2
 Efficiency: 84.1%

Field:
 H Angle: 166.9°
 V Angle: 147.3°
 Lumens: 481.9
 Efficiency: 98.5%

Spill:
 Lumens: 7.1
 Efficiency: 1.5%

— Vertical Distribution through -35-Deg
 - - - Horizontal Distribution through 23.75-Deg



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	1.5	1.5	1.5	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.7
88.75°	1.5	1.6	1.7	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4
87.5°	1.5	1.6	1.7	1.8	1.9	2.1	2.2	2.3	2.5	2.6	2.7
86.25°	1.5	1.6	1.8	1.9	2.1	2.2	2.4	2.5	2.7	2.8	2.9
85°	1.5	1.7	1.8	2.0	2.2	2.4	2.6	2.7	2.9	3.1	3.2
83.75°	1.5	1.7	1.9	2.1	2.3	2.5	2.7	2.9	3.1	3.3	3.5
82.5°	1.5	1.7	2.0	2.2	2.4	2.7	2.9	3.1	3.3	3.6	3.8
81.25°	1.5	1.8	2.0	2.3	2.5	2.8	3.1	3.3	3.6	3.8	4.1
80°	1.5	1.8	2.1	2.4	2.7	3.0	3.2	3.5	3.8	4.1	4.3
78.75°	1.5	1.8	2.1	2.5	2.8	3.1	3.4	3.7	4.0	4.3	4.6
77.5°	1.5	1.9	2.2	2.6	2.9	3.3	3.6	3.9	4.2	4.6	5.2
76.25°	1.5	1.9	2.3	2.6	3.0	3.4	3.8	4.1	4.5	5.1	5.9
75°	1.5	1.9	2.3	2.7	3.1	3.5	3.9	4.3	4.8	5.7	6.6
73.75°	1.5	1.9	2.4	2.8	3.3	3.7	4.1	4.5	5.4	6.3	7.3
72.5°	1.5	2.0	2.4	2.9	3.4	3.8	4.3	4.9	5.9	7.0	8.0
71.25°	1.5	2.0	2.5	3.0	3.5	4.0	4.4	5.4	6.5	7.6	8.7
70°	1.5	2.0	2.6	3.1	3.6	4.1	4.7	5.9	7.1	8.2	9.4
68.75°	1.5	2.1	2.6	3.2	3.7	4.3	5.1	6.4	7.6	8.8	10.1
67.5°	1.5	2.1	2.7	3.2	3.8	4.4	5.5	6.9	8.2	9.5	10.8
66.25°	1.5	2.1	2.7	3.3	3.9	4.6	5.9	7.3	8.7	10.1	11.4
65°	1.5	2.1	2.8	3.4	4.0	4.9	6.4	7.8	9.2	10.7	12.4
63.75°	1.5	2.2	2.8	3.5	4.2	5.2	6.8	8.3	9.8	11.3	13.3
62.5°	1.5	2.2	2.9	3.6	4.3	5.6	7.2	8.7	10.3	12.0	14.2
61.25°	1.5	2.2	2.9	3.7	4.4	5.9	7.6	9.2	10.8	12.9	15.1
60°	1.5	2.2	3.0	3.7	4.5	6.2	7.9	9.7	11.3	13.7	16.0
58.75°	1.5	2.3	3.0	3.8	4.7	6.5	8.3	10.1	12.1	14.5	16.9
57.5°	1.5	2.3	3.1	3.9	5.0	6.9	8.7	10.5	12.8	15.3	17.8
56.25°	1.5	2.3	3.1	4.0	5.2	7.2	9.1	11.0	13.5	16.1	18.7
55°	1.5	2.3	3.2	4.0	5.5	7.5	9.5	11.4	14.2	16.9	19.6
53.75°	1.5	2.4	3.2	4.1	5.7	7.8	9.8	12.0	14.9	17.7	20.4
52.5°	1.5	2.4	3.3	4.2	5.9	8.1	10.2	12.6	15.5	18.4	21.3
51.25°	1.5	2.4	3.3	4.2	6.2	8.4	10.5	13.2	16.2	19.2	22.3
50°	1.5	2.4	3.4	4.3	6.4	8.7	10.9	13.8	16.9	19.9	23.3
48.75°	1.5	2.5	3.4	4.4	6.6	8.9	11.2	14.3	17.5	20.6	24.2
47.5°	1.5	2.5	3.5	4.5	6.9	9.2	11.6	14.9	18.1	21.4	25.1
46.25°	1.5	2.5	3.5	4.7	7.1	9.5	12.1	15.4	18.8	22.2	26.1
45°	1.5	2.5	3.6	4.8	7.3	9.8	12.6	16.0	19.4	23.0	26.9
43.75°	1.5	2.5	3.6	5.0	7.5	10.0	13.0	16.5	20.0	23.8	27.8
42.5°	1.5	2.6	3.6	5.1	7.7	10.3	13.4	17.0	20.6	24.6	28.7
41.25°	1.5	2.6	3.7	5.3	7.9	10.5	13.9	17.5	21.1	25.3	29.5
40°	1.5	2.6	3.7	5.4	8.1	10.7	14.3	18.0	21.8	26.1	30.3
38.75°	1.5	2.6	3.7	5.6	8.3	11.0	14.7	18.5	22.4	26.8	31.1
37.5°	1.5	2.6	3.8	5.7	8.4	11.2	15.1	19.0	23.1	27.5	31.9
36.25°	1.5	2.7	3.8	5.8	8.6	11.5	15.4	19.4	23.7	28.2	32.7
35°	1.5	2.7	3.9	5.9	8.8	11.8	15.8	19.9	24.3	28.9	33.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	1.5	2.7	3.9	6.1	9.0	12.1	16.2	20.3	24.8	29.5	34.3
32.5°	1.5	2.7	3.9	6.2	9.1	12.3	16.5	20.7	25.4	30.1	35.1
31.25°	1.5	2.7	3.9	6.3	9.3	12.6	16.8	21.0	25.9	30.7	35.8
30°	1.5	2.7	4.0	6.4	9.4	12.9	17.1	21.5	26.4	31.3	36.5
28.75°	1.5	2.8	4.0	6.5	9.6	13.1	17.4	21.9	26.9	31.9	37.2
27.5°	1.5	2.8	4.0	6.6	9.7	13.4	17.7	22.3	27.4	32.4	37.9
26.25°	1.5	2.8	4.1	6.7	9.8	13.6	18.0	22.6	27.8	33.0	38.6
25°	1.5	2.8	4.1	6.8	9.9	13.8	18.3	23.0	28.2	33.5	39.2
23.75°	1.5	2.8	4.1	6.9	10.1	14.0	18.5	23.3	28.6	34.0	39.8
22.5°	1.5	2.8	4.1	7.0	10.2	14.2	18.8	23.7	29.0	34.4	40.3
21.25°	1.5	2.8	4.1	7.1	10.3	14.4	19.0	24.0	29.3	34.9	40.7
20°	1.5	2.8	4.2	7.1	10.4	14.6	19.2	24.3	29.6	35.3	41.2
18.75°	1.5	2.8	4.2	7.2	10.5	14.8	19.4	24.5	30.0	35.6	41.5
17.5°	1.5	2.9	4.2	7.3	10.6	14.9	19.6	24.8	30.2	36.0	41.9
16.25°	1.5	2.9	4.2	7.3	10.6	15.1	19.7	25.0	30.5	36.3	42.2
15°	1.5	2.9	4.2	7.4	10.7	15.2	19.9	25.2	30.8	36.5	42.5
13.75°	1.5	2.9	4.2	7.5	10.8	15.3	20.0	25.4	31.0	36.8	42.8
12.5°	1.5	2.9	4.3	7.5	10.8	15.4	20.2	25.6	31.2	37.0	43.0
11.25°	1.5	2.9	4.3	7.5	10.9	15.5	20.3	25.8	31.4	37.2	43.2
10°	1.5	2.9	4.3	7.6	10.9	15.6	20.4	25.9	31.5	37.4	43.3
8.75°	1.5	2.9	4.3	7.6	11.0	15.7	20.5	26.0	31.7	37.5	43.5
7.5°	1.5	2.9	4.3	7.6	11.0	15.8	20.5	26.1	31.8	37.6	43.5
6.25°	1.5	2.9	4.3	7.7	11.1	15.8	20.6	26.2	31.9	37.7	43.6
5°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.3	31.9	37.8	43.6
3.75°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.3	32.0	37.8	43.7
2.5°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.4	32.0	37.8	43.6
1.25°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.4	32.0	37.8	43.6
0°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.4	32.0	37.8	43.5
-1.25°	1.5	2.9	4.3	7.7	11.1	15.9	20.7	26.3	31.9	37.7	43.4
-2.5°	1.5	2.9	4.3	7.7	11.1	15.8	20.6	26.2	31.8	37.6	43.3
-3.75°	1.5	2.9	4.3	7.7	11.1	15.8	20.6	26.1	31.7	37.5	43.2
-5°	1.5	2.9	4.3	7.7	11.0	15.8	20.5	26.0	31.6	37.3	43.0
-6.25°	1.5	2.9	4.3	7.6	11.0	15.7	20.4	25.9	31.4	37.1	42.8
-7.5°	1.5	2.9	4.3	7.6	11.0	15.6	20.3	25.8	31.3	36.9	42.6
-8.75°	1.5	2.9	4.3	7.6	10.9	15.5	20.2	25.6	31.1	36.7	42.4
-10°	1.5	2.9	4.3	7.5	10.9	15.4	20.1	25.4	30.9	36.5	42.1
-11.25°	1.5	2.9	4.2	7.5	10.8	15.3	19.9	25.2	30.6	36.2	41.8
-12.5°	1.5	2.9	4.2	7.4	10.7	15.2	19.8	25.0	30.4	35.9	41.4
-13.75°	1.5	2.9	4.2	7.4	10.7	15.1	19.6	24.8	30.1	35.6	41.1
-15°	1.5	2.9	4.2	7.3	10.6	14.9	19.4	24.5	29.8	35.2	40.7
-16.25°	1.5	2.8	4.2	7.3	10.5	14.8	19.2	24.3	29.5	34.8	40.3
-17.5°	1.5	2.8	4.2	7.2	10.4	14.6	19.0	24.0	29.2	34.5	39.9
-18.75°	1.5	2.8	4.2	7.1	10.3	14.5	18.8	23.7	28.8	34.0	39.4
-20°	1.5	2.8	4.1	7.1	10.2	14.3	18.6	23.4	28.4	33.6	38.9
-21.25°	1.5	2.8	4.1	7.0	10.1	14.1	18.4	23.0	28.0	33.1	38.4



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	1.5	2.8	4.1	6.9	10.0	13.9	18.1	22.7	27.6	32.6	37.9
-23.75°	1.5	2.8	4.1	6.8	9.9	13.7	17.9	22.3	27.2	32.1	37.3
-25°	1.5	2.8	4.0	6.7	9.8	13.5	17.6	22.0	26.8	31.6	36.7
-26.25°	1.5	2.8	4.0	6.6	9.6	13.2	17.3	21.6	26.3	31.1	36.1
-27.5°	1.5	2.7	4.0	6.5	9.5	13.0	17.0	21.2	25.9	30.5	35.5
-28.75°	1.5	2.7	4.0	6.4	9.3	12.7	16.7	20.7	25.4	30.0	34.9
-30°	1.5	2.7	3.9	6.3	9.2	12.5	16.4	20.3	24.9	29.4	34.2
-31.25°	1.5	2.7	3.9	6.2	9.0	12.2	16.1	19.9	24.4	28.9	33.5
-32.5°	1.5	2.7	3.9	6.1	8.9	12.0	15.8	19.5	23.8	28.3	32.8
-33.75°	1.5	2.7	3.8	6.0	8.7	11.7	15.4	19.1	23.3	27.7	32.1
-35°	1.5	2.6	3.8	5.8	8.6	11.4	15.1	18.7	22.8	27.1	31.4
-36.25°	1.5	2.6	3.8	5.7	8.4	11.1	14.7	18.3	22.2	26.4	30.6
-37.5°	1.5	2.6	3.7	5.6	8.2	10.8	14.3	17.8	21.6	25.8	29.8
-38.75°	1.5	2.6	3.7	5.4	8.0	10.6	14.0	17.4	21.1	25.1	29.1
-40°	1.5	2.6	3.6	5.3	7.8	10.4	13.6	17.0	20.5	24.4	28.4
-41.25°	1.5	2.6	3.6	5.2	7.7	10.1	13.2	16.5	19.8	23.7	27.6
-42.5°	1.5	2.5	3.6	5.0	7.5	9.9	12.8	16.1	19.3	23.0	26.8
-43.75°	1.5	2.5	3.5	4.9	7.3	9.6	12.4	15.6	18.8	22.3	26.0
-45°	1.5	2.5	3.5	4.7	7.1	9.4	12.0	15.1	18.2	21.6	25.2
-46.25°	1.5	2.5	3.4	4.5	6.8	9.1	11.5	14.6	17.6	20.8	24.3
-47.5°	1.5	2.4	3.4	4.4	6.6	8.8	11.1	14.1	17.1	20.1	23.5
-48.75°	1.5	2.4	3.3	4.3	6.4	8.6	10.7	13.6	16.5	19.4	22.6
-50°	1.5	2.4	3.3	4.2	6.2	8.3	10.4	13.1	15.9	18.7	21.8
-51.25°	1.5	2.4	3.3	4.1	6.0	8.0	10.1	12.5	15.3	18.0	20.9
-52.5°	1.5	2.4	3.2	4.1	5.7	7.7	9.7	12.0	14.7	17.3	20.0
-53.75°	1.5	2.3	3.2	4.0	5.5	7.4	9.4	11.4	14.0	16.6	19.1
-55°	1.5	2.3	3.1	3.9	5.3	7.2	9.0	10.9	13.4	15.9	18.3
-56.25°	1.5	2.3	3.1	3.8	5.0	6.9	8.7	10.5	12.7	15.2	17.5
-57.5°	1.5	2.3	3.0	3.8	4.8	6.6	8.3	10.0	12.1	14.4	16.7
-58.75°	1.5	2.2	3.0	3.7	4.5	6.3	7.9	9.6	11.4	13.7	15.8
-60°	1.5	2.2	2.9	3.6	4.3	5.9	7.6	9.2	10.8	12.9	15.0
-61.25°	1.5	2.2	2.8	3.5	4.2	5.6	7.2	8.8	10.3	12.2	14.1
-62.5°	1.5	2.1	2.8	3.4	4.1	5.3	6.8	8.3	9.8	11.4	13.3
-63.75°	1.5	2.1	2.7	3.4	4.0	5.0	6.4	7.9	9.3	10.7	12.4
-65°	1.5	2.1	2.7	3.3	3.9	4.7	6.1	7.4	8.8	10.1	11.5
-66.25°	1.5	2.1	2.6	3.2	3.8	4.3	5.7	7.0	8.3	9.5	10.7
-67.5°	1.5	2.0	2.6	3.1	3.6	4.2	5.3	6.5	7.8	8.9	10.0
-68.75°	1.5	2.0	2.5	3.0	3.5	4.0	4.9	6.1	7.2	8.3	9.4
-70°	1.5	2.0	2.5	2.9	3.4	3.9	4.5	5.6	6.7	7.8	8.7
-71.25°	1.5	1.9	2.4	2.8	3.3	3.8	4.2	5.1	6.2	7.2	8.1
-72.5°	1.5	1.9	2.3	2.8	3.2	3.6	4.1	4.7	5.7	6.6	7.4
-73.75°	1.5	1.9	2.3	2.7	3.1	3.5	3.9	4.3	5.1	6.0	6.8
-75°	1.5	1.9	2.2	2.6	2.9	3.3	3.7	4.1	4.6	5.4	6.1
-76.25°	1.5	1.8	2.2	2.5	2.8	3.2	3.5	3.9	4.2	4.8	5.5
-77.5°	1.5	1.8	2.1	2.4	2.7	3.0	3.4	3.7	4.0	4.3	4.8



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	1.5	1.8	2.0	2.3	2.6	2.9	3.2	3.5	3.8	4.0	4.3
-80°	1.5	1.7	2.0	2.2	2.5	2.7	3.0	3.3	3.5	3.8	4.0
-81.25°	1.5	1.7	1.9	2.1	2.4	2.6	2.8	3.1	3.3	3.5	3.7
-82.5°	1.5	1.7	1.9	2.0	2.2	2.4	2.6	2.8	3.1	3.2	3.4
-83.75°	1.5	1.7	1.8	2.0	2.1	2.3	2.5	2.6	2.8	3.0	3.1
-85°	1.5	1.6	1.7	1.9	2.0	2.1	2.3	2.4	2.6	2.7	2.8
-86.25°	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.5
-87.5°	1.5	1.6	1.6	1.7	1.7	1.8	1.9	2.0	2.1	2.2	2.2
-88.75°	1.5	1.5	1.6	1.6	1.6	1.7	1.7	1.8	1.8	1.9	1.9
-90°	1.5	1.6	1.6	1.7	1.7	1.8	1.9	1.9	2.0	2.1	2.1



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.7	1.7	1.7
88.75°	2.5	2.5	2.6	2.7	2.8	2.9	3.0	3.1	3.2	3.3	3.4
87.5°	2.8	2.9	3.0	3.1	3.2	3.3	3.4	3.5	3.7	3.8	3.9
86.25°	3.1	3.2	3.3	3.5	3.6	3.7	3.8	4.0	4.1	4.2	4.3
85°	3.4	3.5	3.7	3.8	3.9	4.1	4.2	4.4	4.5	4.7	4.8
83.75°	3.7	3.9	4.0	4.2	4.3	4.5	4.6	4.8	5.0	5.3	5.6
82.5°	4.0	4.2	4.4	4.6	4.7	4.9	5.4	5.8	6.1	6.5	6.9
81.25°	4.3	4.5	4.7	5.1	5.6	6.0	6.4	6.9	7.3	7.7	8.1
80°	4.6	5.0	5.6	6.1	6.6	7.0	7.5	8.0	8.5	8.9	9.4
78.75°	5.2	5.8	6.5	7.0	7.6	8.1	8.6	9.1	9.6	10.1	10.6
77.5°	5.9	6.7	7.4	8.0	8.6	9.1	9.7	10.2	10.8	11.5	12.3
76.25°	6.7	7.5	8.3	8.9	9.5	10.1	10.7	11.6	12.4	13.3	14.1
75°	7.5	8.4	9.2	9.9	10.5	11.3	12.2	13.2	14.1	15.0	15.8
73.75°	8.3	9.2	10.1	10.8	11.7	12.8	13.8	14.8	15.8	16.7	17.6
72.5°	9.0	10.0	11.0	12.0	13.1	14.2	15.3	16.4	17.5	18.4	19.4
71.25°	9.8	10.9	12.0	13.3	14.5	15.7	16.9	18.0	19.1	20.3	21.5
70°	10.6	11.8	13.3	14.6	15.9	17.2	18.4	19.7	21.0	22.4	23.6
68.75°	11.3	12.9	14.5	16.0	17.3	18.7	20.0	21.6	23.0	24.4	25.7
67.5°	12.3	14.0	15.8	17.3	18.7	20.2	21.8	23.4	25.0	26.4	27.8
66.25°	13.3	15.2	17.0	18.6	20.1	21.9	23.6	25.3	26.9	28.4	30.0
65°	14.3	16.3	18.2	19.9	21.7	23.6	25.4	27.2	28.9	30.6	32.3
63.75°	15.4	17.4	19.4	21.2	23.2	25.2	27.2	29.1	30.9	32.8	34.6
62.5°	16.4	18.5	20.5	22.7	24.8	26.9	29.0	31.1	33.1	35.0	36.9
61.25°	17.4	19.6	21.8	24.1	26.3	28.5	30.7	33.1	35.2	37.2	39.2
60°	18.4	20.6	23.1	25.6	27.9	30.2	32.6	35.1	37.3	39.4	41.5
58.75°	19.3	21.8	24.5	27.0	29.4	31.9	34.5	37.1	39.4	41.7	43.9
57.5°	20.3	23.0	25.8	28.4	30.9	33.7	36.4	39.0	41.5	44.0	46.3
56.25°	21.3	24.2	27.0	29.7	32.5	35.4	38.2	41.0	43.7	46.2	48.7
55°	22.4	25.4	28.3	31.1	34.2	37.2	40.1	43.0	45.8	48.5	51.0
53.75°	23.5	26.6	29.6	32.6	35.8	38.9	41.9	45.0	48.0	50.7	53.4
52.5°	24.6	27.8	30.9	34.1	37.4	40.7	43.9	47.1	50.1	53.0	55.8
51.25°	25.7	29.0	32.2	35.6	39.1	42.4	45.8	49.1	52.3	55.2	58.1
50°	26.7	30.1	33.5	37.1	40.6	44.2	47.7	51.1	54.4	57.5	60.5
48.75°	27.8	31.2	34.9	38.6	42.2	46.0	49.7	53.2	56.5	59.7	62.8
47.5°	28.8	32.4	36.2	40.0	43.7	47.8	51.6	55.2	58.5	61.9	65.2
46.25°	29.9	33.6	37.5	41.4	45.4	49.5	53.5	57.1	60.6	64.0	67.4
45°	30.8	34.8	38.8	42.8	47.0	51.3	55.4	59.0	62.6	66.1	69.7
43.75°	31.8	36.0	40.1	44.2	48.5	52.9	57.2	60.9	64.5	68.2	71.9
42.5°	32.8	37.1	41.3	45.6	50.1	54.6	58.9	62.7	66.5	70.3	74.1
41.25°	33.8	38.3	42.6	47.0	51.6	56.2	60.4	64.5	68.4	72.4	76.3
40°	34.8	39.3	43.8	48.4	53.0	57.7	62.0	66.3	70.3	74.4	78.4
38.75°	35.7	40.4	45.0	49.7	54.5	59.1	63.6	67.9	72.2	76.4	80.5
37.5°	36.7	41.4	46.2	51.0	55.8	60.5	65.1	69.6	74.1	78.4	82.6
36.25°	37.6	42.4	47.3	52.2	57.2	62.0	66.6	71.2	75.8	80.3	84.6
35°	38.5	43.4	48.4	53.5	58.5	63.3	68.1	72.8	77.5	82.2	86.6



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	39.4	44.4	49.5	54.6	59.7	64.7	69.6	74.4	79.2	83.9	88.6
32.5°	40.2	45.3	50.5	55.8	61.0	66.0	71.0	75.9	80.8	85.6	90.5
31.25°	41.0	46.2	51.5	56.9	62.2	67.3	72.4	77.4	82.4	87.3	92.3
30°	41.8	47.1	52.5	57.9	63.3	68.6	73.8	78.8	83.9	88.9	93.9
28.75°	42.6	48.0	53.5	58.9	64.4	69.8	75.1	80.2	85.3	90.4	95.4
27.5°	43.4	48.8	54.4	59.9	65.4	71.0	76.4	81.6	86.7	91.9	96.8
26.25°	44.1	49.7	55.2	60.9	66.5	72.0	77.5	82.9	88.1	93.3	98.1
25°	44.8	50.4	56.1	61.8	67.4	73.1	78.6	84.1	89.4	94.6	99.4
23.75°	45.4	51.2	56.9	62.6	68.4	74.0	79.7	85.2	90.6	95.8	100.7
22.5°	46.1	51.9	57.6	63.5	69.3	75.0	80.7	86.2	91.7	96.9	101.9
21.25°	46.7	52.5	58.4	64.2	70.1	75.9	81.6	87.2	92.7	98.0	103.0
20°	47.2	53.2	59.1	65.0	70.9	76.7	82.5	88.1	93.7	98.9	104.1
18.75°	47.6	53.7	59.7	65.7	71.7	77.5	83.4	89.0	94.6	99.8	105.0
17.5°	48.0	54.2	60.3	66.4	72.4	78.3	84.2	89.9	95.5	100.7	105.9
16.25°	48.3	54.5	60.8	67.0	73.0	79.0	84.9	90.6	96.3	101.5	106.7
15°	48.6	54.9	61.1	67.4	73.7	79.7	85.6	91.4	97.0	102.3	107.5
13.75°	48.9	55.2	61.4	67.7	74.0	80.3	86.2	92.0	97.6	103.0	108.1
12.5°	49.2	55.4	61.7	68.0	74.3	80.6	86.7	92.7	98.3	103.6	108.8
11.25°	49.4	55.6	62.0	68.3	74.6	80.8	86.9	93.0	98.7	104.2	109.3
10°	49.6	55.8	62.2	68.5	74.8	81.0	87.1	93.2	98.9	104.5	109.8
8.75°	49.7	56.0	62.3	68.6	74.9	81.2	87.2	93.3	99.0	104.5	109.8
7.5°	49.8	56.1	62.4	68.8	75.0	81.3	87.3	93.3	99.0	104.6	109.8
6.25°	49.9	56.2	62.5	68.8	75.1	81.3	87.3	93.3	98.9	104.5	109.7
5°	49.9	56.2	62.5	68.8	75.1	81.3	87.3	93.3	98.8	104.4	109.5
3.75°	49.9	56.2	62.5	68.8	75.0	81.3	87.2	93.2	98.7	104.2	109.3
2.5°	49.9	56.2	62.5	68.8	75.0	81.2	87.1	93.0	98.5	104.0	109.0
1.25°	49.8	56.1	62.4	68.7	74.8	81.0	86.9	92.8	98.3	103.7	108.7
0°	49.8	56.0	62.3	68.5	74.7	80.8	86.7	92.5	98.0	103.4	108.4
-1.25°	49.6	55.9	62.1	68.3	74.4	80.6	86.4	92.2	97.6	103.0	108.0
-2.5°	49.5	55.7	61.9	68.1	74.2	80.3	86.1	91.9	97.3	102.6	107.5
-3.75°	49.3	55.5	61.7	67.8	73.9	79.9	85.7	91.5	96.8	102.2	107.0
-5°	49.1	55.3	61.4	67.5	73.5	79.5	85.3	91.0	96.3	101.7	106.5
-6.25°	48.9	55.0	61.1	67.2	73.2	79.1	84.8	90.5	95.8	101.1	105.9
-7.5°	48.6	54.7	60.8	66.8	72.7	78.6	84.3	90.0	95.2	100.5	105.2
-8.75°	48.3	54.4	60.4	66.4	72.3	78.1	83.8	89.3	94.6	99.8	104.6
-10°	48.0	54.0	60.0	65.9	71.7	77.5	83.2	88.7	93.9	99.1	103.8
-11.25°	47.7	53.6	59.5	65.4	71.2	76.9	82.5	88.0	93.2	98.3	103.0
-12.5°	47.3	53.2	59.0	64.9	70.6	76.3	81.8	87.3	92.4	97.4	102.2
-13.75°	46.9	52.7	58.5	64.3	70.0	75.6	81.1	86.4	91.6	96.6	101.3
-15°	46.4	52.2	57.9	63.7	69.3	74.9	80.3	85.6	90.7	95.6	100.3
-16.25°	45.9	51.6	57.3	63.0	68.6	74.1	79.5	84.7	89.8	94.6	99.4
-17.5°	45.4	51.1	56.7	62.3	67.8	73.3	78.6	83.8	88.9	93.6	98.3
-18.75°	44.9	50.5	56.1	61.6	67.1	72.4	77.7	82.8	87.8	92.5	97.2
-20°	44.3	49.9	55.4	60.8	66.3	71.5	76.8	81.8	86.7	91.4	96.0
-21.25°	43.7	49.2	54.7	60.1	65.4	70.6	75.8	80.7	85.6	90.3	94.7



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	43.1	48.5	53.9	59.2	64.5	69.7	74.7	79.6	84.4	89.0	93.2
-23.75°	42.5	47.8	53.1	58.4	63.6	68.7	73.6	78.5	83.2	87.6	91.7
-25°	41.8	47.1	52.3	57.5	62.6	67.6	72.5	77.3	81.8	86.1	90.1
-26.25°	41.2	46.3	51.5	56.6	61.6	66.6	71.4	76.0	80.3	84.6	88.5
-27.5°	40.5	45.5	50.6	55.6	60.6	65.5	70.2	74.6	78.8	83.0	86.9
-28.75°	39.8	44.7	49.7	54.7	59.6	64.4	68.8	73.1	77.3	81.4	85.3
-30°	39.0	43.9	48.8	53.7	58.5	63.1	67.4	71.7	75.8	79.7	83.6
-31.25°	38.3	43.0	47.8	52.6	57.4	61.8	66.0	70.2	74.2	78.0	81.8
-32.5°	37.5	42.1	46.9	51.6	56.1	60.4	64.6	68.6	72.6	76.4	80.0
-33.75°	36.7	41.2	45.9	50.5	54.8	59.0	63.1	67.1	70.9	74.6	78.1
-35°	35.9	40.3	44.8	49.3	53.5	57.6	61.6	65.5	69.2	72.9	76.2
-36.25°	35.0	39.4	43.8	48.0	52.1	56.1	60.1	63.9	67.5	71.0	74.2
-37.5°	34.2	38.4	42.7	46.8	50.8	54.7	58.5	62.2	65.8	69.1	72.2
-38.75°	33.3	37.5	41.5	45.5	49.4	53.2	56.9	60.5	64.0	67.2	70.3
-40°	32.4	36.5	40.4	44.2	48.0	51.7	55.3	58.8	62.1	65.2	68.2
-41.25°	31.4	35.5	39.2	42.9	46.6	50.2	53.7	57.1	60.3	63.3	66.2
-42.5°	30.5	34.4	38.0	41.6	45.2	48.6	52.0	55.3	58.4	61.3	64.1
-43.75°	29.6	33.3	36.8	40.3	43.7	47.1	50.4	53.5	56.5	59.3	62.0
-45°	28.7	32.2	35.6	39.0	42.3	45.6	48.7	51.7	54.6	57.3	59.9
-46.25°	27.8	31.0	34.4	37.6	40.8	44.0	47.0	49.9	52.7	55.3	57.8
-47.5°	26.8	29.9	33.2	36.3	39.4	42.4	45.3	48.1	50.8	53.3	55.7
-48.75°	25.8	28.8	31.9	35.0	37.9	40.8	43.6	46.3	48.8	51.3	53.6
-50°	24.8	27.7	30.7	33.6	36.5	39.2	41.9	44.5	46.9	49.3	51.4
-51.25°	23.8	26.6	29.4	32.3	35.1	37.6	40.2	42.7	45.0	47.3	49.2
-52.5°	22.8	25.5	28.2	30.9	33.6	36.1	38.5	40.8	43.1	45.2	47.1
-53.75°	21.8	24.4	27.0	29.6	32.1	34.5	36.8	39.0	41.2	43.2	44.9
-55°	20.7	23.3	25.8	28.2	30.6	32.9	35.1	37.2	39.3	41.2	42.8
-56.25°	19.7	22.2	24.6	26.9	29.1	31.3	33.4	35.4	37.4	39.1	40.7
-57.5°	18.7	21.0	23.3	25.6	27.6	29.7	31.7	33.7	35.4	37.1	38.6
-58.75°	17.8	19.9	22.1	24.2	26.2	28.1	30.1	31.9	33.6	35.1	36.6
-60°	16.9	18.7	20.8	22.9	24.8	26.6	28.4	30.1	31.7	33.1	34.5
-61.25°	16.0	17.7	19.6	21.5	23.4	25.1	26.7	28.4	29.9	31.2	32.5
-62.5°	15.0	16.7	18.4	20.2	21.9	23.6	25.1	26.6	28.0	29.3	30.5
-63.75°	14.1	15.7	17.3	18.8	20.5	22.1	23.6	24.9	26.2	27.4	28.6
-65°	13.2	14.7	16.2	17.6	19.1	20.6	22.0	23.3	24.4	25.5	26.6
-66.25°	12.2	13.7	15.1	16.4	17.7	19.1	20.4	21.6	22.7	23.7	24.7
-67.5°	11.3	12.7	14.0	15.3	16.5	17.6	18.9	20.0	21.0	22.0	22.8
-68.75°	10.4	11.7	13.0	14.1	15.2	16.3	17.3	18.4	19.4	20.3	21.1
-70°	9.7	10.6	11.9	13.0	14.0	15.0	15.9	16.7	17.7	18.5	19.3
-71.25°	9.0	9.8	10.8	11.8	12.8	13.7	14.6	15.4	16.0	16.8	17.5
-72.5°	8.3	9.1	9.8	10.7	11.6	12.5	13.3	14.0	14.6	15.2	15.8
-73.75°	7.6	8.3	9.0	9.6	10.4	11.2	12.0	12.6	13.2	13.8	14.2
-75°	6.9	7.5	8.2	8.8	9.3	9.9	10.6	11.2	11.8	12.3	12.7
-76.25°	6.1	6.8	7.4	7.9	8.4	8.9	9.3	9.9	10.4	10.9	11.3
-77.5°	5.4	6.0	6.6	7.0	7.5	8.0	8.4	8.7	9.0	9.5	9.8



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	4.7	5.3	5.7	6.2	6.6	7.0	7.4	7.7	8.0	8.2	8.4
-80°	4.2	4.5	4.9	5.3	5.7	6.1	6.4	6.7	7.0	7.2	7.3
-81.25°	3.9	4.0	4.2	4.4	4.8	5.1	5.4	5.7	5.9	6.2	6.3
-82.5°	3.6	3.7	3.8	3.9	4.0	4.1	4.4	4.7	4.9	5.1	5.2
-83.75°	3.2	3.4	3.5	3.6	3.6	3.7	3.7	3.8	3.9	4.1	4.2
-85°	2.9	3.0	3.1	3.2	3.3	3.3	3.4	3.4	3.4	3.5	3.5
-86.25°	2.6	2.7	2.8	2.8	2.9	2.9	3.0	3.0	3.0	3.0	3.0
-87.5°	2.3	2.4	2.4	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6
-88.75°	2.0	2.0	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.1	2.1
-90°	2.2	2.2	2.3	2.4	2.4	2.5	2.6	2.7	2.8	2.9	3.0



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	1.7	1.6	1.6	1.6	1.6	1.5	1.5	1.5	1.5	1.4	1.4
88.75°	3.5	3.6	3.6	3.6	3.6	3.8	3.9	3.9	4.0	4.1	4.1
87.5°	4.0	4.1	4.1	4.1	4.2	4.3	4.4	4.5	4.5	4.6	4.6
86.25°	4.5	4.6	4.7	4.6	4.7	4.8	5.0	5.1	5.1	5.1	5.1
85°	4.9	5.1	5.2	5.3	5.4	5.7	6.0	6.2	6.3	6.4	6.5
83.75°	5.9	6.3	6.6	6.6	6.8	7.1	7.4	7.6	7.8	7.9	8.0
82.5°	7.2	7.6	7.9	8.0	8.1	8.5	8.9	9.1	9.2	9.4	9.5
81.25°	8.5	8.9	9.3	9.4	9.5	9.9	10.3	10.7	10.9	11.2	11.5
80°	9.8	10.2	10.7	10.9	11.1	11.7	12.3	12.7	13.0	13.3	13.6
78.75°	11.2	11.9	12.5	12.9	13.1	13.7	14.3	14.7	15.1	15.4	15.7
77.5°	13.0	13.8	14.4	14.8	15.0	15.7	16.3	16.8	17.2	17.7	18.2
76.25°	14.9	15.6	16.3	16.8	17.0	17.7	18.5	19.2	19.8	20.3	20.9
75°	16.7	17.5	18.2	18.9	19.3	20.0	20.9	21.7	22.3	23.0	23.6
73.75°	18.5	19.5	20.4	21.3	21.7	22.4	23.3	24.2	24.9	25.6	26.3
72.5°	20.6	21.7	22.7	23.7	24.2	24.8	25.7	26.7	27.6	28.4	29.0
71.25°	22.7	23.9	25.0	26.0	26.6	27.3	28.4	29.5	30.4	31.1	31.8
70°	24.9	26.1	27.3	28.5	29.3	29.9	31.1	32.2	33.2	33.9	34.7
68.75°	27.0	28.3	29.7	31.0	32.0	32.6	33.8	35.0	36.1	37.0	37.9
67.5°	29.2	30.8	32.2	33.6	34.7	35.4	36.5	37.9	39.1	40.1	41.1
66.25°	31.6	33.2	34.7	36.2	37.5	38.3	39.4	40.8	42.1	43.2	44.3
65°	33.9	35.6	37.2	38.8	40.4	41.3	42.3	43.8	45.1	46.4	47.5
63.75°	36.3	38.1	39.8	41.6	43.2	44.3	45.3	46.8	48.2	49.6	50.8
62.5°	38.7	40.6	42.5	44.3	46.0	47.4	48.3	49.8	51.4	52.8	54.1
61.25°	41.1	43.1	45.1	47.0	48.8	50.4	51.4	52.8	54.5	56.1	57.4
60°	43.6	45.6	47.7	49.7	51.7	53.5	54.6	55.8	57.6	59.3	60.8
58.75°	46.1	48.2	50.3	52.5	54.5	56.5	57.8	58.9	60.8	62.6	64.1
57.5°	48.5	50.7	53.0	55.2	57.3	59.4	61.0	62.2	63.9	65.8	67.5
56.25°	51.0	53.3	55.6	57.9	60.1	62.3	64.3	65.6	67.1	69.0	70.8
55°	53.5	55.9	58.2	60.6	63.0	65.3	67.5	68.9	70.3	72.3	74.2
53.75°	56.0	58.5	60.8	63.4	65.8	68.2	70.5	72.3	73.7	75.5	77.5
52.5°	58.4	61.0	63.5	66.1	68.7	71.1	73.5	75.8	77.2	78.8	80.8
51.25°	60.9	63.6	66.2	68.8	71.5	74.0	76.6	79.0	80.7	82.0	84.1
50°	63.4	66.2	68.9	71.5	74.3	76.9	79.5	82.1	84.1	85.5	87.4
48.75°	65.8	68.8	71.6	74.3	77.0	79.8	82.5	85.1	87.5	89.1	90.6
47.5°	68.3	71.3	74.3	77.0	79.8	82.6	85.4	88.0	90.6	92.6	93.9
46.25°	70.8	73.9	76.9	79.8	82.5	85.4	88.2	90.9	93.6	95.9	97.4
45°	73.2	76.4	79.5	82.5	85.4	88.1	91.0	93.8	96.4	98.8	100.7
43.75°	75.6	78.9	82.1	85.1	88.1	90.8	93.7	96.6	99.2	101.7	104.0
42.5°	77.9	81.4	84.6	87.8	90.7	93.6	96.5	99.2	101.9	104.5	106.9
41.25°	80.1	83.7	87.1	90.3	93.3	96.3	99.1	101.9	104.6	107.2	109.7
40°	82.3	86.0	89.6	92.8	95.9	98.9	101.7	104.5	107.3	109.9	112.5
38.75°	84.5	88.3	91.9	95.2	98.5	101.5	104.3	107.2	109.9	112.6	115.3
37.5°	86.7	90.6	94.2	97.6	100.9	103.9	106.9	109.7	112.4	115.3	117.8
36.25°	88.8	92.8	96.4	100.0	103.3	106.4	109.5	112.3	115.0	117.7	120.2
35°	90.9	94.9	98.6	102.2	105.6	108.8	111.9	114.7	117.6	120.1	122.7



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	93.0	96.9	100.8	104.4	107.8	111.2	114.2	117.2	120.0	122.5	125.0
32.5°	94.9	98.9	102.9	106.5	110.0	113.4	116.5	119.6	122.2	124.8	127.3
31.25°	96.8	100.9	104.9	108.5	112.1	115.4	118.8	121.7	124.4	127.1	129.4
30°	98.5	102.9	106.8	110.5	114.1	117.4	120.8	123.8	126.6	129.1	131.3
28.75°	100.0	104.7	108.6	112.4	116.0	119.4	122.7	125.7	128.7	131.0	133.2
27.5°	101.5	106.1	110.4	114.3	117.8	121.2	124.5	127.5	130.4	132.7	135.0
26.25°	102.9	107.5	111.8	116.0	119.5	123.0	126.1	129.2	131.9	134.3	136.6
25°	104.3	108.8	113.2	117.3	121.2	124.7	127.7	130.8	133.3	135.8	138.0
23.75°	105.6	110.1	114.5	118.6	122.5	126.1	129.3	132.2	134.7	137.2	139.2
22.5°	106.8	111.3	115.8	119.7	123.7	127.3	130.7	133.5	136.0	138.3	140.3
21.25°	107.9	112.4	116.8	120.9	124.9	128.3	131.8	134.6	137.2	139.4	141.4
20°	108.9	113.5	117.9	121.9	125.8	129.3	132.7	135.5	138.2	140.3	142.4
18.75°	109.8	114.5	118.8	122.9	126.7	130.2	133.4	136.2	138.9	141.1	143.3
17.5°	110.7	115.5	119.7	123.9	127.6	131.1	134.1	136.9	139.5	141.7	143.7
16.25°	111.5	116.3	120.5	124.8	128.3	131.8	134.8	137.6	140.0	142.2	144.1
15°	112.3	117.0	121.3	125.5	129.0	132.6	135.4	138.2	140.5	142.7	144.4
13.75°	113.0	117.7	121.9	126.0	129.6	133.1	135.9	138.7	140.9	143.1	144.7
12.5°	113.7	118.3	122.6	126.6	130.1	133.5	136.3	139.1	141.3	143.4	144.9
11.25°	114.3	118.9	123.1	127.0	130.6	133.9	136.7	139.4	141.6	143.6	145.1
10°	114.8	119.4	123.6	127.5	131.0	134.2	137.1	139.6	141.9	143.8	145.3
8.75°	115.0	119.6	124.1	127.8	131.4	134.5	137.4	139.9	142.1	143.9	145.5
7.5°	114.9	119.5	123.9	127.8	131.5	134.8	137.7	140.1	142.3	144.0	145.6
6.25°	114.8	119.3	123.8	127.6	131.3	134.5	137.5	140.0	142.3	144.1	145.7
5°	114.6	119.1	123.5	127.3	131.0	134.1	137.1	139.5	141.9	143.6	145.4
3.75°	114.4	118.8	123.2	127.0	130.6	133.7	136.7	139.1	141.4	143.1	144.8
2.5°	114.1	118.5	122.9	126.6	130.2	133.2	136.2	138.5	140.9	142.6	144.2
1.25°	113.7	118.1	122.5	126.1	129.8	132.7	135.7	138.0	140.3	142.0	143.6
0°	113.3	117.7	122.0	125.7	129.3	132.2	135.1	137.4	139.7	141.4	143.0
-1.25°	112.9	117.2	121.5	125.2	128.8	131.7	134.6	136.9	139.2	140.9	142.5
-2.5°	112.4	116.7	121.0	124.6	128.2	131.1	134.0	136.4	138.7	140.3	142.0
-3.75°	111.8	116.1	120.4	124.0	127.6	130.6	133.4	135.8	138.1	139.8	141.5
-5°	111.2	115.5	119.8	123.4	127.0	129.9	132.8	135.2	137.5	139.2	140.9
-6.25°	110.6	114.9	119.1	122.7	126.3	129.2	132.1	134.5	136.8	138.6	140.3
-7.5°	109.9	114.2	118.3	122.0	125.5	128.5	131.3	133.8	136.1	137.9	139.6
-8.75°	109.2	113.4	117.6	121.2	124.7	127.7	130.5	133.0	135.3	137.2	138.8
-10°	108.4	112.6	116.7	120.4	123.8	126.8	129.7	132.2	134.4	136.4	138.1
-11.25°	107.5	111.7	115.8	119.5	122.8	125.9	128.8	131.4	133.6	135.6	137.2
-12.5°	106.6	110.8	114.8	118.6	121.8	124.9	127.8	130.6	132.7	134.7	136.3
-13.75°	105.6	109.8	113.8	117.6	120.8	123.9	126.8	129.7	131.7	133.6	135.2
-15°	104.6	108.8	112.7	116.6	119.7	122.8	125.6	128.4	130.4	132.4	134.0
-16.25°	103.5	107.7	111.6	115.5	118.6	121.5	124.3	127.0	129.1	131.1	132.8
-17.5°	102.5	106.5	110.4	114.1	117.2	120.1	122.9	125.5	127.8	129.7	131.5
-18.75°	101.3	105.3	109.0	112.6	115.8	118.7	121.4	124.0	126.5	128.3	130.2
-20°	100.1	103.9	107.5	111.0	114.3	117.1	120.0	122.5	125.0	126.8	128.5
-21.25°	98.7	102.4	106.0	109.4	112.8	115.6	118.4	120.9	123.2	125.0	126.7



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	97.3	100.9	104.4	107.8	111.1	114.0	116.8	119.1	121.3	123.3	124.9
-23.75°	95.8	99.3	102.8	106.1	109.3	112.3	114.8	117.3	119.3	121.4	123.0
-25°	94.1	97.7	101.1	104.4	107.5	110.4	112.8	115.3	117.4	119.4	121.1
-26.25°	92.4	96.0	99.4	102.7	105.5	108.4	110.8	113.2	115.4	117.3	119.1
-27.5°	90.7	94.3	97.6	100.7	103.5	106.3	108.8	111.1	113.3	115.1	116.9
-28.75°	88.9	92.6	95.7	98.7	101.5	104.2	106.7	108.9	111.1	112.9	114.6
-30°	87.2	90.6	93.7	96.6	99.4	102.0	104.5	106.7	108.7	110.5	112.2
-31.25°	85.3	88.6	91.7	94.5	97.3	99.8	102.3	104.3	106.2	108.1	109.8
-32.5°	83.4	86.5	89.6	92.4	95.1	97.6	99.8	101.9	103.7	105.6	107.3
-33.75°	81.4	84.5	87.5	90.2	92.8	95.3	97.3	99.3	101.2	102.9	104.7
-35°	79.4	82.4	85.3	88.0	90.5	92.7	94.8	96.7	98.6	100.3	101.8
-36.25°	77.3	80.2	83.0	85.8	88.0	90.2	92.2	94.1	95.9	97.5	98.9
-37.5°	75.2	78.1	80.8	83.3	85.5	87.6	89.6	91.4	93.1	94.5	95.9
-38.75°	73.1	75.9	78.5	80.8	83.0	84.9	86.8	88.7	90.0	91.3	92.9
-40°	71.0	73.7	76.1	78.3	80.3	82.3	84.1	85.6	86.7	87.9	89.5
-41.25°	68.9	71.5	73.7	75.7	77.6	79.5	81.3	82.3	83.2	84.3	85.8
-42.5°	66.8	69.1	71.2	73.1	75.0	76.8	78.2	78.8	79.6	80.6	81.9
-43.75°	64.6	66.8	68.7	70.5	72.3	74.0	74.8	75.3	76.0	76.8	77.7
-45°	62.3	64.4	66.2	68.0	69.6	70.9	71.5	71.8	72.2	72.9	73.4
-46.25°	60.1	62.0	63.8	65.4	66.9	67.7	68.2	68.4	68.5	68.9	69.4
-47.5°	57.8	59.6	61.3	62.8	64.1	64.7	65.0	65.2	65.1	65.1	65.5
-48.75°	55.5	57.3	58.9	60.3	61.2	61.7	61.9	61.9	61.8	61.9	61.8
-50°	53.3	55.0	56.5	57.8	58.4	58.7	58.9	58.8	58.8	58.8	58.7
-51.25°	51.0	52.7	54.1	55.2	55.6	55.9	56.0	55.8	55.8	55.8	55.6
-52.5°	48.8	50.4	51.8	52.5	52.9	53.1	53.1	53.0	53.0	52.9	52.6
-53.75°	46.6	48.0	49.4	49.9	50.2	50.3	50.3	50.3	50.3	50.1	49.7
-55°	44.3	45.7	46.9	47.3	47.6	47.7	47.6	47.6	47.6	47.3	47.0
-56.25°	42.1	43.5	44.3	44.8	45.0	45.0	45.0	45.0	44.9	44.6	44.3
-57.5°	40.0	41.2	41.9	42.3	42.5	42.4	42.4	42.5	42.4	42.1	41.6
-58.75°	37.9	38.9	39.4	39.8	40.0	39.9	40.0	40.0	39.9	39.6	39.1
-60°	35.7	36.7	37.1	37.4	37.5	37.5	37.6	37.6	37.4	37.1	36.7
-61.25°	33.6	34.4	34.9	35.1	35.2	35.2	35.3	35.3	35.1	34.8	34.4
-62.5°	31.6	32.2	32.6	32.8	32.9	32.9	33.0	33.0	32.8	32.5	32.1
-63.75°	29.6	30.1	30.4	30.6	30.7	30.8	30.8	30.7	30.5	30.3	29.9
-65°	27.5	28.0	28.3	28.4	28.5	28.6	28.6	28.5	28.3	28.1	27.8
-66.25°	25.5	25.9	26.2	26.3	26.4	26.5	26.5	26.4	26.2	26.0	25.7
-67.5°	23.5	23.9	24.2	24.3	24.4	24.5	24.5	24.4	24.2	24.0	23.7
-68.75°	21.6	21.9	22.2	22.3	22.4	22.5	22.5	22.4	22.2	22.0	21.7
-70°	19.8	20.1	20.3	20.4	20.5	20.6	20.6	20.5	20.3	20.1	19.7
-71.25°	17.9	18.3	18.4	18.5	18.6	18.7	18.7	18.6	18.5	18.3	18.0
-72.5°	16.2	16.5	16.7	16.8	16.9	16.9	16.9	16.8	16.7	16.6	16.3
-73.75°	14.4	14.7	14.9	15.0	15.2	15.2	15.2	15.1	15.0	14.9	14.7
-75°	12.9	13.1	13.2	13.3	13.5	13.5	13.5	13.5	13.4	13.3	13.1
-76.25°	11.5	11.6	11.7	11.8	11.8	11.9	11.9	11.9	11.8	11.7	11.6
-77.5°	10.0	10.2	10.2	10.3	10.4	10.4	10.4	10.3	10.3	10.2	10.1



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	8.5	8.7	8.8	8.9	9.0	9.0	9.0	9.0	9.0	8.9	8.8
-80°	7.4	7.4	7.4	7.5	7.6	7.7	7.7	7.7	7.7	7.6	7.5
-81.25°	6.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
-82.5°	5.3	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3	5.2
-83.75°	4.3	4.3	4.4	4.4	4.4	4.5	4.4	4.4	4.4	4.4	4.4
-85°	3.5	3.4	3.4	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5
-86.25°	3.0	3.0	3.0	2.9	2.9	2.8	2.8	2.8	2.7	2.7	2.7
-87.5°	2.6	2.5	2.5	2.5	2.4	2.4	2.4	2.3	2.3	2.3	2.2
-88.75°	2.1	2.1	2.1	2.0	2.0	2.0	1.9	1.9	1.9	1.8	1.8
-90°	3.0	3.1	3.1	3.1	3.1	3.2	3.3	3.4	3.5	3.5	3.6



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	1.4	1.4	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.1	1.1
88.75°	4.2	4.3	4.4	4.4	4.5	4.5	4.5	4.6	4.6	4.6	4.6
87.5°	4.7	4.8	5.0	5.1	5.1	5.1	5.2	5.2	5.2	5.3	5.3
86.25°	5.3	5.5	5.7	5.9	6.0	6.1	6.1	6.2	6.3	6.4	6.5
85°	6.7	7.0	7.2	7.5	7.6	7.7	7.8	7.8	7.9	8.0	8.1
83.75°	8.2	8.5	8.8	9.0	9.2	9.3	9.4	9.4	9.6	9.7	9.8
82.5°	9.7	10.1	10.5	10.8	11.1	11.3	11.4	11.6	11.8	12.0	12.2
81.25°	11.8	12.2	12.6	13.0	13.3	13.5	13.7	14.0	14.2	14.4	14.6
80°	14.0	14.4	14.8	15.2	15.5	15.8	16.0	16.4	16.7	17.0	17.3
78.75°	16.1	16.6	17.1	17.6	18.1	18.5	18.8	19.2	19.5	19.8	20.1
77.5°	18.7	19.3	19.9	20.4	20.8	21.2	21.6	22.0	22.3	22.7	23.0
76.25°	21.5	22.1	22.6	23.1	23.6	24.1	24.5	25.0	25.4	25.8	26.2
75°	24.2	24.8	25.4	26.1	26.7	27.2	27.7	28.1	28.6	29.0	29.4
73.75°	26.9	27.6	28.4	29.1	29.9	30.4	30.9	31.3	31.7	32.3	32.8
72.5°	29.7	30.5	31.3	32.2	33.1	33.7	34.2	34.7	35.1	35.7	36.3
71.25°	32.4	33.3	34.4	35.4	36.3	37.0	37.6	38.1	38.5	39.1	39.7
70°	35.5	36.5	37.6	38.7	39.6	40.4	41.0	41.5	42.0	42.7	43.4
68.75°	38.8	39.8	40.9	41.9	43.0	43.8	44.5	45.1	45.7	46.3	47.0
67.5°	42.0	43.0	44.2	45.3	46.4	47.4	48.1	48.8	49.3	49.9	50.7
66.25°	45.3	46.2	47.5	48.7	49.9	51.0	51.8	52.5	53.1	53.7	54.6
65°	48.6	49.6	50.8	52.1	53.4	54.6	55.5	56.2	56.9	57.6	58.4
63.75°	51.9	52.9	54.1	55.5	56.9	58.2	59.2	60.0	60.7	61.4	62.3
62.5°	55.3	56.3	57.5	59.0	60.4	61.8	62.9	63.7	64.5	65.3	66.2
61.25°	58.7	59.8	60.9	62.4	63.9	65.2	66.5	67.4	68.3	69.2	70.1
60°	62.1	63.3	64.4	65.9	67.4	68.8	70.0	71.1	72.1	73.1	74.1
58.75°	65.5	66.8	68.0	69.3	70.9	72.3	73.7	74.9	76.0	77.1	78.1
57.5°	68.9	70.3	71.6	72.8	74.4	75.9	77.4	78.7	79.9	81.0	81.9
56.25°	72.4	73.8	75.2	76.4	78.0	79.6	81.1	82.5	83.7	84.8	85.7
55°	75.8	77.4	78.8	80.1	81.6	83.2	84.7	86.2	87.5	88.6	89.6
53.75°	79.3	80.9	82.4	83.8	85.1	86.8	88.4	89.9	91.4	92.5	93.5
52.5°	82.7	84.4	86.0	87.4	88.8	90.4	92.0	93.6	95.1	96.3	97.4
51.25°	86.1	88.0	89.5	91.0	92.4	93.9	95.6	97.2	98.8	100.2	101.3
50°	89.5	91.4	93.1	94.6	96.1	97.4	99.1	100.8	102.5	104.0	105.2
48.75°	92.7	94.7	96.6	98.2	99.6	101.0	102.7	104.4	106.0	107.7	109.1
47.5°	95.9	98.0	100.0	101.6	103.1	104.6	106.1	107.8	109.6	111.3	112.8
46.25°	99.1	101.2	103.2	104.9	106.6	108.0	109.5	111.2	113.0	114.5	116.1
45°	102.3	104.2	106.3	108.3	109.8	111.3	112.9	114.4	116.0	117.6	119.3
43.75°	105.5	107.2	109.3	111.2	112.9	114.6	116.1	117.3	118.8	120.6	122.1
42.5°	108.8	110.3	112.2	114.2	116.0	117.6	119.0	120.3	121.6	123.2	124.8
41.25°	112.1	113.6	115.0	117.1	118.9	120.5	122.0	123.3	124.4	125.8	127.4
40°	114.9	116.8	118.2	120.0	121.7	123.4	124.9	126.1	127.2	128.3	129.8
38.75°	117.6	119.9	121.5	122.7	124.6	126.2	127.6	128.9	130.1	131.1	132.2
37.5°	120.2	122.6	124.6	125.9	127.4	128.9	130.3	131.7	132.7	133.7	134.7
36.25°	122.8	125.1	127.2	129.0	130.1	131.5	133.0	134.2	135.3	136.3	137.2
35°	125.2	127.4	129.6	131.6	132.8	134.1	135.4	136.6	137.7	138.7	139.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	127.4	129.7	131.9	133.7	135.4	136.6	137.7	138.9	140.0	140.9	141.8
32.5°	129.5	131.9	133.9	135.7	137.5	139.0	140.1	141.1	142.0	143.0	143.8
31.25°	131.6	133.9	135.8	137.7	139.3	141.1	142.5	143.1	144.0	144.9	145.5
30°	133.7	135.7	137.6	139.4	141.0	142.8	144.3	145.1	145.9	146.6	147.2
28.75°	135.4	137.4	139.4	141.0	142.6	144.2	145.5	146.9	147.6	148.2	148.8
27.5°	137.0	139.0	140.9	142.4	144.1	145.4	146.7	148.0	149.1	149.7	149.9
26.25°	138.6	140.6	142.2	143.7	145.2	146.5	147.9	148.9	150.0	150.9	150.9
25°	140.0	141.9	143.4	145.0	146.3	147.6	148.7	149.7	150.8	151.2	151.7
23.75°	141.3	143.0	144.5	146.0	147.2	148.5	149.4	150.4	151.0	151.4	151.9
22.5°	142.4	144.0	145.6	146.8	148.1	149.2	150.1	151.0	151.2	151.6	151.8
21.25°	143.3	144.8	146.4	147.6	148.8	149.8	150.6	151.2	151.4	151.6	151.6
20°	144.0	145.6	147.0	148.2	149.4	150.3	151.2	151.4	151.6	151.6	151.3
18.75°	144.8	146.3	147.5	148.7	149.7	150.7	151.4	151.6	151.8	151.5	151.2
17.5°	145.4	146.9	148.0	149.2	150.0	150.9	151.4	151.7	151.8	151.4	151.1
16.25°	145.7	147.2	148.4	149.4	150.2	151.0	151.3	151.6	151.5	151.2	150.9
15°	146.0	147.4	148.6	149.6	150.4	150.9	151.2	151.4	151.1	150.8	150.6
13.75°	146.3	147.5	148.7	149.6	150.4	150.8	151.1	151.1	150.8	150.4	150.2
12.5°	146.5	147.6	148.8	149.6	150.4	150.7	151.0	150.8	150.4	150.0	149.7
11.25°	146.6	147.7	148.8	149.5	150.3	150.5	150.8	150.5	150.1	149.7	149.3
10°	146.7	147.8	148.8	149.5	150.1	150.4	150.5	150.2	149.9	149.5	149.1
8.75°	146.8	148.0	148.9	149.6	150.1	150.3	150.3	150.0	149.6	149.3	148.9
7.5°	146.9	148.1	148.9	149.6	150.0	150.2	150.2	149.9	149.5	149.1	148.7
6.25°	147.0	148.1	149.0	149.7	150.0	150.2	150.1	149.8	149.5	149.1	148.7
5°	146.7	148.0	148.9	149.7	150.0	150.2	150.0	149.8	149.4	149.1	148.7
3.75°	146.1	147.4	148.3	149.1	149.4	149.8	149.6	149.5	149.3	149.0	148.7
2.5°	145.5	146.8	147.6	148.5	148.8	149.1	149.0	148.8	148.6	148.4	148.2
1.25°	144.9	146.2	147.0	147.8	148.2	148.5	148.3	148.2	148.0	147.8	147.6
0°	144.3	145.5	146.4	147.2	147.6	147.9	147.7	147.5	147.4	147.2	147.1
-1.25°	143.8	145.1	145.9	146.8	147.2	147.6	147.4	147.2	147.1	147.0	146.9
-2.5°	143.3	144.6	145.5	146.4	146.8	147.2	147.1	147.0	146.9	146.8	146.7
-3.75°	142.8	144.1	145.0	146.0	146.4	146.9	146.9	146.7	146.7	146.6	146.6
-5°	142.2	143.5	144.6	145.5	146.0	146.5	146.5	146.4	146.3	146.2	146.2
-6.25°	141.7	143.0	144.0	145.0	145.5	145.9	146.1	145.9	145.9	145.8	145.8
-7.5°	141.0	142.3	143.4	144.4	145.0	145.4	145.6	145.5	145.5	145.4	145.4
-8.75°	140.3	141.6	142.8	143.8	144.5	144.9	145.2	145.1	145.0	145.0	144.9
-10°	139.6	140.9	142.1	143.1	143.9	144.2	144.5	144.5	144.4	144.4	144.5
-11.25°	138.8	140.1	141.3	142.2	143.1	143.4	143.8	143.9	143.9	143.9	144.0
-12.5°	137.9	139.1	140.4	141.3	142.2	142.6	143.1	143.4	143.3	143.1	143.0
-13.75°	136.7	138.0	139.3	140.3	141.1	141.8	142.2	142.6	142.4	142.2	142.1
-15°	135.6	136.9	138.2	139.2	140.1	140.7	141.1	141.4	141.4	141.3	141.1
-16.25°	134.3	135.8	137.0	138.0	138.8	139.5	139.9	140.3	140.4	140.3	140.2
-17.5°	133.0	134.5	135.5	136.6	137.4	138.1	138.6	139.1	139.4	139.3	139.3
-18.75°	131.5	132.9	134.0	135.1	136.0	136.7	137.4	137.8	138.2	138.3	138.3
-20°	129.9	131.2	132.5	133.5	134.5	135.2	136.0	136.4	136.8	137.2	137.2
-21.25°	128.2	129.5	130.9	131.9	132.9	133.7	134.4	135.0	135.4	135.7	135.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	126.4	127.7	129.1	130.1	131.1	132.0	132.8	133.5	133.7	133.8	133.8
-23.75°	124.5	125.9	127.1	128.3	129.3	130.3	131.0	131.6	131.8	131.9	131.9
-25°	122.6	123.9	125.2	126.4	127.4	128.4	129.0	129.5	129.9	129.9	130.0
-26.25°	120.5	121.9	123.1	124.3	125.4	126.2	126.9	127.3	127.7	127.9	128.2
-27.5°	118.4	119.7	121.0	122.2	123.2	123.8	124.5	125.0	125.4	126.0	126.4
-28.75°	116.2	117.5	118.8	119.8	120.7	121.5	122.1	122.7	123.3	123.9	124.5
-30°	113.9	115.2	116.3	117.4	118.2	119.0	119.6	120.4	121.1	121.7	122.2
-31.25°	111.4	112.8	113.8	114.9	115.7	116.4	117.3	118.0	118.8	119.4	119.8
-32.5°	108.8	110.1	111.2	112.2	113.2	113.9	114.8	115.7	116.4	117.0	117.2
-33.75°	106.0	107.3	108.6	109.5	110.4	111.4	112.2	113.2	114.0	114.2	114.4
-35°	103.3	104.5	105.7	106.7	107.6	108.6	109.5	110.4	111.1	111.3	111.4
-36.25°	100.3	101.6	102.7	103.8	104.7	105.6	106.6	107.4	107.8	108.2	108.3
-37.5°	97.3	98.6	99.6	100.5	101.6	102.5	103.4	104.0	104.3	104.6	105.0
-38.75°	94.2	95.4	96.2	96.9	98.0	99.3	99.7	100.0	100.8	101.1	101.0
-40°	91.0	91.7	92.2	93.2	94.2	95.3	95.6	95.7	96.2	97.3	96.5
-41.25°	87.5	87.4	87.8	88.9	90.1	90.2	90.4	91.0	91.3	91.3	91.1
-42.5°	82.7	82.8	83.0	83.8	85.0	84.7	84.5	85.0	85.9	85.0	84.4
-43.75°	78.1	78.1	77.8	78.3	78.9	78.8	78.2	78.4	78.8	78.3	77.4
-45°	73.6	73.5	73.1	72.5	73.2	73.1	72.2	71.4	72.2	71.8	70.4
-46.25°	69.4	69.1	68.6	68.3	67.8	67.7	67.0	66.3	66.1	66.0	65.0
-47.5°	65.5	65.0	64.4	64.3	63.8	62.9	62.2	62.2	61.7	61.0	60.2
-48.75°	61.8	61.3	60.8	60.4	60.0	59.1	58.4	58.2	57.8	57.1	56.1
-50°	58.3	57.9	57.5	57.0	56.3	55.5	55.2	54.7	54.1	53.5	52.5
-51.25°	55.2	54.7	54.3	53.8	53.0	52.3	52.0	51.5	50.8	50.0	49.1
-52.5°	52.2	51.8	51.2	50.7	49.9	49.2	48.7	48.3	47.7	46.6	45.5
-53.75°	49.3	48.8	48.3	47.6	46.8	46.0	45.3	44.8	44.5	43.1	41.8
-55°	46.5	45.9	45.3	44.6	43.7	42.6	41.7	41.0	40.3	39.2	37.9
-56.25°	43.8	43.2	42.4	41.7	40.7	39.6	38.3	37.1	36.3	35.4	34.1
-57.5°	41.2	40.6	39.8	38.8	37.8	36.6	35.4	34.0	32.8	31.6	30.5
-58.75°	38.6	38.0	37.2	36.3	35.1	33.7	32.5	31.3	30.1	28.8	27.3
-60°	36.2	35.5	34.8	33.8	32.6	31.3	29.9	28.7	27.6	26.4	25.0
-61.25°	33.9	33.2	32.5	31.4	30.3	29.0	27.6	26.6	25.4	24.1	22.8
-62.5°	31.6	31.0	30.2	29.2	28.1	26.8	25.6	24.6	23.5	22.3	20.9
-63.75°	29.4	28.8	28.1	27.1	26.0	24.8	23.7	22.7	21.6	20.5	19.3
-65°	27.3	26.8	26.0	25.1	24.1	22.9	21.9	21.0	20.0	18.8	17.7
-66.25°	25.3	24.8	24.0	23.1	22.2	21.1	20.3	19.4	18.4	17.3	16.3
-67.5°	23.3	22.8	22.1	21.3	20.3	19.4	18.6	17.8	16.9	15.9	15.0
-68.75°	21.3	20.8	20.2	19.4	18.6	17.8	17.1	16.3	15.5	14.6	13.7
-70°	19.4	18.9	18.4	17.7	16.9	16.2	15.6	14.9	14.1	13.3	12.5
-71.25°	17.6	17.1	16.6	16.1	15.4	14.8	14.2	13.6	12.8	12.1	11.3
-72.5°	16.0	15.5	15.0	14.5	13.9	13.4	12.9	12.3	11.7	11.0	10.3
-73.75°	14.4	14.0	13.5	13.0	12.5	12.1	11.6	11.1	10.5	9.9	9.2
-75°	12.8	12.5	12.1	11.6	11.1	10.8	10.3	9.9	9.4	8.8	8.3
-76.25°	11.4	11.1	10.7	10.3	9.8	9.5	9.1	8.7	8.2	7.8	7.3
-77.5°	9.9	9.7	9.3	9.0	8.6	8.3	8.0	7.6	7.2	6.8	6.4



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	8.6	8.3	8.0	7.7	7.5	7.2	7.0	6.7	6.3	6.0	5.6
-80°	7.4	7.1	6.9	6.6	6.4	6.2	6.0	5.8	5.5	5.1	4.8
-81.25°	6.2	6.0	5.8	5.6	5.4	5.3	5.1	4.9	4.7	4.4	4.1
-82.5°	5.1	4.9	4.8	4.6	4.5	4.3	4.2	4.1	3.9	3.6	3.4
-83.75°	4.2	4.1	3.9	3.7	3.6	3.5	3.4	3.3	3.1	3.0	2.8
-85°	3.4	3.3	3.1	3.0	2.9	2.8	2.8	2.7	2.5	2.4	2.3
-86.25°	2.5	2.4	2.3	2.2	2.2	2.1	2.1	2.0	2.0	1.9	1.8
-87.5°	2.2	2.1	2.0	1.9	1.8	1.8	1.7	1.7	1.6	1.5	1.4
-88.75°	1.8	1.7	1.6	1.6	1.5	1.5	1.5	1.4	1.4	1.3	1.2
-90°	3.7	3.7	3.8	3.8	3.8	3.9	3.9	3.9	3.9	4.0	4.0



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	1.0	1.0	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.6
88.75°	4.7	4.7	4.8	4.9	4.9	4.9	4.9	4.9	4.9	5.0	5.0
87.5°	5.3	5.4	5.5	5.6	5.7	5.7	5.6	5.6	5.6	5.6	5.7
86.25°	6.5	6.7	6.8	7.0	7.1	7.1	7.1	7.1	7.1	7.2	7.3
85°	8.2	8.4	8.5	8.7	8.8	8.8	8.9	8.9	8.9	8.9	9.0
83.75°	10.0	10.2	10.4	10.6	10.8	10.9	11.0	11.0	11.0	11.2	11.3
82.5°	12.4	12.6	12.9	13.1	13.3	13.4	13.4	13.5	13.5	13.6	13.8
81.25°	14.8	15.1	15.3	15.5	15.8	15.9	16.0	16.1	16.1	16.3	16.5
80°	17.5	17.8	18.1	18.4	18.7	18.9	19.0	19.0	19.1	19.3	19.5
78.75°	20.4	20.7	21.1	21.4	21.7	21.9	21.9	22.0	22.1	22.3	22.6
77.5°	23.4	23.7	24.1	24.5	24.9	25.1	25.3	25.4	25.5	25.7	26.0
76.25°	26.6	27.0	27.4	27.8	28.2	28.5	28.6	28.8	28.9	29.1	29.4
75°	29.8	30.2	30.7	31.2	31.6	32.0	32.2	32.4	32.6	32.8	33.1
73.75°	33.3	33.8	34.3	34.8	35.2	35.6	35.9	36.0	36.2	36.4	36.8
72.5°	36.8	37.3	37.9	38.4	38.9	39.4	39.6	39.8	40.0	40.2	40.6
71.25°	40.4	40.9	41.6	42.1	42.7	43.2	43.5	43.7	43.9	44.1	44.5
70°	44.0	44.7	45.3	45.9	46.5	47.0	47.3	47.7	47.9	48.2	48.6
68.75°	47.7	48.4	49.1	49.7	50.4	50.9	51.4	51.8	52.1	52.5	52.8
67.5°	51.5	52.3	53.0	53.7	54.3	54.9	55.4	55.9	56.3	56.7	57.1
66.25°	55.4	56.1	56.8	57.6	58.3	59.0	59.6	60.1	60.6	61.0	61.4
65°	59.3	60.1	61.0	61.8	62.5	63.2	63.7	64.3	64.8	65.3	65.7
63.75°	63.3	64.2	65.2	66.0	66.7	67.4	68.0	68.6	69.1	69.6	70.1
62.5°	67.3	68.3	69.3	70.2	70.9	71.6	72.2	72.8	73.4	74.0	74.5
61.25°	71.2	72.3	73.4	74.4	75.1	75.8	76.5	77.1	77.8	78.4	78.9
60°	75.2	76.4	77.5	78.5	79.3	80.1	80.8	81.5	82.1	82.8	83.3
58.75°	79.1	80.3	81.5	82.6	83.5	84.3	85.1	85.7	86.4	87.1	87.7
57.5°	82.9	84.1	85.4	86.6	87.7	88.5	89.2	89.9	90.6	91.3	92.0
56.25°	86.6	87.9	89.3	90.6	91.7	92.6	93.4	94.1	94.8	95.5	96.2
55°	90.5	91.7	93.1	94.5	95.7	96.7	97.5	98.2	98.8	99.6	100.4
53.75°	94.4	95.5	97.0	98.4	99.7	100.7	101.5	102.3	102.9	103.7	104.5
52.5°	98.4	99.3	100.8	102.3	103.6	104.8	105.6	106.3	107.0	107.7	108.6
51.25°	102.4	103.4	104.7	106.1	107.5	108.8	109.6	110.4	111.0	111.8	112.6
50°	106.3	107.4	108.4	109.9	111.2	112.6	113.6	114.3	114.9	115.5	116.4
48.75°	110.2	111.2	112.1	113.5	115.0	116.2	117.3	118.1	118.7	119.3	120.2
47.5°	113.8	114.9	115.9	117.0	118.4	119.7	120.9	121.8	122.4	122.9	123.6
46.25°	117.4	118.5	119.4	120.3	121.7	123.0	124.2	125.1	125.8	126.4	127.1
45°	120.8	121.7	122.7	123.7	124.8	125.9	127.2	128.4	129.1	129.7	130.1
43.75°	123.6	124.7	125.8	126.6	127.4	128.6	130.0	131.2	131.9	132.4	132.9
42.5°	126.3	127.6	128.5	129.3	130.1	131.2	132.4	133.5	134.5	135.1	135.5
41.25°	128.8	130.1	131.1	132.0	132.7	133.4	134.7	135.9	136.8	137.4	137.8
40°	131.2	132.5	133.6	134.4	135.2	135.9	136.9	138.0	138.9	139.7	140.1
38.75°	133.7	134.9	136.0	136.9	137.7	138.3	139.0	140.0	141.1	141.8	142.0
37.5°	135.9	137.1	138.3	139.3	139.9	140.6	141.2	141.9	142.7	143.5	144.0
36.25°	138.1	139.3	140.4	141.3	142.2	142.9	143.1	143.4	144.3	145.1	145.5
35°	140.4	141.3	142.3	143.3	144.2	144.5	144.8	145.1	145.6	146.0	146.4



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	142.5	143.2	144.1	145.0	145.5	146.0	146.3	146.4	146.4	146.8	147.2
32.5°	144.4	145.1	145.7	146.2	146.8	147.3	147.3	147.3	147.4	147.6	147.9
31.25°	146.2	146.7	147.0	147.4	147.9	148.0	148.1	148.1	148.1	148.2	148.5
30°	147.7	147.9	148.3	148.5	148.6	148.6	148.7	148.7	148.7	148.8	148.8
28.75°	148.9	149.1	149.3	149.2	149.1	149.1	149.1	149.1	149.2	149.1	149.1
27.5°	150.0	150.2	149.9	149.8	149.6	149.5	149.5	149.5	149.4	149.3	149.3
26.25°	151.0	150.9	150.4	150.2	150.0	149.8	149.8	149.7	149.6	149.5	149.2
25°	151.8	151.5	151.0	150.5	150.2	150.0	149.9	149.9	149.7	149.4	149.1
23.75°	152.0	151.8	151.5	151.0	150.3	150.1	150.0	149.9	149.7	149.3	148.9
22.5°	151.8	151.8	151.7	151.5	150.8	150.1	149.9	149.7	149.5	149.2	148.5
21.25°	151.6	151.5	151.6	151.4	151.2	150.5	149.7	149.4	149.2	148.7	148.2
20°	151.3	151.2	151.2	151.1	150.9	150.7	150.0	149.2	148.6	148.1	147.6
18.75°	151.0	150.9	150.8	150.6	150.5	150.2	150.1	149.2	148.1	147.4	146.8
17.5°	150.8	150.6	150.3	150.1	149.9	149.6	149.3	149.0	148.2	146.9	146.0
16.25°	150.6	150.3	150.0	149.6	149.4	149.1	148.6	148.1	147.6	146.9	145.6
15°	150.4	150.0	149.6	149.3	148.9	148.5	147.9	147.4	146.7	146.0	145.8
13.75°	149.9	149.7	149.3	149.0	148.6	147.9	147.2	146.6	145.9	145.2	144.7
12.5°	149.5	149.2	148.9	148.6	148.2	147.5	146.8	146.0	145.2	144.6	144.0
11.25°	149.0	148.7	148.4	148.1	147.6	147.0	146.3	145.5	144.7	144.1	143.4
10°	148.7	148.3	147.9	147.6	147.0	146.4	145.7	144.9	144.3	143.7	143.1
8.75°	148.5	148.1	147.7	147.3	146.5	145.7	145.0	144.2	143.7	143.2	142.7
7.5°	148.3	148.0	147.6	147.1	146.3	145.4	144.5	143.6	143.0	142.5	142.0
6.25°	148.3	147.9	147.5	146.9	146.1	145.3	144.3	143.5	142.8	142.0	141.4
5°	148.3	147.9	147.5	146.9	146.1	145.2	144.2	143.3	142.7	141.9	141.2
3.75°	148.3	147.9	147.5	146.9	146.2	145.2	144.2	143.4	142.6	141.9	141.1
2.5°	147.9	147.6	147.3	146.7	146.1	145.1	144.1	143.4	142.7	141.9	141.1
1.25°	147.4	147.1	146.8	146.2	145.6	144.6	143.7	142.9	142.2	141.5	140.8
0°	146.9	146.6	146.3	145.7	145.1	144.2	143.2	142.4	141.6	141.0	140.4
-1.25°	146.8	146.5	146.2	145.6	145.0	144.1	143.2	142.4	141.7	141.1	140.5
-2.5°	146.7	146.4	146.2	145.6	145.0	144.1	143.3	142.5	141.7	141.0	140.3
-3.75°	146.5	146.2	145.9	145.3	144.7	143.7	142.8	141.9	141.1	140.3	139.5
-5°	146.1	145.8	145.5	144.9	144.2	143.3	142.3	141.3	140.6	139.8	139.1
-6.25°	145.7	145.4	145.1	144.5	143.9	143.0	142.0	141.1	140.4	139.6	139.0
-7.5°	145.2	145.0	144.7	144.3	143.6	142.9	141.9	141.0	140.0	139.1	138.2
-8.75°	144.8	144.6	144.3	144.1	143.4	142.6	141.5	140.3	139.3	138.4	137.4
-10°	144.3	144.1	143.9	143.6	142.8	141.9	140.8	139.7	138.7	137.9	137.0
-11.25°	143.7	143.4	143.1	142.7	142.0	141.2	140.3	139.3	138.4	137.5	136.6
-12.5°	142.8	142.6	142.3	141.9	141.4	140.7	140.1	139.1	138.1	136.8	135.6
-13.75°	141.9	141.7	141.6	141.2	140.9	140.3	139.7	138.6	137.2	135.8	134.6
-15°	140.9	140.9	140.8	140.6	140.2	139.7	138.7	137.6	136.2	135.0	134.3
-16.25°	140.1	140.1	140.0	139.9	139.2	138.5	137.5	136.4	135.6	134.8	134.1
-17.5°	139.2	139.2	139.0	138.5	137.9	137.1	136.4	135.7	135.2	134.5	133.5
-18.75°	138.3	138.0	137.5	137.0	136.5	135.9	135.6	135.2	134.7	133.8	132.4
-20°	136.8	136.4	136.0	135.5	135.1	135.0	134.8	134.6	133.6	132.5	131.3
-21.25°	135.2	134.7	134.3	134.2	134.1	134.0	133.9	133.1	132.2	131.1	130.1



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	133.4	133.0	132.9	132.9	132.9	132.9	132.3	131.4	130.6	129.8	128.9
-23.75°	131.7	131.6	131.6	131.6	131.6	131.0	130.4	129.7	129.0	128.3	127.7
-25°	130.2	130.1	130.1	130.1	129.7	129.1	128.5	127.9	127.3	126.7	125.9
-26.25°	128.6	128.6	128.6	128.2	127.7	127.1	126.6	126.0	125.5	124.9	123.8
-27.5°	126.7	127.1	126.7	126.2	125.7	125.1	124.6	124.0	123.5	122.6	121.6
-28.75°	124.7	124.9	124.7	124.2	123.7	123.1	122.5	122.0	121.2	120.3	119.3
-30°	122.6	122.5	122.3	122.1	121.6	121.0	120.4	119.7	118.8	117.9	116.9
-31.25°	120.0	120.1	119.9	119.7	119.4	118.8	118.2	117.4	116.4	115.5	114.6
-32.5°	117.3	117.4	117.4	117.1	116.9	116.6	115.8	114.9	114.0	113.0	112.1
-33.75°	114.6	114.6	114.6	114.5	114.2	113.8	113.3	112.4	111.5	110.5	109.6
-35°	111.7	111.7	111.5	111.5	111.4	110.7	110.1	109.5	108.8	107.7	106.7
-36.25°	108.4	108.4	108.3	108.1	107.9	107.5	106.7	106.0	105.3	104.6	103.6
-37.5°	105.0	104.8	104.8	104.7	104.1	103.6	103.1	102.4	101.6	100.8	100.2
-38.75°	101.1	101.2	101.0	100.4	100.2	99.5	98.9	98.1	97.8	96.9	96.2
-40°	96.2	96.6	96.9	95.4	94.7	94.8	94.2	93.1	92.4	92.0	92.1
-41.25°	90.7	90.8	90.3	89.9	88.7	88.0	87.4	87.5	86.7	85.4	84.8
-42.5°	84.3	84.0	82.8	81.9	81.4	80.3	79.1	78.5	78.5	78.0	76.6
-43.75°	76.9	76.3	74.8	73.6	72.8	72.1	70.3	68.8	69.1	69.2	68.3
-45°	69.4	69.1	67.9	65.7	64.7	64.5	63.3	61.2	60.8	61.0	60.8
-46.25°	63.6	62.4	61.6	59.8	59.1	58.0	57.1	56.3	56.1	55.4	54.6
-47.5°	59.2	57.9	56.3	55.1	54.5	53.7	52.4	51.8	51.5	51.1	50.6
-48.75°	55.0	53.8	52.3	51.3	50.4	49.5	48.7	48.4	47.9	47.3	46.7
-50°	51.4	50.0	48.7	47.9	46.9	45.9	45.3	45.0	44.6	44.0	43.4
-51.25°	48.0	46.6	45.4	44.5	43.5	42.5	42.1	41.8	41.4	40.8	40.2
-52.5°	44.6	43.4	42.1	41.0	39.9	39.2	39.0	38.6	38.1	37.4	36.6
-53.75°	40.6	39.6	38.6	37.4	36.2	35.2	34.8	34.6	34.7	33.7	32.6
-55°	36.5	35.3	34.2	33.1	32.1	31.0	30.1	29.4	29.0	28.6	27.9
-56.25°	32.6	31.0	29.7	28.4	27.4	26.7	25.7	24.3	23.4	23.0	22.5
-57.5°	29.1	27.7	26.0	24.0	22.9	22.6	22.0	21.0	20.0	18.9	17.7
-58.75°	25.8	24.6	23.1	21.3	20.3	19.5	18.7	17.9	17.2	16.2	15.2
-60°	23.5	22.0	20.4	18.8	18.2	17.5	16.7	15.8	14.9	13.9	12.8
-61.25°	21.5	20.0	18.5	17.0	16.3	15.5	14.8	14.0	13.1	12.1	11.1
-62.5°	19.6	18.1	16.6	15.5	14.9	14.1	13.4	12.5	11.5	10.4	9.4
-63.75°	18.0	16.6	15.2	14.2	13.5	12.8	12.1	11.3	10.5	9.5	8.5
-65°	16.6	15.3	13.9	13.2	12.5	11.8	11.0	10.3	9.5	8.7	7.9
-66.25°	15.2	14.0	12.9	12.3	11.6	10.9	10.2	9.5	8.8	8.1	7.2
-67.5°	13.9	12.8	11.9	11.3	10.7	10.1	9.4	8.8	8.1	7.4	6.6
-68.75°	12.7	11.7	10.9	10.4	9.9	9.3	8.7	8.1	7.5	6.8	6.1
-70°	11.6	10.6	10.0	9.5	9.0	8.5	8.0	7.4	6.9	6.2	5.6
-71.25°	10.5	9.7	9.2	8.7	8.3	7.8	7.3	6.8	6.3	5.7	5.1
-72.5°	9.5	8.7	8.3	7.9	7.5	7.0	6.6	6.2	5.7	5.2	4.6
-73.75°	8.5	7.9	7.5	7.2	6.8	6.4	6.0	5.6	5.1	4.7	4.2
-75°	7.6	7.0	6.7	6.4	6.1	5.7	5.4	5.0	4.6	4.2	3.7
-76.25°	6.8	6.3	6.0	5.7	5.4	5.1	4.8	4.4	4.1	3.7	3.3
-77.5°	5.9	5.6	5.3	5.1	4.8	4.5	4.2	3.9	3.6	3.3	2.9



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	5.2	4.9	4.7	4.4	4.2	3.9	3.7	3.4	3.2	2.9	2.6
-80°	4.4	4.2	4.0	3.8	3.6	3.4	3.2	3.0	2.8	2.5	2.3
-81.25°	3.7	3.5	3.4	3.2	3.1	2.9	2.7	2.6	2.4	2.2	1.9
-82.5°	3.2	3.0	2.9	2.8	2.6	2.5	2.3	2.2	2.0	1.9	1.7
-83.75°	2.6	2.5	2.4	2.3	2.2	2.1	1.9	1.8	1.7	1.6	1.4
-85°	2.1	2.0	2.0	1.9	1.8	1.7	1.6	1.5	1.4	1.3	1.2
-86.25°	1.7	1.6	1.6	1.5	1.4	1.4	1.3	1.2	1.1	1.0	0.9
-87.5°	1.3	1.3	1.2	1.2	1.1	1.1	1.0	0.9	0.9	0.8	0.7
-88.75°	1.2	1.1	1.1	1.0	1.0	0.9	0.9	0.8	0.7	0.7	0.6
-90°	4.0	4.1	4.1	4.2	4.2	4.2	4.3	4.3	4.3	4.3	4.4



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.2	0.2
88.75°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
87.5°	5.7	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.9	5.9
86.25°	7.3	7.4	7.4	7.4	7.5	7.5	7.5	7.6	7.6	7.7	7.7
85°	9.1	9.2	9.2	9.2	9.2	9.2	9.3	9.4	9.4	9.5	9.5
83.75°	11.4	11.5	11.5	11.6	11.6	11.7	11.7	11.8	11.9	12.0	12.0
82.5°	13.9	14.0	14.1	14.1	14.1	14.2	14.3	14.3	14.4	14.5	14.5
81.25°	16.7	16.9	17.0	17.0	17.0	17.1	17.2	17.3	17.3	17.4	17.5
80°	19.7	19.9	20.0	20.0	20.1	20.1	20.2	20.3	20.4	20.4	20.5
78.75°	22.9	23.1	23.2	23.3	23.3	23.4	23.5	23.6	23.7	23.8	23.9
77.5°	26.2	26.4	26.5	26.6	26.7	26.8	26.9	27.1	27.2	27.3	27.4
76.25°	29.7	29.9	30.1	30.2	30.3	30.4	30.5	30.7	30.8	31.0	31.1
75°	33.4	33.8	34.0	34.1	34.1	34.1	34.2	34.4	34.6	34.7	34.8
73.75°	37.2	37.6	37.8	37.9	37.9	37.9	38.0	38.2	38.3	38.5	38.6
72.5°	41.0	41.3	41.6	41.7	41.7	41.8	41.9	42.0	42.1	42.2	42.4
71.25°	44.8	45.1	45.4	45.6	45.7	45.8	46.0	46.2	46.3	46.5	46.7
70°	49.0	49.3	49.5	49.7	49.9	50.0	50.2	50.4	50.6	50.8	51.0
68.75°	53.2	53.4	53.7	53.9	54.1	54.3	54.5	54.7	54.9	55.0	55.2
67.5°	57.5	57.8	58.0	58.3	58.5	58.6	58.8	59.0	59.1	59.2	59.4
66.25°	61.8	62.1	62.4	62.7	62.9	63.0	63.2	63.4	63.6	63.8	64.0
65°	66.1	66.5	66.9	67.1	67.4	67.6	67.7	68.0	68.3	68.5	68.8
63.75°	70.5	71.0	71.3	71.6	71.9	72.1	72.2	72.6	72.9	73.1	73.3
62.5°	75.0	75.4	75.8	76.2	76.4	76.7	76.8	77.1	77.4	77.6	77.8
61.25°	79.4	79.9	80.3	80.7	81.0	81.2	81.4	81.7	82.1	82.4	82.6
60°	83.9	84.4	84.8	85.2	85.6	85.8	86.1	86.4	86.9	87.3	87.7
58.75°	88.3	88.8	89.3	89.8	90.1	90.4	90.7	91.0	91.5	92.0	92.5
57.5°	92.6	93.2	93.7	94.2	94.6	94.9	95.2	95.5	96.1	96.6	97.1
56.25°	96.8	97.4	98.0	98.5	98.9	99.3	99.7	99.9	100.5	101.0	101.4
55°	101.1	101.7	102.3	102.8	103.2	103.6	104.0	104.2	104.7	105.1	105.4
53.75°	105.2	105.9	106.5	107.0	107.5	107.9	108.3	108.5	108.9	109.3	109.6
52.5°	109.3	110.0	110.6	111.2	111.7	112.1	112.5	112.7	113.1	113.4	113.7
51.25°	113.3	114.0	114.7	115.3	115.9	116.3	116.7	116.9	117.2	117.5	117.8
50°	117.2	118.0	118.8	119.3	119.8	120.2	120.6	120.8	121.1	121.5	121.8
48.75°	121.0	121.8	122.4	123.0	123.6	124.0	124.4	124.7	124.9	125.3	125.5
47.5°	124.5	125.3	126.1	126.7	127.2	127.6	128.0	128.2	128.4	128.8	129.1
46.25°	128.0	128.7	129.4	130.0	130.6	131.1	131.5	131.8	131.9	132.1	132.4
45°	130.8	131.7	132.6	133.3	133.7	134.1	134.3	134.5	134.7	135.0	135.3
43.75°	133.6	134.5	135.2	135.8	136.2	136.6	137.0	137.2	137.4	137.5	137.7
42.5°	135.9	136.7	137.4	138.1	138.6	138.8	139.0	139.1	139.2	139.2	139.5
41.25°	138.2	138.8	139.4	140.0	140.3	140.6	140.7	140.9	140.9	140.9	141.1
40°	140.3	140.5	141.1	141.7	142.1	142.3	142.3	142.3	142.3	142.2	142.4
38.75°	142.2	142.2	142.7	143.2	143.6	143.6	143.6	143.5	143.5	143.5	143.5
37.5°	144.0	143.8	143.8	144.2	144.6	144.8	144.7	144.6	144.5	144.5	144.5
36.25°	145.3	145.0	144.8	145.2	145.5	145.7	145.6	145.5	145.5	145.4	145.4
35°	146.5	146.2	145.8	145.9	146.3	146.7	146.5	146.3	146.2	146.2	146.1



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	147.5	147.2	146.9	146.7	146.9	147.2	147.2	147.1	147.0	146.9	146.7
32.5°	148.2	148.2	147.7	147.2	147.3	147.6	147.8	147.6	147.3	147.2	147.0
31.25°	148.7	148.9	148.4	147.9	147.6	147.8	148.0	147.8	147.6	147.4	147.2
30°	149.0	149.1	149.0	148.4	147.7	147.8	148.0	147.9	147.5	147.1	146.9
28.75°	149.2	149.2	149.3	148.7	148.0	147.5	147.5	147.5	147.1	146.7	146.5
27.5°	149.1	149.2	149.2	148.9	148.0	147.1	147.0	147.0	146.6	146.1	145.8
26.25°	149.1	149.0	148.8	148.6	147.8	146.9	146.2	146.1	145.9	145.4	145.0
25°	148.9	148.6	148.3	148.0	147.5	146.4	145.3	145.2	145.1	144.8	144.4
23.75°	148.4	148.1	147.7	147.2	146.8	146.0	144.9	144.3	144.3	144.1	143.8
22.5°	147.9	147.4	146.9	146.4	146.0	145.7	144.7	143.6	143.5	143.6	143.3
21.25°	147.5	146.6	146.0	145.6	145.3	145.0	144.5	143.4	142.8	143.0	142.9
20°	146.9	146.0	145.2	144.9	144.6	144.4	144.1	143.2	142.2	142.3	142.3
18.75°	146.2	145.5	144.8	144.1	143.9	143.7	143.4	143.0	142.0	141.4	141.6
17.5°	145.4	145.1	144.5	143.7	143.2	143.0	142.8	142.5	141.8	140.7	140.7
16.25°	144.8	144.4	144.2	143.6	142.8	142.2	142.0	141.8	141.4	140.3	139.6
15°	144.7	143.7	143.5	143.3	142.6	141.6	141.1	141.0	140.6	140.0	138.8
13.75°	144.6	143.9	142.7	142.5	142.2	141.4	140.3	139.8	139.7	139.4	138.6
12.5°	143.5	143.3	143.1	141.8	141.2	140.9	140.1	138.9	138.7	138.7	138.4
11.25°	143.0	142.6	142.0	142.1	140.9	139.8	139.5	139.0	137.8	137.7	137.8
10°	142.6	142.1	141.4	140.7	140.3	139.7	138.3	138.4	138.0	136.9	137.0
8.75°	142.2	141.6	140.9	140.1	139.2	138.4	138.8	137.4	137.3	137.4	136.0
7.5°	141.6	141.1	140.5	139.6	138.7	138.0	137.3	137.0	137.0	136.3	136.6
6.25°	140.8	140.2	139.7	139.0	138.2	137.5	137.0	136.5	135.9	136.4	135.0
5°	140.4	139.7	138.8	137.9	137.2	136.7	136.4	136.1	135.7	135.0	134.2
3.75°	140.3	139.4	138.5	137.6	136.7	135.9	135.3	135.0	134.8	134.6	133.9
2.5°	140.3	139.4	138.4	137.4	136.6	135.7	135.2	134.7	134.0	133.3	132.6
1.25°	140.0	139.2	138.2	137.2	136.4	135.6	135.1	134.5	133.9	133.2	132.3
0°	139.6	138.7	137.6	136.5	135.8	135.1	134.6	134.0	133.4	132.8	132.0
-1.25°	139.7	138.9	137.9	136.9	136.1	135.3	134.8	134.2	133.4	132.6	131.6
-2.5°	139.4	138.5	137.3	136.1	135.1	134.1	133.4	132.9	132.4	131.9	131.1
-3.75°	138.5	137.5	136.5	135.5	134.7	133.9	133.3	132.5	131.6	130.6	129.9
-5°	138.3	137.5	136.6	135.5	134.2	133.0	131.9	131.4	130.8	130.0	129.1
-6.25°	138.1	137.0	135.8	134.4	133.2	132.3	131.5	130.8	129.8	129.4	129.3
-7.5°	137.2	136.1	135.1	134.1	133.0	131.9	130.6	129.7	129.6	129.1	127.9
-8.75°	136.6	135.8	134.9	133.7	132.2	130.8	130.2	129.9	128.9	127.9	127.7
-10°	136.3	135.3	134.1	132.7	131.6	130.8	130.2	129.0	127.9	127.6	126.4
-11.25°	135.4	134.3	133.1	132.4	131.8	130.7	129.4	128.4	127.7	126.3	125.2
-12.5°	134.4	133.5	133.1	132.5	131.3	129.9	128.9	128.1	126.7	125.3	124.3
-13.75°	133.8	133.3	132.9	131.6	130.3	129.4	128.6	127.2	125.5	124.4	123.6
-15°	133.7	132.9	131.8	130.6	129.6	128.9	127.7	126.1	124.8	123.6	122.9
-16.25°	133.2	131.9	130.7	129.8	129.0	127.9	126.4	125.2	124.0	123.1	122.5
-17.5°	132.1	130.9	129.9	129.0	128.0	126.6	125.2	124.1	123.2	122.5	122.1
-18.75°	131.0	130.0	129.0	128.0	126.6	125.2	124.1	123.0	122.3	121.7	121.5
-20°	130.1	129.1	128.1	126.6	125.2	124.0	122.8	121.9	121.3	121.0	120.5
-21.25°	129.2	128.2	126.7	125.2	123.8	122.6	121.6	120.8	120.2	119.9	119.4



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	128.1	126.8	125.3	123.8	122.5	121.2	120.4	119.5	119.2	118.8	117.9
-23.75°	126.5	125.2	123.9	122.5	121.1	120.0	119.1	118.4	117.9	117.3	116.5
-25°	124.7	123.4	122.2	121.0	119.7	118.7	117.8	117.2	116.7	115.9	115.0
-26.25°	122.6	121.5	120.3	119.1	118.3	117.5	116.7	116.0	115.3	114.4	113.8
-27.5°	120.5	119.4	118.4	117.4	116.6	115.8	115.3	114.8	113.9	113.0	112.7
-28.75°	118.3	117.3	116.2	115.5	114.8	114.2	113.7	113.1	112.3	111.5	111.4
-30°	116.0	115.0	114.2	113.5	112.8	112.4	112.0	111.4	110.6	109.9	109.9
-31.25°	113.6	112.6	112.0	111.4	110.8	110.4	110.0	109.3	108.6	108.3	108.2
-32.5°	111.1	110.4	109.8	109.1	108.7	108.3	107.9	107.2	106.5	106.3	106.3
-33.75°	108.5	107.9	107.3	106.9	106.5	106.1	105.5	104.9	104.3	104.3	104.2
-35°	106.0	105.3	104.6	104.2	104.0	103.8	103.1	102.3	101.8	101.6	101.5
-36.25°	103.0	102.3	101.8	101.4	101.0	100.6	100.0	99.3	99.1	98.9	98.6
-37.5°	99.7	99.1	98.5	98.2	97.8	97.4	96.7	95.9	95.8	95.5	95.2
-38.75°	95.7	95.2	95.1	94.8	94.3	93.6	92.9	92.4	92.3	92.1	91.6
-40°	91.3	90.6	90.1	90.0	89.9	89.5	88.8	88.2	87.8	87.5	86.9
-41.25°	84.9	85.4	84.6	83.9	82.8	81.8	81.4	81.9	82.4	82.1	81.6
-42.5°	75.9	76.1	76.3	76.5	74.9	72.9	71.4	71.4	71.4	71.5	71.5
-43.75°	67.1	66.6	66.6	66.4	65.5	64.0	62.3	61.2	60.1	60.1	60.5
-45°	60.5	59.8	58.5	57.1	56.6	55.8	55.2	54.6	53.7	53.1	52.7
-46.25°	54.3	54.1	53.4	52.3	51.1	49.7	49.0	48.5	48.0	47.9	47.7
-47.5°	50.1	49.5	48.8	47.7	46.6	45.3	44.9	44.3	43.7	43.5	43.3
-48.75°	46.3	45.7	44.9	43.8	42.6	41.4	40.9	40.3	39.7	39.6	39.4
-50°	42.8	42.1	41.1	40.1	39.0	38.1	37.5	36.9	36.3	36.1	35.8
-51.25°	39.5	38.8	37.7	36.6	35.5	34.7	34.2	33.6	33.1	32.9	32.6
-52.5°	35.9	35.3	34.3	33.2	32.1	31.3	30.6	29.9	29.5	29.3	29.0
-53.75°	31.7	30.5	29.3	28.3	27.6	27.4	27.0	26.1	25.6	25.2	24.7
-55°	27.1	25.5	23.7	22.1	21.0	20.8	20.5	20.1	20.1	20.0	19.8
-56.25°	21.8	20.4	18.7	16.7	15.2	14.3	13.9	13.5	13.7	13.8	13.7
-57.5°	16.5	15.6	14.4	12.9	12.0	11.4	10.6	9.9	9.6	9.3	8.9
-58.75°	14.0	12.7	11.3	9.8	9.1	8.5	8.0	7.5	7.2	6.9	6.6
-60°	11.7	10.5	9.2	7.9	7.3	6.8	6.1	5.6	5.3	4.9	4.5
-61.25°	10.0	8.8	7.5	6.2	5.6	5.1	4.6	4.1	3.8	3.4	3.0
-62.5°	8.5	7.4	6.2	5.2	4.7	4.1	3.5	3.1	2.7	2.3	1.9
-63.75°	7.5	6.3	5.2	4.3	3.8	3.3	2.8	2.4	2.1	1.8	1.4
-65°	6.9	5.8	4.8	4.0	3.5	2.9	2.4	2.0	1.7	1.4	1.1
-66.25°	6.3	5.3	4.4	3.7	3.2	2.7	2.2	1.9	1.6	1.3	1.1
-67.5°	5.8	4.9	4.0	3.5	3.0	2.5	2.0	1.8	1.5	1.2	1.0
-68.75°	5.3	4.5	3.7	3.3	2.8	2.4	2.0	1.7	1.4	1.1	0.9
-70°	4.8	4.1	3.4	3.0	2.6	2.2	1.8	1.6	1.3	1.0	0.8
-71.25°	4.4	3.7	3.1	2.7	2.4	2.0	1.7	1.4	1.2	0.9	0.8
-72.5°	4.0	3.4	2.9	2.5	2.2	1.8	1.5	1.3	1.1	0.9	0.7
-73.75°	3.7	3.2	2.7	2.3	2.0	1.6	1.4	1.2	1.0	0.8	0.7
-75°	3.3	2.8	2.4	2.1	1.8	1.5	1.3	1.1	0.9	0.7	0.6
-76.25°	2.9	2.5	2.2	1.9	1.7	1.4	1.2	1.0	0.9	0.7	0.6
-77.5°	2.6	2.2	1.9	1.7	1.5	1.3	1.1	1.0	0.8	0.6	0.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	2.3	2.0	1.8	1.6	1.4	1.2	1.0	0.9	0.7	0.6	0.5
-80°	2.0	1.7	1.5	1.4	1.2	1.0	0.9	0.8	0.6	0.5	0.4
-81.25°	1.7	1.5	1.3	1.2	1.0	0.9	0.8	0.7	0.6	0.5	0.4
-82.5°	1.5	1.3	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.4
-83.75°	1.3	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.5	0.4	0.4
-85°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.5	0.4	0.4	0.3
-86.25°	0.9	0.8	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.3
-87.5°	0.7	0.6	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.2
-88.75°	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.2	0.2
-90°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
88.75°	5.1	5.1	5.1	5.1	5.1	5.1	5.0	5.1	5.1	5.1	5.1
87.5°	5.9	5.9	5.9	5.9	5.8	5.8	5.8	5.8	5.8	5.9	5.9
86.25°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
85°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
83.75°	12.0	12.0	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
82.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6
81.25°	17.6	17.6	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7	17.7
80°	20.6	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
78.75°	24.0	24.1	24.1	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.1
77.5°	27.5	27.5	27.6	27.6	27.7	27.7	27.7	27.7	27.7	27.6	27.6
76.25°	31.2	31.3	31.3	31.4	31.4	31.5	31.5	31.5	31.4	31.4	31.3
75°	35.0	35.1	35.1	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.1
73.75°	38.8	39.0	39.1	39.2	39.2	39.2	39.2	39.2	39.2	39.2	39.1
72.5°	42.7	42.9	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2
71.25°	46.9	47.2	47.3	47.4	47.4	47.4	47.4	47.4	47.4	47.4	47.3
70°	51.2	51.4	51.5	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.5
68.75°	55.5	55.7	55.9	56.0	56.0	56.0	56.0	56.0	56.0	56.0	55.9
67.5°	59.7	60.0	60.3	60.4	60.4	60.4	60.4	60.4	60.4	60.4	60.3
66.25°	64.3	64.6	64.8	65.0	65.0	65.0	65.0	65.0	65.0	65.0	64.8
65°	69.1	69.3	69.4	69.6	69.6	69.6	69.6	69.6	69.6	69.6	69.4
63.75°	73.6	73.9	74.1	74.2	74.3	74.3	74.3	74.3	74.3	74.2	74.1
62.5°	78.1	78.4	78.7	78.8	78.9	78.9	78.9	78.9	78.9	78.8	78.7
61.25°	83.0	83.2	83.4	83.5	83.6	83.6	83.6	83.6	83.6	83.5	83.4
60°	87.9	88.0	88.1	88.1	88.2	88.2	88.2	88.2	88.2	88.1	88.1
58.75°	92.6	92.6	92.5	92.5	92.7	92.7	92.8	92.7	92.7	92.5	92.5
57.5°	97.2	97.1	97.0	96.9	97.1	97.2	97.3	97.2	97.1	96.9	97.0
56.25°	101.5	101.5	101.4	101.4	101.5	101.6	101.6	101.6	101.5	101.4	101.4
55°	105.6	105.7	105.8	105.9	105.9	106.0	105.9	106.0	105.9	105.9	105.8
53.75°	109.8	109.9	110.0	110.0	110.1	110.1	110.0	110.1	110.1	110.0	110.0
52.5°	113.9	114.1	114.2	114.2	114.2	114.2	114.1	114.2	114.2	114.2	114.2
51.25°	118.0	118.1	118.1	118.0	118.1	118.1	118.1	118.1	118.1	118.0	118.1
50°	122.0	122.0	122.0	121.9	122.0	122.0	122.0	122.0	122.0	121.9	122.0
48.75°	125.8	125.7	125.7	125.5	125.6	125.7	125.7	125.7	125.6	125.5	125.7
47.5°	129.3	129.4	129.3	129.2	129.3	129.3	129.3	129.3	129.3	129.2	129.3
46.25°	132.6	132.6	132.4	132.2	132.3	132.3	132.3	132.3	132.3	132.2	132.4
45°	135.6	135.6	135.5	135.2	135.2	135.3	135.3	135.3	135.2	135.2	135.5
43.75°	137.9	137.9	137.6	137.2	137.2	137.2	137.1	137.2	137.2	137.2	137.6
42.5°	139.7	139.7	139.5	139.1	139.0	139.0	138.9	139.0	139.0	139.1	139.5
41.25°	141.3	141.2	140.9	140.4	140.2	140.1	140.0	140.1	140.2	140.4	140.9
40°	142.5	142.6	142.1	141.6	141.4	141.3	141.2	141.3	141.4	141.6	142.1
38.75°	143.7	143.7	143.2	142.7	142.4	142.3	142.2	142.3	142.4	142.7	143.2
37.5°	144.6	144.8	144.3	143.8	143.5	143.3	143.2	143.3	143.5	143.8	144.3
36.25°	145.5	145.6	145.2	144.6	144.2	144.1	144.0	144.1	144.2	144.6	145.2
35°	146.2	146.3	146.0	145.4	144.9	144.9	144.8	144.9	144.9	145.4	146.0



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°
33.75°	146.7	146.8	146.5	145.8	145.3	145.2	145.1	145.2	145.3
32.5°	147.0	147.1	147.0	146.2	145.6	145.4	145.3	145.4	145.6
31.25°	147.1	147.1	146.9	146.1	145.3	145.2	145.1	145.2	145.3
30°	146.7	146.7	146.7	145.8	144.9	144.9	144.8	144.9	144.9
28.75°	146.2	146.1	146.0	145.2	144.3	144.2	144.1	144.2	144.3
27.5°	145.5	145.3	145.2	144.6	143.7	143.5	143.4	143.5	143.7
26.25°	144.8	144.7	144.6	144.1	143.2	142.9	142.9	142.9	143.2
25°	144.2	144.1	144.1	143.7	142.7	142.4	142.4	142.4	142.7
23.75°	143.6	143.6	143.6	143.3	142.4	142.0	142.0	142.0	142.4
22.5°	143.1	143.1	143.1	143.0	142.0	141.5	141.5	141.5	142.0
21.25°	142.7	142.6	142.5	142.5	141.5	140.9	140.8	140.9	141.5
20°	142.1	142.0	141.8	141.8	141.0	140.2	140.1	140.2	141.0
18.75°	141.5	141.3	141.1	141.0	140.3	139.4	139.3	139.4	140.3
17.5°	140.6	140.4	140.2	140.1	139.5	138.5	138.5	138.5	139.5
16.25°	139.7	139.5	139.4	139.4	139.0	137.9	137.9	137.9	139.0
15°	138.7	138.8	138.7	138.8	138.6	137.3	137.3	137.3	138.6
13.75°	137.8	138.1	138.1	138.3	138.3	137.0	137.0	137.0	138.3
12.5°	137.4	137.4	137.6	137.8	137.9	136.7	136.6	136.7	137.9
11.25°	137.5	136.5	137.0	137.1	137.2	136.2	136.0	136.2	137.2
10°	137.2	136.3	136.0	136.3	136.6	135.8	135.4	135.8	136.6
8.75°	136.3	136.2	134.9	135.3	135.5	134.9	134.4	134.9	135.5
7.5°	135.0	135.4	134.7	133.9	134.3	134.2	133.3	134.2	134.3
6.25°	135.4	133.6	133.9	132.6	133.0	133.3	132.4	133.3	133.0
5°	134.2	133.8	132.1	132.5	131.5	132.3	131.4	132.3	131.5
3.75°	133.0	132.5	132.0	130.7	131.1	131.5	131.0	131.5	131.1
2.5°	132.2	131.8	131.0	131.0	130.0	130.3	130.5	130.3	130.0
1.25°	131.5	130.7	129.9	130.4	130.2	129.7	130.1	129.7	130.2
0°	131.1	130.4	129.7	129.8	129.9	129.7	129.6	129.7	129.9
-1.25°	130.5	129.9	129.7	129.2	128.9	129.0	129.1	129.0	128.9
-2.5°	129.8	128.9	128.3	128.4	128.1	127.7	128.6	127.7	128.1
-3.75°	129.1	128.2	128.0	127.3	126.3	126.4	127.6	126.4	126.3
-5°	128.9	127.7	127.4	126.0	125.9	125.9	126.6	125.9	125.9
-6.25°	127.9	127.6	126.1	125.6	125.3	125.4	126.2	125.4	125.3
-7.5°	127.8	126.3	125.5	125.5	124.9	125.0	125.9	125.0	124.9
-8.75°	126.4	125.5	125.2	125.1	124.9	124.7	125.5	124.7	124.9
-10°	125.4	124.9	124.9	124.3	124.5	124.4	125.1	124.4	124.5
-11.25°	124.6	124.3	124.3	123.7	123.8	123.6	124.4	123.6	123.8
-12.5°	123.7	123.7	123.3	123.3	123.0	122.9	123.8	122.9	123.0
-13.75°	123.1	123.0	122.3	122.6	122.0	122.1	122.9	122.1	122.0
-15°	122.7	122.2	121.7	121.8	121.2	121.3	122.1	121.3	121.2
-16.25°	122.2	121.4	121.3	121.1	120.6	120.7	121.4	120.7	120.6
-17.5°	121.6	120.6	120.8	120.3	119.9	120.1	120.8	120.1	119.9
-18.75°	120.8	120.2	120.3	119.6	119.4	119.5	120.1	119.5	119.4
-20°	119.7	119.5	119.5	118.9	118.7	119.0	119.5	119.0	118.7
-21.25°	118.6	118.7	118.5	117.8	117.7	117.9	118.4	117.9	117.7

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

3.75°	5°		-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°
145.8	146.5	-22.5°	117.5	117.6	117.3	116.7	116.7	116.9	117.4	116.9	116.7
146.2	147.0	-23.75°	116.3	116.4	115.9	115.4	115.3	115.6	116.1	115.6	115.3
146.1	146.9	-25°	115.1	115.0	114.4	114.0	113.9	114.3	114.8	114.3	113.9
145.8	146.7	-26.25°	113.9	113.6	112.9	112.6	112.5	112.9	113.3	112.9	112.5
145.2	146.0	-27.5°	112.6	112.1	111.4	111.2	111.1	111.5	111.9	111.5	111.1
144.6	145.2	-28.75°	111.3	110.7	109.9	109.9	109.8	110.2	110.5	110.2	109.8
144.1	144.6	-30°	109.7	109.1	108.4	108.5	108.5	108.9	109.2	108.9	108.5
143.7	144.1	-31.25°	107.9	107.2	106.6	106.7	106.7	107.1	107.4	107.1	106.7
143.3	143.6	-32.5°	105.9	105.2	104.8	104.9	105.0	105.3	105.6	105.3	105.0
143.0	143.1	-33.75°	103.7	103.0	102.7	102.8	102.9	103.2	103.4	103.2	102.9
142.5	142.5	-35°	101.0	100.5	100.4	100.5	100.7	101.0	101.3	101.0	100.7
141.8	141.8	-36.25°	98.0	97.4	97.3	97.4	97.5	97.8	98.1	97.8	97.5
141.0	141.1	-37.5°	94.6	94.0	94.0	94.1	94.3	94.6	94.9	94.6	94.3
140.1	140.2	-38.75°	90.9	90.2	90.2	90.2	90.4	90.7	90.9	90.7	90.4
139.4	139.4	-40°	86.3	85.8	85.9	86.0	86.4	86.8	87.0	86.8	86.4
138.8	138.7	-41.25°	80.6	79.9	79.8	79.6	79.9	80.2	80.4	80.2	79.9
138.3	138.1	-42.5°	71.1	70.9	70.9	70.7	71.1	71.5	71.7	71.5	71.1
137.8	137.6	-43.75°	60.5	60.6	60.8	60.7	61.2	61.6	61.7	61.6	61.2
137.1	137.0	-45°	52.2	51.9	51.6	51.3	51.5	51.7	51.8	51.7	51.5
136.3	136.0	-46.25°	47.3	47.2	47.0	46.7	47.0	47.2	47.3	47.2	47.0
135.3	134.9	-47.5°	42.9	42.8	42.6	42.3	42.5	42.7	42.8	42.7	42.5
133.9	134.7	-48.75°	39.1	39.0	38.8	38.6	38.8	39.0	39.1	39.0	38.8
132.6	133.9	-50°	35.5	35.4	35.2	34.9	35.1	35.3	35.4	35.3	35.1
132.5	132.1	-51.25°	32.3	32.2	32.0	31.8	31.9	31.9	31.9	31.9	31.9
130.7	132.0	-52.5°	28.8	28.7	28.6	28.5	28.5	28.4	28.3	28.4	28.5
131.0	131.0	-53.75°	24.4	24.1	23.7	23.4	23.2	23.0	22.7	23.0	23.2
130.4	129.9	-55°	19.5	19.2	18.8	18.3	18.0	17.6	17.1	17.6	18.0
129.8	129.7	-56.25°	13.7	13.6	13.3	13.1	12.9	12.7	12.4	12.7	12.9
129.2	129.7	-57.5°	8.7	8.5	8.3	8.1	8.0	7.9	7.7	7.9	8.0
128.4	128.3	-58.75°	6.4	6.2	6.0	5.8	5.7	5.6	5.5	5.6	5.7
127.3	128.0	-60°	4.3	4.0	3.8	3.6	3.5	3.4	3.2	3.4	3.5
126.0	127.4	-61.25°	2.8	2.5	2.3	2.1	2.0	1.8	1.7	1.8	2.0
125.6	126.1	-62.5°	1.5	1.2	0.8	0.6	0.5	0.3	0.2	0.3	0.5
125.5	125.5	-63.75°	1.2	0.9	0.7	0.5	0.3	0.2	0.1	0.2	0.3
125.1	125.2	-65°	0.9	0.7	0.5	0.3	0.2	0.1	0.0	0.1	0.2
124.3	124.9	-66.25°	0.9	0.6	0.4	0.3	0.2	0.1	0.0	0.1	0.2
123.7	124.3	-67.5°	0.8	0.6	0.4	0.2	0.2	0.1	0.0	0.1	0.2
123.3	123.3	-68.75°	0.7	0.5	0.4	0.2	0.2	0.1	0.0	0.1	0.2
122.6	122.3	-70°	0.7	0.5	0.3	0.2	0.2	0.1	0.0	0.1	0.2
121.8	121.7	-71.25°	0.6	0.5	0.3	0.2	0.2	0.1	0.0	0.1	0.2
121.1	121.3	-72.5°	0.6	0.5	0.3	0.2	0.2	0.1	0.0	0.1	0.2
120.3	120.8	-73.75°	0.5	0.4	0.3	0.2	0.2	0.1	0.1	0.1	0.2
119.6	120.3	-75°	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.2	0.2
118.9	119.5	-76.25°	0.5	0.4	0.3	0.2	0.2	0.1	0.1	0.1	0.2
117.8	118.5	-77.5°	0.4	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

3.75°	5°		-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°
116.7	117.3	-78.75°	0.4	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2
115.4	115.9	-80°	0.4	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2
114.0	114.4	-81.25°	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2
112.6	112.9	-82.5°	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2
111.2	111.4	-83.75°	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.2
109.9	109.9	-85°	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.2
108.5	108.4	-86.25°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
106.7	106.6	-87.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
104.9	104.8	-88.75°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
102.8	102.7	-90°	4.4	4.4	4.4	4.4	4.4	4.3	4.3	4.3	4.4
100.5	100.4										
97.4	97.3										
94.1	94.0										
90.2	90.2										
86.0	85.9										
79.6	79.8										
70.7	70.9										
60.7	60.8										
51.3	51.6										
46.7	47.0										
42.3	42.6										
38.6	38.8										
34.9	35.2										
31.8	32.0										
28.5	28.6										
23.4	23.7										
18.3	18.8										
13.1	13.3										
8.1	8.3										
5.8	6.0										
3.6	3.8										
2.1	2.3										
0.6	0.8										
0.5	0.7										
0.3	0.5										
0.3	0.4										
0.2	0.4										
0.2	0.4										
0.2	0.3										
0.2	0.3										
0.2	0.3										
0.2	0.3										
0.3	0.3										
0.2	0.3										
0.2	0.2										

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

3.75°	5°		6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°
0.2	0.2	90°	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.4
0.2	0.2	88.75°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
0.2	0.2	87.5°	5.9	5.9	5.9	5.9	5.8	5.8	5.8	5.8	5.8
0.2	0.2	86.25°	7.7	7.7	7.7	7.7	7.6	7.6	7.5	7.5	7.5
0.2	0.2	85°	9.5	9.5	9.5	9.5	9.4	9.4	9.3	9.2	9.2
0.2	0.2	83.75°	12.0	12.0	12.0	12.0	11.9	11.8	11.7	11.7	11.6
0.1	0.1	82.5°	14.6	14.6	14.5	14.5	14.4	14.3	14.3	14.2	14.1
0.1	0.1	81.25°	17.6	17.6	17.5	17.4	17.3	17.3	17.2	17.1	17.0
0.1	0.1	80°	20.7	20.6	20.5	20.4	20.4	20.3	20.2	20.1	20.1
4.4	4.4	78.75°	24.1	24.0	23.9	23.8	23.7	23.6	23.5	23.4	23.3
		77.5°	27.5	27.5	27.4	27.3	27.2	27.1	26.9	26.8	26.7
		76.25°	31.3	31.2	31.1	31.0	30.8	30.7	30.5	30.4	30.3
		75°	35.1	35.0	34.8	34.7	34.6	34.4	34.2	34.1	34.1
		73.75°	39.0	38.8	38.6	38.5	38.3	38.2	38.0	37.9	37.9
		72.5°	42.9	42.7	42.4	42.2	42.1	42.0	41.9	41.8	41.7
		71.25°	47.2	46.9	46.7	46.5	46.3	46.2	46.0	45.8	45.7
		70°	51.4	51.2	51.0	50.8	50.6	50.4	50.2	50.0	49.9
		68.75°	55.7	55.5	55.2	55.0	54.9	54.7	54.5	54.3	54.1
		67.5°	60.0	59.7	59.4	59.2	59.1	59.0	58.8	58.6	58.5
		66.25°	64.6	64.3	64.0	63.8	63.6	63.4	63.2	63.0	62.9
		65°	69.3	69.1	68.8	68.5	68.3	68.0	67.7	67.6	67.4
		63.75°	73.9	73.6	73.3	73.1	72.9	72.6	72.2	72.1	71.9
		62.5°	78.4	78.1	77.8	77.6	77.4	77.1	76.8	76.7	76.4
		61.25°	83.2	83.0	82.6	82.4	82.1	81.7	81.4	81.2	81.0
		60°	88.0	87.9	87.7	87.3	86.9	86.4	86.1	85.8	85.6
		58.75°	92.6	92.6	92.5	92.0	91.5	91.0	90.7	90.4	90.1
		57.5°	97.1	97.2	97.1	96.6	96.1	95.5	95.2	94.9	94.6
		56.25°	101.5	101.5	101.4	101.0	100.5	99.9	99.7	99.3	98.9
		55°	105.7	105.6	105.4	105.1	104.7	104.2	104.0	103.6	103.2
		53.75°	109.9	109.8	109.6	109.3	108.9	108.5	108.3	107.9	107.5
		52.5°	114.1	113.9	113.7	113.4	113.1	112.7	112.5	112.1	111.7
		51.25°	118.1	118.0	117.8	117.5	117.2	116.9	116.7	116.3	115.9
		50°	122.0	122.0	121.8	121.5	121.1	120.8	120.6	120.2	119.8
		48.75°	125.7	125.8	125.5	125.3	124.9	124.7	124.4	124.0	123.6
		47.5°	129.4	129.3	129.1	128.8	128.4	128.2	128.0	127.6	127.2
		46.25°	132.6	132.6	132.4	132.1	131.9	131.8	131.5	131.1	130.6
		45°	135.6	135.6	135.3	135.0	134.7	134.5	134.3	134.1	133.7
		43.75°	137.9	137.9	137.7	137.5	137.4	137.2	137.0	136.6	136.2
		42.5°	139.7	139.7	139.5	139.2	139.2	139.1	139.0	138.8	138.6
		41.25°	141.2	141.3	141.1	140.9	140.9	140.9	140.7	140.6	140.3
		40°	142.6	142.5	142.4	142.2	142.3	142.3	142.3	142.3	142.1
		38.75°	143.7	143.7	143.5	143.5	143.5	143.5	143.6	143.6	143.6
		37.5°	144.8	144.6	144.5	144.5	144.5	144.6	144.7	144.8	144.6
		36.25°	145.6	145.5	145.4	145.4	145.5	145.5	145.6	145.7	145.5
		35°	146.3	146.2	146.1	146.2	146.2	146.3	146.5	146.7	146.3



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

17.5°	18.75°		6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°
0.5	0.5	33.75°	146.8	146.7	146.7	146.9	147.0	147.1	147.2	147.2	146.9
5.1	5.1	32.5°	147.1	147.0	147.0	147.2	147.3	147.6	147.8	147.6	147.3
5.8	5.8	31.25°	147.1	147.1	147.2	147.4	147.6	147.8	148.0	147.8	147.6
7.4	7.4	30°	146.7	146.7	146.9	147.1	147.5	147.9	148.0	147.8	147.7
9.2	9.2	28.75°	146.1	146.2	146.5	146.7	147.1	147.5	147.5	147.5	148.0
11.6	11.5	27.5°	145.3	145.5	145.8	146.1	146.6	147.0	147.0	147.1	148.0
14.1	14.1	26.25°	144.7	144.8	145.0	145.4	145.9	146.1	146.2	146.9	147.8
17.0	17.0	25°	144.1	144.2	144.4	144.8	145.1	145.2	145.3	146.4	147.5
20.0	20.0	23.75°	143.6	143.6	143.8	144.1	144.3	144.3	144.9	146.0	146.8
23.3	23.2	22.5°	143.1	143.1	143.3	143.6	143.5	143.6	144.7	145.7	146.0
26.6	26.5	21.25°	142.6	142.7	142.9	143.0	142.8	143.4	144.5	145.0	145.3
30.2	30.1	20°	142.0	142.1	142.3	142.3	142.2	143.2	144.1	144.4	144.6
34.1	34.0	18.75°	141.3	141.5	141.6	141.4	142.0	143.0	143.4	143.7	143.9
37.9	37.8	17.5°	140.4	140.6	140.7	140.7	141.8	142.5	142.8	143.0	143.2
41.7	41.6	16.25°	139.5	139.7	139.6	140.3	141.4	141.8	142.0	142.2	142.8
45.6	45.4	15°	138.8	138.7	138.8	140.0	140.6	141.0	141.1	141.6	142.6
49.7	49.5	13.75°	138.1	137.8	138.6	139.4	139.7	139.8	140.3	141.4	142.2
53.9	53.7	12.5°	137.4	137.4	138.4	138.7	138.7	138.9	140.1	140.9	141.2
58.3	58.0	11.25°	136.5	137.5	137.8	137.7	137.8	139.0	139.5	139.8	140.9
62.7	62.4	10°	136.3	137.2	137.0	136.9	138.0	138.4	138.3	139.7	140.3
67.1	66.9	8.75°	136.2	136.3	136.0	137.4	137.3	137.4	138.8	138.4	139.2
71.6	71.3	7.5°	135.4	135.0	136.6	136.3	137.0	137.0	137.3	138.0	138.7
76.2	75.8	6.25°	133.6	135.4	135.0	136.4	135.9	136.5	137.0	137.5	138.2
80.7	80.3	5°	133.8	134.2	134.2	135.0	135.7	136.1	136.4	136.7	137.2
85.2	84.8	3.75°	132.5	133.0	133.9	134.6	134.8	135.0	135.3	135.9	136.7
89.8	89.3	2.5°	131.8	132.2	132.6	133.3	134.0	134.7	135.2	135.7	136.6
94.2	93.7	1.25°	130.7	131.5	132.3	133.2	133.9	134.5	135.1	135.6	136.4
98.5	98.0	0°	130.4	131.1	132.0	132.8	133.4	134.0	134.6	135.1	135.8
102.8	102.3	-1.25°	129.9	130.5	131.6	132.6	133.4	134.2	134.8	135.3	136.1
107.0	106.5	-2.5°	128.9	129.8	131.1	131.9	132.4	132.9	133.4	134.1	135.1
111.2	110.6	-3.75°	128.2	129.1	129.9	130.6	131.6	132.5	133.3	133.9	134.7
115.3	114.7	-5°	127.7	128.9	129.1	130.0	130.8	131.4	131.9	133.0	134.2
119.3	118.8	-6.25°	127.6	127.9	129.3	129.4	129.8	130.8	131.5	132.3	133.2
123.0	122.4	-7.5°	126.3	127.8	127.9	129.1	129.6	129.7	130.6	131.9	133.0
126.7	126.1	-8.75°	125.5	126.4	127.7	127.9	128.9	129.9	130.2	130.8	132.2
130.0	129.4	-10°	124.9	125.4	126.4	127.6	127.9	129.0	130.2	130.8	131.6
133.3	132.6	-11.25°	124.3	124.6	125.2	126.3	127.7	128.4	129.4	130.7	131.8
135.8	135.2	-12.5°	123.7	123.7	124.3	125.3	126.7	128.1	128.9	129.9	131.3
138.1	137.4	-13.75°	123.0	123.1	123.6	124.4	125.5	127.2	128.6	129.4	130.3
140.0	139.4	-15°	122.2	122.7	122.9	123.6	124.8	126.1	127.7	128.9	129.6
141.7	141.1	-16.25°	121.4	122.2	122.5	123.1	124.0	125.2	126.4	127.9	129.0
143.2	142.7	-17.5°	120.6	121.6	122.1	122.5	123.2	124.1	125.2	126.6	128.0
144.2	143.8	-18.75°	120.2	120.8	121.5	121.7	122.3	123.0	124.1	125.2	126.6
145.2	144.8	-20°	119.5	119.7	120.5	121.0	121.3	121.9	122.8	124.0	125.2
145.9	145.8	-21.25°	118.7	118.6	119.4	119.9	120.2	120.8	121.6	122.6	123.8

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

17.5°	18.75°		6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°
146.7	146.9	-22.5°	117.6	117.5	117.9	118.8	119.2	119.5	120.4	121.2	122.5
147.2	147.7	-23.75°	116.4	116.3	116.5	117.3	117.9	118.4	119.1	120.0	121.1
147.9	148.4	-25°	115.0	115.1	115.0	115.9	116.7	117.2	117.8	118.7	119.7
148.4	149.0	-26.25°	113.6	113.9	113.8	114.4	115.3	116.0	116.7	117.5	118.3
148.7	149.3	-27.5°	112.1	112.6	112.7	113.0	113.9	114.8	115.3	115.8	116.6
148.9	149.2	-28.75°	110.7	111.3	111.4	111.5	112.3	113.1	113.7	114.2	114.8
148.6	148.8	-30°	109.1	109.7	109.9	109.9	110.6	111.4	112.0	112.4	112.8
148.0	148.3	-31.25°	107.2	107.9	108.2	108.3	108.6	109.3	110.0	110.4	110.8
147.2	147.7	-32.5°	105.2	105.9	106.3	106.3	106.5	107.2	107.9	108.3	108.7
146.4	146.9	-33.75°	103.0	103.7	104.2	104.3	104.3	104.9	105.5	106.1	106.5
145.6	146.0	-35°	100.5	101.0	101.5	101.6	101.8	102.3	103.1	103.8	104.0
144.9	145.2	-36.25°	97.4	98.0	98.6	98.9	99.1	99.3	100.0	100.6	101.0
144.1	144.8	-37.5°	94.0	94.6	95.2	95.5	95.8	95.9	96.7	97.4	97.8
143.7	144.5	-38.75°	90.2	90.9	91.6	92.1	92.3	92.4	92.9	93.6	94.3
143.6	144.2	-40°	85.8	86.3	86.9	87.5	87.8	88.2	88.8	89.5	89.9
143.3	143.5	-41.25°	79.9	80.6	81.6	82.1	82.4	81.9	81.4	81.8	82.8
142.5	142.7	-42.5°	70.9	71.1	71.5	71.5	71.4	71.4	71.4	72.9	74.9
141.8	143.1	-43.75°	60.6	60.5	60.5	60.1	60.1	61.2	62.3	64.0	65.5
142.1	142.0	-45°	51.9	52.2	52.7	53.1	53.7	54.6	55.2	55.8	56.6
140.7	141.4	-46.25°	47.2	47.3	47.7	47.9	48.0	48.5	49.0	49.7	51.1
140.1	140.9	-47.5°	42.8	42.9	43.3	43.5	43.7	44.3	44.9	45.3	46.6
139.6	140.5	-48.75°	39.0	39.1	39.4	39.6	39.7	40.3	40.9	41.4	42.6
139.0	139.7	-50°	35.4	35.5	35.8	36.1	36.3	36.9	37.5	38.1	39.0
137.9	138.8	-51.25°	32.2	32.3	32.6	32.9	33.1	33.6	34.2	34.7	35.5
137.6	138.5	-52.5°	28.7	28.8	29.0	29.3	29.5	29.9	30.6	31.3	32.1
137.4	138.4	-53.75°	24.1	24.4	24.7	25.2	25.6	26.1	27.0	27.4	27.6
137.2	138.2	-55°	19.2	19.5	19.8	20.0	20.1	20.1	20.5	20.8	21.0
136.5	137.6	-56.25°	13.6	13.7	13.7	13.8	13.7	13.5	13.9	14.3	15.2
136.9	137.9	-57.5°	8.5	8.7	8.9	9.3	9.6	9.9	10.6	11.4	12.0
136.1	137.3	-58.75°	6.2	6.4	6.6	6.9	7.2	7.5	8.0	8.5	9.1
135.5	136.5	-60°	4.0	4.3	4.5	4.9	5.3	5.6	6.1	6.8	7.3
135.5	136.6	-61.25°	2.5	2.8	3.0	3.4	3.8	4.1	4.6	5.1	5.6
134.4	135.8	-62.5°	1.2	1.5	1.9	2.3	2.7	3.1	3.5	4.1	4.7
134.1	135.1	-63.75°	0.9	1.2	1.4	1.8	2.1	2.4	2.8	3.3	3.8
133.7	134.9	-65°	0.7	0.9	1.1	1.4	1.7	2.0	2.4	2.9	3.5
132.7	134.1	-66.25°	0.6	0.9	1.1	1.3	1.6	1.9	2.2	2.7	3.2
132.4	133.1	-67.5°	0.6	0.8	1.0	1.2	1.5	1.8	2.0	2.5	3.0
132.5	133.1	-68.75°	0.5	0.7	0.9	1.1	1.4	1.7	2.0	2.4	2.8
131.6	132.9	-70°	0.5	0.7	0.8	1.0	1.3	1.6	1.8	2.2	2.6
130.6	131.8	-71.25°	0.5	0.6	0.8	0.9	1.2	1.4	1.7	2.0	2.4
129.8	130.7	-72.5°	0.5	0.6	0.7	0.9	1.1	1.3	1.5	1.8	2.2
129.0	129.9	-73.75°	0.4	0.5	0.7	0.8	1.0	1.2	1.4	1.6	2.0
128.0	129.0	-75°	0.4	0.5	0.6	0.7	0.9	1.1	1.3	1.5	1.8
126.6	128.1	-76.25°	0.4	0.5	0.6	0.7	0.9	1.0	1.2	1.4	1.7
125.2	126.7	-77.5°	0.3	0.4	0.5	0.6	0.8	1.0	1.1	1.3	1.5

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

17.5°	18.75°		6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°
123.8	125.3	-78.75°	0.3	0.4	0.5	0.6	0.7	0.9	1.0	1.2	1.4
122.5	123.9	-80°	0.3	0.4	0.4	0.5	0.6	0.8	0.9	1.0	1.2
121.0	122.2	-81.25°	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
119.1	120.3	-82.5°	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.8	0.9
117.4	118.4	-83.75°	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.7	0.8
115.5	116.2	-85°	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.7
113.5	114.2	-86.25°	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6
111.4	112.0	-87.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.4
109.1	109.8	-88.75°	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.4
106.9	107.3	-90°	4.4	4.4	4.3	4.3	4.3	4.4	4.4	4.4	4.4
104.2	104.6										
101.4	101.8										
98.2	98.5										
94.8	95.1										
90.0	90.1										
83.9	84.6										
76.5	76.3										
66.4	66.6										
57.1	58.5										
52.3	53.4										
47.7	48.8										
43.8	44.9										
40.1	41.1										
36.6	37.7										
33.2	34.3										
28.3	29.3										
22.1	23.7										
16.7	18.7										
12.9	14.4										
9.8	11.3										
7.9	9.2										
6.2	7.5										
5.2	6.2										
4.3	5.2										
4.0	4.8										
3.7	4.4										
3.5	4.0										
3.3	3.7										
3.0	3.4										
2.7	3.1										
2.5	2.9										
2.3	2.7										
2.1	2.4										
1.9	2.2										
1.7	1.9										

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

17.5°	18.75°		20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°
1.6	1.8	90°	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.8	0.8
1.4	1.5	88.75°	5.1	5.1	5.0	5.0	4.9	4.9	4.9	4.9	4.9
1.2	1.3	87.5°	5.8	5.7	5.7	5.6	5.6	5.6	5.6	5.7	5.7
1.0	1.1	86.25°	7.4	7.3	7.3	7.2	7.1	7.1	7.1	7.1	7.1
0.9	1.0	85°	9.2	9.1	9.0	8.9	8.9	8.9	8.9	8.8	8.8
0.8	0.9	83.75°	11.5	11.4	11.3	11.2	11.0	11.0	11.0	10.9	10.8
0.6	0.7	82.5°	14.0	13.9	13.8	13.6	13.5	13.5	13.4	13.4	13.3
0.5	0.5	81.25°	16.9	16.7	16.5	16.3	16.1	16.1	16.0	15.9	15.8
0.5	0.5	80°	19.9	19.7	19.5	19.3	19.1	19.0	19.0	18.9	18.7
4.4	4.4	78.75°	23.1	22.9	22.6	22.3	22.1	22.0	21.9	21.9	21.7
		77.5°	26.4	26.2	26.0	25.7	25.5	25.4	25.3	25.1	24.9
		76.25°	29.9	29.7	29.4	29.1	28.9	28.8	28.6	28.5	28.2
		75°	33.8	33.4	33.1	32.8	32.6	32.4	32.2	32.0	31.6
		73.75°	37.6	37.2	36.8	36.4	36.2	36.0	35.9	35.6	35.2
		72.5°	41.3	41.0	40.6	40.2	40.0	39.8	39.6	39.4	38.9
		71.25°	45.1	44.8	44.5	44.1	43.9	43.7	43.5	43.2	42.7
		70°	49.3	49.0	48.6	48.2	47.9	47.7	47.3	47.0	46.5
		68.75°	53.4	53.2	52.8	52.5	52.1	51.8	51.4	50.9	50.4
		67.5°	57.8	57.5	57.1	56.7	56.3	55.9	55.4	54.9	54.3
		66.25°	62.1	61.8	61.4	61.0	60.6	60.1	59.6	59.0	58.3
		65°	66.5	66.1	65.7	65.3	64.8	64.3	63.7	63.2	62.5
		63.75°	71.0	70.5	70.1	69.6	69.1	68.6	68.0	67.4	66.7
		62.5°	75.4	75.0	74.5	74.0	73.4	72.8	72.2	71.6	70.9
		61.25°	79.9	79.4	78.9	78.4	77.8	77.1	76.5	75.8	75.1
		60°	84.4	83.9	83.3	82.8	82.1	81.5	80.8	80.1	79.3
		58.75°	88.8	88.3	87.7	87.1	86.4	85.7	85.1	84.3	83.5
		57.5°	93.2	92.6	92.0	91.3	90.6	89.9	89.2	88.5	87.7
		56.25°	97.4	96.8	96.2	95.5	94.8	94.1	93.4	92.6	91.7
		55°	101.7	101.1	100.4	99.6	98.8	98.2	97.5	96.7	95.7
		53.75°	105.9	105.2	104.5	103.7	102.9	102.3	101.5	100.7	99.7
		52.5°	110.0	109.3	108.6	107.7	107.0	106.3	105.6	104.8	103.6
		51.25°	114.0	113.3	112.6	111.8	111.0	110.4	109.6	108.8	107.5
		50°	118.0	117.2	116.4	115.5	114.9	114.3	113.6	112.6	111.2
		48.75°	121.8	121.0	120.2	119.3	118.7	118.1	117.3	116.2	115.0
		47.5°	125.3	124.5	123.6	122.9	122.4	121.8	120.9	119.7	118.4
		46.25°	128.7	128.0	127.1	126.4	125.8	125.1	124.2	123.0	121.7
		45°	131.7	130.8	130.1	129.7	129.1	128.4	127.2	125.9	124.8
		43.75°	134.5	133.6	132.9	132.4	131.9	131.2	130.0	128.6	127.4
		42.5°	136.7	135.9	135.5	135.1	134.5	133.5	132.4	131.2	130.1
		41.25°	138.8	138.2	137.8	137.4	136.8	135.9	134.7	133.4	132.7
		40°	140.5	140.3	140.1	139.7	138.9	138.0	136.9	135.9	135.2
		38.75°	142.2	142.2	142.0	141.8	141.1	140.0	139.0	138.3	137.7
		37.5°	143.8	144.0	144.0	143.5	142.7	141.9	141.2	140.6	139.9
		36.25°	145.0	145.3	145.5	145.1	144.3	143.4	143.1	142.9	142.2
		35°	146.2	146.5	146.4	146.0	145.6	145.1	144.8	144.5	144.2

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

31.25°	32.5°		20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°
0.9	0.9	33.75°	147.2	147.5	147.2	146.8	146.4	146.4	146.3	146.0	145.5
4.9	4.8	32.5°	148.2	148.2	147.9	147.6	147.4	147.3	147.3	147.3	146.8
5.6	5.5	31.25°	148.9	148.7	148.5	148.2	148.1	148.1	148.1	148.0	147.9
7.0	6.8	30°	149.1	149.0	148.8	148.8	148.7	148.7	148.7	148.6	148.6
8.7	8.5	28.75°	149.2	149.2	149.1	149.1	149.2	149.1	149.1	149.1	149.1
10.6	10.4	27.5°	149.2	149.1	149.3	149.3	149.4	149.5	149.5	149.5	149.6
13.1	12.9	26.25°	149.0	149.1	149.2	149.5	149.6	149.7	149.8	149.8	150.0
15.5	15.3	25°	148.6	148.9	149.1	149.4	149.7	149.9	149.9	150.0	150.2
18.4	18.1	23.75°	148.1	148.4	148.9	149.3	149.7	149.9	150.0	150.1	150.3
21.4	21.1	22.5°	147.4	147.9	148.5	149.2	149.5	149.7	149.9	150.1	150.8
24.5	24.1	21.25°	146.6	147.5	148.2	148.7	149.2	149.4	149.7	150.5	151.2
27.8	27.4	20°	146.0	146.9	147.6	148.1	148.6	149.2	150.0	150.7	150.9
31.2	30.7	18.75°	145.5	146.2	146.8	147.4	148.1	149.2	150.1	150.2	150.5
34.8	34.3	17.5°	145.1	145.4	146.0	146.9	148.2	149.0	149.3	149.6	149.9
38.4	37.9	16.25°	144.4	144.8	145.6	146.9	147.6	148.1	148.6	149.1	149.4
42.1	41.6	15°	143.7	144.7	145.8	146.0	146.7	147.4	147.9	148.5	148.9
45.9	45.3	13.75°	143.9	144.6	144.7	145.2	145.9	146.6	147.2	147.9	148.6
49.7	49.1	12.5°	143.3	143.5	144.0	144.6	145.2	146.0	146.8	147.5	148.2
53.7	53.0	11.25°	142.6	143.0	143.4	144.1	144.7	145.5	146.3	147.0	147.6
57.6	56.8	10°	142.1	142.6	143.1	143.7	144.3	144.9	145.7	146.4	147.0
61.8	61.0	8.75°	141.6	142.2	142.7	143.2	143.7	144.2	145.0	145.7	146.5
66.0	65.2	7.5°	141.1	141.6	142.0	142.5	143.0	143.6	144.5	145.4	146.3
70.2	69.3	6.25°	140.2	140.8	141.4	142.0	142.8	143.5	144.3	145.3	146.1
74.4	73.4	5°	139.7	140.4	141.2	141.9	142.7	143.3	144.2	145.2	146.1
78.5	77.5	3.75°	139.4	140.3	141.1	141.9	142.6	143.4	144.2	145.2	146.2
82.6	81.5	2.5°	139.4	140.3	141.1	141.9	142.7	143.4	144.1	145.1	146.1
86.6	85.4	1.25°	139.2	140.0	140.8	141.5	142.2	142.9	143.7	144.6	145.6
90.6	89.3	0°	138.7	139.6	140.4	141.0	141.6	142.4	143.2	144.2	145.1
94.5	93.1	-1.25°	138.9	139.7	140.5	141.1	141.7	142.4	143.2	144.1	145.0
98.4	97.0	-2.5°	138.5	139.4	140.3	141.0	141.7	142.5	143.3	144.1	145.0
102.3	100.8	-3.75°	137.5	138.5	139.5	140.3	141.1	141.9	142.8	143.7	144.7
106.1	104.7	-5°	137.5	138.3	139.1	139.8	140.6	141.3	142.3	143.3	144.2
109.9	108.4	-6.25°	137.0	138.1	139.0	139.6	140.4	141.1	142.0	143.0	143.9
113.5	112.1	-7.5°	136.1	137.2	138.2	139.1	140.0	141.0	141.9	142.9	143.6
117.0	115.9	-8.75°	135.8	136.6	137.4	138.4	139.3	140.3	141.5	142.6	143.4
120.3	119.4	-10°	135.3	136.3	137.0	137.9	138.7	139.7	140.8	141.9	142.8
123.7	122.7	-11.25°	134.3	135.4	136.6	137.5	138.4	139.3	140.3	141.2	142.0
126.6	125.8	-12.5°	133.5	134.4	135.6	136.8	138.1	139.1	140.1	140.7	141.4
129.3	128.5	-13.75°	133.3	133.8	134.6	135.8	137.2	138.6	139.7	140.3	140.9
132.0	131.1	-15°	132.9	133.7	134.3	135.0	136.2	137.6	138.7	139.7	140.2
134.4	133.6	-16.25°	131.9	133.2	134.1	134.8	135.6	136.4	137.5	138.5	139.2
136.9	136.0	-17.5°	130.9	132.1	133.5	134.5	135.2	135.7	136.4	137.1	137.9
139.3	138.3	-18.75°	130.0	131.0	132.4	133.8	134.7	135.2	135.6	135.9	136.5
141.3	140.4	-20°	129.1	130.1	131.3	132.5	133.6	134.6	134.8	135.0	135.1
143.3	142.3	-21.25°	128.2	129.2	130.1	131.1	132.2	133.1	133.9	134.0	134.1

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

31.25°	32.5°		20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°
145.0	144.1	-22.5°	126.8	128.1	128.9	129.8	130.6	131.4	132.3	132.9	132.9
146.2	145.7	-23.75°	125.2	126.5	127.7	128.3	129.0	129.7	130.4	131.0	131.6
147.4	147.0	-25°	123.4	124.7	125.9	126.7	127.3	127.9	128.5	129.1	129.7
148.5	148.3	-26.25°	121.5	122.6	123.8	124.9	125.5	126.0	126.6	127.1	127.7
149.2	149.3	-27.5°	119.4	120.5	121.6	122.6	123.5	124.0	124.6	125.1	125.7
149.8	149.9	-28.75°	117.3	118.3	119.3	120.3	121.2	122.0	122.5	123.1	123.7
150.2	150.4	-30°	115.0	116.0	116.9	117.9	118.8	119.7	120.4	121.0	121.6
150.5	151.0	-31.25°	112.6	113.6	114.6	115.5	116.4	117.4	118.2	118.8	119.4
151.0	151.5	-32.5°	110.4	111.1	112.1	113.0	114.0	114.9	115.8	116.6	116.9
151.5	151.7	-33.75°	107.9	108.5	109.6	110.5	111.5	112.4	113.3	113.8	114.2
151.4	151.6	-35°	105.3	106.0	106.7	107.7	108.8	109.5	110.1	110.7	111.4
151.1	151.2	-36.25°	102.3	103.0	103.6	104.6	105.3	106.0	106.7	107.5	107.9
150.6	150.8	-37.5°	99.1	99.7	100.2	100.8	101.6	102.4	103.1	103.6	104.1
150.1	150.3	-38.75°	95.2	95.7	96.2	96.9	97.8	98.1	98.9	99.5	100.2
149.6	150.0	-40°	90.6	91.3	92.1	92.0	92.4	93.1	94.2	94.8	94.7
149.3	149.6	-41.25°	85.4	84.9	84.8	85.4	86.7	87.5	87.4	88.0	88.7
149.0	149.3	-42.5°	76.1	75.9	76.6	78.0	78.5	78.5	79.1	80.3	81.4
148.6	148.9	-43.75°	66.6	67.1	68.3	69.2	69.1	68.8	70.3	72.1	72.8
148.1	148.4	-45°	59.8	60.5	60.8	61.0	60.8	61.2	63.3	64.5	64.7
147.6	147.9	-46.25°	54.1	54.3	54.6	55.4	56.1	56.3	57.1	58.0	59.1
147.3	147.7	-47.5°	49.5	50.1	50.6	51.1	51.5	51.8	52.4	53.7	54.5
147.1	147.6	-48.75°	45.7	46.3	46.7	47.3	47.9	48.4	48.7	49.5	50.4
146.9	147.5	-50°	42.1	42.8	43.4	44.0	44.6	45.0	45.3	45.9	46.9
146.9	147.5	-51.25°	38.8	39.5	40.2	40.8	41.4	41.8	42.1	42.5	43.5
146.9	147.5	-52.5°	35.3	35.9	36.6	37.4	38.1	38.6	39.0	39.2	39.9
146.7	147.3	-53.75°	30.5	31.7	32.6	33.7	34.7	34.6	34.8	35.2	36.2
146.2	146.8	-55°	25.5	27.1	27.9	28.6	29.0	29.4	30.1	31.0	32.1
145.7	146.3	-56.25°	20.4	21.8	22.5	23.0	23.4	24.3	25.7	26.7	27.4
145.6	146.2	-57.5°	15.6	16.5	17.7	18.9	20.0	21.0	22.0	22.6	22.9
145.6	146.2	-58.75°	12.7	14.0	15.2	16.2	17.2	17.9	18.7	19.5	20.3
145.3	145.9	-60°	10.5	11.7	12.8	13.9	14.9	15.8	16.7	17.5	18.2
144.9	145.5	-61.25°	8.8	10.0	11.1	12.1	13.1	14.0	14.8	15.5	16.3
144.5	145.1	-62.5°	7.4	8.5	9.4	10.4	11.5	12.5	13.4	14.1	14.9
144.3	144.7	-63.75°	6.3	7.5	8.5	9.5	10.5	11.3	12.1	12.8	13.5
144.1	144.3	-65°	5.8	6.9	7.9	8.7	9.5	10.3	11.0	11.8	12.5
143.6	143.9	-66.25°	5.3	6.3	7.2	8.1	8.8	9.5	10.2	10.9	11.6
142.7	143.1	-67.5°	4.9	5.8	6.6	7.4	8.1	8.8	9.4	10.1	10.7
141.9	142.3	-68.75°	4.5	5.3	6.1	6.8	7.5	8.1	8.7	9.3	9.9
141.2	141.6	-70°	4.1	4.8	5.6	6.2	6.9	7.4	8.0	8.5	9.0
140.6	140.8	-71.25°	3.7	4.4	5.1	5.7	6.3	6.8	7.3	7.8	8.3
139.9	140.0	-72.5°	3.4	4.0	4.6	5.2	5.7	6.2	6.6	7.0	7.5
138.5	139.0	-73.75°	3.2	3.7	4.2	4.7	5.1	5.6	6.0	6.4	6.8
137.0	137.5	-75°	2.8	3.3	3.7	4.2	4.6	5.0	5.4	5.7	6.1
135.5	136.0	-76.25°	2.5	2.9	3.3	3.7	4.1	4.4	4.8	5.1	5.4
134.2	134.3	-77.5°	2.2	2.6	2.9	3.3	3.6	3.9	4.2	4.5	4.8

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

31.25°	32.5°		20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°
132.9	132.9	-78.75°	2.0	2.3	2.6	2.9	3.2	3.4	3.7	3.9	4.2
131.6	131.6	-80°	1.7	2.0	2.3	2.5	2.8	3.0	3.2	3.4	3.6
130.1	130.1	-81.25°	1.5	1.7	1.9	2.2	2.4	2.6	2.7	2.9	3.1
128.2	128.6	-82.5°	1.3	1.5	1.7	1.9	2.0	2.2	2.3	2.5	2.6
126.2	126.7	-83.75°	1.1	1.3	1.4	1.6	1.7	1.8	1.9	2.1	2.2
124.2	124.7	-85°	1.0	1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8
122.1	122.3	-86.25°	0.8	0.9	0.9	1.0	1.1	1.2	1.3	1.4	1.4
119.7	119.9	-87.5°	0.6	0.7	0.7	0.8	0.9	0.9	1.0	1.1	1.1
117.1	117.4	-88.75°	0.5	0.6	0.6	0.7	0.7	0.8	0.9	0.9	1.0
114.5	114.6	-90°	4.4	4.4	4.4	4.3	4.3	4.3	4.3	4.2	4.2
111.5	111.5										
108.1	108.3										
104.7	104.8										
100.4	101.0										
95.4	96.9										
89.9	90.3										
81.9	82.8										
73.6	74.8										
65.7	67.9										
59.8	61.6										
55.1	56.3										
51.3	52.3										
47.9	48.7										
44.5	45.4										
41.0	42.1										
37.4	38.6										
33.1	34.2										
28.4	29.7										
24.0	26.0										
21.3	23.1										
18.8	20.4										
17.0	18.5										
15.5	16.6										
14.2	15.2										
13.2	13.9										
12.3	12.9										
11.3	11.9										
10.4	10.9										
9.5	10.0										
8.7	9.2										
7.9	8.3										
7.2	7.5										
6.4	6.7										
5.7	6.0										
5.1	5.3										



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

31.25°	32.5°		33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°
4.4	4.7	90°	1.0	1.0	1.1	1.1	1.2	1.2	1.2	1.3	1.3
3.8	4.0	88.75°	4.7	4.7	4.6	4.6	4.6	4.6	4.5	4.5	4.5
3.2	3.4	87.5°	5.4	5.3	5.3	5.3	5.2	5.2	5.2	5.1	5.1
2.8	2.9	86.25°	6.7	6.5	6.5	6.4	6.3	6.2	6.1	6.1	6.0
2.3	2.4	85°	8.4	8.2	8.1	8.0	7.9	7.8	7.8	7.7	7.6
1.9	2.0	83.75°	10.2	10.0	9.8	9.7	9.6	9.4	9.4	9.3	9.2
1.5	1.6	82.5°	12.6	12.4	12.2	12.0	11.8	11.6	11.4	11.3	11.1
1.2	1.2	81.25°	15.1	14.8	14.6	14.4	14.2	14.0	13.7	13.5	13.3
1.0	1.1	80°	17.8	17.5	17.3	17.0	16.7	16.4	16.0	15.8	15.5
4.2	4.1	78.75°	20.7	20.4	20.1	19.8	19.5	19.2	18.8	18.5	18.1
		77.5°	23.7	23.4	23.0	22.7	22.3	22.0	21.6	21.2	20.8
		76.25°	27.0	26.6	26.2	25.8	25.4	25.0	24.5	24.1	23.6
		75°	30.2	29.8	29.4	29.0	28.6	28.1	27.7	27.2	26.7
		73.75°	33.8	33.3	32.8	32.3	31.7	31.3	30.9	30.4	29.9
		72.5°	37.3	36.8	36.3	35.7	35.1	34.7	34.2	33.7	33.1
		71.25°	40.9	40.4	39.7	39.1	38.5	38.1	37.6	37.0	36.3
		70°	44.7	44.0	43.4	42.7	42.0	41.5	41.0	40.4	39.6
		68.75°	48.4	47.7	47.0	46.3	45.7	45.1	44.5	43.8	43.0
		67.5°	52.3	51.5	50.7	49.9	49.3	48.8	48.1	47.4	46.4
		66.25°	56.1	55.4	54.6	53.7	53.1	52.5	51.8	51.0	49.9
		65°	60.1	59.3	58.4	57.6	56.9	56.2	55.5	54.6	53.4
		63.75°	64.2	63.3	62.3	61.4	60.7	60.0	59.2	58.2	56.9
		62.5°	68.3	67.3	66.2	65.3	64.5	63.7	62.9	61.8	60.4
		61.25°	72.3	71.2	70.1	69.2	68.3	67.4	66.5	65.2	63.9
		60°	76.4	75.2	74.1	73.1	72.1	71.1	70.0	68.8	67.4
		58.75°	80.3	79.1	78.1	77.1	76.0	74.9	73.7	72.3	70.9
		57.5°	84.1	82.9	81.9	81.0	79.9	78.7	77.4	75.9	74.4
		56.25°	87.9	86.6	85.7	84.8	83.7	82.5	81.1	79.6	78.0
		55°	91.7	90.5	89.6	88.6	87.5	86.2	84.7	83.2	81.6
		53.75°	95.5	94.4	93.5	92.5	91.4	89.9	88.4	86.8	85.1
		52.5°	99.3	98.4	97.4	96.3	95.1	93.6	92.0	90.4	88.8
		51.25°	103.4	102.4	101.3	100.2	98.8	97.2	95.6	93.9	92.4
		50°	107.4	106.3	105.2	104.0	102.5	100.8	99.1	97.4	96.1
		48.75°	111.2	110.2	109.1	107.7	106.0	104.4	102.7	101.0	99.6
		47.5°	114.9	113.8	112.8	111.3	109.6	107.8	106.1	104.6	103.1
		46.25°	118.5	117.4	116.1	114.5	113.0	111.2	109.5	108.0	106.6
		45°	121.7	120.8	119.3	117.6	116.0	114.4	112.9	111.3	109.8
		43.75°	124.7	123.6	122.1	120.6	118.8	117.3	116.1	114.6	112.9
		42.5°	127.6	126.3	124.8	123.2	121.6	120.3	119.0	117.6	116.0
		41.25°	130.1	128.8	127.4	125.8	124.4	123.3	122.0	120.5	118.9
		40°	132.5	131.2	129.8	128.3	127.2	126.1	124.9	123.4	121.7
		38.75°	134.9	133.7	132.2	131.1	130.1	128.9	127.6	126.2	124.6
		37.5°	137.1	135.9	134.7	133.7	132.7	131.7	130.3	128.9	127.4
		36.25°	139.3	138.1	137.2	136.3	135.3	134.2	133.0	131.5	130.1
		35°	141.3	140.4	139.5	138.7	137.7	136.6	135.4	134.1	132.8

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

45°	46.25°		33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°
1.3	1.3	33.75°	143.2	142.5	141.8	140.9	140.0	138.9	137.7	136.6	135.4
4.4	4.4	32.5°	145.1	144.4	143.8	143.0	142.0	141.1	140.1	139.0	137.5
5.1	5.0	31.25°	146.7	146.2	145.5	144.9	144.0	143.1	142.5	141.1	139.3
5.9	5.7	30°	147.9	147.7	147.2	146.6	145.9	145.1	144.3	142.8	141.0
7.5	7.2	28.75°	149.1	148.9	148.8	148.2	147.6	146.9	145.5	144.2	142.6
9.0	8.8	27.5°	150.2	150.0	149.9	149.7	149.1	148.0	146.7	145.4	144.1
10.8	10.5	26.25°	150.9	151.0	150.9	150.9	150.0	148.9	147.9	146.5	145.2
13.0	12.6	25°	151.5	151.8	151.7	151.2	150.8	149.7	148.7	147.6	146.3
15.2	14.8	23.75°	151.8	152.0	151.9	151.4	151.0	150.4	149.4	148.5	147.2
17.6	17.1	22.5°	151.8	151.8	151.8	151.6	151.2	151.0	150.1	149.2	148.1
20.4	19.9	21.25°	151.5	151.6	151.6	151.6	151.4	151.2	150.6	149.8	148.8
23.1	22.6	20°	151.2	151.3	151.3	151.6	151.6	151.4	151.2	150.3	149.4
26.1	25.4	18.75°	150.9	151.0	151.2	151.5	151.8	151.6	151.4	150.7	149.7
29.1	28.4	17.5°	150.6	150.8	151.1	151.4	151.8	151.7	151.4	150.9	150.0
32.2	31.3	16.25°	150.3	150.6	150.9	151.2	151.5	151.6	151.3	151.0	150.2
35.4	34.4	15°	150.0	150.4	150.6	150.8	151.1	151.4	151.2	150.9	150.4
38.7	37.6	13.75°	149.7	149.9	150.2	150.4	150.8	151.1	151.1	150.8	150.4
41.9	40.9	12.5°	149.2	149.5	149.7	150.0	150.4	150.8	151.0	150.7	150.4
45.3	44.2	11.25°	148.7	149.0	149.3	149.7	150.1	150.5	150.8	150.5	150.3
48.7	47.5	10°	148.3	148.7	149.1	149.5	149.9	150.2	150.5	150.4	150.1
52.1	50.8	8.75°	148.1	148.5	148.9	149.3	149.6	150.0	150.3	150.3	150.1
55.5	54.1	7.5°	148.0	148.3	148.7	149.1	149.5	149.9	150.2	150.2	150.0
59.0	57.5	6.25°	147.9	148.3	148.7	149.1	149.5	149.8	150.1	150.2	150.0
62.4	60.9	5°	147.9	148.3	148.7	149.1	149.4	149.8	150.0	150.2	150.0
65.9	64.4	3.75°	147.9	148.3	148.7	149.0	149.3	149.5	149.6	149.8	149.4
69.3	68.0	2.5°	147.6	147.9	148.2	148.4	148.6	148.8	149.0	149.1	148.8
72.8	71.6	1.25°	147.1	147.4	147.6	147.8	148.0	148.2	148.3	148.5	148.2
76.4	75.2	0°	146.6	146.9	147.1	147.2	147.4	147.5	147.7	147.9	147.6
80.1	78.8	-1.25°	146.5	146.8	146.9	147.0	147.1	147.2	147.4	147.6	147.2
83.8	82.4	-2.5°	146.4	146.7	146.7	146.8	146.9	147.0	147.1	147.2	146.8
87.4	86.0	-3.75°	146.2	146.5	146.6	146.6	146.7	146.7	146.9	146.9	146.4
91.0	89.5	-5°	145.8	146.1	146.2	146.2	146.3	146.4	146.5	146.5	146.0
94.6	93.1	-6.25°	145.4	145.7	145.8	145.8	145.9	145.9	146.1	145.9	145.5
98.2	96.6	-7.5°	145.0	145.2	145.4	145.4	145.5	145.5	145.6	145.4	145.0
101.6	100.0	-8.75°	144.6	144.8	144.9	145.0	145.0	145.1	145.2	144.9	144.5
104.9	103.2	-10°	144.1	144.3	144.5	144.4	144.4	144.5	144.5	144.2	143.9
108.3	106.3	-11.25°	143.4	143.7	144.0	143.9	143.9	143.9	143.8	143.4	143.1
111.2	109.3	-12.5°	142.6	142.8	143.0	143.1	143.3	143.4	143.1	142.6	142.2
114.2	112.2	-13.75°	141.7	141.9	142.1	142.2	142.4	142.6	142.2	141.8	141.1
117.1	115.0	-15°	140.9	140.9	141.1	141.3	141.4	141.4	141.1	140.7	140.1
120.0	118.2	-16.25°	140.1	140.1	140.2	140.3	140.4	140.3	139.9	139.5	138.8
122.7	121.5	-17.5°	139.2	139.2	139.3	139.3	139.4	139.1	138.6	138.1	137.4
125.9	124.6	-18.75°	138.0	138.3	138.3	138.3	138.2	137.8	137.4	136.7	136.0
129.0	127.2	-20°	136.4	136.8	137.2	137.2	136.8	136.4	136.0	135.2	134.5
131.6	129.6	-21.25°	134.7	135.2	135.5	135.7	135.4	135.0	134.4	133.7	132.9

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

45°	46.25°		33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°
133.7	131.9	-22.5°	133.0	133.4	133.8	133.8	133.7	133.5	132.8	132.0	131.1
135.7	133.9	-23.75°	131.6	131.7	131.9	131.9	131.8	131.6	131.0	130.3	129.3
137.7	135.8	-25°	130.1	130.2	130.0	129.9	129.9	129.5	129.0	128.4	127.4
139.4	137.6	-26.25°	128.6	128.6	128.2	127.9	127.7	127.3	126.9	126.2	125.4
141.0	139.4	-27.5°	127.1	126.7	126.4	126.0	125.4	125.0	124.5	123.8	123.2
142.4	140.9	-28.75°	124.9	124.7	124.5	123.9	123.3	122.7	122.1	121.5	120.7
143.7	142.2	-30°	122.5	122.6	122.2	121.7	121.1	120.4	119.6	119.0	118.2
145.0	143.4	-31.25°	120.1	120.0	119.8	119.4	118.8	118.0	117.3	116.4	115.7
146.0	144.5	-32.5°	117.4	117.3	117.2	117.0	116.4	115.7	114.8	113.9	113.2
146.8	145.6	-33.75°	114.6	114.6	114.4	114.2	114.0	113.2	112.2	111.4	110.4
147.6	146.4	-35°	111.7	111.7	111.4	111.3	111.1	110.4	109.5	108.6	107.6
148.2	147.0	-36.25°	108.4	108.4	108.3	108.2	107.8	107.4	106.6	105.6	104.7
148.7	147.5	-37.5°	104.8	105.0	105.0	104.6	104.3	104.0	103.4	102.5	101.6
149.2	148.0	-38.75°	101.2	101.1	101.0	101.1	100.8	100.0	99.7	99.3	98.0
149.4	148.4	-40°	96.6	96.2	96.5	97.3	96.2	95.7	95.6	95.3	94.2
149.6	148.6	-41.25°	90.8	90.7	91.1	91.3	91.3	91.0	90.4	90.2	90.1
149.6	148.7	-42.5°	84.0	84.3	84.4	85.0	85.9	85.0	84.5	84.7	85.0
149.6	148.8	-43.75°	76.3	76.9	77.4	78.3	78.8	78.4	78.2	78.8	78.9
149.5	148.8	-45°	69.1	69.4	70.4	71.8	72.2	71.4	72.2	73.1	73.2
149.5	148.8	-46.25°	62.4	63.6	65.0	66.0	66.1	66.3	67.0	67.7	67.8
149.6	148.9	-47.5°	57.9	59.2	60.2	61.0	61.7	62.2	62.2	62.9	63.8
149.6	148.9	-48.75°	53.8	55.0	56.1	57.1	57.8	58.2	58.4	59.1	60.0
149.7	149.0	-50°	50.0	51.4	52.5	53.5	54.1	54.7	55.2	55.5	56.3
149.7	148.9	-51.25°	46.6	48.0	49.1	50.0	50.8	51.5	52.0	52.3	53.0
149.1	148.3	-52.5°	43.4	44.6	45.5	46.6	47.7	48.3	48.7	49.2	49.9
148.5	147.6	-53.75°	39.6	40.6	41.8	43.1	44.5	44.8	45.3	46.0	46.8
147.8	147.0	-55°	35.3	36.5	37.9	39.2	40.3	41.0	41.7	42.6	43.7
147.2	146.4	-56.25°	31.0	32.6	34.1	35.4	36.3	37.1	38.3	39.6	40.7
146.8	145.9	-57.5°	27.7	29.1	30.5	31.6	32.8	34.0	35.4	36.6	37.8
146.4	145.5	-58.75°	24.6	25.8	27.3	28.8	30.1	31.3	32.5	33.7	35.1
146.0	145.0	-60°	22.0	23.5	25.0	26.4	27.6	28.7	29.9	31.3	32.6
145.5	144.6	-61.25°	20.0	21.5	22.8	24.1	25.4	26.6	27.6	29.0	30.3
145.0	144.0	-62.5°	18.1	19.6	20.9	22.3	23.5	24.6	25.6	26.8	28.1
144.4	143.4	-63.75°	16.6	18.0	19.3	20.5	21.6	22.7	23.7	24.8	26.0
143.8	142.8	-65°	15.3	16.6	17.7	18.8	20.0	21.0	21.9	22.9	24.1
143.1	142.1	-66.25°	14.0	15.2	16.3	17.3	18.4	19.4	20.3	21.1	22.2
142.2	141.3	-67.5°	12.8	13.9	15.0	15.9	16.9	17.8	18.6	19.4	20.3
141.3	140.4	-68.75°	11.7	12.7	13.7	14.6	15.5	16.3	17.1	17.8	18.6
140.3	139.3	-70°	10.6	11.6	12.5	13.3	14.1	14.9	15.6	16.2	16.9
139.2	138.2	-71.25°	9.7	10.5	11.3	12.1	12.8	13.6	14.2	14.8	15.4
138.0	137.0	-72.5°	8.7	9.5	10.3	11.0	11.7	12.3	12.9	13.4	13.9
136.6	135.5	-73.75°	7.9	8.5	9.2	9.9	10.5	11.1	11.6	12.1	12.5
135.1	134.0	-75°	7.0	7.6	8.3	8.8	9.4	9.9	10.3	10.8	11.1
133.5	132.5	-76.25°	6.3	6.8	7.3	7.8	8.2	8.7	9.1	9.5	9.8
131.9	130.9	-77.5°	5.6	5.9	6.4	6.8	7.2	7.6	8.0	8.3	8.6

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

45°	46.25°		33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°
130.1	129.1	-78.75°	4.9	5.2	5.6	6.0	6.3	6.7	7.0	7.2	7.5
128.3	127.1	-80°	4.2	4.4	4.8	5.1	5.5	5.8	6.0	6.2	6.4
126.4	125.2	-81.25°	3.5	3.7	4.1	4.4	4.7	4.9	5.1	5.3	5.4
124.3	123.1	-82.5°	3.0	3.2	3.4	3.6	3.9	4.1	4.2	4.3	4.5
122.2	121.0	-83.75°	2.5	2.6	2.8	3.0	3.1	3.3	3.4	3.5	3.6
119.8	118.8	-85°	2.0	2.1	2.3	2.4	2.5	2.7	2.8	2.8	2.9
117.4	116.3	-86.25°	1.6	1.7	1.8	1.9	2.0	2.0	2.1	2.1	2.2
114.9	113.8	-87.5°	1.3	1.3	1.4	1.5	1.6	1.7	1.7	1.8	1.8
112.2	111.2	-88.75°	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.5	1.5
109.5	108.6	-90°	4.1	4.0	4.0	4.0	3.9	3.9	3.9	3.9	3.8
106.7	105.7										
103.8	102.7										
100.5	99.6										
96.9	96.2										
93.2	92.2										
88.9	87.8										
83.8	83.0										
78.3	77.8										
72.5	73.1										
68.3	68.6										
64.3	64.4										
60.4	60.8										
57.0	57.5										
53.8	54.3										
50.7	51.2										
47.6	48.3										
44.6	45.3										
41.7	42.4										
38.8	39.8										
36.3	37.2										
33.8	34.8										
31.4	32.5										
29.2	30.2										
27.1	28.1										
25.1	26.0										
23.1	24.0										
21.3	22.1										
19.4	20.2										
17.7	18.4										
16.1	16.6										
14.5	15.0										
13.0	13.5										
11.6	12.1										
10.3	10.7										
9.0	9.3										

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

45°	46.25°		47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°
7.7	8.0	90°	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.6
6.6	6.9	88.75°	4.3	4.2	4.1	4.1	4.0	3.9	3.9	3.8	3.6
5.6	5.8	87.5°	4.8	4.7	4.6	4.6	4.5	4.5	4.4	4.3	4.2
4.6	4.8	86.25°	5.5	5.3	5.1	5.1	5.1	5.1	5.0	4.8	4.7
3.7	3.9	85°	7.0	6.7	6.5	6.4	6.3	6.2	6.0	5.7	5.4
3.0	3.1	83.75°	8.5	8.2	8.0	7.9	7.8	7.6	7.4	7.1	6.8
2.2	2.3	82.5°	10.1	9.7	9.5	9.4	9.2	9.1	8.9	8.5	8.1
1.9	2.0	81.25°	12.2	11.8	11.5	11.2	10.9	10.7	10.3	9.9	9.5
1.6	1.6	80°	14.4	14.0	13.6	13.3	13.0	12.7	12.3	11.7	11.1
3.8	3.8	78.75°	16.6	16.1	15.7	15.4	15.1	14.7	14.3	13.7	13.1
		77.5°	19.3	18.7	18.2	17.7	17.2	16.8	16.3	15.7	15.0
		76.25°	22.1	21.5	20.9	20.3	19.8	19.2	18.5	17.7	17.0
		75°	24.8	24.2	23.6	23.0	22.3	21.7	20.9	20.0	19.3
		73.75°	27.6	26.9	26.3	25.6	24.9	24.2	23.3	22.4	21.7
		72.5°	30.5	29.7	29.0	28.4	27.6	26.7	25.7	24.8	24.2
		71.25°	33.3	32.4	31.8	31.1	30.4	29.5	28.4	27.3	26.6
		70°	36.5	35.5	34.7	33.9	33.2	32.2	31.1	29.9	29.3
		68.75°	39.8	38.8	37.9	37.0	36.1	35.0	33.8	32.6	32.0
		67.5°	43.0	42.0	41.1	40.1	39.1	37.9	36.5	35.4	34.7
		66.25°	46.2	45.3	44.3	43.2	42.1	40.8	39.4	38.3	37.5
		65°	49.6	48.6	47.5	46.4	45.1	43.8	42.3	41.3	40.4
		63.75°	52.9	51.9	50.8	49.6	48.2	46.8	45.3	44.3	43.2
		62.5°	56.3	55.3	54.1	52.8	51.4	49.8	48.3	47.4	46.0
		61.25°	59.8	58.7	57.4	56.1	54.5	52.8	51.4	50.4	48.8
		60°	63.3	62.1	60.8	59.3	57.6	55.8	54.6	53.5	51.7
		58.75°	66.8	65.5	64.1	62.6	60.8	58.9	57.8	56.5	54.5
		57.5°	70.3	68.9	67.5	65.8	63.9	62.2	61.0	59.4	57.3
		56.25°	73.8	72.4	70.8	69.0	67.1	65.6	64.3	62.3	60.1
		55°	77.4	75.8	74.2	72.3	70.3	68.9	67.5	65.3	63.0
		53.75°	80.9	79.3	77.5	75.5	73.7	72.3	70.5	68.2	65.8
		52.5°	84.4	82.7	80.8	78.8	77.2	75.8	73.5	71.1	68.7
		51.25°	88.0	86.1	84.1	82.0	80.7	79.0	76.6	74.0	71.5
		50°	91.4	89.5	87.4	85.5	84.1	82.1	79.5	76.9	74.3
		48.75°	94.7	92.7	90.6	89.1	87.5	85.1	82.5	79.8	77.0
		47.5°	98.0	95.9	93.9	92.6	90.6	88.0	85.4	82.6	79.8
		46.25°	101.2	99.1	97.4	95.9	93.6	90.9	88.2	85.4	82.5
		45°	104.2	102.3	100.7	98.8	96.4	93.8	91.0	88.1	85.4
		43.75°	107.2	105.5	104.0	101.7	99.2	96.6	93.7	90.8	88.1
		42.5°	110.3	108.8	106.9	104.5	101.9	99.2	96.5	93.6	90.7
		41.25°	113.6	112.1	109.7	107.2	104.6	101.9	99.1	96.3	93.3
		40°	116.8	114.9	112.5	109.9	107.3	104.5	101.7	98.9	95.9
		38.75°	119.9	117.6	115.3	112.6	109.9	107.2	104.3	101.5	98.5
		37.5°	122.6	120.2	117.8	115.3	112.4	109.7	106.9	103.9	100.9
		36.25°	125.1	122.8	120.2	117.7	115.0	112.3	109.5	106.4	103.3
		35°	127.4	125.2	122.7	120.1	117.6	114.7	111.9	108.8	105.6

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

58.75°	60°		47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°
1.6	1.6	33.75°	129.7	127.4	125.0	122.5	120.0	117.2	114.2	111.2	107.8
3.6	3.6	32.5°	131.9	129.5	127.3	124.8	122.2	119.6	116.5	113.4	110.0
4.1	4.1	31.25°	133.9	131.6	129.4	127.1	124.4	121.7	118.8	115.4	112.1
4.6	4.7	30°	135.7	133.7	131.3	129.1	126.6	123.8	120.8	117.4	114.1
5.3	5.2	28.75°	137.4	135.4	133.2	131.0	128.7	125.7	122.7	119.4	116.0
6.6	6.6	27.5°	139.0	137.0	135.0	132.7	130.4	127.5	124.5	121.2	117.8
8.0	7.9	26.25°	140.6	138.6	136.6	134.3	131.9	129.2	126.1	123.0	119.5
9.4	9.3	25°	141.9	140.0	138.0	135.8	133.3	130.8	127.7	124.7	121.2
10.9	10.7	23.75°	143.0	141.3	139.2	137.2	134.7	132.2	129.3	126.1	122.5
12.9	12.5	22.5°	144.0	142.4	140.3	138.3	136.0	133.5	130.7	127.3	123.7
14.8	14.4	21.25°	144.8	143.3	141.4	139.4	137.2	134.6	131.8	128.3	124.9
16.8	16.3	20°	145.6	144.0	142.4	140.3	138.2	135.5	132.7	129.3	125.8
18.9	18.2	18.75°	146.3	144.8	143.3	141.1	138.9	136.2	133.4	130.2	126.7
21.3	20.4	17.5°	146.9	145.4	143.7	141.7	139.5	136.9	134.1	131.1	127.6
23.7	22.7	16.25°	147.2	145.7	144.1	142.2	140.0	137.6	134.8	131.8	128.3
26.0	25.0	15°	147.4	146.0	144.4	142.7	140.5	138.2	135.4	132.6	129.0
28.5	27.3	13.75°	147.5	146.3	144.7	143.1	140.9	138.7	135.9	133.1	129.6
31.0	29.7	12.5°	147.6	146.5	144.9	143.4	141.3	139.1	136.3	133.5	130.1
33.6	32.2	11.25°	147.7	146.6	145.1	143.6	141.6	139.4	136.7	133.9	130.6
36.2	34.7	10°	147.8	146.7	145.3	143.8	141.9	139.6	137.1	134.2	131.0
38.8	37.2	8.75°	148.0	146.8	145.5	143.9	142.1	139.9	137.4	134.5	131.4
41.6	39.8	7.5°	148.1	146.9	145.6	144.0	142.3	140.1	137.7	134.8	131.5
44.3	42.5	6.25°	148.1	147.0	145.7	144.1	142.3	140.0	137.5	134.5	131.3
47.0	45.1	5°	148.0	146.7	145.4	143.6	141.9	139.5	137.1	134.1	131.0
49.7	47.7	3.75°	147.4	146.1	144.8	143.1	141.4	139.1	136.7	133.7	130.6
52.5	50.3	2.5°	146.8	145.5	144.2	142.6	140.9	138.5	136.2	133.2	130.2
55.2	53.0	1.25°	146.2	144.9	143.6	142.0	140.3	138.0	135.7	132.7	129.8
57.9	55.6	0°	145.5	144.3	143.0	141.4	139.7	137.4	135.1	132.2	129.3
60.6	58.2	-1.25°	145.1	143.8	142.5	140.9	139.2	136.9	134.6	131.7	128.8
63.4	60.8	-2.5°	144.6	143.3	142.0	140.3	138.7	136.4	134.0	131.1	128.2
66.1	63.5	-3.75°	144.1	142.8	141.5	139.8	138.1	135.8	133.4	130.6	127.6
68.8	66.2	-5°	143.5	142.2	140.9	139.2	137.5	135.2	132.8	129.9	127.0
71.5	68.9	-6.25°	143.0	141.7	140.3	138.6	136.8	134.5	132.1	129.2	126.3
74.3	71.6	-7.5°	142.3	141.0	139.6	137.9	136.1	133.8	131.3	128.5	125.5
77.0	74.3	-8.75°	141.6	140.3	138.8	137.2	135.3	133.0	130.5	127.7	124.7
79.8	76.9	-10°	140.9	139.6	138.1	136.4	134.4	132.2	129.7	126.8	123.8
82.5	79.5	-11.25°	140.1	138.8	137.2	135.6	133.6	131.4	128.8	125.9	122.8
85.1	82.1	-12.5°	139.1	137.9	136.3	134.7	132.7	130.6	127.8	124.9	121.8
87.8	84.6	-13.75°	138.0	136.7	135.2	133.6	131.7	129.7	126.8	123.9	120.8
90.3	87.1	-15°	136.9	135.6	134.0	132.4	130.4	128.4	125.6	122.8	119.7
92.8	89.6	-16.25°	135.8	134.3	132.8	131.1	129.1	127.0	124.3	121.5	118.6
95.2	91.9	-17.5°	134.5	133.0	131.5	129.7	127.8	125.5	122.9	120.1	117.2
97.6	94.2	-18.75°	132.9	131.5	130.2	128.3	126.5	124.0	121.4	118.7	115.8
100.0	96.4	-20°	131.2	129.9	128.5	126.8	125.0	122.5	120.0	117.1	114.3
102.2	98.6	-21.25°	129.5	128.2	126.7	125.0	123.2	120.9	118.4	115.6	112.8

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

58.75°	60°		47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°
104.4	100.8	-22.5°	127.7	126.4	124.9	123.3	121.3	119.1	116.8	114.0	111.1
106.5	102.9	-23.75°	125.9	124.5	123.0	121.4	119.3	117.3	114.8	112.3	109.3
108.5	104.9	-25°	123.9	122.6	121.1	119.4	117.4	115.3	112.8	110.4	107.5
110.5	106.8	-26.25°	121.9	120.5	119.1	117.3	115.4	113.2	110.8	108.4	105.5
112.4	108.6	-27.5°	119.7	118.4	116.9	115.1	113.3	111.1	108.8	106.3	103.5
114.3	110.4	-28.75°	117.5	116.2	114.6	112.9	111.1	108.9	106.7	104.2	101.5
116.0	111.8	-30°	115.2	113.9	112.2	110.5	108.7	106.7	104.5	102.0	99.4
117.3	113.2	-31.25°	112.8	111.4	109.8	108.1	106.2	104.3	102.3	99.8	97.3
118.6	114.5	-32.5°	110.1	108.8	107.3	105.6	103.7	101.9	99.8	97.6	95.1
119.7	115.8	-33.75°	107.3	106.0	104.7	102.9	101.2	99.3	97.3	95.3	92.8
120.9	116.8	-35°	104.5	103.3	101.8	100.3	98.6	96.7	94.8	92.7	90.5
121.9	117.9	-36.25°	101.6	100.3	98.9	97.5	95.9	94.1	92.2	90.2	88.0
122.9	118.8	-37.5°	98.6	97.3	95.9	94.5	93.1	91.4	89.6	87.6	85.5
123.9	119.7	-38.75°	95.4	94.2	92.9	91.3	90.0	88.7	86.8	84.9	83.0
124.8	120.5	-40°	91.7	91.0	89.5	87.9	86.7	85.6	84.1	82.3	80.3
125.5	121.3	-41.25°	87.4	87.5	85.8	84.3	83.2	82.3	81.3	79.5	77.6
126.0	121.9	-42.5°	82.8	82.7	81.9	80.6	79.6	78.8	78.2	76.8	75.0
126.6	122.6	-43.75°	78.1	78.1	77.7	76.8	76.0	75.3	74.8	74.0	72.3
127.0	123.1	-45°	73.5	73.6	73.4	72.9	72.2	71.8	71.5	70.9	69.6
127.5	123.6	-46.25°	69.1	69.4	69.4	68.9	68.5	68.4	68.2	67.7	66.9
127.8	124.1	-47.5°	65.0	65.5	65.5	65.1	65.1	65.2	65.0	64.7	64.1
127.8	123.9	-48.75°	61.3	61.8	61.8	61.9	61.8	61.9	61.9	61.7	61.2
127.6	123.8	-50°	57.9	58.3	58.7	58.8	58.8	58.8	58.9	58.7	58.4
127.3	123.5	-51.25°	54.7	55.2	55.6	55.8	55.8	55.8	56.0	55.9	55.6
127.0	123.2	-52.5°	51.8	52.2	52.6	52.9	53.0	53.0	53.1	53.1	52.9
126.6	122.9	-53.75°	48.8	49.3	49.7	50.1	50.3	50.3	50.3	50.3	50.2
126.1	122.5	-55°	45.9	46.5	47.0	47.3	47.6	47.6	47.6	47.7	47.6
125.7	122.0	-56.25°	43.2	43.8	44.3	44.6	44.9	45.0	45.0	45.0	45.0
125.2	121.5	-57.5°	40.6	41.2	41.6	42.1	42.4	42.5	42.4	42.4	42.5
124.6	121.0	-58.75°	38.0	38.6	39.1	39.6	39.9	40.0	40.0	39.9	40.0
124.0	120.4	-60°	35.5	36.2	36.7	37.1	37.4	37.6	37.6	37.5	37.5
123.4	119.8	-61.25°	33.2	33.9	34.4	34.8	35.1	35.3	35.3	35.2	35.2
122.7	119.1	-62.5°	31.0	31.6	32.1	32.5	32.8	33.0	33.0	32.9	32.9
122.0	118.3	-63.75°	28.8	29.4	29.9	30.3	30.5	30.7	30.8	30.8	30.7
121.2	117.6	-65°	26.8	27.3	27.8	28.1	28.3	28.5	28.6	28.6	28.5
120.4	116.7	-66.25°	24.8	25.3	25.7	26.0	26.2	26.4	26.5	26.5	26.4
119.5	115.8	-67.5°	22.8	23.3	23.7	24.0	24.2	24.4	24.5	24.5	24.4
118.6	114.8	-68.75°	20.8	21.3	21.7	22.0	22.2	22.4	22.5	22.5	22.4
117.6	113.8	-70°	18.9	19.4	19.7	20.1	20.3	20.5	20.6	20.6	20.5
116.6	112.7	-71.25°	17.1	17.6	18.0	18.3	18.5	18.6	18.7	18.7	18.6
115.5	111.6	-72.5°	15.5	16.0	16.3	16.6	16.7	16.8	16.9	16.9	16.9
114.1	110.4	-73.75°	14.0	14.4	14.7	14.9	15.0	15.1	15.2	15.2	15.2
112.6	109.0	-75°	12.5	12.8	13.1	13.3	13.4	13.5	13.5	13.5	13.5
111.0	107.5	-76.25°	11.1	11.4	11.6	11.7	11.8	11.9	11.9	11.9	11.8
109.4	106.0	-77.5°	9.7	9.9	10.1	10.2	10.3	10.3	10.4	10.4	10.4

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

58.75°	60°		47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°
107.8	104.4	-78.75°	8.3	8.6	8.8	8.9	9.0	9.0	9.0	9.0	9.0
106.1	102.8	-80°	7.1	7.4	7.5	7.6	7.7	7.7	7.7	7.7	7.6
104.4	101.1	-81.25°	6.0	6.2	6.4	6.4	6.4	6.4	6.4	6.4	6.4
102.7	99.4	-82.5°	4.9	5.1	5.2	5.3	5.4	5.4	5.4	5.4	5.4
100.7	97.6	-83.75°	4.1	4.2	4.4	4.4	4.4	4.4	4.4	4.5	4.4
98.7	95.7	-85°	3.3	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5
96.6	93.7	-86.25°	2.4	2.5	2.7	2.7	2.7	2.8	2.8	2.8	2.9
94.5	91.7	-87.5°	2.1	2.2	2.2	2.3	2.3	2.3	2.4	2.4	2.4
92.4	89.6	-88.75°	1.7	1.8	1.8	1.8	1.9	1.9	1.9	2.0	2.0
90.2	87.5	-90°	3.7	3.7	3.6	3.5	3.5	3.4	3.3	3.2	3.1
88.0	85.3										
85.8	83.0										
83.3	80.8										
80.8	78.5										
78.3	76.1										
75.7	73.7										
73.1	71.2										
70.5	68.7										
68.0	66.2										
65.4	63.8										
62.8	61.3										
60.3	58.9										
57.8	56.5										
55.2	54.1										
52.5	51.8										
49.9	49.4										
47.3	46.9										
44.8	44.3										
42.3	41.9										
39.8	39.4										
37.4	37.1										
35.1	34.9										
32.8	32.6										
30.6	30.4										
28.4	28.3										
26.3	26.2										
24.3	24.2										
22.3	22.2										
20.4	20.3										
18.5	18.4										
16.8	16.7										
15.0	14.9										
13.3	13.2										
11.8	11.7										
10.3	10.2										

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

58.75°	60°		61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°
8.9	8.8	90°	1.6	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8
7.5	7.4	88.75°	3.6	3.5	3.4	3.3	3.2	3.1	3.0	2.9	2.8
6.4	6.4	87.5°	4.1	4.0	3.9	3.8	3.7	3.5	3.4	3.3	3.2
5.4	5.4	86.25°	4.6	4.5	4.3	4.2	4.1	4.0	3.8	3.7	3.6
4.4	4.4	85°	5.1	4.9	4.8	4.7	4.5	4.4	4.2	4.1	3.9
3.4	3.4	83.75°	6.3	5.9	5.6	5.3	5.0	4.8	4.6	4.5	4.3
2.9	3.0	82.5°	7.6	7.2	6.9	6.5	6.1	5.8	5.4	4.9	4.7
2.5	2.5	81.25°	8.9	8.5	8.1	7.7	7.3	6.9	6.4	6.0	5.6
2.0	2.1	80°	10.2	9.8	9.4	8.9	8.5	8.0	7.5	7.0	6.6
3.1	3.1	78.75°	11.9	11.2	10.6	10.1	9.6	9.1	8.6	8.1	7.6
		77.5°	13.8	13.0	12.3	11.5	10.8	10.2	9.7	9.1	8.6
		76.25°	15.6	14.9	14.1	13.3	12.4	11.6	10.7	10.1	9.5
		75°	17.5	16.7	15.8	15.0	14.1	13.2	12.2	11.3	10.5
		73.75°	19.5	18.5	17.6	16.7	15.8	14.8	13.8	12.8	11.7
		72.5°	21.7	20.6	19.4	18.4	17.5	16.4	15.3	14.2	13.1
		71.25°	23.9	22.7	21.5	20.3	19.1	18.0	16.9	15.7	14.5
		70°	26.1	24.9	23.6	22.4	21.0	19.7	18.4	17.2	15.9
		68.75°	28.3	27.0	25.7	24.4	23.0	21.6	20.0	18.7	17.3
		67.5°	30.8	29.2	27.8	26.4	25.0	23.4	21.8	20.2	18.7
		66.25°	33.2	31.6	30.0	28.4	26.9	25.3	23.6	21.9	20.1
		65°	35.6	33.9	32.3	30.6	28.9	27.2	25.4	23.6	21.7
		63.75°	38.1	36.3	34.6	32.8	30.9	29.1	27.2	25.2	23.2
		62.5°	40.6	38.7	36.9	35.0	33.1	31.1	29.0	26.9	24.8
		61.25°	43.1	41.1	39.2	37.2	35.2	33.1	30.7	28.5	26.3
		60°	45.6	43.6	41.5	39.4	37.3	35.1	32.6	30.2	27.9
		58.75°	48.2	46.1	43.9	41.7	39.4	37.1	34.5	31.9	29.4
		57.5°	50.7	48.5	46.3	44.0	41.5	39.0	36.4	33.7	30.9
		56.25°	53.3	51.0	48.7	46.2	43.7	41.0	38.2	35.4	32.5
		55°	55.9	53.5	51.0	48.5	45.8	43.0	40.1	37.2	34.2
		53.75°	58.5	56.0	53.4	50.7	48.0	45.0	41.9	38.9	35.8
		52.5°	61.0	58.4	55.8	53.0	50.1	47.1	43.9	40.7	37.4
		51.25°	63.6	60.9	58.1	55.2	52.3	49.1	45.8	42.4	39.1
		50°	66.2	63.4	60.5	57.5	54.4	51.1	47.7	44.2	40.6
		48.75°	68.8	65.8	62.8	59.7	56.5	53.2	49.7	46.0	42.2
		47.5°	71.3	68.3	65.2	61.9	58.5	55.2	51.6	47.8	43.7
		46.25°	73.9	70.8	67.4	64.0	60.6	57.1	53.5	49.5	45.4
		45°	76.4	73.2	69.7	66.1	62.6	59.0	55.4	51.3	47.0
		43.75°	78.9	75.6	71.9	68.2	64.5	60.9	57.2	52.9	48.5
		42.5°	81.4	77.9	74.1	70.3	66.5	62.7	58.9	54.6	50.1
		41.25°	83.7	80.1	76.3	72.4	68.4	64.5	60.4	56.2	51.6
		40°	86.0	82.3	78.4	74.4	70.3	66.3	62.0	57.7	53.0
		38.75°	88.3	84.5	80.5	76.4	72.2	67.9	63.6	59.1	54.5
		37.5°	90.6	86.7	82.6	78.4	74.1	69.6	65.1	60.5	55.8
		36.25°	92.8	88.8	84.6	80.3	75.8	71.2	66.6	62.0	57.2
		35°	94.9	90.9	86.6	82.2	77.5	72.8	68.1	63.3	58.5

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

72.5°	73.75°		61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°
1.8	1.7	33.75°	96.9	93.0	88.6	83.9	79.2	74.4	69.6	64.7	59.7
2.7	2.6	32.5°	98.9	94.9	90.5	85.6	80.8	75.9	71.0	66.0	61.0
3.1	3.0	31.25°	100.9	96.8	92.3	87.3	82.4	77.4	72.4	67.3	62.2
3.5	3.3	30°	102.9	98.5	93.9	88.9	83.9	78.8	73.8	68.6	63.3
3.8	3.7	28.75°	104.7	100.0	95.4	90.4	85.3	80.2	75.1	69.8	64.4
4.2	4.0	27.5°	106.1	101.5	96.8	91.9	86.7	81.6	76.4	71.0	65.4
4.6	4.4	26.25°	107.5	102.9	98.1	93.3	88.1	82.9	77.5	72.0	66.5
5.1	4.7	25°	108.8	104.3	99.4	94.6	89.4	84.1	78.6	73.1	67.4
6.1	5.6	23.75°	110.1	105.6	100.7	95.8	90.6	85.2	79.7	74.0	68.4
7.0	6.5	22.5°	111.3	106.8	101.9	96.9	91.7	86.2	80.7	75.0	69.3
8.0	7.4	21.25°	112.4	107.9	103.0	98.0	92.7	87.2	81.6	75.9	70.1
8.9	8.3	20°	113.5	108.9	104.1	98.9	93.7	88.1	82.5	76.7	70.9
9.9	9.2	18.75°	114.5	109.8	105.0	99.8	94.6	89.0	83.4	77.5	71.7
10.8	10.1	17.5°	115.5	110.7	105.9	100.7	95.5	89.9	84.2	78.3	72.4
12.0	11.0	16.25°	116.3	111.5	106.7	101.5	96.3	90.6	84.9	79.0	73.0
13.3	12.0	15°	117.0	112.3	107.5	102.3	97.0	91.4	85.6	79.7	73.7
14.6	13.3	13.75°	117.7	113.0	108.1	103.0	97.6	92.0	86.2	80.3	74.0
16.0	14.5	12.5°	118.3	113.7	108.8	103.6	98.3	92.7	86.7	80.6	74.3
17.3	15.8	11.25°	118.9	114.3	109.3	104.2	98.7	93.0	86.9	80.8	74.6
18.6	17.0	10°	119.4	114.8	109.8	104.5	98.9	93.2	87.1	81.0	74.8
19.9	18.2	8.75°	119.6	115.0	109.8	104.5	99.0	93.3	87.2	81.2	74.9
21.2	19.4	7.5°	119.5	114.9	109.8	104.6	99.0	93.3	87.3	81.3	75.0
22.7	20.5	6.25°	119.3	114.8	109.7	104.5	98.9	93.3	87.3	81.3	75.1
24.1	21.8	5°	119.1	114.6	109.5	104.4	98.8	93.3	87.3	81.3	75.1
25.6	23.1	3.75°	118.8	114.4	109.3	104.2	98.7	93.2	87.2	81.3	75.0
27.0	24.5	2.5°	118.5	114.1	109.0	104.0	98.5	93.0	87.1	81.2	75.0
28.4	25.8	1.25°	118.1	113.7	108.7	103.7	98.3	92.8	86.9	81.0	74.8
29.7	27.0	0°	117.7	113.3	108.4	103.4	98.0	92.5	86.7	80.8	74.7
31.1	28.3	-1.25°	117.2	112.9	108.0	103.0	97.6	92.2	86.4	80.6	74.4
32.6	29.6	-2.5°	116.7	112.4	107.5	102.6	97.3	91.9	86.1	80.3	74.2
34.1	30.9	-3.75°	116.1	111.8	107.0	102.2	96.8	91.5	85.7	79.9	73.9
35.6	32.2	-5°	115.5	111.2	106.5	101.7	96.3	91.0	85.3	79.5	73.5
37.1	33.5	-6.25°	114.9	110.6	105.9	101.1	95.8	90.5	84.8	79.1	73.2
38.6	34.9	-7.5°	114.2	109.9	105.2	100.5	95.2	90.0	84.3	78.6	72.7
40.0	36.2	-8.75°	113.4	109.2	104.6	99.8	94.6	89.3	83.8	78.1	72.3
41.4	37.5	-10°	112.6	108.4	103.8	99.1	93.9	88.7	83.2	77.5	71.7
42.8	38.8	-11.25°	111.7	107.5	103.0	98.3	93.2	88.0	82.5	76.9	71.2
44.2	40.1	-12.5°	110.8	106.6	102.2	97.4	92.4	87.3	81.8	76.3	70.6
45.6	41.3	-13.75°	109.8	105.6	101.3	96.6	91.6	86.4	81.1	75.6	70.0
47.0	42.6	-15°	108.8	104.6	100.3	95.6	90.7	85.6	80.3	74.9	69.3
48.4	43.8	-16.25°	107.7	103.5	99.4	94.6	89.8	84.7	79.5	74.1	68.6
49.7	45.0	-17.5°	106.5	102.5	98.3	93.6	88.9	83.8	78.6	73.3	67.8
51.0	46.2	-18.75°	105.3	101.3	97.2	92.5	87.8	82.8	77.7	72.4	67.1
52.2	47.3	-20°	103.9	100.1	96.0	91.4	86.7	81.8	76.8	71.5	66.3
53.5	48.4	-21.25°	102.4	98.7	94.7	90.3	85.6	80.7	75.8	70.6	65.4

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

72.5°	73.75°		61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°
54.6	49.5	-22.5°	100.9	97.3	93.2	89.0	84.4	79.6	74.7	69.7	64.5
55.8	50.5	-23.75°	99.3	95.8	91.7	87.6	83.2	78.5	73.6	68.7	63.6
56.9	51.5	-25°	97.7	94.1	90.1	86.1	81.8	77.3	72.5	67.6	62.6
57.9	52.5	-26.25°	96.0	92.4	88.5	84.6	80.3	76.0	71.4	66.6	61.6
58.9	53.5	-27.5°	94.3	90.7	86.9	83.0	78.8	74.6	70.2	65.5	60.6
59.9	54.4	-28.75°	92.6	88.9	85.3	81.4	77.3	73.1	68.8	64.4	59.6
60.9	55.2	-30°	90.6	87.2	83.6	79.7	75.8	71.7	67.4	63.1	58.5
61.8	56.1	-31.25°	88.6	85.3	81.8	78.0	74.2	70.2	66.0	61.8	57.4
62.6	56.9	-32.5°	86.5	83.4	80.0	76.4	72.6	68.6	64.6	60.4	56.1
63.5	57.6	-33.75°	84.5	81.4	78.1	74.6	70.9	67.1	63.1	59.0	54.8
64.2	58.4	-35°	82.4	79.4	76.2	72.9	69.2	65.5	61.6	57.6	53.5
65.0	59.1	-36.25°	80.2	77.3	74.2	71.0	67.5	63.9	60.1	56.1	52.1
65.7	59.7	-37.5°	78.1	75.2	72.2	69.1	65.8	62.2	58.5	54.7	50.8
66.4	60.3	-38.75°	75.9	73.1	70.3	67.2	64.0	60.5	56.9	53.2	49.4
67.0	60.8	-40°	73.7	71.0	68.2	65.2	62.1	58.8	55.3	51.7	48.0
67.4	61.1	-41.25°	71.5	68.9	66.2	63.3	60.3	57.1	53.7	50.2	46.6
67.7	61.4	-42.5°	69.1	66.8	64.1	61.3	58.4	55.3	52.0	48.6	45.2
68.0	61.7	-43.75°	66.8	64.6	62.0	59.3	56.5	53.5	50.4	47.1	43.7
68.3	62.0	-45°	64.4	62.3	59.9	57.3	54.6	51.7	48.7	45.6	42.3
68.5	62.2	-46.25°	62.0	60.1	57.8	55.3	52.7	49.9	47.0	44.0	40.8
68.6	62.3	-47.5°	59.6	57.8	55.7	53.3	50.8	48.1	45.3	42.4	39.4
68.8	62.4	-48.75°	57.3	55.5	53.6	51.3	48.8	46.3	43.6	40.8	37.9
68.8	62.5	-50°	55.0	53.3	51.4	49.3	46.9	44.5	41.9	39.2	36.5
68.8	62.5	-51.25°	52.7	51.0	49.2	47.3	45.0	42.7	40.2	37.6	35.1
68.8	62.5	-52.5°	50.4	48.8	47.1	45.2	43.1	40.8	38.5	36.1	33.6
68.8	62.5	-53.75°	48.0	46.6	44.9	43.2	41.2	39.0	36.8	34.5	32.1
68.7	62.4	-55°	45.7	44.3	42.8	41.2	39.3	37.2	35.1	32.9	30.6
68.5	62.3	-56.25°	43.5	42.1	40.7	39.1	37.4	35.4	33.4	31.3	29.1
68.3	62.1	-57.5°	41.2	40.0	38.6	37.1	35.4	33.7	31.7	29.7	27.6
68.1	61.9	-58.75°	38.9	37.9	36.6	35.1	33.6	31.9	30.1	28.1	26.2
67.8	61.7	-60°	36.7	35.7	34.5	33.1	31.7	30.1	28.4	26.6	24.8
67.5	61.4	-61.25°	34.4	33.6	32.5	31.2	29.9	28.4	26.7	25.1	23.4
67.2	61.1	-62.5°	32.2	31.6	30.5	29.3	28.0	26.6	25.1	23.6	21.9
66.8	60.8	-63.75°	30.1	29.6	28.6	27.4	26.2	24.9	23.6	22.1	20.5
66.4	60.4	-65°	28.0	27.5	26.6	25.5	24.4	23.3	22.0	20.6	19.1
65.9	60.0	-66.25°	25.9	25.5	24.7	23.7	22.7	21.6	20.4	19.1	17.7
65.4	59.5	-67.5°	23.9	23.5	22.8	22.0	21.0	20.0	18.9	17.6	16.5
64.9	59.0	-68.75°	21.9	21.6	21.1	20.3	19.4	18.4	17.3	16.3	15.2
64.3	58.5	-70°	20.1	19.8	19.3	18.5	17.7	16.7	15.9	15.0	14.0
63.7	57.9	-71.25°	18.3	17.9	17.5	16.8	16.0	15.4	14.6	13.7	12.8
63.0	57.3	-72.5°	16.5	16.2	15.8	15.2	14.6	14.0	13.3	12.5	11.6
62.3	56.7	-73.75°	14.7	14.4	14.2	13.8	13.2	12.6	12.0	11.2	10.4
61.6	56.1	-75°	13.1	12.9	12.7	12.3	11.8	11.2	10.6	9.9	9.3
60.8	55.4	-76.25°	11.6	11.5	11.3	10.9	10.4	9.9	9.3	8.9	8.4
60.1	54.7	-77.5°	10.2	10.0	9.8	9.5	9.0	8.7	8.4	8.0	7.5

REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

72.5°	73.75°		61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°
59.2	53.9	-78.75°	8.7	8.5	8.4	8.2	8.0	7.7	7.4	7.0	6.6
58.4	53.1	-80°	7.4	7.4	7.3	7.2	7.0	6.7	6.4	6.1	5.7
57.5	52.3	-81.25°	6.4	6.3	6.3	6.2	5.9	5.7	5.4	5.1	4.8
56.6	51.5	-82.5°	5.4	5.3	5.2	5.1	4.9	4.7	4.4	4.1	4.0
55.6	50.6	-83.75°	4.3	4.3	4.2	4.1	3.9	3.8	3.7	3.7	3.6
54.7	49.7	-85°	3.4	3.5	3.5	3.5	3.4	3.4	3.4	3.3	3.3
53.7	48.8	-86.25°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9	2.9
52.6	47.8	-87.5°	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.5
51.6	46.9	-88.75°	2.1	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.1
50.5	45.9	-90°	3.1	3.0	3.0	2.9	2.8	2.7	2.6	2.5	2.4
49.3	44.8										
48.0	43.8										
46.8	42.7										
45.5	41.5										
44.2	40.4										
42.9	39.2										
41.6	38.0										
40.3	36.8										
39.0	35.6										
37.6	34.4										
36.3	33.2										
35.0	31.9										
33.6	30.7										
32.3	29.4										
30.9	28.2										
29.6	27.0										
28.2	25.8										
26.9	24.6										
25.6	23.3										
24.2	22.1										
22.9	20.8										
21.5	19.6										
20.2	18.4										
18.8	17.3										
17.6	16.2										
16.4	15.1										
15.3	14.0										
14.1	13.0										
13.0	11.9										
11.8	10.8										
10.7	9.8										
9.6	9.0										
8.8	8.2										
7.9	7.4										
7.0	6.6										



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

72.5°	73.75°		75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°
6.2	5.7	90°	1.7	1.7	1.7	1.6	1.6	1.6	1.6	1.5	1.5
5.3	4.9	88.75°	2.5	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8
4.4	4.2	87.5°	2.9	2.8	2.7	2.6	2.5	2.3	2.2	2.1	1.9
3.9	3.8	86.25°	3.2	3.1	2.9	2.8	2.7	2.5	2.4	2.2	2.1
3.6	3.5	85°	3.5	3.4	3.2	3.1	2.9	2.7	2.6	2.4	2.2
3.2	3.1	83.75°	3.9	3.7	3.5	3.3	3.1	2.9	2.7	2.5	2.3
2.8	2.8	82.5°	4.2	4.0	3.8	3.6	3.3	3.1	2.9	2.7	2.4
2.5	2.4	81.25°	4.5	4.3	4.1	3.8	3.6	3.3	3.1	2.8	2.5
2.1	2.1	80°	5.0	4.6	4.3	4.1	3.8	3.5	3.2	3.0	2.7
2.4	2.3	78.75°	5.8	5.2	4.6	4.3	4.0	3.7	3.4	3.1	2.8
		77.5°	6.7	5.9	5.2	4.6	4.2	3.9	3.6	3.3	2.9
		76.25°	7.5	6.7	5.9	5.1	4.5	4.1	3.8	3.4	3.0
		75°	8.4	7.5	6.6	5.7	4.8	4.3	3.9	3.5	3.1
		73.75°	9.2	8.3	7.3	6.3	5.4	4.5	4.1	3.7	3.3
		72.5°	10.0	9.0	8.0	7.0	5.9	4.9	4.3	3.8	3.4
		71.25°	10.9	9.8	8.7	7.6	6.5	5.4	4.4	4.0	3.5
		70°	11.8	10.6	9.4	8.2	7.1	5.9	4.7	4.1	3.6
		68.75°	12.9	11.3	10.1	8.8	7.6	6.4	5.1	4.3	3.7
		67.5°	14.0	12.3	10.8	9.5	8.2	6.9	5.5	4.4	3.8
		66.25°	15.2	13.3	11.4	10.1	8.7	7.3	5.9	4.6	3.9
		65°	16.3	14.3	12.4	10.7	9.2	7.8	6.4	4.9	4.0
		63.75°	17.4	15.4	13.3	11.3	9.8	8.3	6.8	5.2	4.2
		62.5°	18.5	16.4	14.2	12.0	10.3	8.7	7.2	5.6	4.3
		61.25°	19.6	17.4	15.1	12.9	10.8	9.2	7.6	5.9	4.4
		60°	20.6	18.4	16.0	13.7	11.3	9.7	7.9	6.2	4.5
		58.75°	21.8	19.3	16.9	14.5	12.1	10.1	8.3	6.5	4.7
		57.5°	23.0	20.3	17.8	15.3	12.8	10.5	8.7	6.9	5.0
		56.25°	24.2	21.3	18.7	16.1	13.5	11.0	9.1	7.2	5.2
		55°	25.4	22.4	19.6	16.9	14.2	11.4	9.5	7.5	5.5
		53.75°	26.6	23.5	20.4	17.7	14.9	12.0	9.8	7.8	5.7
		52.5°	27.8	24.6	21.3	18.4	15.5	12.6	10.2	8.1	5.9
		51.25°	29.0	25.7	22.3	19.2	16.2	13.2	10.5	8.4	6.2
		50°	30.1	26.7	23.3	19.9	16.9	13.8	10.9	8.7	6.4
		48.75°	31.2	27.8	24.2	20.6	17.5	14.3	11.2	8.9	6.6
		47.5°	32.4	28.8	25.1	21.4	18.1	14.9	11.6	9.2	6.9
		46.25°	33.6	29.9	26.1	22.2	18.8	15.4	12.1	9.5	7.1
		45°	34.8	30.8	26.9	23.0	19.4	16.0	12.6	9.8	7.3
		43.75°	36.0	31.8	27.8	23.8	20.0	16.5	13.0	10.0	7.5
		42.5°	37.1	32.8	28.7	24.6	20.6	17.0	13.4	10.3	7.7
		41.25°	38.3	33.8	29.5	25.3	21.1	17.5	13.9	10.5	7.9
		40°	39.3	34.8	30.3	26.1	21.8	18.0	14.3	10.7	8.1
		38.75°	40.4	35.7	31.1	26.8	22.4	18.5	14.7	11.0	8.3
		37.5°	41.4	36.7	31.9	27.5	23.1	19.0	15.1	11.2	8.4
		36.25°	42.4	37.6	32.7	28.2	23.7	19.4	15.4	11.5	8.6
		35°	43.4	38.5	33.5	28.9	24.3	19.9	15.8	11.8	8.8



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

86.25°	87.5°		75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°
1.5	1.5	33.75°	44.4	39.4	34.3	29.5	24.8	20.3	16.2	12.1	9.0
1.7	1.7	32.5°	45.3	40.2	35.1	30.1	25.4	20.7	16.5	12.3	9.1
1.8	1.7	31.25°	46.2	41.0	35.8	30.7	25.9	21.0	16.8	12.6	9.3
1.9	1.8	30°	47.1	41.8	36.5	31.3	26.4	21.5	17.1	12.9	9.4
2.0	1.8	28.75°	48.0	42.6	37.2	31.9	26.9	21.9	17.4	13.1	9.6
2.1	1.9	27.5°	48.8	43.4	37.9	32.4	27.4	22.3	17.7	13.4	9.7
2.2	2.0	26.25°	49.7	44.1	38.6	33.0	27.8	22.6	18.0	13.6	9.8
2.3	2.0	25°	50.4	44.8	39.2	33.5	28.2	23.0	18.3	13.8	9.9
2.4	2.1	23.75°	51.2	45.4	39.8	34.0	28.6	23.3	18.5	14.0	10.1
2.5	2.1	22.5°	51.9	46.1	40.3	34.4	29.0	23.7	18.8	14.2	10.2
2.6	2.2	21.25°	52.5	46.7	40.7	34.9	29.3	24.0	19.0	14.4	10.3
2.6	2.3	20°	53.2	47.2	41.2	35.3	29.6	24.3	19.2	14.6	10.4
2.7	2.3	18.75°	53.7	47.6	41.5	35.6	30.0	24.5	19.4	14.8	10.5
2.8	2.4	17.5°	54.2	48.0	41.9	36.0	30.2	24.8	19.6	14.9	10.6
2.9	2.4	16.25°	54.5	48.3	42.2	36.3	30.5	25.0	19.7	15.1	10.6
3.0	2.5	15°	54.9	48.6	42.5	36.5	30.8	25.2	19.9	15.2	10.7
3.1	2.6	13.75°	55.2	48.9	42.8	36.8	31.0	25.4	20.0	15.3	10.8
3.2	2.6	12.5°	55.4	49.2	43.0	37.0	31.2	25.6	20.2	15.4	10.8
3.2	2.7	11.25°	55.6	49.4	43.2	37.2	31.4	25.8	20.3	15.5	10.9
3.3	2.7	10°	55.8	49.6	43.3	37.4	31.5	25.9	20.4	15.6	10.9
3.4	2.8	8.75°	56.0	49.7	43.5	37.5	31.7	26.0	20.5	15.7	11.0
3.5	2.8	7.5°	56.1	49.8	43.5	37.6	31.8	26.1	20.5	15.8	11.0
3.6	2.9	6.25°	56.2	49.9	43.6	37.7	31.9	26.2	20.6	15.8	11.1
3.7	2.9	5°	56.2	49.9	43.6	37.8	31.9	26.3	20.7	15.9	11.1
3.7	3.0	3.75°	56.2	49.9	43.7	37.8	32.0	26.3	20.7	15.9	11.1
3.8	3.0	2.5°	56.2	49.9	43.6	37.8	32.0	26.4	20.7	15.9	11.1
3.9	3.1	1.25°	56.1	49.8	43.6	37.8	32.0	26.4	20.7	15.9	11.1
4.0	3.1	0°	56.0	49.8	43.5	37.8	32.0	26.4	20.7	15.9	11.1
4.0	3.2	-1.25°	55.9	49.6	43.4	37.7	31.9	26.3	20.7	15.9	11.1
4.1	3.2	-2.5°	55.7	49.5	43.3	37.6	31.8	26.2	20.6	15.8	11.1
4.2	3.3	-3.75°	55.5	49.3	43.2	37.5	31.7	26.1	20.6	15.8	11.1
4.2	3.3	-5°	55.3	49.1	43.0	37.3	31.6	26.0	20.5	15.8	11.0
4.3	3.4	-6.25°	55.0	48.9	42.8	37.1	31.4	25.9	20.4	15.7	11.0
4.4	3.4	-7.5°	54.7	48.6	42.6	36.9	31.3	25.8	20.3	15.6	11.0
4.5	3.5	-8.75°	54.4	48.3	42.4	36.7	31.1	25.6	20.2	15.5	10.9
4.7	3.5	-10°	54.0	48.0	42.1	36.5	30.9	25.4	20.1	15.4	10.9
4.8	3.6	-11.25°	53.6	47.7	41.8	36.2	30.6	25.2	19.9	15.3	10.8
5.0	3.6	-12.5°	53.2	47.3	41.4	35.9	30.4	25.0	19.8	15.2	10.7
5.1	3.6	-13.75°	52.7	46.9	41.1	35.6	30.1	24.8	19.6	15.1	10.7
5.3	3.7	-15°	52.2	46.4	40.7	35.2	29.8	24.5	19.4	14.9	10.6
5.4	3.7	-16.25°	51.6	45.9	40.3	34.8	29.5	24.3	19.2	14.8	10.5
5.6	3.7	-17.5°	51.1	45.4	39.9	34.5	29.2	24.0	19.0	14.6	10.4
5.7	3.8	-18.75°	50.5	44.9	39.4	34.0	28.8	23.7	18.8	14.5	10.3
5.8	3.8	-20°	49.9	44.3	38.9	33.6	28.4	23.4	18.6	14.3	10.2
5.9	3.9	-21.25°	49.2	43.7	38.4	33.1	28.0	23.0	18.4	14.1	10.1



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

86.25°	87.5°		75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°
6.1	3.9	-22.5°	48.5	43.1	37.9	32.6	27.6	22.7	18.1	13.9	10.0
6.2	3.9	-23.75°	47.8	42.5	37.3	32.1	27.2	22.3	17.9	13.7	9.9
6.3	3.9	-25°	47.1	41.8	36.7	31.6	26.8	22.0	17.6	13.5	9.8
6.4	4.0	-26.25°	46.3	41.2	36.1	31.1	26.3	21.6	17.3	13.2	9.6
6.5	4.0	-27.5°	45.5	40.5	35.5	30.5	25.9	21.2	17.0	13.0	9.5
6.6	4.0	-28.75°	44.7	39.8	34.9	30.0	25.4	20.7	16.7	12.7	9.3
6.7	4.1	-30°	43.9	39.0	34.2	29.4	24.9	20.3	16.4	12.5	9.2
6.8	4.1	-31.25°	43.0	38.3	33.5	28.9	24.4	19.9	16.1	12.2	9.0
6.9	4.1	-32.5°	42.1	37.5	32.8	28.3	23.8	19.5	15.8	12.0	8.9
7.0	4.1	-33.75°	41.2	36.7	32.1	27.7	23.3	19.1	15.4	11.7	8.7
7.1	4.1	-35°	40.3	35.9	31.4	27.1	22.8	18.7	15.1	11.4	8.6
7.1	4.2	-36.25°	39.4	35.0	30.6	26.4	22.2	18.3	14.7	11.1	8.4
7.2	4.2	-37.5°	38.4	34.2	29.8	25.8	21.6	17.8	14.3	10.8	8.2
7.3	4.2	-38.75°	37.5	33.3	29.1	25.1	21.1	17.4	14.0	10.6	8.0
7.3	4.2	-40°	36.5	32.4	28.4	24.4	20.5	17.0	13.6	10.4	7.8
7.4	4.2	-41.25°	35.5	31.4	27.6	23.7	19.8	16.5	13.2	10.1	7.7
7.5	4.2	-42.5°	34.4	30.5	26.8	23.0	19.3	16.1	12.8	9.9	7.5
7.5	4.3	-43.75°	33.3	29.6	26.0	22.3	18.8	15.6	12.4	9.6	7.3
7.5	4.3	-45°	32.2	28.7	25.2	21.6	18.2	15.1	12.0	9.4	7.1
7.6	4.3	-46.25°	31.0	27.8	24.3	20.8	17.6	14.6	11.5	9.1	6.8
7.6	4.3	-47.5°	29.9	26.8	23.5	20.1	17.1	14.1	11.1	8.8	6.6
7.6	4.3	-48.75°	28.8	25.8	22.6	19.4	16.5	13.6	10.7	8.6	6.4
7.7	4.3	-50°	27.7	24.8	21.8	18.7	15.9	13.1	10.4	8.3	6.2
7.7	4.3	-51.25°	26.6	23.8	20.9	18.0	15.3	12.5	10.1	8.0	6.0
7.7	4.3	-52.5°	25.5	22.8	20.0	17.3	14.7	12.0	9.7	7.7	5.7
7.7	4.3	-53.75°	24.4	21.8	19.1	16.6	14.0	11.4	9.4	7.4	5.5
7.7	4.3	-55°	23.3	20.7	18.3	15.9	13.4	10.9	9.0	7.2	5.3
7.7	4.3	-56.25°	22.2	19.7	17.5	15.2	12.7	10.5	8.7	6.9	5.0
7.7	4.3	-57.5°	21.0	18.7	16.7	14.4	12.1	10.0	8.3	6.6	4.8
7.7	4.3	-58.75°	19.9	17.8	15.8	13.7	11.4	9.6	7.9	6.3	4.5
7.7	4.3	-60°	18.7	16.9	15.0	12.9	10.8	9.2	7.6	5.9	4.3
7.7	4.3	-61.25°	17.7	16.0	14.1	12.2	10.3	8.8	7.2	5.6	4.2
7.6	4.3	-62.5°	16.7	15.0	13.3	11.4	9.8	8.3	6.8	5.3	4.1
7.6	4.3	-63.75°	15.7	14.1	12.4	10.7	9.3	7.9	6.4	5.0	4.0
7.6	4.3	-65°	14.7	13.2	11.5	10.1	8.8	7.4	6.1	4.7	3.9
7.5	4.3	-66.25°	13.7	12.2	10.7	9.5	8.3	7.0	5.7	4.3	3.8
7.5	4.2	-67.5°	12.7	11.3	10.0	8.9	7.8	6.5	5.3	4.2	3.6
7.4	4.2	-68.75°	11.7	10.4	9.4	8.3	7.2	6.1	4.9	4.0	3.5
7.4	4.2	-70°	10.6	9.7	8.7	7.8	6.7	5.6	4.5	3.9	3.4
7.3	4.2	-71.25°	9.8	9.0	8.1	7.2	6.2	5.1	4.2	3.8	3.3
7.3	4.2	-72.5°	9.1	8.3	7.4	6.6	5.7	4.7	4.1	3.6	3.2
7.2	4.2	-73.75°	8.3	7.6	6.8	6.0	5.1	4.3	3.9	3.5	3.1
7.1	4.2	-75°	7.5	6.9	6.1	5.4	4.6	4.1	3.7	3.3	2.9
7.1	4.1	-76.25°	6.8	6.1	5.5	4.8	4.2	3.9	3.5	3.2	2.8
7.0	4.1	-77.5°	6.0	5.4	4.8	4.3	4.0	3.7	3.4	3.0	2.7



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

86.25°	87.5°		75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°
6.9	4.1	-78.75°	5.3	4.7	4.3	4.0	3.8	3.5	3.2	2.9	2.6
6.8	4.1	-80°	4.5	4.2	4.0	3.8	3.5	3.3	3.0	2.7	2.5
6.7	4.0	-81.25°	4.0	3.9	3.7	3.5	3.3	3.1	2.8	2.6	2.4
6.6	4.0	-82.5°	3.7	3.6	3.4	3.2	3.1	2.8	2.6	2.4	2.2
6.5	4.0	-83.75°	3.4	3.2	3.1	3.0	2.8	2.6	2.5	2.3	2.1
6.4	4.0	-85°	3.0	2.9	2.8	2.7	2.6	2.4	2.3	2.1	2.0
6.3	3.9	-86.25°	2.7	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.9
6.2	3.9	-87.5°	2.4	2.3	2.2	2.2	2.1	2.0	1.9	1.8	1.7
6.1	3.9	-88.75°	2.0	2.0	1.9	1.9	1.8	1.8	1.7	1.7	1.6
6.0	3.8	-90°	2.2	2.2	2.1	2.1	2.0	1.9	1.9	1.8	1.7
5.8	3.8										
5.7	3.8										
5.6	3.7										
5.4	3.7										
5.3	3.6										
5.2	3.6										
5.0	3.6										
4.9	3.5										
4.7	3.5										
4.5	3.4										
4.4	3.4										
4.3	3.3										
4.2	3.3										
4.1	3.3										
4.1	3.2										
4.0	3.2										
3.9	3.1										
3.8	3.1										
3.8	3.0										
3.7	3.0										
3.6	2.9										
3.5	2.8										
3.4	2.8										
3.4	2.7										
3.3	2.7										
3.2	2.6										
3.1	2.6										
3.0	2.5										
2.9	2.5										
2.8	2.4										
2.8	2.3										
2.7	2.3										
2.6	2.2										
2.5	2.2										
2.4	2.1										



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

86.25°	87.5°		88.75°	90°
2.3	2.0	90°	1.5	1.5
2.2	2.0	88.75°	1.6	1.5
2.1	1.9	87.5°	1.6	1.5
2.0	1.9	86.25°	1.6	1.5
2.0	1.8	85°	1.7	1.5
1.9	1.7	83.75°	1.7	1.5
1.8	1.7	82.5°	1.7	1.5
1.7	1.6	81.25°	1.8	1.5
1.6	1.6	80°	1.8	1.5
1.7	1.6	78.75°	1.8	1.5
		77.5°	1.9	1.5
		76.25°	1.9	1.5
		75°	1.9	1.5
		73.75°	1.9	1.5
		72.5°	2.0	1.5
		71.25°	2.0	1.5
		70°	2.0	1.5
		68.75°	2.1	1.5
		67.5°	2.1	1.5
		66.25°	2.1	1.5
		65°	2.1	1.5
		63.75°	2.2	1.5
		62.5°	2.2	1.5
		61.25°	2.2	1.5
		60°	2.2	1.5
		58.75°	2.3	1.5
		57.5°	2.3	1.5
		56.25°	2.3	1.5
		55°	2.3	1.5
		53.75°	2.4	1.5
		52.5°	2.4	1.5
		51.25°	2.4	1.5
		50°	2.4	1.5
		48.75°	2.5	1.5
		47.5°	2.5	1.5
		46.25°	2.5	1.5
		45°	2.5	1.5
		43.75°	2.5	1.5
		42.5°	2.6	1.5
		41.25°	2.6	1.5
		40°	2.6	1.5
		38.75°	2.6	1.5
		37.5°	2.6	1.5
		36.25°	2.7	1.5
		35°	2.7	1.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	2.7	1.5
32.5°	2.7	1.5
31.25°	2.7	1.5
30°	2.7	1.5
28.75°	2.8	1.5
27.5°	2.8	1.5
26.25°	2.8	1.5
25°	2.8	1.5
23.75°	2.8	1.5
22.5°	2.8	1.5
21.25°	2.8	1.5
20°	2.8	1.5
18.75°	2.8	1.5
17.5°	2.9	1.5
16.25°	2.9	1.5
15°	2.9	1.5
13.75°	2.9	1.5
12.5°	2.9	1.5
11.25°	2.9	1.5
10°	2.9	1.5
8.75°	2.9	1.5
7.5°	2.9	1.5
6.25°	2.9	1.5
5°	2.9	1.5
3.75°	2.9	1.5
2.5°	2.9	1.5
1.25°	2.9	1.5
0°	2.9	1.5
-1.25°	2.9	1.5
-2.5°	2.9	1.5
-3.75°	2.9	1.5
-5°	2.9	1.5
-6.25°	2.9	1.5
-7.5°	2.9	1.5
-8.75°	2.9	1.5
-10°	2.9	1.5
-11.25°	2.9	1.5
-12.5°	2.9	1.5
-13.75°	2.9	1.5
-15°	2.9	1.5
-16.25°	2.8	1.5
-17.5°	2.8	1.5
-18.75°	2.8	1.5
-20°	2.8	1.5
-21.25°	2.8	1.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	2.8	1.5
-23.75°	2.8	1.5
-25°	2.8	1.5
-26.25°	2.8	1.5
-27.5°	2.7	1.5
-28.75°	2.7	1.5
-30°	2.7	1.5
-31.25°	2.7	1.5
-32.5°	2.7	1.5
-33.75°	2.7	1.5
-35°	2.6	1.5
-36.25°	2.6	1.5
-37.5°	2.6	1.5
-38.75°	2.6	1.5
-40°	2.6	1.5
-41.25°	2.6	1.5
-42.5°	2.5	1.5
-43.75°	2.5	1.5
-45°	2.5	1.5
-46.25°	2.5	1.5
-47.5°	2.4	1.5
-48.75°	2.4	1.5
-50°	2.4	1.5
-51.25°	2.4	1.5
-52.5°	2.4	1.5
-53.75°	2.3	1.5
-55°	2.3	1.5
-56.25°	2.3	1.5
-57.5°	2.3	1.5
-58.75°	2.2	1.5
-60°	2.2	1.5
-61.25°	2.2	1.5
-62.5°	2.1	1.5
-63.75°	2.1	1.5
-65°	2.1	1.5
-66.25°	2.1	1.5
-67.5°	2.0	1.5
-68.75°	2.0	1.5
-70°	2.0	1.5
-71.25°	1.9	1.5
-72.5°	1.9	1.5
-73.75°	1.9	1.5
-75°	1.9	1.5
-76.25°	1.8	1.5
-77.5°	1.8	1.5



REPORT NUMBER: P394845 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 303-S1-LEDB1-2700-UNV-T2-DIM10-EDGE

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	1.8	1.5
-80°	1.7	1.5
-81.25°	1.7	1.5
-82.5°	1.7	1.5
-83.75°	1.7	1.5
-85°	1.6	1.5
-86.25°	1.6	1.5
-87.5°	1.6	1.5
-88.75°	1.5	1.5
-90°	1.6	1.5

(END OF REPORT)