

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220353

Luminaire Tested: **9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29415)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 746.4 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.63
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220353

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220353

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	86	83	96	90	86	83	89	85	82	87	84	81	86	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	73
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	77	73	71	70
9	84	77	72	69	84	76	72	68	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	68	66	72	68	65	71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	791529
5°	794156
10°	737308
15°	612839
20°	422345
25°	249056
30°	111320
35°	47462
40°	19000
45°	6838
50°	2303
55°	688
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P220353

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	20.0
10°-20°	323.0	43.3
20°-30°	209.3	28.0
30°-40°	55.0	7.4
40°-50°	9.2	1.2
50°-60°	1.0	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.3	91.3
0°-40°	736.2	98.6
0°-60°	746.4	100.0
0°-90°	746.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	746.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1604	
5°	1604	149
15°	1200	323
25°	458	209
35°	79	55
45°	10	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220353

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1604.3
1°	1599.0
2°	1597.4
3°	1600.5
4°	1604.3
5°	1603.5
6°	1594.4
7°	1576.2
8°	1546.7
9°	1511.8
10°	1471.7
11°	1427.8
12°	1380.1
13°	1327.8
14°	1267.2
15°	1199.8
16°	1125.6
17°	1046.8
18°	965.7
19°	883.2
20°	804.4
22.5°	621.9
25°	457.5
26°	396.9
27°	336.3
28°	281.8
29°	234.8
30°	195.4
32.5°	122.7
35°	78.8
37.5°	48.5
40°	29.5
42.5°	17.4
45°	9.8
47.5°	5.3
50°	3.0
52.5°	1.5
55°	0.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P220353

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)