

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220368

Luminaire Tested: **9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29416)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 753.3 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220368

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220368

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	74	68	64	82	74	68	64	73	67	64	71	67	63	70	66	63	62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	433237
5°	443559
10°	431553
15°	391056
20°	334190
25°	286183
30°	219280
35°	150516
40°	94999
45°	55192
50°	11513
55°	688
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P220368

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	11.2
10°-20°	211.3	28.1
20°-30°	237.4	31.5
30°-40°	157.9	21.0
40°-50°	59.8	7.9
50°-60°	2.3	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.2	70.8
0°-40°	691.2	91.7
0°-60°	753.3	100.0
0°-90°	753.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	878	
5°	896	85
15°	766	211
25°	526	237
35°	250	158
45°	79	60
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220368

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	878.1
1°	875.6
2°	877.2
3°	883.1
4°	889.7
5°	895.6
6°	898.9
7°	896.4
8°	888.1
9°	875.6
10°	861.4
11°	844.7
12°	827.2
13°	808.9
14°	788.1
15°	765.6
16°	738.9
17°	711.4
18°	684.8
19°	660.6
20°	636.5
21°	614.8
22°	592.3
23°	569.8
24°	548.2
25°	525.7
26°	502.3
27°	476.5
28°	448.2
29°	415.7
30°	384.9
32.5°	314.1
35°	249.9
37.5°	194.1
40°	147.5
42.5°	110.8
45°	79.1
47.5°	45.0
50°	15.0
52.5°	1.7
55°	0.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: P220368

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4097-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)