

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221262

Luminaire Tested: **9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29409)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.2 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	101	98	96	93	94	91	89	87	78	77	75		66	65	64		55	54	54	49
2	96	91	87	83	89	85	81	79	74	71	69		63	62	61		54	53	52	48
3	91	85	80	76	85	79	75	72	70	67	65		61	59	58		52	51	51	47
4	86	79	74	70	81	75	70	67	66	63	61		59	57	55		51	50	49	46
5	83	75	69	66	77	71	66	63	64	60	58		57	55	53		50	49	48	46
6	79	71	66	62	74	68	63	60	61	58	55		55	53	51		49	48	47	45
7	76	68	62	59	72	65	60	57	59	56	53		54	51	50		49	47	46	44
8	73	65	60	56	69	62	58	55	57	54	52		52	50	48		48	46	45	44
9	71	62	57	54	67	60	56	53	55	52	50		51	49	47		47	46	45	43
10	68	60	55	52	65	58	54	51	54	51	49		50	48	46		46	45	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2394864
5°	1653539
10°	595928
15°	121618
20°	57597
25°	28308
30°	10198
35°	5361
40°	3671
45°	3419
50°	3147
55°	2839
60°	2368
65°	1868
70°	2308
75°	1525
80°	2273
85°	0



TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.3	32.8
10°-20°	90.8	11.9
20°-30°	24.9	3.3
30°-40°	6.1	0.8
40°-50°	3.6	0.5
50°-60°	2.9	0.4
60°-70°	1.7	0.2
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.5	0.1
100°-110°	1.0	0.1
110°-120°	1.7	0.2
120°-130°	2.9	0.4
130°-140°	3.6	0.5
140°-150°	6.1	0.8
150°-160°	24.9	3.3
160°-170°	90.8	11.9
170°-180°	249.3	32.8
0°-30°	365.0	48.0
0°-40°	371.1	48.8
0°-60°	377.6	49.6
0°-90°	380.6	50.0
90°-120°	3.2	0.4
90°-150°	15.8	2.1
90°-180°	381.0	50.1
0°-180°	761.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4854	
5°	3339	249
15°	238	91
25°	52	25
35°	9	6
45°	5	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	0
95°	0	0
105°	1	1
115°	2	2
125°	3	3
135°	5	4
145°	9	6
155°	52	25
165°	238	91
175°	3339	249
180°	4854	



TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4854.0
1°	4754.1
2°	4525.0
3°	4182.9
4°	3768.5
5°	3338.7
6°	2911.3
7°	2480.6
8°	2038.6
9°	1599.9
10°	1189.5
11°	841.0
12°	584.2
13°	412.0
14°	305.5
15°	238.1
17.5°	151.9
20°	109.7
22.5°	80.4
25°	52.0
27.5°	30.1
30°	17.9
32.5°	11.4
35°	8.9
37.5°	7.3
40°	5.7
42.5°	4.9
45°	4.9
47.5°	4.1
50°	4.1
52.5°	4.1
55°	3.3
57.5°	2.4
60°	2.4
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.6
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.8
100°	0.8
102.5°	0.8
105°	0.8
107.5°	0.8
110°	1.6
112.5°	1.6
115°	1.6
117.5°	1.6
120°	2.4
122.5°	2.4
125°	3.3
127.5°	4.1
130°	4.1
132.5°	4.1
135°	4.9
137.5°	4.9
140°	5.7
142.5°	7.3
145°	8.9
147.5°	11.4
150°	17.9
152.5°	30.1
155°	52.0
157.5°	80.4
160°	109.7
162.5°	151.9
165°	238.1
166°	305.5
167°	412.0
168°	584.2
169°	841.0
170°	1189.5
171°	1599.9
172°	2038.6
173°	2480.6
174°	2911.3
175°	3338.7
176°	3768.5
177°	4182.9
178°	4525.0
179°	4754.1



TEST NUMBER: P221262

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

180° | $\frac{0^\circ}{4854.0}$

(END OF REPORT)