

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220865

Luminaire Tested: **9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220865  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29493)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 792.1 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220865  
CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220865

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	90	87	85	84
5	99	92	87	84	97	91	87	84	89	86	83	88	85	82	86	84	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77
7	92	84	80	76	91	84	79	76	83	79	76	82	78	75	81	77	75	74
8	89	81	76	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71
9	86	78	73	70	85	77	73	70	77	73	70	76	72	70	75	72	69	68
10	83	75	70	67	82	75	70	67	74	70	67	73	70	67	73	69	67	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	247456
5°	239264
10°	210981
15°	162418
20°	100756
25°	61638
30°	41959
35°	5556
40°	1578
45°	384
50°	307
55°	194
60°	148
65°	175
70°	108
75°	0
80°	0
85°	0



TEST NUMBER: P220865

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.5	22.3
10°-20°	341.2	43.1
20°-30°	218.8	27.6
30°-40°	51.6	6.5
40°-50°	2.5	0.3
50°-60°	0.9	0.1
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.5	93.0
0°-40°	788.1	99.5
0°-60°	791.5	99.9
0°-90°	792.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2006	
5°	1932	177
15°	1272	341
25°	453	219
35°	37	52
45°	2	2
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220865

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2006.2
1°	1998.9
2°	1987.2
3°	1974.0
4°	1956.6
5°	1932.4
6°	1899.9
7°	1858.6
8°	1804.9
9°	1746.6
10°	1684.5
11°	1614.1
12°	1538.8
13°	1457.1
14°	1366.6
15°	1271.9
16°	1171.7
17°	1067.9
18°	964.4
19°	864.2
20°	767.6
21°	681.9
22°	605.2
23°	540.9
24°	492.0
25°	452.9
26°	423.6
27°	400.9
28°	380.7
29°	346.3
30°	294.6
32.5°	140.7
35°	36.9
37.5°	19.6
40°	9.8
42.5°	3.2
45°	2.2
47.5°	1.9
50°	1.6
52.5°	1.3
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P220865

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-F-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)