

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221285

Luminaire Tested: **9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29413)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1032.4 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.25
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	101	98	96	93	94	91	89	87	78	77	76	66	65	65	55	55	54	49
2	96	91	87	84	89	85	82	79	74	72	70	63	62	61	54	53	53	48
3	91	85	80	76	85	80	76	73	70	67	65	61	59	58	53	52	51	48
4	87	80	75	71	81	75	71	68	67	64	62	59	57	56	52	51	50	47
5	83	75	70	66	78	71	67	64	64	61	59	57	55	54	51	50	49	46
6	79	72	66	63	75	68	64	60	62	59	56	56	54	52	50	49	48	46
7	76	68	63	59	72	65	61	58	60	56	54	54	52	50	49	48	47	45
8	74	66	60	57	70	63	58	55	58	55	52	53	51	49	48	47	46	44
9	71	63	58	55	68	61	56	53	56	53	51	52	50	48	48	46	45	44
10	69	61	56	53	66	59	55	52	55	52	49	51	49	47	47	46	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3246931
5°	2254740
10°	837406
15°	179541
20°	80227
25°	39250
30°	13046
35°	5903
40°	3542
45°	2303
50°	1689
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.9	33.0
10°-20°	131.1	12.7
20°-30°	34.4	3.3
30°-40°	7.0	0.7
40°-50°	2.4	0.2
50°-60°	0.5	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.7	0.1
130°-140°	2.4	0.2
140°-150°	7.0	0.7
150°-160°	34.4	3.3
160°-170°	131.1	12.7
170°-180°	340.9	33.0
0°-30°	506.3	49.0
0°-40°	513.3	49.7
0°-60°	516.2	50.0
0°-90°	516.2	50.0
90°-120°	0.0	0.0
90°-150°	10.1	1.0
90°-180°	516.0	50.0
0°-180°	1032.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6581	
5°	4553	341
15°	352	131
25°	72	34
35°	10	7
45°	3	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	1
135°	3	2
145°	10	7
155°	72	34
165°	352	131
175°	4553	341
180°	6581	



TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	6581.0
1°	6430.3
2°	6107.2
3°	5651.9
4°	5121.3
5°	4552.6
6°	3983.8
7°	3398.6
8°	2800.3
9°	2214.0
10°	1671.5
11°	1207.5
12°	850.5
13°	604.8
14°	449.8
15°	351.5
17.5°	216.2
20°	152.8
22.5°	111.4
25°	72.1
27.5°	41.5
30°	22.9
32.5°	14.2
35°	9.8
37.5°	7.6
40°	5.5
42.5°	3.3
45°	3.3
47.5°	2.2
50°	2.2
52.5°	1.1
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	1.1
130°	2.2
132.5°	2.2
135°	3.3
137.5°	3.3
140°	5.5
142.5°	7.6
145°	9.8
147.5°	14.2
150°	22.9
152.5°	41.5
155°	72.1
157.5°	111.4
160°	152.8
162.5°	216.2
165°	351.5
166°	449.8
167°	604.8
168°	850.5
169°	1207.5
170°	1671.5
171°	2214.0
172°	2800.3
173°	3398.6
174°	3983.8
175°	4552.6
176°	5121.3
177°	5651.9
178°	6107.2
179°	6430.3



TEST NUMBER: P221285

CATALOG NUMBER: 9002-W2-[RW, RI]-LED5080-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

180° $\overbrace{\hspace{1.5cm}}^{0^\circ}$
6581.0

(END OF REPORT)