

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220844

Luminaire Tested: **9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29492)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 723.5 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220844

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220844

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	78	76	82	78	75	81	77	75	80	77	75	74
9	88	80	76	73	87	80	76	73	79	75	73	78	75	72	78	75	72	71
10	85	78	73	70	84	77	73	70	77	73	70	76	73	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332355
5°	304924
10°	224984
15°	131323
20°	71209
25°	50329
30°	36476
35°	4532
40°	1546
45°	611
50°	384
55°	323
60°	222
65°	175
70°	108
75°	143
80°	213
85°	0



TEST NUMBER: P220844

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.5	29.5
10°-20°	286.4	39.6
20°-30°	173.7	24.0
30°-40°	44.5	6.1
40°-50°	3.2	0.4
50°-60°	1.3	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	673.6	93.1
0°-40°	718.1	99.3
0°-60°	722.5	99.9
0°-90°	723.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	723.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2694	
5°	2463	214
15°	1028	286
25°	370	174
35°	30	44
45°	4	3
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220844

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2694.5
1°	2677.3
2°	2646.6
3°	2602.8
4°	2542.8
5°	2462.7
6°	2362.8
7°	2250.2
8°	2106.4
9°	1952.9
10°	1796.3
11°	1631.4
12°	1469.5
13°	1314.5
14°	1165.7
15°	1028.4
16°	905.6
17°	794.8
18°	696.0
19°	612.7
20°	542.5
21°	487.3
22°	443.4
23°	411.0
24°	387.9
25°	369.8
26°	355.2
27°	342.6
28°	327.7
29°	300.5
30°	256.1
32.5°	121.9
35°	30.1
37.5°	16.4
40°	9.6
42.5°	4.4
45°	3.5
47.5°	2.9
50°	2.0
52.5°	1.8
55°	1.5
57.5°	1.2
60°	0.9
62.5°	0.9
65°	0.6



TEST NUMBER: P220844

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)