

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220740

Luminaire Tested: **9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29488)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 774.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220740

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220740

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	102	99	107	104	100	98	100	98	95	97	95	93	95	93	92	90
3	105	100	95	92	103	98	94	91	96	93	90	93	91	89	91	89	87	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73
8	88	80	76	72	87	80	75	72	79	75	72	78	74	72	77	74	71	70
9	85	77	73	70	84	77	73	69	76	72	69	75	72	69	75	71	69	68
10	83	75	70	67	82	74	70	67	74	70	67	73	69	67	72	69	67	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	336512
5°	308589
10°	226449
15°	132626
20°	72365
25°	51553
30°	38142
35°	5496
40°	3011
45°	2146
50°	2188
55°	2258
60°	2516
65°	2802
70°	3282
75°	4051
80°	4759
85°	4529



TEST NUMBER: P220740

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.7	27.9
10°-20°	288.8	37.3
20°-30°	178.3	23.0
30°-40°	49.7	6.4
40°-50°	10.1	1.3
50°-60°	9.5	1.2
60°-70°	9.6	1.2
70°-80°	8.7	1.1
80°-90°	3.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.8	88.2
0°-40°	732.5	94.6
0°-60°	752.1	97.2
0°-90°	774.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2728	
5°	2492	216
15°	1039	289
25°	379	178
35°	36	50
45°	12	10
55°	10	10
65°	10	10
75°	8	9
85°	3	4
90°	0	

TEST NUMBER: P220740

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2728.2
1°	2711.2
2°	2679.9
3°	2635.5
4°	2574.4
5°	2492.3
6°	2390.5
7°	2269.5
8°	2125.1
9°	1969.9
10°	1808.0
11°	1643.1
12°	1480.3
13°	1321.5
14°	1174.2
15°	1038.6
16°	913.8
17°	801.8
18°	703.6
19°	619.7
20°	551.3
21°	494.9
22°	452.5
23°	420.3
24°	396.4
25°	378.8
26°	364.5
27°	351.9
28°	340.0
29°	313.1
30°	267.8
32.5°	129.8
35°	36.5
37.5°	25.1
40°	18.7
42.5°	13.2
45°	12.3
47.5°	11.7
50°	11.4
52.5°	10.8
55°	10.5
57.5°	10.5
60°	10.2
62.5°	10.2
65°	9.6



TEST NUMBER: P220740

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-M-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	9.4
70°	9.1
72.5°	8.8
75°	8.5
77.5°	7.6
80°	6.7
82.5°	5.3
85°	3.2
87.5°	1.5
90°	0.0

(END OF REPORT)