

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220896

Luminaire Tested: **9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29494)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 697.7 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220896

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220896

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	73
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115735
5°	117626
10°	113387
15°	104213
20°	88982
25°	74758
30°	55960
35°	17557
40°	10402
45°	6315
50°	2629
55°	430
60°	296
65°	175
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220896

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.3	12.8
10°-20°	225.1	32.3
20°-30°	250.7	35.9
30°-40°	100.0	14.3
40°-50°	28.6	4.1
50°-60°	3.2	0.5
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.1	81.0
0°-40°	665.1	95.3
0°-60°	696.8	99.9
0°-90°	697.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	697.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	938	
5°	950	89
15°	816	225
25°	549	251
35°	117	100
45°	36	29
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220896

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	938.3
1°	938.0
2°	939.8
3°	944.2
4°	948.3
5°	950.0
6°	948.9
7°	942.7
8°	932.2
9°	919.3
10°	905.3
11°	890.1
12°	874.3
13°	856.8
14°	837.5
15°	816.1
16°	791.3
17°	764.7
18°	735.8
19°	706.2
20°	677.9
21°	650.4
22°	624.1
23°	598.4
24°	574.1
25°	549.3
26°	525.9
27°	505.7
28°	484.7
29°	447.5
30°	392.9
32.5°	229.8
35°	116.6
37.5°	86.2
40°	64.6
42.5°	47.9
45°	36.2
47.5°	26.9
50°	13.7
52.5°	3.5
55°	2.0
57.5°	1.5
60°	1.2
62.5°	0.9
65°	0.6



TEST NUMBER: P220896

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2797-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)