

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220502

Luminaire Tested: **9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 657.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220502

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220502

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1235011
5°	946134
10°	396920
15°	167515
20°	108976
25°	47737
30°	6457
35°	2436
40°	1746
45°	1333
50°	1194
55°	1147
60°	965
65°	675
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220502

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.6	49.3
10°-20°	225.6	34.3
20°-30°	93.0	14.2
30°-40°	7.3	1.1
40°-50°	3.5	0.5
50°-60°	2.6	0.4
60°-70°	1.3	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.2	97.7
0°-40°	649.6	98.9
0°-60°	655.6	99.8
0°-90°	657.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	657.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5632	
5°	4298	324
15°	738	226
25°	197	93
35°	9	7
45°	4	3
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220502

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5632.1
1°	5560.2
2°	5391.9
3°	5117.9
4°	4752.2
5°	4298.3
6°	3793.2
7°	3263.9
8°	2719.5
9°	2220.5
10°	1782.6
11°	1435.9
12°	1179.3
13°	990.2
14°	852.1
15°	737.9
16°	645.7
17°	585.5
18°	539.2
19°	498.6
20°	467.0
21°	438.0
22°	393.8
23°	333.7
24°	265.3
25°	197.3
26°	137.2
27°	82.2
28°	45.9
29°	30.7
30°	25.5
32.5°	16.4
35°	9.1
37.5°	6.9
40°	6.1
42.5°	5.2
45°	4.3
47.5°	3.9
50°	3.5
52.5°	3.0
55°	3.0
57.5°	2.6
60°	2.2
62.5°	1.7
65°	1.3



TEST NUMBER: P220502

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3090-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)