

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220710

Luminaire Tested: **9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220710  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29487)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.  
Light Source: (1) 3000K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 881.2 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220710

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220710

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	91	95	92	90	93	90	89	87
4	102	96	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	93	88	85	98	92	88	84	90	86	84	89	85	83	87	84	82	81
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	78
7	93	86	82	78	92	86	81	78	84	81	78	83	80	77	82	79	77	76
8	90	83	79	76	89	83	79	76	82	78	75	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72
10	86	78	74	71	85	78	74	71	77	74	71	77	73	71	76	73	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	728368
5°	566004
10°	239851
15°	102541
20°	70028
25°	55800
30°	41717
35°	5526
40°	2947
45°	2146
50°	2303
55°	2516
60°	2788
65°	3210
70°	3715
75°	4432
80°	5185
85°	5236



TEST NUMBER: P220710

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.9	39.1
10°-20°	247.2	28.1
20°-30°	190.8	21.6
30°-40°	52.9	6.0
40°-50°	10.2	1.2
50°-60°	10.5	1.2
60°-70°	10.9	1.2
70°-80°	9.7	1.1
80°-90°	4.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	782.9	88.8
0°-40°	835.8	94.8
0°-60°	856.5	97.2
0°-90°	881.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5905	
5°	4571	345
15°	803	247
25°	410	191
35°	37	53
45°	12	10
55°	12	10
65°	11	11
75°	9	10
85°	4	4
90°	0	



TEST NUMBER: P220710

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5905.1
1°	5822.4
2°	5650.9
3°	5390.3
4°	5028.0
5°	4571.3
6°	4055.5
7°	3511.0
8°	2921.5
9°	2387.1
10°	1915.0
11°	1543.0
12°	1260.8
13°	1056.6
14°	912.1
15°	803.0
16°	722.0
17°	661.2
18°	613.5
19°	571.8
20°	533.5
22.5°	462.1
25°	410.0
26°	396.7
27°	385.3
28°	371.7
29°	342.0
30°	292.9
32.5°	140.8
35°	36.7
37.5°	23.7
40°	18.3
42.5°	13.7
45°	12.3
47.5°	12.0
50°	12.0
52.5°	11.7
55°	11.7
57.5°	11.7
60°	11.3
62.5°	11.3
65°	11.0
67.5°	10.7
70°	10.3
72.5°	10.0



TEST NUMBER: P220710

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-S-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
75°	9.3
77.5°	8.7
80°	7.3
82.5°	6.0
85°	3.7
87.5°	1.7
90°	0.0

(END OF REPORT)