

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220559

Luminaire Tested: **9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 594.0 lumens  
Efficiency: N/A  
Efficacy: 60.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220559

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220559

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 105 | 104 | 102 | 102 | 101 | 99  | 98  | 97  | 97  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 93  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 90  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 76  |
| 6   | 92  | 84  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 75  | 81  | 77  | 74  | 80  | 76  | 74  | 72  |
| 7   | 88  | 80  | 75  | 71  | 87  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |
| 8   | 85  | 77  | 71  | 68  | 84  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 73  | 70  | 67  | 66  |
| 9   | 82  | 73  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 64  | 63  |
| 10  | 78  | 70  | 65  | 62  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 64  | 61  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 232481 |
| 5°  | 233457 |
| 10° | 218388 |
| 15° | 186585 |
| 20° | 158564 |
| 25° | 94215  |
| 30° | 42867  |
| 35° | 27198  |
| 40° | 15400  |
| 45° | 5644   |
| 50° | 1774   |
| 55° | 1338   |
| 60° | 1140   |
| 65° | 675    |
| 70° | 256    |
| 75° | 339    |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P220559

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 98.8   | 16.6      |
| 10°-20°   | 229.7  | 38.7      |
| 20°-30°   | 178.3  | 30.0      |
| 30°-40°   | 65.0   | 10.9      |
| 40°-50°   | 17.2   | 2.9       |
| 50°-60°   | 3.2    | 0.5       |
| 60°-70°   | 1.4    | 0.2       |
| 70°-80°   | 0.4    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 506.8  | 85.3      |
| 0°-40°    | 571.8  | 96.3      |
| 0°-60°    | 592.2  | 99.7      |
| 0°-90°    | 594.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 594.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1060 |      |
| 5°  | 1061 | 99   |
| 15° | 822  | 230  |
| 25° | 389  | 178  |
| 35° | 102  | 65   |
| 45° | 18   | 17   |
| 55° | 4    | 3    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P220559

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1060.2 |
| 1°    | 1057.2 |
| 2°    | 1057.2 |
| 3°    | 1060.2 |
| 4°    | 1061.9 |
| 5°    | 1060.6 |
| 6°    | 1055.4 |
| 7°    | 1044.6 |
| 8°    | 1027.6 |
| 9°    | 1005.5 |
| 10°   | 980.8  |
| 11°   | 952.1  |
| 12°   | 920.4  |
| 13°   | 887.0  |
| 14°   | 852.7  |
| 15°   | 821.9  |
| 16°   | 794.1  |
| 17°   | 764.5  |
| 18°   | 736.3  |
| 19°   | 707.7  |
| 20°   | 679.5  |
| 21°   | 648.2  |
| 22°   | 598.7  |
| 23°   | 533.6  |
| 24°   | 462.8  |
| 25°   | 389.4  |
| 26°   | 320.4  |
| 27°   | 258.8  |
| 28°   | 212.3  |
| 29°   | 185.8  |
| 30°   | 169.3  |
| 32.5° | 133.3  |
| 35°   | 101.6  |
| 37.5° | 76.4   |
| 40°   | 53.8   |
| 42.5° | 35.6   |
| 45°   | 18.2   |
| 47.5° | 8.2    |
| 50°   | 5.2    |
| 52.5° | 3.9    |
| 55°   | 3.5    |
| 57.5° | 3.0    |
| 60°   | 2.6    |
| 62.5° | 1.7    |
| 65°   | 1.3    |



TEST NUMBER: P220559

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-W-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 1.3 |
| 70°   | 0.4 |
| 72.5° | 0.4 |
| 75°   | 0.4 |
| 77.5° | 0.4 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)