

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220971

Luminaire Tested: **9004-W1-FL-LED2790-F-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED2790-F-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.1 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220971

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220971

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247604
5°	239264
10°	210818
15°	162788
20°	101058
25°	61638
30°	51117
35°	31200
40°	5281
45°	1919
50°	422
55°	194
60°	148
65°	175
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220971

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.5	20.2
10°-20°	341.4	39.0
20°-30°	222.3	25.4
30°-40°	123.5	14.1
40°-50°	9.6	1.1
50°-60°	1.0	0.1
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.2	84.6
0°-40°	863.6	98.7
0°-60°	874.3	99.9
0°-90°	875.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2007	
5°	1932	177
15°	1275	341
25°	453	222
35°	207	123
45°	11	10
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220971

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2007.4
1°	1998.6
2°	1985.7
3°	1972.1
4°	1956.0
5°	1932.4
6°	1900.5
7°	1858.6
8°	1806.5
9°	1746.9
10°	1683.2
11°	1613.8
12°	1538.5
13°	1457.7
14°	1368.8
15°	1274.8
16°	1172.6
17°	1066.0
18°	965.1
19°	863.5
20°	769.9
21°	681.5
22°	604.9
23°	540.9
24°	491.1
25°	452.9
26°	425.1
27°	403.1
28°	385.7
29°	371.8
30°	358.9
32.5°	304.3
35°	207.2
37.5°	106.3
40°	32.8
42.5°	15.8
45°	11.0
47.5°	6.9
50°	2.2
52.5°	1.3
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P220971

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)