

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220945

Luminaire Tested: **9004-W1-FL-LED3090-M-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED3090-M-WT-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3000K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 942.8 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220945

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220945

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	86	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	380521
5°	349176
10°	256559
15°	149367
20°	81448
25°	57896
30°	52171
35°	41093
40°	9130
45°	2494
50°	825
55°	495
60°	321
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220945

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.3	25.9
10°-20°	326.0	34.6
20°-30°	203.9	21.6
30°-40°	151.2	16.0
40°-50°	14.1	1.5
50°-60°	2.2	0.2
60°-70°	0.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	774.2	82.1
0°-40°	925.4	98.2
0°-60°	941.7	99.9
0°-90°	942.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3085	
5°	2820	244
15°	1170	326
25°	425	204
35°	273	151
45°	14	14
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220945

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3085.0
1°	3064.7
2°	3030.0
3°	2979.9
4°	2911.2
5°	2820.1
6°	2707.0
7°	2570.6
8°	2411.4
9°	2233.9
10°	2048.4
11°	1858.6
12°	1674.8
13°	1495.6
14°	1325.5
15°	1169.7
16°	1027.9
17°	904.1
18°	793.0
19°	698.9
20°	620.5
21°	558.5
22°	508.8
23°	472.1
24°	445.1
25°	425.4
26°	410.7
27°	398.0
28°	386.3
29°	376.3
30°	366.3
32.5°	338.6
35°	272.9
37.5°	165.1
40°	56.7
42.5°	19.7
45°	14.3
47.5°	10.3
50°	4.3
52.5°	3.3
55°	2.3
57.5°	1.7
60°	1.3
62.5°	1.0
65°	0.7



TEST NUMBER: P220945

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)