

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220918

Luminaire Tested: **9004-W1-FL-LED3090-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3090-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 934.5 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220918

CATALOG NUMBER: 9004-W1-FL-LED3090-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220918

CATALOG NUMBER: 9004-W1-FL-LED3090-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71	77	74	71	76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	723841
5°	563441
10°	234665
15°	99220
20°	68099
25°	54343
30°	50220
35°	41093
40°	8647
45°	1971
50°	710
55°	581
60°	321
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220918

CATALOG NUMBER: 9004-W1-FL-LED3090-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.0	36.6
10°-20°	239.7	25.6
20°-30°	188.9	20.2
30°-40°	148.7	15.9
40°-50°	12.0	1.3
50°-60°	2.3	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	770.6	82.5
0°-40°	919.3	98.4
0°-60°	933.6	99.9
0°-90°	934.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	934.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5868	
5°	4551	342
15°	777	240
25°	399	189
35°	273	149
45°	11	12
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220918

CATALOG NUMBER: 9004-W1-FL-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5868.4
1°	5787.7
2°	5619.9
3°	5359.6
4°	5003.7
5°	4550.6
6°	4027.5
7°	3462.3
8°	2907.9
9°	2349.7
10°	1873.6
11°	1493.6
12°	1218.1
13°	1022.9
14°	881.4
15°	777.0
16°	698.6
17°	641.2
18°	597.5
19°	555.8
20°	518.8
21°	488.1
22°	460.7
23°	436.7
24°	415.7
25°	399.3
26°	387.0
27°	377.7
28°	368.7
29°	360.6
30°	352.6
32.5°	332.6
35°	272.9
37.5°	162.8
40°	53.7
42.5°	16.0
45°	11.3
47.5°	8.0
50°	3.7
52.5°	3.3
55°	2.7
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.7



TEST NUMBER: P220918

CATALOG NUMBER: 9004-W1-FL-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)