

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220521

Luminaire Tested: **9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 782.2 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220521

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220521

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85	89	87	84	88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	822390
5°	736956
10°	517759
15°	277845
20°	146149
25°	65351
30°	12635
35°	4658
40°	2634
45°	2171
50°	1842
55°	1453
60°	1184
65°	830
70°	321
75°	0
80°	0
85°	0



TEST NUMBER: P220521

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.4	36.6
10°-20°	345.2	44.1
20°-30°	125.9	16.1
30°-40°	13.9	1.8
40°-50°	5.5	0.7
50°-60°	3.4	0.4
60°-70°	1.6	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	757.6	96.9
0°-40°	771.5	98.6
0°-60°	780.4	99.8
0°-90°	782.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	782.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3750	
5°	3348	286
15°	1224	345
25°	270	126
35°	17	14
45°	7	5
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220521

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3750.4
1°	3720.0
2°	3666.9
3°	3588.8
4°	3480.9
5°	3348.0
6°	3189.1
7°	3002.6
8°	2791.1
9°	2561.7
10°	2325.3
11°	2087.2
12°	1851.3
13°	1628.5
14°	1415.9
15°	1223.9
16°	1047.7
17°	904.0
18°	787.4
19°	695.2
20°	626.3
21°	569.9
22°	505.4
23°	428.9
24°	349.2
25°	270.1
26°	194.7
27°	127.4
28°	80.3
29°	58.6
30°	49.9
32.5°	33.6
35°	17.4
37.5°	11.4
40°	9.2
42.5°	8.1
45°	7.0
47.5°	6.0
50°	5.4
52.5°	4.3
55°	3.8
57.5°	3.3
60°	2.7
62.5°	2.2
65°	1.6



TEST NUMBER: P220521

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)