

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221078

Luminaire Tested: **9004-W1-FL-LED3590-F-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29498)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3590-F-BK-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 970.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221078
CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221078

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		97	95	94		95	93	92	90
3	105	99	95	92	103	98	94	91	96	92	90		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	85	82	81
5	97	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		82	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	65	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	70	66	62	70	65	62		69	65	62		68	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266044
5°	256932
10°	226211
15°	173770
20°	107477
25°	66592
30°	55490
35°	44420
40°	9677
45°	2058
50°	384
55°	215
60°	173
65°	88
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P221078

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	19.5
10°-20°	364.9	37.6
20°-30°	239.6	24.7
30°-40°	161.6	16.7
40°-50°	12.7	1.3
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.1	81.9
0°-40°	955.7	98.5
0°-60°	969.3	99.9
0°-90°	970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2157	
5°	2075	190
15°	1361	365
25°	489	240
35°	295	162
45°	12	13
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P221078

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2156.9
1°	2147.4
2°	2133.6
3°	2118.4
4°	2100.5
5°	2075.1
6°	2040.3
7°	1995.0
8°	1939.3
9°	1874.7
10°	1806.1
11°	1730.8
12°	1648.7
13°	1559.1
14°	1463.8
15°	1360.8
16°	1252.3
17°	1140.1
18°	1027.9
19°	922.5
20°	818.8
21°	728.9
22°	648.1
23°	581.2
24°	529.5
25°	489.3
26°	460.2
27°	437.9
28°	419.0
29°	403.5
30°	389.6
32.5°	360.6
35°	295.0
37.5°	175.4
40°	60.1
42.5°	17.9
45°	11.8
47.5°	7.4
50°	2.0
52.5°	1.0
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.3



TEST NUMBER: P221078

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)