

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P221026

Luminaire Tested: **9004-W1-FL-LED3590-S-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221026  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED3590-S-BK-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC,  
BLACK HOUSING.  
Light Source: (1) 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 946.6 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221026  
CATALOG NUMBER: 9004-W1-FL-LED3590-S-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221026

CATALOG NUMBER: 9004-W1-FL-LED3590-S-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71	77	74	71	76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	733154
5°	570684
10°	237684
15°	100497
20°	68978
25°	55051
30°	50875
35°	41620
40°	8759
45°	2006
50°	710
55°	581
60°	345
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P221026

CATALOG NUMBER: 9004-W1-FL-LED3590-S-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	346.4	36.6
10°-20°	242.8	25.6
20°-30°	191.3	20.2
30°-40°	150.6	15.9
40°-50°	12.2	1.3
50°-60°	2.4	0.3
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.5	82.5
0°-40°	931.1	98.4
0°-60°	945.6	99.9
0°-90°	946.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5944	
5°	4609	346
15°	787	243
25°	404	191
35°	276	151
45°	12	12
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P221026

CATALOG NUMBER: 9004-W1-FL-LED3590-S-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5943.9
1°	5862.1
2°	5692.1
3°	5428.6
4°	5068.0
5°	4609.1
6°	4079.3
7°	3506.9
8°	2945.2
9°	2379.9
10°	1897.7
11°	1512.8
12°	1233.7
13°	1036.0
14°	892.8
15°	787.0
16°	707.6
17°	649.5
18°	605.2
19°	563.0
20°	525.5
21°	494.4
22°	466.7
23°	442.3
24°	421.0
25°	404.5
26°	392.0
27°	382.5
28°	373.4
29°	365.3
30°	357.2
32.5°	336.9
35°	276.4
37.5°	164.9
40°	54.4
42.5°	16.2
45°	11.5
47.5°	8.1
50°	3.7
52.5°	3.4
55°	2.7
57.5°	2.0
60°	1.4
62.5°	0.7
65°	0.7



TEST NUMBER: P221026

CATALOG NUMBER: 9004-W1-FL-LED3590-S-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)