

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220475

Luminaire Tested: **9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220475  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29470)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 4000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 807.2 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220475

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220475

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84
4	100	94	89	85	99	92	88	84	90	87	83	88	85	83	87	84	82	80
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73
7	89	82	77	73	88	81	76	73	80	76	72	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	73	70	76	72	69	75	72	69	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	65
10	81	73	68	65	80	72	68	65	72	67	65	71	67	64	70	67	64	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	454459
5°	443692
10°	391376
15°	304542
20°	190230
25°	74278
30°	20256
35°	11859
40°	9475
45°	9613
50°	10132
55°	10360
60°	10175
65°	9391
70°	8014
75°	7286
80°	8082
85°	7548



TEST NUMBER: P220475

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.2	22.8
10°-20°	359.6	44.5
20°-30°	154.2	19.1
30°-40°	30.4	3.8
40°-50°	24.1	3.0
50°-60°	24.0	3.0
60°-70°	17.8	2.2
70°-80°	9.5	1.2
80°-90°	3.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.0	86.5
0°-40°	728.5	90.2
0°-60°	776.6	96.2
0°-90°	807.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2072	
5°	2016	184
15°	1342	360
25°	307	154
35°	44	30
45°	31	24
55°	27	24
65°	18	18
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P220475

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2072.5
1°	2066.4
2°	2060.0
3°	2054.0
4°	2039.8
5°	2015.7
6°	1983.5
7°	1941.3
8°	1887.6
9°	1826.9
10°	1757.7
11°	1683.8
12°	1606.8
13°	1523.4
14°	1435.7
15°	1341.5
16°	1240.9
17°	1135.1
18°	1025.9
19°	918.8
20°	815.2
21°	716.8
22°	611.0
23°	502.6
24°	399.4
25°	307.0
26°	226.6
27°	160.4
28°	114.4
29°	90.7
30°	80.0
32.5°	60.6
35°	44.3
37.5°	36.1
40°	33.1
42.5°	31.8
45°	31.0
47.5°	30.5
50°	29.7
52.5°	28.4
55°	27.1
57.5°	25.4
60°	23.2
62.5°	21.1
65°	18.1



TEST NUMBER: P220475

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-F-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	15.0
70°	12.5
72.5°	10.3
75°	8.6
77.5°	7.7
80°	6.4
82.5°	4.7
85°	3.0
87.5°	1.3
90°	0.0

(END OF REPORT)