

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221005

Luminaire Tested: **9004-W1-FL-LED4097-W-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29499)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4097-W-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 924.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221005

CATALOG NUMBER: 9004-W1-FL-LED4097-W-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221005

CATALOG NUMBER: 9004-W1-FL-LED4097-W-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70	66	63	61
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55	54
10	72	62	56	53	71	62	56	52	61	56	52		60	55	52		59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129723
5°	132150
10°	127954
15°	117839
20°	100980
25°	86122
30°	73649
35°	55051
40°	19531
45°	9141
50°	6045
55°	4064
60°	2048
65°	496
70°	361
75°	334
80°	0
85°	0



TEST NUMBER: P221005

CATALOG NUMBER: 9004-W1-FL-LED4097-W-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	10.9
10°-20°	254.7	27.5
20°-30°	290.7	31.4
30°-40°	213.4	23.1
40°-50°	45.3	4.9
50°-60°	17.1	1.9
60°-70°	2.4	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.9	69.8
0°-40°	859.3	92.9
0°-60°	921.8	99.7
0°-90°	924.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1052	
5°	1067	100
15°	923	255
25°	633	291
35°	366	213
45°	52	45
55°	19	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221005

CATALOG NUMBER: 9004-W1-FL-LED4097-W-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1051.7
1°	1051.4
2°	1054.1
3°	1059.4
4°	1064.3
5°	1067.3
6°	1066.7
7°	1061.0
8°	1050.1
9°	1036.5
10°	1021.6
11°	1004.7
12°	987.4
13°	967.9
14°	946.7
15°	922.8
16°	895.6
17°	865.5
18°	834.3
19°	801.5
20°	769.3
21°	739.5
22°	710.7
23°	683.5
24°	657.6
25°	632.8
26°	608.6
27°	584.0
28°	560.5
29°	538.6
30°	517.1
32.5°	459.1
35°	365.6
37.5°	246.9
40°	121.3
42.5°	68.3
45°	52.4
47.5°	41.1
50°	31.5
52.5°	24.9
55°	18.9
57.5°	13.6
60°	8.3
62.5°	2.3
65°	1.7



TEST NUMBER: P221005

CATALOG NUMBER: 9004-W1-FL-LED4097-W-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.3
70°	1.0
72.5°	1.0
75°	0.7
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)