

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220822

Luminaire Tested: **9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29491)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1445.3 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220822

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220822

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	82	86	83	81	86	83	81	80
8	93	86	82	80	92	86	82	79	85	82	79	84	81	79	83	81	78	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	78	76	75
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	79	77	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1271706
5°	993568
10°	418505
15°	177358
20°	120078
25°	95336
30°	70587
35°	6400
40°	2351
45°	715
50°	556
55°	624
60°	419
65°	350
70°	216
75°	286
80°	426
85°	0



TEST NUMBER: P220822

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	604.1	41.8
10°-20°	426.8	29.5
20°-30°	325.9	22.5
30°-40°	79.9	5.5
40°-50°	4.3	0.3
50°-60°	2.3	0.2
60°-70°	1.1	0.1
70°-80°	0.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.8	93.9
0°-40°	1436.7	99.4
0°-60°	1443.3	99.9
0°-90°	1445.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1445.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10310	
5°	8024	604
15°	1389	427
25°	700	326
35°	42	80
45°	4	4
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220822

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

	0°
0°	10310.1
1°	10177.9
2°	9886.8
3°	9440.1
4°	8814.7
5°	8024.5
6°	7116.1
7°	6117.9
8°	5112.8
9°	4192.8
10°	3341.4
11°	2667.1
12°	2173.3
13°	1823.9
14°	1575.2
15°	1388.9
16°	1245.6
17°	1141.4
18°	1058.7
19°	981.2
20°	914.8
22.5°	789.1
25°	700.5
26°	676.7
27°	656.9
28°	637.1
29°	584.7
30°	495.6
32.5°	223.0
35°	42.5
37.5°	23.3
40°	14.6
42.5°	6.4
45°	4.1
47.5°	3.5
50°	2.9
52.5°	2.9
55°	2.9
57.5°	2.3
60°	1.7
62.5°	1.7
65°	1.2
67.5°	0.6
70°	0.6
72.5°	0.6



TEST NUMBER: P220822

CATALOG NUMBER: 9004-W1-[RW, RI]-LED2790-S-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)