

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220522

Luminaire Tested: **9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220522
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 812.6 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220522

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220522

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	95	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85		89	87	84		88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82		87	84	82		86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80		85	82	80		84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78		83	80	77		82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76		81	78	75		80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	854318
5°	765571
10°	537866
15°	288628
20°	151843
25°	67867
30°	13116
35°	4818
40°	2748
45°	2264
50°	1910
55°	1491
60°	1228
65°	882
70°	385
75°	0
80°	0
85°	0



TEST NUMBER: P220522

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.6	36.6
10°-20°	358.6	44.1
20°-30°	130.8	16.1
30°-40°	14.4	1.8
40°-50°	5.7	0.7
50°-60°	3.6	0.4
60°-70°	1.7	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.0	96.8
0°-40°	801.4	98.6
0°-60°	810.7	99.8
0°-90°	812.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	812.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3896	
5°	3478	298
15°	1271	359
25°	280	131
35°	18	14
45°	7	6
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220522

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3896.0
1°	3864.5
2°	3809.3
3°	3728.1
4°	3616.0
5°	3478.0
6°	3313.0
7°	3119.2
8°	2899.5
9°	2661.2
10°	2415.6
11°	2168.3
12°	1923.2
13°	1691.7
14°	1470.9
15°	1271.4
16°	1088.4
17°	939.1
18°	818.0
19°	722.2
20°	650.7
21°	592.1
22°	525.0
23°	445.6
24°	362.8
25°	280.5
26°	202.2
27°	132.4
28°	83.4
29°	60.8
30°	51.8
32.5°	34.9
35°	18.0
37.5°	11.8
40°	9.6
42.5°	8.5
45°	7.3
47.5°	6.2
50°	5.6
52.5°	4.5
55°	3.9
57.5°	3.4
60°	2.8
62.5°	2.3
65°	1.7



TEST NUMBER: P220522

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)