

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220606

Luminaire Tested: **9003-W1-FL-LED3090-F-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220606  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29478)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-FL-LED3090-F-WT-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3000K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 773.4 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220606

CATALOG NUMBER: 9003-W1-FL-LED3090-F-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220606

CATALOG NUMBER: 9003-W1-FL-LED3090-F-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104		103	101	100		99	98	98	96
2	110	107	103	101	108	105	102	100	102	99	97		99	97	95		96	95	93	92
3	107	101	98	94	105	100	97	94	98	95	92		95	93	91		93	91	89	88
4	103	97	93	89	101	96	92	89	94	90	88		92	89	87		90	88	86	85
5	99	93	88	85	98	92	88	85	90	87	84		89	86	83		87	85	82	81
6	96	89	84	81	95	88	84	81	87	83	80		86	82	80		84	82	79	78
7	93	85	81	78	91	85	81	77	84	80	77		83	79	77		82	79	76	75
8	90	82	78	75	89	82	77	74	81	77	74		80	76	74		79	76	74	72
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77	73	71	70
10	84	77	72	69	83	76	72	69	75	72	69		75	71	69		74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	455599
5°	442108
10°	390841
15°	300138
20°	186823
25°	105345
30°	40006
35°	8566
40°	3349
45°	1085
50°	887
55°	650
60°	570
65°	675
70°	577
75°	763
80°	505
85°	0



TEST NUMBER: P220606

CATALOG NUMBER: 9003-W1-FL-LED3090-F-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.9	23.8
10°-20°	354.8	45.9
20°-30°	197.8	25.6
30°-40°	29.9	3.9
40°-50°	3.3	0.4
50°-60°	1.7	0.2
60°-70°	1.1	0.1
70°-80°	0.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.5	95.2
0°-40°	766.4	99.1
0°-60°	771.4	99.7
0°-90°	773.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	773.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2078	
5°	2008	184
15°	1322	355
25°	435	198
35°	32	30
45°	4	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220606

CATALOG NUMBER: 9003-W1-FL-LED3090-F-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2077.7
1°	2070.4
2°	2058.3
3°	2045.7
4°	2029.7
5°	2008.5
6°	1979.9
7°	1938.8
8°	1886.0
9°	1823.7
10°	1755.3
11°	1678.7
12°	1595.6
13°	1509.5
14°	1417.3
15°	1322.1
16°	1219.1
17°	1112.7
18°	1004.5
19°	901.0
20°	800.6
21°	707.6
22°	625.4
23°	556.1
24°	496.0
25°	435.4
26°	376.1
27°	318.5
28°	262.7
29°	209.0
30°	158.0
32.5°	63.2
35°	32.0
37.5°	19.9
40°	11.7
42.5°	4.3
45°	3.5
47.5°	2.6
50°	2.6
52.5°	2.2
55°	1.7
57.5°	1.7
60°	1.3
62.5°	1.3
65°	1.3



TEST NUMBER: P220606

CATALOG NUMBER: 9003-W1-FL-LED3090-F-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)