

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220854

Luminaire Tested: **9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220854  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29492)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1348.3 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220854

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220854

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	78	76	82	78	75	81	77	75	80	77	75	74
9	88	80	76	73	87	80	76	73	79	75	73	78	75	72	78	75	72	71
10	85	78	73	71	84	77	73	70	77	73	70	76	73	70	75	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619454
5°	568331
10°	419319
15°	244756
20°	132732
25°	93798
30°	67981
35°	8447
40°	2898
45°	1134
50°	729
55°	581
60°	395
65°	321
70°	180
75°	238
80°	355
85°	0



TEST NUMBER: P220854

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	398.0	29.5
10°-20°	533.7	39.6
20°-30°	323.8	24.0
30°-40°	82.8	6.1
40°-50°	5.9	0.4
50°-60°	2.4	0.2
60°-70°	1.0	0.1
70°-80°	0.5	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1255.5	93.1
0°-40°	1338.3	99.3
0°-60°	1346.6	99.9
0°-90°	1348.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1348.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5022	
5°	4590	398
15°	1917	534
25°	689	324
35°	56	83
45°	6	6
55°	3	2
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P220854

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5022.1
1°	4990.0
2°	4932.8
3°	4851.1
4°	4739.4
5°	4590.1
6°	4403.8
7°	4194.0
8°	3926.0
9°	3639.9
10°	3347.9
11°	3040.6
12°	2738.8
13°	2450.0
14°	2172.7
15°	1916.7
16°	1687.8
17°	1481.4
18°	1297.2
19°	1141.9
20°	1011.2
21°	908.2
22°	826.5
23°	766.0
24°	723.0
25°	689.2
26°	662.0
27°	638.5
28°	610.7
29°	560.1
30°	477.3
32.5°	227.2
35°	56.1
37.5°	30.5
40°	18.0
42.5°	8.2
45°	6.5
47.5°	5.4
50°	3.8
52.5°	3.3
55°	2.7
57.5°	2.2
60°	1.6
62.5°	1.6
65°	1.1



TEST NUMBER: P220854

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)