

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220825

Luminaire Tested: **9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29491)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1915.8 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220825

CATALOG NUMBER: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220825

CATALOG NUMBER: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	86	83	81	80
8	93	86	82	80	92	86	82	79	85	82	79	84	81	79	83	81	78	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	78	76	75
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	79	77	74	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1685641
5°	1316965
10°	554725
15°	235077
20°	159168
25°	126380
30°	93560
35°	8477
40°	3108
45°	942
50°	748
55°	839
60°	567
65°	438
70°	289
75°	381
80°	568
85°	0



TEST NUMBER: P220825

CATALOG NUMBER: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	800.7	41.8
10°-20°	565.8	29.5
20°-30°	432.0	22.5
30°-40°	105.9	5.5
40°-50°	5.7	0.3
50°-60°	3.1	0.2
60°-70°	1.5	0.1
70°-80°	0.8	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1798.4	93.9
0°-40°	1904.3	99.4
0°-60°	1913.1	99.9
0°-90°	1915.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1915.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13666	
5°	10636	801
15°	1841	566
25°	929	432
35°	56	106
45°	5	6
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220825

CATALOG NUMBER: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	13666.0
1°	13490.8
2°	13104.8
3°	12512.8
4°	11683.8
5°	10636.4
6°	9432.3
7°	8109.3
8°	6777.0
9°	5557.5
10°	4429.0
11°	3535.2
12°	2880.6
13°	2417.5
14°	2087.9
15°	1840.9
16°	1651.0
17°	1512.9
18°	1403.3
19°	1300.6
20°	1212.6
22.5°	1045.9
25°	928.6
26°	896.9
27°	870.7
28°	844.4
29°	775.0
30°	656.9
32.5°	295.6
35°	56.3
37.5°	30.9
40°	19.3
42.5°	8.5
45°	5.4
47.5°	4.6
50°	3.9
52.5°	3.9
55°	3.9
57.5°	3.1
60°	2.3
62.5°	2.3
65°	1.5
67.5°	0.8
70°	0.8
72.5°	0.8



TEST NUMBER: P220825

CATALOG NUMBER: 9004-W1-[RW, RI]-LED4080-S-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)