

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P221090

Luminaire Tested: **9004-W1-FL-LED2797-F-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221090  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29498)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED2797-F-BK-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1549.4 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221090  
CATALOG NUMBER: 9004-W1-FL-LED2797-F-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221090

CATALOG NUMBER: 9004-W1-FL-LED2797-F-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		97	95	94		95	93	92	90
3	105	99	95	92	103	98	94	91	96	92	90		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	85	82	81
5	97	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		82	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	65	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	70	66	62	70	65	62		69	65	62		68	65	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	424938
5°	410391
10°	361329
15°	277549
20°	171664
25°	106360
30°	88632
35°	70952
40°	15474
45°	3297
50°	614
55°	344
60°	271
65°	146
70°	180
75°	238
80°	0
85°	0



TEST NUMBER: P221090

CATALOG NUMBER: 9004-W1-FL-LED2797-F-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.7	19.5
10°-20°	582.9	37.6
20°-30°	382.8	24.7
30°-40°	258.1	16.7
40°-50°	20.4	1.3
50°-60°	1.4	0.1
60°-70°	0.7	0.0
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1268.3	81.9
0°-40°	1526.4	98.5
0°-60°	1548.3	99.9
0°-90°	1549.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1549.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3445	
5°	3314	303
15°	2174	583
25°	782	383
35°	471	258
45°	19	20
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P221090

CATALOG NUMBER: 9004-W1-FL-LED2797-F-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3445.1
1°	3430.0
2°	3407.9
3°	3383.6
4°	3355.0
5°	3314.5
6°	3258.9
7°	3186.6
8°	3097.5
9°	2994.4
10°	2884.9
11°	2764.5
12°	2633.3
13°	2490.3
14°	2338.1
15°	2173.5
16°	2000.2
17°	1821.0
18°	1641.9
19°	1473.5
20°	1307.8
21°	1164.2
22°	1035.2
23°	928.3
24°	845.8
25°	781.5
26°	735.1
27°	699.5
28°	669.3
29°	644.4
30°	622.3
32.5°	575.9
35°	471.2
37.5°	280.1
40°	96.1
42.5°	28.6
45°	18.9
47.5°	11.9
50°	3.2
52.5°	1.6
55°	1.6
57.5°	1.1
60°	1.1
62.5°	1.1
65°	0.5



TEST NUMBER: P221090

CATALOG NUMBER: 9004-W1-FL-LED2797-F-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)