

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221086

Luminaire Tested: **9004-W1-FL-LED3090-F-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29498)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3090-F-BK-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1768.4 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221086
CATALOG NUMBER: 9004-W1-FL-LED3090-F-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221086

CATALOG NUMBER: 9004-W1-FL-LED3090-F-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		97	95	94		95	93	92	90
3	105	99	95	92	103	98	94	91	96	92	90		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	85	82	81
5	97	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		82	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	65	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	70	66	62	70	65	62		69	65	62		68	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	484995
5°	468387
10°	412380
15°	316765
20°	195921
25°	121398
30°	101166
35°	80980
40°	17647
45°	3768
50°	710
55°	387
60°	296
65°	175
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P221086

CATALOG NUMBER: 9004-W1-FL-LED3090-F-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.5	19.5
10°-20°	665.2	37.6
20°-30°	436.9	24.7
30°-40°	294.6	16.7
40°-50°	23.3	1.3
50°-60°	1.6	0.1
60°-70°	0.8	0.0
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1447.6	81.9
0°-40°	1742.2	98.5
0°-60°	1767.0	99.9
0°-90°	1768.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1768.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3932	
5°	3783	345
15°	2481	665
25°	892	437
35°	538	295
45°	22	23
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221086

CATALOG NUMBER: 9004-W1-FL-LED3090-F-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3932.0
1°	3914.7
2°	3889.4
3°	3861.7
4°	3829.1
5°	3782.9
6°	3719.4
7°	3636.9
8°	3535.2
9°	3417.6
10°	3292.5
11°	3155.2
12°	3005.5
13°	2842.2
14°	2668.5
15°	2480.6
16°	2282.9
17°	2078.4
18°	1873.9
19°	1681.7
20°	1492.6
21°	1328.7
22°	1181.5
23°	1059.5
24°	965.3
25°	892.0
26°	839.0
27°	798.3
28°	763.8
29°	735.5
30°	710.3
32.5°	657.3
35°	537.8
37.5°	319.7
40°	109.6
42.5°	32.6
45°	21.6
47.5°	13.6
50°	3.7
52.5°	1.8
55°	1.8
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P221086

CATALOG NUMBER: 9004-W1-FL-LED3090-F-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)