

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220699

Luminaire Tested: **9003-W1-FL-LED3597-W-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220699  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29479)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-FL-LED3597-W-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 707.5 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220699

CATALOG NUMBER: 9003-W1-FL-LED3597-W-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220699

CATALOG NUMBER: 9003-W1-FL-LED3597-W-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	88	84	81		87	83	80		85	82	79	78
5	94	86	81	77	93	86	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	68	64	72	67	64		71	66	63		70	66	63	62
9	79	70	64	61	78	69	64	60	68	64	60		68	63	60		67	63	60	59
10	75	66	61	57	75	66	61	57	65	60	57		64	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	231341
5°	233083
10°	220214
15°	189422
20°	162601
25°	134572
30°	71783
35°	32658
40°	20868
45°	13738
50°	9620
55°	4817
60°	1140
65°	1141
70°	1090
75°	763
80°	505
85°	1006



TEST NUMBER: P220699

CATALOG NUMBER: 9003-W1-FL-LED3597-W-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.0	14.0
10°-20°	233.4	33.0
20°-30°	238.5	33.7
30°-40°	86.4	12.2
40°-50°	35.6	5.0
50°-60°	11.5	1.6
60°-70°	2.0	0.3
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.8	80.7
0°-40°	657.1	92.9
0°-60°	704.2	99.5
0°-90°	707.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1055	
5°	1059	99
15°	834	233
25°	556	238
35°	122	86
45°	44	36
55°	13	11
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220699

CATALOG NUMBER: 9003-W1-FL-LED3597-W-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1055.0
1°	1052.0
2°	1052.4
3°	1056.3
4°	1059.8
5°	1058.9
6°	1055.9
7°	1046.3
8°	1031.1
9°	1011.1
10°	989.0
11°	962.5
12°	933.4
13°	900.9
14°	867.0
15°	834.4
16°	803.2
17°	775.8
18°	750.7
19°	722.9
20°	696.8
21°	672.1
22°	647.8
23°	624.3
24°	596.5
25°	556.2
26°	506.7
27°	452.8
28°	395.9
29°	338.6
30°	283.5
32.5°	170.2
35°	122.0
37.5°	94.2
40°	72.9
42.5°	55.6
45°	44.3
47.5°	35.6
50°	28.2
52.5°	20.8
55°	12.6
57.5°	3.5
60°	2.6
62.5°	2.2
65°	2.2



TEST NUMBER: P220699

CATALOG NUMBER: 9003-W1-FL-LED3597-W-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.7
70°	1.7
72.5°	1.3
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)