

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220981

Luminaire Tested: **9004-W1-FL-LED3090-F-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3090-F-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1709.3 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220981

CATALOG NUMBER: 9004-W1-FL-LED3090-F-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220981

CATALOG NUMBER: 9004-W1-FL-LED3090-F-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	483626
5°	467322
10°	411767
15°	317952
20°	197378
25°	120391
30°	99842
35°	60939
40°	10321
45°	3768
50°	825
55°	387
60°	296
65°	350
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P220981

CATALOG NUMBER: 9004-W1-FL-LED3090-F-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.8	20.2
10°-20°	666.7	39.0
20°-30°	434.2	25.4
30°-40°	241.1	14.1
40°-50°	18.9	1.1
50°-60°	2.0	0.1
60°-70°	1.1	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1445.7	84.6
0°-40°	1686.8	98.7
0°-60°	1707.7	99.9
0°-90°	1709.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1709.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3921	
5°	3774	345
15°	2490	667
25°	885	434
35°	405	241
45°	22	19
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220981

CATALOG NUMBER: 9004-W1-FL-LED3090-F-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3920.9
1°	3903.6
2°	3878.4
3°	3851.9
4°	3820.5
5°	3774.3
6°	3712.0
7°	3630.1
8°	3528.5
9°	3412.1
10°	3287.6
11°	3152.1
12°	3004.9
13°	2847.2
14°	2673.5
15°	2489.9
16°	2290.3
17°	2082.1
18°	1885.0
19°	1686.6
20°	1503.7
21°	1331.2
22°	1181.5
23°	1056.4
24°	959.1
25°	884.6
26°	830.4
27°	787.3
28°	753.4
29°	726.3
30°	701.0
32.5°	594.4
35°	404.7
37.5°	207.6
40°	64.1
42.5°	30.8
45°	21.6
47.5°	13.6
50°	4.3
52.5°	2.5
55°	1.8
57.5°	1.8
60°	1.2
62.5°	1.2
65°	1.2



TEST NUMBER: P220981

CATALOG NUMBER: 9004-W1-FL-LED3090-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)