

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220960

Luminaire Tested: **9004-W1-FL-LED3597-M-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3597-M-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1746.5 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220960

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220960

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90		94	91	89		92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85		90	87	85		88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81		86	83	80		85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77		83	79	77		82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	704846
5°	646782
10°	475243
15°	276668
20°	150872
25°	107231
30°	96637
35°	76117
40°	16923
45°	4640
50°	1535
55°	925
60°	617
65°	350
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P220960

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.5	25.9
10°-20°	603.9	34.6
20°-30°	377.7	21.6
30°-40°	280.1	16.0
40°-50°	26.1	1.5
50°-60°	4.2	0.2
60°-70°	1.4	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1434.1	82.1
0°-40°	1714.2	98.2
0°-60°	1744.5	99.9
0°-90°	1746.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1746.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5714	
5°	5224	453
15°	2167	604
25°	788	378
35°	506	280
45°	27	26
55°	4	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220960

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5714.4
1°	5676.7
2°	5612.4
3°	5519.7
4°	5392.4
5°	5223.7
6°	5014.2
7°	4761.5
8°	4466.7
9°	4137.9
10°	3794.4
11°	3442.7
12°	3102.2
13°	2770.4
14°	2455.2
15°	2166.6
16°	1904.0
17°	1674.7
18°	1468.9
19°	1294.7
20°	1149.4
21°	1034.5
22°	942.4
23°	874.4
24°	824.4
25°	787.9
26°	760.7
27°	737.2
28°	715.6
29°	697.1
30°	678.5
32.5°	627.2
35°	505.5
37.5°	305.9
40°	105.1
42.5°	36.5
45°	26.6
47.5°	19.2
50°	8.0
52.5°	6.2
55°	4.3
57.5°	3.1
60°	2.5
62.5°	1.9
65°	1.2



TEST NUMBER: P220960

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)