

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220956

Luminaire Tested: **9004-W1-FL-LED4080-M-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220956  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED4080-M-WT-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2181.5 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220956

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220956

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90		94	91	89		92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85		90	87	85		88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81		86	83	80		85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77		83	79	77		82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	880379
5°	807855
10°	593590
15°	345573
20°	188452
25°	133933
30°	120707
35°	95074
40°	21125
45°	5791
50°	1919
55°	1161
60°	765
65°	438
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220956

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	565.2	25.9
10°-20°	754.3	34.6
20°-30°	471.7	21.6
30°-40°	349.9	16.0
40°-50°	32.6	1.5
50°-60°	5.2	0.2
60°-70°	1.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1791.3	82.1
0°-40°	2141.2	98.2
0°-60°	2178.9	99.9
0°-90°	2181.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2181.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7138	
5°	6525	565
15°	2706	754
25°	984	472
35°	631	350
45°	33	33
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220956

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7137.5
1°	7090.4
2°	7010.1
3°	6894.4
4°	6735.4
5°	6524.6
6°	6263.0
7°	5947.3
8°	5579.1
9°	5168.5
10°	4739.3
11°	4300.1
12°	3874.8
13°	3460.3
14°	3066.6
15°	2706.2
16°	2378.1
17°	2091.8
18°	1834.7
19°	1617.1
20°	1435.7
21°	1292.1
22°	1177.1
23°	1092.2
24°	1029.7
25°	984.1
26°	950.2
27°	920.8
28°	893.8
29°	870.7
30°	847.5
32.5°	783.5
35°	631.4
37.5°	382.1
40°	131.2
42.5°	45.5
45°	33.2
47.5°	23.9
50°	10.0
52.5°	7.7
55°	5.4
57.5°	3.9
60°	3.1
62.5°	2.3
65°	1.5



TEST NUMBER: P220956

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.5
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)