

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220531

Luminaire Tested: **9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1008.7 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220531

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220531

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	95	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85		89	87	84		88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82		87	84	82		86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80		85	82	80		84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78		83	80	77		82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76		81	78	75		80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1060441
5°	950295
10°	667634
15°	358277
20°	188456
25°	84247
30°	16281
35°	5996
40°	3406
45°	2822
50°	2388
55°	1873
60°	1535
65°	1090
70°	449
75°	0
80°	0
85°	0



TEST NUMBER: P220531

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.3	36.6
10°-20°	445.1	44.1
20°-30°	162.4	16.1
30°-40°	18.0	1.8
40°-50°	7.1	0.7
50°-60°	4.4	0.4
60°-70°	2.1	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	976.8	96.8
0°-40°	994.8	98.6
0°-60°	1006.3	99.8
0°-90°	1008.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4836	
5°	4317	369
15°	1578	445
25°	348	162
35°	22	18
45°	9	7
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220531

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4836.0
1°	4796.8
2°	4728.3
3°	4627.6
4°	4488.5
5°	4317.2
6°	4112.3
7°	3871.7
8°	3599.0
9°	3303.2
10°	2998.4
11°	2691.4
12°	2387.2
13°	2099.8
14°	1825.7
15°	1578.2
16°	1350.9
17°	1165.6
18°	1015.3
19°	896.4
20°	807.6
21°	734.9
22°	651.7
23°	553.1
24°	450.3
25°	348.2
26°	251.0
27°	164.3
28°	103.5
29°	75.5
30°	64.3
32.5°	43.4
35°	22.4
37.5°	14.7
40°	11.9
42.5°	10.5
45°	9.1
47.5°	7.7
50°	7.0
52.5°	5.6
55°	4.9
57.5°	4.2
60°	3.5
62.5°	2.8
65°	2.1



TEST NUMBER: P220531

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-M-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.4
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)