

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220565

Luminaire Tested: **9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220565  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 956.8 lumens  
Efficiency: N/A  
Efficacy: 47.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220565

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220565

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	67	74	70	67	73	69	67	66
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63
10	78	70	65	61	78	70	65	61	69	64	61	68	64	61	67	64	61	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	374444
5°	376028
10°	351719
15°	300501
20°	255359
25°	151751
30°	69049
35°	43794
40°	24818
45°	9117
50°	2866
55°	2141
60°	1842
65°	1090
70°	449
75°	593
80°	0
85°	0



TEST NUMBER: P220565

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.1	16.6
10°-20°	369.9	38.7
20°-30°	287.2	30.0
30°-40°	104.7	10.9
40°-50°	27.7	2.9
50°-60°	5.1	0.5
60°-70°	2.3	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	816.3	85.3
0°-40°	921.0	96.3
0°-60°	953.8	99.7
0°-90°	956.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1708	
5°	1708	159
15°	1324	370
25°	627	287
35°	164	105
45°	29	28
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220565

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1707.6
1°	1702.7
2°	1702.7
3°	1707.6
4°	1710.4
5°	1708.3
6°	1699.9
7°	1682.4
8°	1655.1
9°	1619.5
10°	1579.6
11°	1533.5
12°	1482.4
13°	1428.6
14°	1373.3
15°	1323.7
16°	1278.9
17°	1231.4
18°	1185.9
19°	1139.8
20°	1094.3
21°	1044.0
22°	964.3
23°	859.4
24°	745.4
25°	627.2
26°	516.0
27°	416.8
28°	341.9
29°	299.3
30°	272.7
32.5°	214.7
35°	163.6
37.5°	123.1
40°	86.7
42.5°	57.3
45°	29.4
47.5°	13.3
50°	8.4
52.5°	6.3
55°	5.6
57.5°	4.9
60°	4.2
62.5°	2.8
65°	2.1



TEST NUMBER: P220565

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-W-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.1
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)