

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220529

Luminaire Tested: **9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1166.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220529

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220529

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85	89	87	84	88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1225867
5°	1098522
10°	771774
15°	414168
20°	217859
25°	97385
30°	18838
35°	6933
40°	3922
45°	3256
50°	2763
55°	2179
60°	1754
65°	1245
70°	513
75°	0
80°	0
85°	0



TEST NUMBER: P220529

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.0	36.6
10°-20°	514.6	44.1
20°-30°	187.7	16.1
30°-40°	20.8	1.8
40°-50°	8.1	0.7
50°-60°	5.1	0.4
60°-70°	2.4	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1129.3	96.9
0°-40°	1150.0	98.6
0°-60°	1163.3	99.8
0°-90°	1166.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1166.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5590	
5°	4991	427
15°	1824	515
25°	402	188
35°	26	21
45°	10	8
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220529

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5590.4
1°	5545.1
2°	5465.9
3°	5349.5
4°	5188.7
5°	4990.6
6°	4753.8
7°	4475.7
8°	4160.5
9°	3818.5
10°	3466.1
11°	3111.3
12°	2759.6
13°	2427.4
14°	2110.5
15°	1824.4
16°	1561.7
17°	1347.5
18°	1173.7
19°	1036.3
20°	933.6
21°	849.6
22°	753.4
23°	639.4
24°	520.6
25°	402.5
26°	290.2
27°	190.0
28°	119.6
29°	87.3
30°	74.4
32.5°	50.1
35°	25.9
37.5°	17.0
40°	13.7
42.5°	12.1
45°	10.5
47.5°	8.9
50°	8.1
52.5°	6.5
55°	5.7
57.5°	4.8
60°	4.0
62.5°	3.2
65°	2.4



TEST NUMBER: P220529

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-M-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)