

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220806

Luminaire Tested: **9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29490)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2073.1 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220806

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220806

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	98	95	105	101	97	94	97	94	91	94	92	90	92	89	88	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	65	61	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324744
5°	327372
10°	313660
15°	288608
20°	246693
25°	207670
30°	156969
35°	52160
40°	33153
45°	22555
50°	13164
55°	7892
60°	8659
65°	9544
70°	10927
75°	13296
80°	15840
85°	15851



TEST NUMBER: P220806

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.9	12.0
10°-20°	623.4	30.1
20°-30°	698.2	33.7
30°-40°	292.0	14.1
40°-50°	101.4	4.9
50°-60°	36.8	1.8
60°-70°	32.4	1.6
70°-80°	28.9	1.4
80°-90°	12.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1569.4	75.7
0°-40°	1861.4	89.8
0°-60°	1999.7	96.5
0°-90°	2073.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2073.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2633	
5°	2644	248
15°	2260	623
25°	1526	698
35°	346	292
45°	129	101
55°	37	37
65°	33	32
75°	28	29
85°	11	12
90°	0	



TEST NUMBER: P220806

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2632.8
1°	2630.4
2°	2632.8
3°	2640.8
4°	2645.6
5°	2644.0
6°	2634.4
7°	2613.7
8°	2580.9
9°	2544.2
10°	2504.3
11°	2462.0
12°	2418.9
13°	2370.3
14°	2318.4
15°	2260.1
16°	2190.7
17°	2118.1
18°	2039.9
19°	1958.5
20°	1879.4
21°	1806.0
22°	1735.0
23°	1664.8
24°	1596.1
25°	1525.9
26°	1464.4
27°	1410.2
28°	1354.3
29°	1252.2
30°	1102.1
32.5°	660.8
35°	346.4
37.5°	265.0
40°	205.9
42.5°	160.4
45°	129.3
47.5°	103.7
50°	68.6
52.5°	40.7
55°	36.7
57.5°	35.9
60°	35.1
62.5°	34.3
65°	32.7



TEST NUMBER: P220806

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3090-W-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	31.1
70°	30.3
72.5°	29.5
75°	27.9
77.5°	25.5
80°	22.3
82.5°	17.6
85°	11.2
87.5°	4.8
90°	0.0

(END OF REPORT)