

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220963

Luminaire Tested: **9004-W1-FL-LED3090-M-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3090-M-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2255.5 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220963

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220963

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90		94	91	89		92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85		90	87	85		88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81		86	83	80		85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77		83	79	77		82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	910254
5°	835268
10°	613730
15°	357296
20°	194845
25°	138479
30°	124809
35°	98297
40°	21850
45°	5983
50°	1996
55°	1204
60°	789
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220963

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	584.4	25.9
10°-20°	779.9	34.6
20°-30°	487.7	21.6
30°-40°	361.8	16.0
40°-50°	33.7	1.5
50°-60°	5.4	0.2
60°-70°	1.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1852.0	82.1
0°-40°	2213.8	98.2
0°-60°	2252.9	99.9
0°-90°	2255.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2255.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7380	
5°	6746	584
15°	2798	780
25°	1018	488
35°	653	362
45°	34	34
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220963

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	7379.7
1°	7331.0
2°	7248.0
3°	7128.3
4°	6963.9
5°	6746.0
6°	6475.5
7°	6149.1
8°	5768.4
9°	5343.8
10°	4900.1
11°	4446.0
12°	4006.3
13°	3577.7
14°	3170.7
15°	2798.0
16°	2458.8
17°	2162.8
18°	1897.0
19°	1671.9
20°	1484.4
21°	1336.0
22°	1217.0
23°	1129.3
24°	1064.6
25°	1017.5
26°	982.4
27°	952.1
28°	924.2
29°	900.2
30°	876.3
32.5°	810.0
35°	652.8
37.5°	395.0
40°	135.7
42.5°	47.1
45°	34.3
47.5°	24.7
50°	10.4
52.5°	8.0
55°	5.6
57.5°	4.0
60°	3.2
62.5°	2.4
65°	1.6



TEST NUMBER: P220963

CATALOG NUMBER: 9004-W1-FL-LED3090-M-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)