

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220969

Luminaire Tested: **9004-W1-FL-LED3597-M-WT-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220969  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED3597-M-WT-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2262.7 lumens  
Efficiency: N/A  
Efficacy: 79.1 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220969

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220969

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20					20				20				20			
RC	80				70					50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78			78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	913165
5°	837942
10°	615696
15°	358445
20°	195462
25°	138928
30°	125208
35°	98613
40°	21914
45°	6001
50°	1996
55°	1204
60°	789
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220969

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	586.3	25.9
10°-20°	782.4	34.6
20°-30°	489.3	21.6
30°-40°	362.9	16.0
40°-50°	33.8	1.5
50°-60°	5.4	0.2
60°-70°	1.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1858.0	82.1
0°-40°	2220.9	98.2
0°-60°	2260.1	99.9
0°-90°	2262.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2262.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7403	
5°	6768	586
15°	2807	782
25°	1021	489
35°	655	363
45°	34	34
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220969

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7403.3
1°	7354.5
2°	7271.2
3°	7151.1
4°	6986.2
5°	6767.6
6°	6496.2
7°	6168.7
8°	5786.8
9°	5360.9
10°	4915.8
11°	4460.2
12°	4019.1
13°	3589.2
14°	3180.8
15°	2807.0
16°	2466.7
17°	2169.7
18°	1903.1
19°	1677.3
20°	1489.1
21°	1340.2
22°	1220.9
23°	1132.9
24°	1068.0
25°	1020.8
26°	985.6
27°	955.1
28°	927.1
29°	903.1
30°	879.1
32.5°	812.6
35°	654.9
37.5°	396.3
40°	136.1
42.5°	47.2
45°	34.4
47.5°	24.8
50°	10.4
52.5°	8.0
55°	5.6
57.5°	4.0
60°	3.2
62.5°	2.4
65°	1.6



TEST NUMBER: P220969

CATALOG NUMBER: 9004-W1-FL-LED3597-M-WT-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)