

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P221048

Luminaire Tested: **9004-W1-FL-LED3597-S-BK-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED3597-S-BK-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC,  
BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2242.7 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221048  
CATALOG NUMBER: 9004-W1-FL-LED3597-S-BK-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221048

CATALOG NUMBER: 9004-W1-FL-LED3597-S-BK-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104		103	101	100		99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77		82	79	76		81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74		80	76	74		79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71		77	74	71		76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1737052
5°	1352129
10°	563142
15°	238103
20°	163421
25°	130422
30°	120522
35°	98613
40°	20755
45°	4745
50°	1689
55°	1376
60°	789
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P221048

CATALOG NUMBER: 9004-W1-FL-LED3597-S-BK-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	820.7	36.6
10°-20°	575.1	25.6
20°-30°	453.3	20.2
30°-40°	356.9	15.9
40°-50°	28.8	1.3
50°-60°	5.6	0.2
60°-70°	1.5	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1849.2	82.5
0°-40°	2206.1	98.4
0°-60°	2240.5	99.9
0°-90°	2242.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2242.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14083	
5°	10920	821
15°	1865	575
25°	958	453
35°	655	357
45°	27	29
55°	6	6
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221048

CATALOG NUMBER: 9004-W1-FL-LED3597-S-BK-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	14082.8
1°	13889.1
2°	13486.3
3°	12861.9
4°	12007.6
5°	10920.4
6°	9665.0
7°	8308.8
8°	6978.2
9°	5638.7
10°	4496.2
11°	3584.3
12°	2923.0
13°	2454.7
14°	2115.2
15°	1864.6
16°	1676.5
17°	1538.8
18°	1433.9
19°	1333.8
20°	1245.0
21°	1171.3
22°	1105.6
23°	1048.0
24°	997.6
25°	958.3
26°	928.7
27°	906.3
28°	884.7
29°	865.5
30°	846.2
32.5°	798.2
35°	654.9
37.5°	390.7
40°	128.9
42.5°	38.4
45°	27.2
47.5°	19.2
50°	8.8
52.5°	8.0
55°	6.4
57.5°	4.8
60°	3.2
62.5°	1.6
65°	1.6



TEST NUMBER: P221048

CATALOG NUMBER: 9004-W1-FL-LED3597-S-BK-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)